



* The 25A- series have the same specifications and dimensions as those of the JMHZ2-X6900(A, B) (made-to-order individual specifications). For details, refer to the Web Catalog.



@SMC

* The 25A- series have the same specifications and dimensions as those of the JMHZ2-X7460 (made-to-order individual specifications). For details, refer to the Web Catalog.

Parallel Type Air Gripper Standard Type **25A-MHZ2 Series** ø10, ø16, ø20, ø25, ø32, ø40



182

Parallel Type Air Gripper Long Stroke Type **25A-MHZL2** Series RoHS ø10, ø16, ø20, ø25 How to Order 25A-MHZL2-16D -M9BW Series compatible with Number of auto switches secondary batteries Nil 2 S 1 n n Number of fingers 2 2 fingers Auto switch Nil Without auto switch (Built-in magnet) Bore size Click here for details on applicable auto switch Symbol Bore size [mm] models. 10 10 mm 16 16 mm Finger option 20 20 mm 25 25 mm Nil: Basic type

Action

D Double acting

1: Side tapped

mounting

2: Through-holes in opening/closing direction3: Flat type fingers

* The 25A- series specifications and dimensions are the same as those of the standard model.





₿SMC

Low Profile Air Gripper **25A-MHF2 Series** Ø8, Ø12, Ø16, Ø20, Ø25, Ø32



* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

RoHS

Parallel Type Air Gripper: Wide Type **25A-MHL2 Series** Ø10, Ø16, Ø20, Ø25, Ø32, Ø40 RoHS





* The 25A- series specifications and dimensions are the same as those of the standard model.



Parallel Type Air Gripper 25A-MHS Series ø16, ø20, ø25, ø32 RoHS How to Order <u>25A</u>-MHS <u>3</u>-20D-M9BW Number of auto switches Series compatible with Nil secondary batteries 2 S 1 Number of fingers Auto switch 3 3 fingers Nil Without auto switch (Built-in magnet) 4 4 fingers Click here for details on applicable auto switch

Action

D Double acting

Bore size

16 16 mm

20 mm25 mm32 mm

models.

* The 25A- series specifications and dimensions are the same as those of the standard model.



Action

D Double acting

* The 25A- series specifications and dimensions are the same as those of the standard model.

180° Angular Type Air Gripper Cam Type **25A-MHY2 Series** Ø10, Ø16, Ø20, Ø25



* The 25A- series specifications and dimensions are the same as those of the standard model.





* Change of material and surface treatment are not available for the bearing or the parallel key.

* As metal-to-metal collision occurs when the fingers are fully closed, dust particles may be generated.

* The 25A- series specifications and dimensions are the same as those of the standard model.