

Transmitters: Relay Valve


RoHS

Series VR4151/4152

Appropriate output sequences are affected according to the signal received from the mechanical valve. It is equivalent to the auxiliary relay of an electrical system.



Symbol



⚠ Precautions

Be sure to read before handling. Refer to front matter 53 for Safety Instructions and pages 3 to 8 for 3/4/5 Port Solenoid Valve Precautions.

Environment

⚠ Caution

Operate the valve in an area in which the vibration does not exceed 5 G. Vibrations could cause the valve to malfunction.

Specifications


Fluid		Air		
Operating pressure		0 to 1.0 MPa		
Pilot pressure		0.15 to 1.0 MPa		
Ambient and fluid temperature		-5 to 60°C (No freezing)		
Flow-rate characteristics		C[dm³/(s·bar)]	b	Cv
Side ported	1(P) ↔ 2(B)/4(A)	1.6	0.15	0.38
	2(B)/4(A) ↔ 3(S)/5(R)	1.5	0.2	0.36
Bottom ported	1(P) ↔ 2(B)/4(A)	1.6	0.2	0.38
	2(B)/4(A) ↔ 3(S)/5(R)	1.5	0.25	0.36
Port size		1/8		
Weight	Side ported	350 g		
	Bottom ported	300 g		
Lubrication		Not required (Use turbine oil Class 1 ISO VG32, if lubricated.)		

Model


Function	Sub-plate	Model	Indicator
Single pilot	W/o sub-plate	VR4151-00-0	—
		VR4151-00-1	○
	W/ sub-plate	VR4151-01A-0	—
	Side piping	VR4151-01A-1	○
	W/ sub-plate	VR4151-01B-0	—
	Bottom piping	VR4151-01B-1	○
Double pilot	W/o sub-plate	VR4152-00-0	—
		VR4152-00-1	○
	W/ sub-plate	VR4152-01A-0	—
	Side piping	VR4152-01A-1	○
	W/ sub-plate	VR4152-01B-0	—
	Bottom piping	VR4152-01B-1	○

Construction

VR4151



VR4152



Component Parts

No.	Description	Material	No.	Description	Material
1	Valve	ADC	8	Manual button	POM
2	Sub-plate	ZDC	9	Piston	POM
3	Pilot cover	ADC	10	Spring	Steel
4	Spool	Stainless steel	11	Spring	Stainless steel
5	Sleeve	Stainless steel	12	Gasket	NBR
6	Detent assembly		13	Gasket	NBR
7	Piston cover	Brass	14	O-ring	NBR

VM

VMG

VR

VR51

VHK

VH

VHS

VHS

How to Order

VR41 5 1 - 01 A - 1

Indicator light

0	No
1	Yes

Sub-plate

A	Side piping
B	Bottom piping

Port size

00	W/o sub-plate
01	Rc 1/8
N01	NPT 1/8
F01	G 1/8

Number of pilot ports


1	Single pilot
2	Double pilot

Number of ports


5	5 port
---	--------

Dimensions

Side ported



Bottom ported



* When "no indicator light" is selected, the plug is attached.

Transmitters: Shuttle Valve

RoHS


Series VR1210/1220

Relay valves for controlling the pneumatic signal lines.

This valve is also called “OR valve”. As the air is supplied to either IN side, it is output from the OUT side. When the air pressure levels are different, the air with higher pressure flows to the OUT side.



Symbol



Model/Specifications

Model		VR1210-01	VR1220-02
Max. operating pressure		1.0 MPa	
Min. operating pressure		0.05 MPa	
Ambient and fluid temperature		-5 to 60°C (No freezing)	
Flow-rate characteristics	C [dm ³ /(s·bar)]	1.3	2.9
	b	0.2	0.2
Port size		1/8	1/4
Weight		24 g	45 g

How to Order

VR12 1 0 - 01

Port size	Applicable model
01 1/8	VR 1210
02 1/4	VR 1220

Thread type


Nll	Rc
N	NPT
F	G

Body size


1	1/8 standard
2	1/4 standard

Construction

When right port has higher pressure



When left port has higher pressure




Component Parts


No.	Description	Material	Note	No.	Description	Material	Note
1	Valve body	ADC	Platinum silver	3	Valve	Brass, NBR	
2	Valve guide	Brass		4	O-ring	NBR	

Dimensions

VR1210



VR1220



2363

VM

VMG

VR

VR51

VHK

VH

VHS

VHS


Transmitters: Shuttle Valve with One-touch Fittings Series *VR1210F/1220F*

RoHS


Relay valves for controlling pneumatic signal lines



When the difference in input air pressure between two IN sides is 0.05 MPa or more, the air with higher pressure constantly flows to the OUT side.



Symbol



Model

Model	Applicable tubing O.D.									
	Metric size					Inch size				
	3.2	4	6	8	10	1/8"	5/32"	1/4"	5/16"	3/8"
VR1210F	●	●	●	●	●	●	●	●	●	●
VR1220F			●	●	●			●	●	●

Specifications

Proof pressure	1.5 MPa
Max. operating pressure	1.0 MPa
Min. operating pressure	0.05 MPa
Ambient and fluid temperature	-5 to 60°C (No freezing)
Applicable tubing material ⁽¹⁾	Nylon, Soft nylon, Polyurethane

Note 1) Use caution about the maximum operating pressure when soft nylon and polyurethane is used. (Refer to Best Pneumatics No. 6.)

Note 2) Brass components are all electroless nickel plated as standard.
(Copper-free and fluorine-free)

Flow-rate characteristics

Applicable tubing O.D.	Model	VR1210F				VR1220F			
	Metric size	ø3.2	ø4	ø6	ø8	ø6	ø8	ø10	
	Inch size	ø1/8"	ø5/32"	ø1/4"	ø5/16"	ø1/4"	ø5/16"	ø3/8"	
Flow-rate characteristics	C[dm ³ /(s·bar)]	0.5	0.7	1.3	1.5	1.4	2.1	3.1	
	b	0.25	0.25	0.25	0.25	0.25	0.25	0.25	

How to Order

VR 12 **1** 0 F - **06**

Body size

1	1/8 standard
2	1/4 standard

Shuttle valve

With One-touch fittings

Applicable tubing O.D.


Metric size	Inch size
23 ø3.2*	01 ø1/8"
04 ø4	03 ø5/32"
06 ø6	07 ø1/4"
08 ø8	09 ø5/16"
10 ø10	11 ø3/8"

* For ø3.2, use ø1/8" tubing.

Example of Operating Circuit


OR circuit

- If either A or B is turned ON, cylinder is actuated.




Self-hold circuit

1. If A is turned ON, the output turns ON.
2. Even though A is turned OFF, the output remains in ON state.
3. If B is turned ON in 2. state, the output is turned OFF.




Interlock circuit

- When either A or B is turned ON, even though C turns ON, the output 3 will not be turned ON.
- Only when both A and B are in OFF state, if C turns ON, the output 3 is turned ON.



Dimensions



Metric Size

Model	d	D1	D2	D3	L1	L2	L3	L4	L5	M1	M2	Weight (g)
VR1210F-23	3.2	11.4	8.4	14.8	52	6.2	19.4	29.8	17.5	12.7	12.9	21.4
VR1210F-04	4	11	10.4		53	6	20.3	31.5	21.9	16.5	15.8	15.6
VR1210F-06	6	12.8	12.8		53.2	6.8	22.5	35.6	25.2	16.8	16.8	23.0
VR1210F-08	8	15.2	15.2		60.4	8.1		38.2	28.2	18.7	18.7	24.0
VR1220F-06	6	12.8	12.8	19.8	59	7.4	23.9	37.7	25.2	16.8	16.8	27.2
VR1220F-08	8	15.2	15.2		65	8.2	23.9	39.7	28.2	18.7	18.7	31.9
VR1220F-10	10	18.5	18.5		71.6	9.8		44.8	31	20.8	20.8	43.2

Inch Size

Model	d	D1	D2	D3	L1	L2	L3	L4	L5	M1	M2	Weight (g)
VR1210F-01	1/8"	11.4	8.4	14.8	52	6.2	19.4	29.8	17.5	12.7	12.9	21.4
VR1210F-03	5/32"	11	10.4		53	6	20.3	31.5	21.9	16.5	15.8	15.6
VR1210F-07	1/4"	13.2	13.2		54.4	7.1	22.5	36.2	25.6	16.8	16.8	23.5
VR1210F-09	5/16"	15.2	15.2		60.4	8.1		38.2	28.2	18.7	18.7	24.0
VR1220F-07	1/4"	13.2	13.2	19.8	59	7.4	23.9	37.9	25.6	16.8	16.8	31.4
VR1220F-09	5/16"	15.2	15.2		65	8.2	23.9	39.7	28.2	18.7	18.7	31.9
VR1220F-11	3/8"	17.9	18.5		69.8	9.5		44.5	31	20.8	20.8	53.0

Transmitters: AND Valve with One-touch Fittings Series **VR1211F**


RoHS

Relay valves for controlling pneumatic signal lines





Only when air is supplied to both P₁ and P₂ does air flow to the OUT side.

When air pressure differs, pressure in the lower amount flows to the OUT side.




If air is supplied only to either P₁ or P₂, it does not flow to the OUT side.

Note) Air may flow to the OUT side for a moment until the valve switches. (About 1/100 second) If there is any effect on the connected equipment due to the above air flow, install a speed controller, etc. on the OUT side, and adjust to prevent this effect before use.



Symbol



Model

Model	Applicable tubing O.D.					
	Metric size			Inch size		
	3.2	4	6	1/8"	5/32"	1/4"
VR1211F	●	●	●	●	●	●

Specifications

Proof pressure	1.5 MPa
Max. operating pressure	1.0 MPa
Min. operating pressure	0.05 MPa
Ambient temperature and operating fluid temperature	−5 to 60°C (No freezing)
Applicable tubing material ⁽¹⁾	Nylon, Soft nylon, Polyurethane

Note 1) Use caution about the maximum operating pressure when soft nylon and polyurethane is used. (Refer to Best Pneumatics No. 6.)

Note 2) Brass components are all electroleless nickel plated as standard.
(Copper-free and fluorine-free)

Flow-rate characteristics

Model		VR1211F			
Applicable tubing O.D.	Metric size	ø3.2	ø4	ø6	—
	Inch size	ø1/8"	ø5/32"	—	ø1/4"
Flow-rate characteristics	C[dm ³ /(s·bar)]	0.3	0.4	0.5	0.6
	b	0.25	0.25	0.25	0.25

How to Order

VR 12 1 1 F - 06

Body size

1	1/8 standard
---	--------------

AND valve


With One-touch fittings

Applicable tubing O.D.

Metric size	Inch size
23 ø3.2 *	01 ø1/8"
04 ø4	03 ø5/32"
06 ø6	07 ø1/4"


* For ø3.2, use ø1/8" tubing.

Example of Operating Circuit



- If both A and B are turned ON, which are in different pressure conditions, both output 1 and 2 will turn ON
- Only when output 1 and 2 are in the ON state, and C turns ON, will output 3 turn ON.
- If either A or B is turned OFF, output 3 will not be turned ON, even if C is turned ON.

Dimensions



VM
VMG
VR
VR51
VHK
VH
VHS
VHS

Metric Size

Model	d	D1	D2	D3	L1	L2	L3	L4	L5	M1	M2	Weight (g)
VR1211F-23	3.2	11.4	8.4	14.8	52	6.2	25.7	36.1	17.5	12.7	12.9	26.4
VR1211F-04	4	11	10.4		53	6.8	26.6	37.8	21.9	16.5	15.8	20.8
VR1211F-06	6	12.8	12.8		53.2		28.8	41.9	25.2	16.8	16.8	25.0

Inch Size

Model	d	D1	D2	D3	L1	L2	L3	L4	L5	M1	M2	Weight (g)
VR1211F-01	1/8"	11.4	8.4	14.8	52	6.2	25.7	36.1	17.5	12.7	12.9	26.4
VR1211F-03	5/32"	11	10.4		53	6.8	26.6	37.8	21.9	16.5	15.8	20.8
VR1211F-07	1/4"	13.2	13.2		54.4	7.1	28.8	42.5	25.6	16.8	16.8	27.0


Transmitters: Time Delay Valve Series VR2110

RoHS


Combination of adjustable orifice and fixed flow allows transmission of a pneumatic signal after a fixed time period.



Symbol




Input Signal (PIL) vs. Time Delay



Example) (A) is the point, which is set by the input signal pressure 0.25 MPa, with a delay time of 60 sec. With the same status, if the input signal pressure is increased to 0.8 MPa, the delay time varies to the (B) point (= 40 sec).

Piping Length vs. Release Time



If the input signal (PIL) is turned OFF, the release time of the time delay valve changes depending upon the effective area of the valve and the length of piping. Please refer to the above graph for the standard values.


Model/Specifications

Model		VR2110-01
Supply pressure		0 to 1.0 MPa
Signal pressure		0.25 to 0.8 MPa
Time delay		0.5 to 60 s
Repeatability*		±10% F.S. (Representative valve)
Operating and fluid temperature		-5 to 60°C (No freezing)
Flow-rate characteristics	C[dm ³ /(s·bar)]	0.5 (P→A), 0.4 (A→R)
	b	0.2 (P→A), 0.15 (A→R)
Port size		1/8
Weight		500 g


*) The dispersion is shown excluding the first actuation when actuated 4 times continuously.

Construction


Non-actuated



Actuated after time set



Actuated before time set



Component Parts

No.	Description	Material	Note	No.	Description	Material	Note
1	Valve body	ADC	Platinum silver	5	Return spring	Steel	
2	Differential piston	Brass, NBR	Rubber lined	6	Valve body	ZDC	Platinum silver
3	Exhaust piston	Brass, NBR	Rubber lined	7	Plunger	POM	
4	Needle	Brass		8	Valve	NBR	

How to Order

VR2110 - 01 -

Option

X3	Secondary tank connection port Rc 1/4
X102	N.O. N.C. common type (With VM430)


Port size

01	Rc 1/8
N01	NPT 1/8
F01	G 1/8

Dimensions

Bracket mounted

Panel mounted



VM

VMG

VR

VR51

VHK

VH

VHS

VHS

Transmitters: Pneumatic-electric Relay




RoHS

Series VR3200/3201

Pneumatic-electric relay converts pneumatic signal to electric relay.



Symbol



Precautions

Be sure to read before handling.
Refer to front matter 53 for
Safety Instructions and pages 3
to 8 for 3/4/5 Port Solenoid Valve
Precautions.

Piping

Warning

When connecting a pipe fitting to the IN port, place the wrench over the hexagon portion of the lid.

If the wrench is placed over the micro-switch body, the neck of the microswitch could break.

Model/Specifications


Model	VR3200-01	VR3201-01
Construction	Open type	Splashproof (IP44 equivalent)
Weight	130 g	260 g
Operating pressure	0.1 to 1.0 MPa	
Ambient and fluid temperature	-5 to 60°C (No freezing)	
Contacts	1ab	
Port size	1/8	
Standard (CE-compliant)	EN60947-5-1:2004 <small>Note)</small>	

Note) Voltage is up to 30 VDC. Voltage other than that will be inapplicable.


Microswitch Rating

Voltage	Non-inductive load (A)				Inductive load (A)			
	Resistance load		Light load		Inductive load		Electric motor load	
	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.
125 VAC	15	15	3	1.5	15	15	5	2.5
250 VAC	15	15	2.5	1.25	15	15	3	1.5
8 VDC	15	15	3	1.5	15	15	5	2.5
14 VDC	15	15	3	1.5	10	10	5	2.5
30 VDC	6	6	3	1.5	5	5	5	2.5
125 VDC	0.5	0.5	0.5	0.5	0.05	0.05	0.05	0.05
250 VDC	0.25	0.25	0.25	0.25	0.03	0.03	0.03	0.03

How to Order



Construction




Component Parts


No.	Description	Material	Note	No.	Description	Material	Note
1	Body	Brass		4	Spring	Stainless steel	
2	Cap	Brass		5	Microswitch		Contacts 1 ab
3	Piston	POM					

Dimensions

VR3200



VR3201



VM

VMG

VR

VR51

VHK

VH

VHS□

VHS

Transmitters: Pneumatic Indicator Series **VR3100**

RoHS

Indicates the presence of pneumatic pressure. It is equivalent to the pilot lamp of an electrical system.




Symbol



Model/Specifications


Model	VR3100-01R	VR3100-01G	VR3100-01O
Color of indicator	Red	Green	Orange
Operating pressure	0.1 to 0.8 MPa		
Ambient and fluid temp.	-5 to 60°C (No freezing)		
Frequency	100 c.p.m. or less		
Port size	Rc 1/8		
Weight	40g		

Construction



No.	Description	Material	Note
1	Body	Aluminum alloy	
2	Indicator window	Acrylic	
3	Piston	POM	
4	Return spring	Stainless steel	
5	O-ring	NBR	

Dimensions



Transmitters: Miniature Pneumatic Indicator Series **VR3110**

RoHS

This is an ultra-compact air indicator light to monitor the presence of air pressure.

It is equivalent to the pilot lamp of an electrical system.




Symbol



Model/Specifications

Model	VR3110-01R	VR3110-01G
Color of indicator	Red	Green
Operating pressure	0.15 to 1.0 MPa	
Ambient and fluid temp.	-5 to 60°C (No freezing)	
Frequency	300 c.p.m. or less	
Port size	R 1/8	
Weight	6g	

Construction



No.	Description	Material	Note
1	Body	Brass	
2	Piston A	POM	
3	Plug	PE	
4	Spring	Stainless steel	
5	O-ring	NBR	

Dimensions

