

Micro Mechanical Valve

Series VM1000

RoHS

Miniature structure requires little mounting space.

Built-in hose nipple connection.

Piping options:

Side piping, Bottom piping

Over Travel after actuation (mechanical operated types)



Standard Specifications

Valve type	N.C. poppet		
Number of ports	2 or 3		
Piping	Side or bottom ported		
Fluid	Air/Inert gas		
Operating pressure	0 to 0.8 MPa		
Ambient and fluid temperature	-5 to 60°C (No freezing)		
Flow characteristics	C[dm ³ /(s·bar)]		Cv
	b		
	Side ported	1(P)–2(A)	0.2
	Bottom ported	2(A)–3(R)	0.2
Flow characteristics	C[dm ³ /(s·bar)]		Cv
	b		
	Side ported	1(P)–2(A)	0.2
	Bottom ported	2(A)–3(R)	0.2
Lubrication	Not required (Use turbine oil Class 1 ISO VG32, if lubricated.)		
Fitting	With hose nipple		

Semi-standard Specification

Total travel (T.T.)	2.5 mm (Basic)
• T.T. 2.5 mm is available for basic style only.	

Model

	Actuator	Piping	Number of ports	Applicable tubing		Note	Weight (g)
				T0425	TU0425/T0403		
Mechanical operation	Basic	Side ported	3 port	VM1000-4N-00	VM1000-4NU-00	—	6
			2 port	VM1100-4N-00	VM1100-4NU-00	—	
		Bottom ported	3 port	VM1010-4N-00	VM1010-4NU-00	—	
			2 port	VM1110-4N-00	VM1110-4NU-00	—	
	Roller lever	Side ported	3 port	VM1000-4N-01	VM1000-4NU-01	—	11
			2 port	VM1100-4N-01	VM1100-4NU-01	—	
		Bottom ported	3 port	VM1010-4N-01	VM1010-4NU-01	—	
			2 port	VM1110-4N-01	VM1110-4NU-01	—	
	One way roller lever	Side ported	3 port	VM1000-4N-02	VM1000-4NU-02	—	12
			2 port	VM1100-4N-02	VM1100-4NU-02	—	
		Bottom ported	3 port	VM1010-4N-02	VM1010-4NU-02	—	
			2 port	VM1110-4N-02	VM1110-4NU-02	—	
Manual operation	Toggle lever	Side ported	3 port	VM1000-4N-08	VM1000-4NU-08	—	20
			2 port	VM1100-4N-08	VM1100-4NU-08	—	
		Bottom ported	3 port	VM1010-4N-08	VM1010-4NU-08	—	
			2 port	VM1110-4N-08	VM1110-4NU-08	—	
	Push button	Side ported	3 port	VM1000-4N-32R	VM1000-4NU-32R	Red	31
			2 port	VM1100-4N-32R	VM1100-4NU-32R	Red	
		Bottom ported	3 port	VM1010-4N-32R	VM1010-4NU-32R	Red	
			2 port	VM1110-4N-32R	VM1110-4NU-32R	Red	
		Side ported	3 port	VM1000-4N-32B	VM1000-4NU-32B	Black	
			2 port	VM1100-4N-32B	VM1100-4NU-32B	Black	
		Bottom ported	3 port	VM1010-4N-32B	VM1010-4NU-32B	Black	
			2 port	VM1110-4N-32B	VM1110-4NU-32B	Black	
		Side ported	3 port	VM1000-4N-32G	VM1000-4NU-32G	Green	
			2 port	VM1100-4N-32G	VM1100-4NU-32G	Green	
		Bottom ported	3 port	VM1010-4N-32G	VM1010-4NU-32G	Green	
			2 port	VM1110-4N-32G	VM1110-4NU-32G	Green	

Note) To replace the push button and push button cover alone, refer to page 2348.
Other parts and actuator cannot be replaced.

How to Order

VM1 **0** **0** **0** - **4N** - **00** **R**

• Applicable tubing (Material/Size)

4N	Nylon ø4/2.5 (T0425)
	Nylon ø4/3 (T0403)
4NU	Soft Nylon ø4/2.5 (TS0425)
	Polyurethane ø4/2.5 (TU0425)

• Total travel/Basic (T.T.)

0	4.8 mm
1	2.5 mm (Option)* * Basic only.

• Piping

0	Side ported
1	Bottom ported

• Number of ports

0	3 port
1	2 port

• Actuator type


00	Basic
01	Roller lever
02	One way roller lever
08	Toggle lever
32	Push button

• Color of push button


R	Red
G	Green
B	Black

Construction


Side ported/Non-actuated




Bottom ported/Non-actuated



Side ported/Actuated



Bottom ported/Actuated



Component Parts

No.	Description	Material	Note
1	Body	PBT	
2	Valve	POM	
3	Valve	NBR	
4	Retainer	POM	
5	Valve return spring	Stainless steel	

No.	Description	Material	Note
6	Lever return spring	Stainless steel	
7	Plunger	POM	T.T. = 2.5 mm only, w/threads
8	Lever	Stainless steel	
9	Packing	NBR	
10	O-ring	NBR	

VM

VMG

VR

VR51

VHK

VH

VHS

VHS



Series VM1000/Bottom Ported

Basic


VM1010-4N-00
VM1010-4NU-00
VM1110-4N-00
VM1110-4NU-00




[]: T.T. = 2.5 mm



Symbol/2 port



3 port




= 0.5 MPa supply


		Applicable tubing	
		T0425	TU0425, T0403, TS0425
Bottom ported	3 port	VM1010-4N-00	VM1010-4NU-00
	2 port	VM1110-4N-00	VM1110-4NU-00
F.O.F. *		6 N	
P.T.		2.5mm	
O.T.		2.3mm[0.5mm]	
T.T.		4.8mm[2.5mm]	

Roller lever


VM1010-4N-01
VM1010-4NU-01
VM1110-4N-01
VM1110-4NU-01



Symbol/2 port



3 port




= 0.5 MPa supply


		Applicable tubing	
		T0425	TU0425, T0403, TS0425
Bottom ported	3 port	VM1010-4N-01	VM1010-4NU-01
	2 port	VM1110-4N-01	VM1110-4NU-01
F.O.F. *		6 N	
P.T.		2.5 mm	
O.T.		2.0 mm	
T.T.		4.5 mm	

One way roller lever


VM1010-4N-02
VM1010-4NU-02
VM1110-4N-02
VM1110-4NU-02



Symbol/2 port



3 port





= 0.5 MPa supply


		Applicable tubing	
		T0425	TU0425, T0403, TS0425
Bottom ported	3 port	VM1010-4N-02	VM1010-4NU-02
	2 port	VM1110-4N-02	VM1110-4NU-02
F.O.F. *		6 N	
P.T.		2.5 mm	
O.T.		2.0 mm	
T.T.		4.5 mm	

Toggle lever


M1010-4N-08
VM1010-4NU-08
VM1110-4N-08
VM1110-4NU-08



Symbol/2 port



3 port





= 0.5 MPa supply


		Applicable tubing	
		T0425	TU0425, T0403, TS0425
Bottom ported	3 port	VM1010-4N-08	VM1010-4NU-08
	2 port	VM1110-4N-08	VM1110-4NU-08
F.O.F. *		4N	
P.T.		40°	

Push button


VM1010-4N-32
VM1010-4NU-32
VM1110-4N-32
VM1110-4NU-32



Symbol/2 port



3 port



= 0.5 MPa supply

		Applicable tubing	
		T0425	TU0425, T0403, TS0425
Bottom ported	3 port	VM1010-4N-32	VM1010-4NU-32
	2 port	VM1110-4N-32	VM1110-4NU-32
F.O.F. *		6 N	
P.T.		2.5 mm	
O.T.		2.0 mm	
T.T.		4.5 mm	

2/3 Port Mechanical Valve

Series VM100

RoHS

Series VM100 has been remodeled.
When selecting this model, please consider the new **VM100-A series**.

Compact size.
Piping options:
Side piping, Bottom piping
A variety of actuator types.



Specifications

Piping		Side ported		Bottom ported	
Fluid		Air/Inert gas			
Operating pressure		-100 kPa to 1.0 MPa			
Ambient and fluid temperature		-5 to 60°C (No freezing)			
Flow characteristics		C(dm³/(s·bar))		b	Cv
Side ported	1(P)→2(A)	0.5		0.2	0.11
	2(A)→3(R)	0.4		0.15	0.10
Bottom ported	1(P)→2(A)	0.5		0.2	0.11
	2(A)→3(R)	0.4		0.15	0.10
Lubrication		Not required (Use turbine oil Class 1 ISO VG32, if lubricated.)			
Port size		1/8		M5 x 0.8	

Model

		Side ported		Bottom ported		Actuator part no.	Application	Weight(g)	
		2 port	3 port	2 port	3 port			Side ported	Bottom ported
Mechanical operation	Basic	VM120-01-00	VM130-01-00	VM122-M5-00	VM132-M5-00	—	—	95	110
		VM121-01-00	VM131-01-00	VM123-M5-00	VM133-M5-00	—	—		
	Roller lever	VM121-01-01	VM131-01-01	VM123-M5-01	VM133-M5-01	—	Polycetal roller	101	120
		VM121-01-01S	VM131-01-01S	VM123-M5-01S	VM133-M5-01S	—	Hard steel roller	102	121
	One way roller lever	VM121-01-02	VM131-01-02	VM123-M5-02	VM133-M5-02	—	Polycetal roller	107	120
		VM121-01-02S	VM131-01-02S	VM123-M5-02S	VM133-M5-02S	—	Hard steel roller	117	130
	Straight plunger	VM120-01-05	VM130-01-05	VM122-M5-05	VM132-M5-05	VM-05B	—	138	150
	Roller plunger	VM120-01-06	VM130-01-06	VM122-M5-06	VM132-M5-06	VM-06B	Polycetal roller	139	150
		VM120-01-06S	VM130-01-06S	VM122-M5-06S	VM132-M5-06S	VM-06BS	Hard steel roller	140	151
	Cross roller plunger	VM120-01-07	VM130-01-07	VM122-M5-07	VM132-M5-07	VM-07B	Polycetal roller	139	150
		VM120-01-07S	VM130-01-07S	VM122-M5-07S	VM132-M5-07S	VM-07BS	Hard steel roller	140	151
	Toggle lever	VM120-01-08	VM130-01-08	VM122-M5-08	VM132-M5-08	VM-08B	—	136	150
Manual operation	Push button (Mushroom)	VM120-01-30R	VM130-01-30R	VM122-M5-30R	VM132-M5-30R	VM-30AR	Red	153	168
		VM120-01-30B	VM130-01-30B	VM122-M5-30B	VM132-M5-30B	VM-30AB	Black		
		VM120-01-30G	VM130-01-30G	VM122-M5-30G	VM132-M5-30G	VM-30AG	Green		
		VM120-01-30Y	VM130-01-30Y	VM122-M5-30Y	VM132-M5-30Y	VM-30AY	Yellow		
	Push button (Extended)	VM120-01-32R	VM130-01-32R	VM122-M5-32R	VM132-M5-32R	VM-32AR	Red	147	162
		VM120-01-32B	VM130-01-32B	VM122-M5-32B	VM132-M5-32B	VM-32AB	Black		
		VM120-01-32G	VM130-01-32G	VM122-M5-32G	VM132-M5-32G	VM-32AG	Green		
		VM120-01-32Y	VM130-01-32Y	VM122-M5-32Y	VM132-M5-32Y	VM-32AY	Yellow		
	Push button (Flush)	VM120-01-33	VM130-01-33	VM122-M5-33	VM132-M5-33	VM-33A	With a set of red, black, green, yellow	152	167
	Twist selector (2 position)	VM120-01-34R	VM130-01-34R	VM122-M5-34R	VM132-M5-34R	VM-34AR	Red	153	168
		VM120-01-34B	VM130-01-34B	VM122-M5-34B	VM132-M5-34B	VM-34AB	Black		
		VM120-01-34G	VM130-01-34G	VM122-M5-34G	VM132-M5-34G	VM-34AG	Green		
		VM120-01-34Y	VM130-01-34Y	VM122-M5-34Y	VM132-M5-34Y	VM-34AY	Yellow		
	Key selector (2 position)	VM120-01-36	VM130-01-36	VM122-M5-36	VM132-M5-36	VM-36A	—	173	188
	Twist selector (3 position)	(3 port)	(5 port)	(3 port)	(5 port)	—	—	301	341
		VM131-01-35R	VM151-01-35R	VM133-M5-35R	VM153-M5-35R	—	Red		
		VM131-01-35B	VM151-01-35B	VM133-M5-35B	VM153-M5-35B	—	Black		
		VM131-01-35G	VM151-01-35G	VM133-M5-35G	VM153-M5-35G	—	Green		
		VM131-01-35Y	VM151-01-35Y	VM133-M5-35Y	VM153-M5-35Y	—	Yellow		

Note 1) Actuator replacement is available for all types except for roller lever, one way roller lever, and 3 position selector.

Note 2) For push button (mushroom), push button (extended), push button (flush) and a single unit of fastening ring, refer to pages 2347 and 2348. The other parts are not replaceable.

Note 3) The handle of the selector (2 position and 3 position) cannot be removed or replaced alone.

How to Order

VM1 **3** **1** - **01** - **01** **S** **-** **-**

• **Made to Order**
(Refer to pages 2342 to 2345 for details.)
X207 Alternate type, Mushroom push button
X219 Push-lock turn-reset type, Mushroom push button

• **Port size**

01	Rc 1/8
M5	M5 x 0.8 (Female thread)
N01	NPT 1/8
F01	G 1/8

• **Piping direction and the length of push rod**

0	Long	Side ported
1	Short	Side ported
2	Long	Bottom ported
3	Short	Bottom ported

• **Number of ports**

2	2 port
3	3 port

• **Actuator type**

00	Basic
01	Roller lever
02	One way roller lever
05	Straight plunger
06	Roller plunger
07	Cross roller plunger
08	Toggle lever
30	Push button (Mushroom)
32	Push button (Extended)
33	Push button (Flush)
34	Twist selector (2 position)
36	Key selector (2 position)
35	Twist selector (3 position)

Note 1) When selecting the flush type, it is not necessary to select the suffix for the actuator.

• **Suffix for actuator**

S	Hard steel roller
R	Red
B	Black
G	Green
Y	Yellow

Color of push button selector

• **Suffix for indicator light**


Z	With miniature indicator light (Green) (Bottom piping type only)
----------	--

Combination possible: ○, Combination impossible: ×


Actuator	Side ported		Bottom ported	
	Long	Short	Long	Short
Basic	○	○	○	○
Roller lever	×	○	×	○
One way roller lever	×	○	×	○
Straight plunger	○	×	○	×
Roller plunger	○	×	○	×
Cross roller plunger	○	×	○	×
Toggle lever	○	×	○	×
Push button (Mushroom)	○	×	○	×
Push button (Extended)	○	×	○	×
Push button (Flush)	○	×	○	×
Twist selector (2 position)	○	×	○	×
Key selector (2 position)	○	×	○	×
Twist selector (3 position)	×	○	×	○

Construction

Side ported



Bottom ported



Component Parts


No.	Description	Material	Note
1	Valve	ZDC	Platinum silver
2	Plunger	POM	
3	Valve sheet	POM	
4	Valve	NBR	
5	Spring	Stainless steel	

No.	Description	Material	Note
6	Gasket	NBR	
7	Cover	Rolled steel	
8	Sub-plate	ZDC	Platinum silver
9	Hexagon socket head plug	Rolled steel	

Series VM100/Side Ported

Cross roller plunger

VM120-01-07
VM130-01-07
VM120-01-07S
VM130-01-07S




Panel mounting hole




Symbol

2 port



3 port




* 0.5 MPa supply

F.O.F. *	23 N
P.T.	2.0 mm
O.T.	1.5 mm
T.T.	3.5 mm

Toggle lever

VM120-01-08
VM130-01-08




Panel mounting hole




Symbol

2 port




3 port




* 0.5 MPa supply

F.O.F. *	10 N
T.T.	60°

Push button (Mushroom) VM120-01-30R/B/G/Y VM130-01-30R/B/G/Y




Panel mounting hole




Symbol

2 port




3 port




* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.9 mm
O.T.	1.6 mm
T.T.	6.5 mm

Push button (Extended) VM120-01-32R/B/G/Y VM130-01-32R/B/G/Y




Panel mounting hole




Symbol

2 port




3 port




* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.9 mm
O.T.	1.6 mm
T.T.	6.5 mm

Push button (Flush) VM120-01-33 VM130-01-33




Panel mounting hole




Symbol

2 port



3 port




* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.9 mm
O.T.	1.6 mm
T.T.	6.5 mm

Series VM100

Series VM100/Side Ported


Twist selector (2 position)
 VM120-01-34R/B/G/Y
 VM130-01-34R/B/G/Y




Panel mounting hole



Symbol
 2 port



3 port




* 0.5 MPa supply

F.O.F. *	15 N
T.T.	90°

Key selector (2 position)


VM120-01-36
 VM130-01-36




Panel mounting hole



Symbol
 2 port



3 port




* 0.5 MPa supply

F.O.F. *	15 N
T.T.	90°


Key can be removed at the "on" and "off" positions.

Twist selector (3 position)


VM131-01-35R/B/G/Y
 VM151-01-35R/B/G/Y




Panel mounting hole



Symbol
 3 port



5 port



* 0.5 MPa supply

F.O.F. *	15 N
T.T.	45°

2/3 Port Mechanical Valve

Series VM200

RoHS

Series VM200 has been remodeled.
When selecting this model, please
consider the new VM200-A series.

Large flow capacity.
A variety of actuator types.



Specifications

Fluid	Air/Inert gas		
Operating pressure	0 to 1.0 MPa		
Ambient and fluid temperature	-5 to 60°C (No freezing)		
Flow characteristics	C[dm ³ /(s·bar)]		Cv
	1(IN)→2(OUT)	3.7	0.4
	2(OUT)→3(R)	3.2	0.1
Lubrication	Not required (Use turbine oil Class 1 ISO VG32, if lubricated.)		
Port size	1/4		

Model

No. of ports		2 port	3 port	Actuator part no.	Application	Weight (g)
Mechanical operation	Actuator					
	Basic	VM220-02-00	VM230-02-00	—	—	110
	Roller lever	VM220-02-01	VM230-02-01	VM-01A	Polycetal roller	160
		VM220-02-01S	VM230-02-01S	VM-01AS	Hard steel roller	170
	One way roller lever	VM220-02-02	VM230-02-02	VM-02A	Polycetal roller	170
		VM220-02-02S	VM230-02-02S	VM-02AS	Hard steel roller	180
	Straight plunger	VM220-02-05	VM230-02-05	VM-05A	—	240
	Roller plunger	VM220-02-06	VM230-02-06	VM-06A	Polycetal roller	230
		VM220-02-06S	VM230-02-06S	VM-06AS	Hard steel roller	240
	Cross roller plunger	VM220-02-07	VM230-02-07	VM-07A	Polycetal roller	230
Manual operation		VM220-02-07S	VM230-02-07S	VM-07AS	Hard steel roller	240
	Toggle lever	VM220-02-08	VM230-02-08	VM-08A	—	220
	Push button (Mushroom)	VM220-02-30R	VM230-02-30R	VM-30AR	Red	169
		VM220-02-30B	VM230-02-30B	VM-30AB	Black	
		VM220-02-30G	VM230-02-30G	VM-30AG	Green	
		VM220-02-30Y	VM230-02-30Y	VM-30AY	Yellow	
	Push button (Extended)	VM220-02-32R	VM230-02-32R	VM-32AR	Red	163
		VM220-02-32B	VM230-02-32B	VM-32AB	Black	
		VM220-02-32G	VM230-02-32G	VM-32AG	Green	
		VM220-02-32Y	VM230-02-32Y	VM-32AY	Yellow	
	Push button (Flush)	VM220-02-33	VM230-02-33	VM-33A	With a set of red, black, green, yellow	168
	Twist selector (2 position)	VM220-02-34R	VM230-02-34R	VM-34AR	Red	169
		VM220-02-34B	VM230-02-34B	VM-34AB	Black	
		VM220-02-34G	VM230-02-34G	VM-34AG	Green	
		VM220-02-34Y	VM230-02-34Y	VM-34AY	Yellow	
	Key selector (2 position)	VM220-02-36	VM230-02-36	VM-36A	—	189
		(3 port)	(5 port)	—	—	
	Twist selector (3 position)	VM230-02-35R	VM250-02-35R	—	Red	451
		VM230-02-35B	VM250-02-35B	—	Black	
		VM230-02-35G	VM250-02-35G	—	Green	
		VM230-02-35Y	VM250-02-35Y	—	Yellow	
	Foot pedal	VM220-02-40	VM230-02-40	—	—	450

Note 1) Actuator replacement is available for all types except twist selector (3 position) and foot pedal.
Note 2) For push button (mushroom), push button (extended), push button (flush) and a single unit of fastening ring, refer to pages 2347 and 2348. The other parts are not replaceable.
Note 3) The handle of the selector (2 position and 3 position) cannot be removed or replaced alone.

How to Order

VM2 **3** **0** - **02** - **01** **S** -

Made to Order

(Refer to pages 2342 to 2345 for details.)

X207	Alternate type, Mushroom push button
X219	Push-lock turn-reset type, Mushroom push button

Port size

02	Rc 1/4
N02	NPT 1/4
F02	G 1/4

Number of ports

2	2 port
3	3 port

Actuator type

00	Basic
01	Roller lever
02	One way roller lever
05	Straight plunger
06	Roller plunger
07	Cross roller plunger
08	Toggle lever
30	Push button (Mushroom)
32	Push button (Extended)
33	Push button (Flush) ^{Note 1)}
34	Twist selector (2 position)
36	Key selector (2 position)
35	Twist selector (3 position)
40	Foot pedal


Suffix for actuator

S	Hard steel roller	
R	Red	Color of push button selector
B	Black	
G	Green	
Y	Yellow	


Note 1) When selecting the flush type, it is not necessary to select the suffix for the actuator.

Construction

Non-actuated



Actuated



Component Parts

No.	Description	Material	Note
1	Valve	ADC	Platinum silver
2	Plunger	POM	
3	Plunger retainer	PBT	

No.	Description	Material	Note
4	Cover	POM	
5	Valve	Brass, NBR	
6	Spring	Steel	


VM
VMG
VR
VR51
VHK
VH
VHS
VHS

Series VM200

Series VM200


Basic

VM220-02-00
VM230-02-00




Symbol

2 port



3 port




* 0.5 MPa supply

F.O.F. *	52 N
P.T.	3.0 mm
O.T.	2.0 mm
T.T.	5.0 mm


Roller lever

VM220-02-01
VM230-02-01
VM220-02-01S
VM230-02-01S




Symbol

2 port



3 port




* 0.5 MPa supply

F.O.F. *	24 N
P.T.	3.0 mm
O.T.	4.5 mm
T.T.	11.0 mm


One way roller lever

VM220-02-02
VM230-02-02
VM220-02-02S
VM230-02-02S




Symbol

2 port



3 port




* 0.5 MPa supply

F.O.F. *	22 N
P.T.	7.0 mm
O.T.	5.0 mm
T.T.	12.0 mm


Straight plunger

VM220-02-05
VM230-02-05




Symbol

2 port



3 port



* 0.5 MPa supply

F.O.F. *	56 N
P.T.	3.5 mm
O.T.	2.0 mm
T.T.	5.5 mm

Series VM200


Roller plunger

VM220-02-06

VM230-02-06


VM220-02-06S

VM230-02-06S




Symbol


2 port



3 port



Panel mounting hole



* 0.5 MPa supply

F.O.F. *	56 N
P.T.	3.5 mm
O.T.	2.0 mm
T.T.	5.5 mm


Cross roller plunger

VM220-02-07

VM230-02-07


VM220-02-07S

VM230-02-07S




Symbol


2 port



3 port



Panel mounting hole




* 0.5 MPa supply

F.O.F. *	56 N
P.T.	3.5 mm
O.T.	2.0 mm
T.T.	5.5 mm

Toggle lever


VM220-02-08

VM230-02-08




Symbol


2 port



3 port



Panel mounting hole




* 0.5 MPa supply

F.O.F. *	12 N
T.T.	60°

Push button (Mushroom)

VM220-02-30R/B/G/Y

VM230-02-30R/B/G/Y




Panel mounting hole




Symbol

2 port



3 port






* 0.5 MPa supply

F.O.F. *	52 N
P.T.	4.9 mm
O.T.	1.6 mm
T.T.	6.5 mm


Series VM200

Series VM200


Push button (Extended)
VM220-02-32R/B/G/Y
VM230-02-32R/B/G/Y




Symbol
2 port



3 port






Panel mounting hole




* 0.5 MPa supply	
F.O.F. *	52 N
P.T.	4.9 mm
O.T.	1.6 mm
T.T.	6.5 mm


Push button (Flush)
VM220-02-33
VM230-02-33




Symbol
2 port



3 port







Panel mounting hole




* 0.5 MPa supply	
F.O.F. *	52 N
P.T.	4.9 mm
O.T.	1.6 mm
T.T.	6.5 mm


Twist selector (2 position)
VM220-02-34R/B/G/Y
VM230-02-34R/B/G/Y




Symbol
2 port



3 port



Panel mounting hole





* 0.5 MPa supply	
F.O.F. *	32 N
T.T.	90°


Series VM200

Key selector (2 position)

VM220-02-36
VM230-02-36




Panel mounting hole




Symbol

2 port



3 port





* 0.5 MPa supply

F.O.F. *	32 N
T.T.	90°


Key can be removed at the "on" and "off" positions.

Twist selector (3 position)

VM230-02-35R/B/G/Y
VM250-02-35R/B/G/Y




Panel mounting hole




Symbol

3 port



5 port




* 0.5 MPa supply

F.O.F. *	40 N
T.T.	45°


Foot pedal

VM220-02-40
VM230-02-40




Symbol

2 port



3 port



* 0.5 MPa supply

F.O.F. *	65 N
T.T.	1.2°

3 Port Mechanical Valve Series VM400

RoHS

Either N.C. or N.O. is available.

Piping possible to any port.

Proper countermeasures can be taken for applications in which the noise of the exhaust could cause problems to the surroundings.



Specifications

Fluid	Air/Inert gas		
Operating pressure	-100 kPa to 1.0 MPa		
Ambient and fluid temperature	-5 to 60°C (No freezing)		
Flow characteristics	C[dm ³ /(s·bar)]		
	1(NC)↔2(OUT)	1.4	0.2
	2(NO)↔3(OUT)	1.4	0.15
Lubrication	Not required (Use turbine oil Class 1 ISO VG32, if lubricated)		
Port size	1/8		

Model

	Actuator	Model	Actuator part no.	Application	Weight (g)
Mechanical operation	Basic	VM430-01-00	—	—	110
	Roller lever	VM430-01-01	VM-01A	Polyacetal roller	140
		VM430-01-01S	VM-01AS	Hard steel roller	150
	One way roller lever	VM430-01-02	VM-02A	Polyacetal roller	150
		VM430-01-02S	VM-02AS	Hard steel roller	160
	Straight plunger	VM430-01-05	VM-05A	—	220
	Roller plunger	VM430-01-06	VM-06A	Polyacetal roller	210
		VM430-01-06S	VM-06AS	Hard steel roller	220
	Cross roller plunger	VM430-01-07	VM-07A	Polyacetal roller	210
		VM430-01-07S	VM-07AS	Hard steel roller	220
Manual operation	Toggle lever	VM430-01-08	VM-08A	—	200
	Push button (Mushroom)	VM430-01-30R	VM-30AR	Red	168
		VM430-01-30B	VM-30AB	Black	
		VM430-01-30G	VM-30AG	Green	
		VM430-01-30Y	VM-30AY	Yellow	
	Push button (Extended)	VM430-01-32R	VM-32AR	Red	162
		VM430-01-32B	VM-32AB	Black	
		VM430-01-32G	VM-32AG	Green	
		VM430-01-32Y	VM-32AY	Yellow	
	Push button (Flush)	VM430-01-33	VM-33A	With a set of red, black, green, yellow	167
	Twist selector (2 position)	VM430-01-34R	VM-34AR	Red	168
		VM430-01-34B	VM-34AB	Black	
		VM430-01-34G	VM-34AG	Green	
		VM430-01-34Y	VM-34AY	Yellow	
	Key selector (2 position)	VM430-01-36	VM-36A	—	188

Note 1) Actuator replacement is available for all types.

Note 2) For push button (mushroom), push button (extended), push button (flush) and a single unit of fastening ring, refer to pages 2347 and 2348. The other parts are not replaceable.

Note 3) The handle of the selector (2 position) cannot be removed or replaced alone.

How to Order

VM4 3 0 - 01 - 01 S -

• Made to Order

(Refer to pages 2342 to 2345 for details.)

X207	Alternate type, Mushroom push button
X219	Push-lock turn-reset type, Mushroom push button

• Suffix for actuator

S	Hard steel roller
R	Red
B	Black
G	Green
Y	Yellow

• Actuator type

00	Basic
01	Roller lever
02	One way roller lever
05	Straight plunger
06	Roller plunger
07	Cross roller plunger
08	Toggle lever
30	Push button (Mushroom)
32	Push button (Extended)
33	Push button (Flush) Note 1)
34	Twist selector (2 position)
36	Key selector (2 position)

• Port size


01	Rc 1/8
N01	NPT 1/8
F01	G 1/8

• Number of ports


3	3 port
---	--------

Construction

Non-actuated



Actuated



Component Parts

No.	Description	Material	Note
1	Body	ADC	Platinum silver
2	Plunger	POM	
3	Upper lid	Brass	Black zinc chromated
4	Spool valve	Aluminum alloy, NBR	Rubber lined



No.	Description	Material	Note
5	Over travel spring	Stainless steel	
6	Retainer	Brass	
7	Spring	Stainless steel	
8	Spring	Stainless steel	

VM
VMG
VR
VR51
VHK
VH
VHS
VHS

Series VM400

Basic

VM430-01-00



Symbol





F.O.F.	26 N
P.T.	1.5 mm
O.T.	2.0 mm
T.T.	3.5 mm


Roller lever

VM430-01-01

VM430-01-01S



Symbol






F.O.F.	12 N
P.T.	4.0 mm
O.T.	4.5 mm
T.T.	8.5 mm

One way roller lever

VM430-01-02


VM430-01-02S

**Symbol**


F.O.F.	11 N
P.T.	4.0 mm
O.T.	5.0 mm
T.T.	9.0 mm

Straight plunger


VM430-01-05



Panel mounting hole




Symbol




F.O.F.	30 N
P.T.	3.5 mm
O.T.	2.0 mm
T.T.	5.5 mm

Series VM400


Roller plunger VM430-01-06 VM430-01-06S



Panel mounting hole




Symbol




F.O.F.	30 N
P.T.	3.5 mm
O.T.	2.0 mm
T.T.	5.5 mm


Cross roller plunger VM430-01-07 VM430-01-07S



Panel mounting hole




Symbol




F.O.F.	30 N
P.T.	3.5 mm
O.T.	2.0 mm
T.T.	5.5 mm


Toggle lever VM430-01-08



Panel mounting hole




Symbol




F.O.F.	7 N
T.T.	60°


Push button (Mushroom) VM430-01-30R/B/G/Y



Panel mounting hole



Symbol




F.O.F.	26 N
P.T.	4.6 mm
O.T.	1.6 mm
T.T.	6.5 mm


Series VM400

Series VM400


Push button (Extended) VM430-01-32R/B/G/Y



Push button (Flush) VM430-01-33




Twist selector (2 position) VM430-01-34R/B/G/Y




Series VM400

Key selector (2 position)
VM430-01-36




Key can be removed at the "on" and "off" positions.

Panel mounting hole



Symbol



F.O.F.	20 N
T.T.	90°

VM

VMG

VR

VR51

VHK

VH

VHS

VHS

3 Port Mechanical Valve: Heavy Duty Type

Series VM800

RoHS

Sturdy construction.

Either N.C. or N.O. is available.

Piping possible to any port.

Proper countermeasures can be taken for applications in which the noise of the exhaust could cause problems to the surroundings.

Many actuator positions and orientation options.



Specifications

Fluid	Air/Inert gas			
Operating pressure	-100 kPa to 1.0 MPa			
Ambient and fluid temperature	-5 to 60°C (No freezing)			
Flow characteristics	C [dm ³ /(s·bar)]	b	Cv	
	1 (NC) ↔ 2 (OUT)	1.4	0.2	0.29
	2 (NO) ↔ 3 (OUT)	1.4	0.15	0.29
Lubrication	Not required (Use turbine oil Class 1 ISO VG32, if lubricated.)			
Port size	1/8			

Model

Actuator	Model	Actuator part no.	Weight (g)
Basic	VM830-01-00	—	180
Roller lever	VM830-01-01	VM-01F	280
Adjustable roller lever	VM830-01-13	VM-13F	300
Adjustable rod lever	VM830-01-14	VM-14F	276

• Actuator replacement is available.

How to Order


VM830 - 01 - 01

Port size		Actuator type	
01	Rc 1/8	00	Basic
N01	NPT 1/8	01	Roller lever
F01	G 1/8	13	Adjustable roller lever
		14	Adjustable rod lever


Number of ports	
3	3 port

Application


• Movement is changeable.




• Roller can be mounted to inside of lever.





• Lever location can be changed.



• Head direction can be changed.




• Lever length adjustment.



It can be operated by bending the rod. In this case, make sure that the minimum bending radius of the rod is 10R or more.

Construction




Component Parts

No.	Description	Material	Note
1	Body	ADC	Platinum silver
2	Plunger	POM	
3	Spool valve	Aluminum alloy, NBR	Rubber lined


No.	Description	Material	Note
4	Over travel spring	Stainless steel	
5	Retainer	Brass	
6	Spring	Steel	Zinc chromated

Series VM800

Basic / VM830-01-00



Symbol




F.O.F.	23 N
P.T.	1.0 mm
O.T.	2.0 mm
T.T.	3.0 mm


Series VM800

Series VM800


Roller lever / VM830-01-01



Adjustable roller lever / VM830-01-13



Adjustable rod lever / VM830-01-14



5 Port Mechanical Valve Metal Seal

Series VZM400

RoHS

**Compact design,
large flow capacity
High cycle rate,
long life/300 c.p.m. or less
Piping possible to any EXH
port.**

Proper countermeasures can be taken for applications in which the noise of the exhaust could cause problems to the surroundings.

**Pilot type is selectable.
(Internal pilot and external pilot)**



Specifications

Fluid	Air/Inert gas		
Operating pressure	0.15 to 1.0 MPa ⁽¹⁾		
Ambient and fluid temperature	-5 to 60°C (No freezing)		
Flow characteristics	C[dm ³ /(s·bar)]	b	Cv
1(P)→2(B)/4(A)	2.0	0.14	0.49
2(B)/4(A)→4(EB)/5(EA)	1.7	0.25	0.44
Maximum frequency (Mechanical operation type)	300 c.p.m. or less		
Lubrication	Not required (Use turbine oil class 1 ISO VG32, if lubricated.)		
Port size	Main valve 1/8		
	Pilot valve (EXH)/M5 x 0.8		
Option	Foot bracket ⁽²⁾		

Note 1) External pilot type Main valve: 0 to 1.0 MPa
Pilot valve: 0.15 to 1.0 MPa

Note 2) The standard body can not be retrofitted with a foot bracket.

Model

	Actuator	Model	Actuator part no.	Application	Weight (g)
Mechanical operation	Basic	VZM450-01-00	—	—	120
	Roller lever	VZM450-01-01	VM-01C	Polyacetal roller	160
		VZM450-01-01S	VM-01CS	Hard steel roller	170
	One way roller lever	VZM450-01-02	VM-02C	Polyacetal roller	170
		VZM450-01-02S	VM-02CS	Hard steel roller	180
	Straight plunger	VZM450-01-05	VM-05C	—	200
Manual operation	Roller plunger	VZM450-01-06	VM-06C	Polyacetal roller	200
		VZM450-01-06S	VM-06CS	Hard steel roller	200
	Toggle lever	VZM450-01-08	VM-08C	—	190
	Push button (Mushroom)	VZM450-01-30R	VM-30CR	Red	199
		VZM450-01-30B	VM-30CB	Black	
		VZM450-01-30G	VM-30CG	Green	
		VZM450-01-30Y	VM-30CY	Yellow	
	Push button (Extended)	VZM450-01-32R	VM-32CR	Red	192
		VZM450-01-32B	VM-32CB	Black	
		VZM450-01-32G	VM-32CG	Green	
		VZM450-01-32Y	VM-32CY	Yellow	
	Push button (Flush)	VZM450-01-33	VM-33C	With a set of red, black, green, yellow	197
		VZM450-01-34R	VM-34CR	Red	
	Twist selector (2 position)	VZM450-01-34B	VM-34CB	Black	198
		VZM450-01-34G	VM-34CG	Green	
		VZM450-01-34Y	VM-34CY	Yellow	
	Key selector (2 position)	VZM450-01-36	VM-36C	—	217

Note 1) Actuator replacement is available for all types.

Note 2) For push button (mushroom), push button (extended), push button (flush) and a single unit of fastening ring, refer to pages 2347 and 2348. The other parts are not replaceable.

Note 3) The handle of the selector (2 position) cannot be removed or replaced alone.

How to Order

VZM45

0

-

01

-

01

-

S

-

-

● Made to Order

(Refer to pages 2342 to 2345 for details.)

X207

Alternate type, Mushroom push button

X219

Push-lock turn-reset type, Mushroom push button

● Option

F

Foot bracket
(Only internal pilot)

● Port size

01

Rc 1/8

N01

NPT 1/8

F01

G 1/8

● Actuator type

00

Basic

01

Roller lever

02

One Way Roller Lever

05

Straight plunger

06

Roller plunger

08

Toggle lever

30

Push button (Mushroom)

32

Push button (Extended)

33

Push button (Flush) Note 1)

34

Twist selector (2 position)

36

Key selector (2 position)

● Suffix for actuator

S

Hard steel roller

R

Red

B

Black

G

Green

Y

Yellow

Color of
push button
selector

● Body option

0

Internal pilot type


1

External pilot type


Note 1) When selecting the flush type, it is not necessary to select the suffix for the actuator.

Construction

Non-actuated



Actuated




Component Parts

No.	Description	Material	Note
1	Body	ADC	Platinum silver
2	Pilot body	PBT	ZDC only for external pilot type
3	Head cover	ZDC	Black zinc chromated
4	Spool/sleeve	Stainless steel	
5	End cover	POM	
6	Piston A	POM	
7	Plunger	POM	
8	Valve seat (A)	POM	
9	Valve seat (B)	POM	


No.	Description	Material	Note
10	Valve	NBR	
11	Piston guide B	Aluminum alloy	
12	Return spring	Stainless steel	
13	Cushion	Rubber	
14	Cushion	Rubber	
15	Valve spring	Stainless steel	
16	Return spring	Stainless steel	
17	Piston B	POM	

Series VZM400


Basic / VZM450-01-00



Roller lever / VZM450-01-01 · VZM450-01-01S




One way roller lever / VZM450-01-02 · VZM450-01-02S




Series VZM400


Push button (Mushroom) / VZM450-01-30R/B/G/Y



Push button (Extended) / VZM450-01-32R/B/G/Y



Push button (Flush) / VZM450-01-33



5 Port Mechanical Valve Rubber Seal

Series VZM500

RoHS

**Compact design,
large flow capacity
High cycle rate,
long life/300 c.p.m. or less
Piping possible to any EXH
port.**

Proper countermeasures can be taken for applications in which the noise of the exhaust could cause problems to the surroundings.

**Pilot type is selectable.
(Internal pilot and external pilot)**

**Foot bracket and manifold
mounting possible.**



Specifications

Fluid	Air/Inert gas		
Operating pressure	0.15 to 0.7 MPa ⁽¹⁾		
Ambient and fluid temperature	-5 to 60°C (No freezing)		
Flow characteristics	C[dm ³ /(s·bar)]	b	Cv
	1(P)→2(B)/4(A) 2(B)/4(A)→4(R2)/5(R1)	2.2 2.4	0.36 0.34 0.58 0.63
Maximum frequency (Mechanical operation type)	300 c.p.m. or less		
Lubrication	Not required (Use turbine oil Class 1 ISO VG32, if lubricated.)		
Port size	Main valve 1/8		
	Pilot valve (EXH)/M5 x 0.8		
Option	Foot bracket ⁽²⁾		

* Please contact SMC for manifold mounting style.

Note 1) External pilot type Main valve: 0 to 0.7 MPa

Pilot valve: 0.15 to 0.7 MPa

Note 2) The standard body can not be retrofitted with a foot bracket.

Model

	Actuator	Model	Actuator part no.	Application	Weight (g)
Mechanical operation	Basic	VZM550-01-00	—	—	110
	Roller lever	VZM550-01-01	VM-01C	Polyacetal roller	140
		VZM550-01-01S	VM-01CS	Hard steel roller	150
	One way roller lever	VZM550-01-02	VM-02C	Polyacetal roller	150
		VZM550-01-02S	VM-02CS	Hard steel roller	160
	Straight plunger	VZM550-01-05	VM-05C	—	180
	Roller plunger	VZM550-01-06	VM-06C	Polyacetal roller	180
		VZM550-01-06S	VM-06CS	Hard steel roller	180
Manual operation	Toggle lever	VZM550-01-08	VM-08C	—	170
	Push button (Mushroom)	VZM550-01-30R	VM-30CR	Red	179
		VZM550-01-30B	VM-30CB	Black	
		VZM550-01-30G	VM-30CG	Green	
		VZM550-01-30Y	VM-30CY	Yellow	
	Push button (Extended)	VZM550-01-32R	VM-32CR	Red	172
		VZM550-01-32B	VM-32CB	Black	
		VZM550-01-32G	VM-32CG	Green	
		VZM550-01-32Y	VM-32CY	Yellow	
	Push button (Flush)	VZM550-01-33	VM-33C	With a set of red, black, green, yellow	177
		VZM550-01-34R	VM-34CR	Red	178
	Twist selector (2 position)	VZM550-01-34B	VM-34CB	Black	
		VZM550-01-34G	VM-34CG	Green	
		VZM550-01-34Y	VM-34CY	Yellow	
	Key selector (2 position)	VZM550-01-36	VM-36C	—	197
	Push-pull	VZM550-01-37	—	Black	170

Note 1) Actuator replacement is available for all types. (Except push-pull)

Note 2) For push button (mushroom), push button (extended), push button (flush) and a single unit of fastening ring, refer to pages 2347 and 2348. The other parts are not replaceable.

Note 3) The handle of the selector (2 position) cannot be removed or replaced alone.

How to Order

VZM55

0

01

01

S

●Made to Order
(Refer to pages 2342 to 2345 for details.)
X207 Alternate type, Mushroom push button
X219 Push-lock turn-reset type, Mushroom push button

●Option
F Foot bracket

●Port size
01 Rc 1/8
N01 NPT 1/8
F01 G 1/8

●Body option
0 Standard
1 * External pilot type
* Except VZM550-01-37


●Actuator type
00 Basic
01 Roller lever
02 One way roller lever
05 Straight plunger
06 Roller plunger
08 Toggle lever
30 Push button (Mushroom)
32 Push button (Extended)
33 Push button (Flush) Note 1
34 Twist selector (2 position)
36 Key selector (2 position)
37 Push-pull

●Suffix for actuator
S Hard steel roller
R Red
B Black
G Green
Y Yellow
Color of push button selector


Note 1) When selecting the flush type, it is not necessary to select the suffix for the actuator.

Construction

Non-actuated



Actuated



Component Parts


No.	Description	Material	Note
1	Body	ADC	Platinum silver
2	Pilot body	PBT	ZDC only for external pilot type
3	Head cover	ZDC	Black zinc chromated
4	Spool valve assembly		
5	End cover	ZDC	Matt-black
6	Piston	POM	
7	Plunger	POM	

No.	Description	Material	Note
8	Valve seat (A)	POM	
9	Valve seat (B)	POM	
10	Valve assembly	NBR	
11	Valve spring	Stainless steel	
12	Return spring	Stainless steel	
13	Spool spring	Stainless steel	

Series VZM500

Basic


VZM550-01-00



Roller lever

VZM550-01-01


VZM550-01-01S



One way roller lever

VZM550-01-02


VZM550-01-02S




Series VZM500

Series VZM500


Straight plunger VZM550-01-05



Panel mounting hole




Symbol




0.5 MPa supply

F.O.F. *	18 N
P.T.	1.5 mm
O.T.	2.0 mm
T.T.	3.5 mm


Roller plunger VZM550-01-06 VZM550-01-06S



Panel mounting hole




Symbol



0.5 MPa supply

F.O.F. *	18 N
P.T.	1.5 mm
O.T.	2.0 mm
T.T.	3.5 mm


Toggle lever VZM550-01-08



Panel mounting hole



Symbol




0.5 MPa supply

F.O.F. *	15 N
T.T.	40°


Series VZM500

Push button (Mushroom)


VZM550-01-30R/B/G/Y



Panel mounting hole



Symbol




* 0.5 MPa supply


F.O.F. *	21 N
P.T.	4.8 mm
O.T.	1.7 mm
T.T.	6.5 mm

Push button (Extended)


VZM550-01-32R/B/G/Y



Panel mounting hole



Symbol




* 0.5 MPa supply


F.O.F. *	21 N
P.T.	4.8 mm
O.T.	1.7 mm
T.T.	6.5 mm

Push button (Flush)


VZM550-01-33



Panel mounting hole



Symbol



* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.8 mm
O.T.	1.7 mm
T.T.	6.5 mm

VM

VMG

VR

VR51


VHK

VH


VHS

VHS

External pilot type
VZM551 type



With foot bracket
VZM55□-01-□□-F



VM
VMG
VR
VR51
VHK
VH
VHS□
VHS

5 Port Mechanical Valve Rubber Seal

Series VFM300

RoHS

**Compact design,
large flow capacity
High cycle rate,
long life/300 c.p.m. or less
Piping possible to any EXH
port.**

Proper countermeasures can be taken for applications in which the noise of the exhaust could cause problems to the surroundings.

**Pilot type is selectable.
(Internal pilot and external pilot)**



Specifications

Fluid	Air/Inert gas		
Operating pressure	0.15 to 0.9 MPa ⁽¹⁾		
Ambient and fluid temperature	-5 to 60°C (No freezing)		
Flow characteristics	C[dm ³ /(s·bar)]		b
	1(P)→2(C2)/4(C1)		0.36
	2(C2)/4(C1)→3(E2)/5(E1)		0.32
Maximum frequency (Mechanical operation type)	300 c.p.m. or less		
Lubrication	Not required (Use turbine oil Class 1 ISO VG32, if lubricated.)		
Port size	Main valve/1P, 4A, 2B port 1/4, 5EA/3EB port 1/8		
	Pilot valve (EXH)/M5 x 0.8		
Option	Foot bracket ⁽²⁾		

Note 1) External pilot type Main valve: 0 to 0.9 MPa
Pilot valve: 0.15 to 0.9 MPa

Note 2) The standard body can not be retrofitted with a foot bracket.

Model

	Actuator	Model	Actuator part no.	Application	Weight (g)
Mechanical operation	Basic	VFM350-02-00	—	—	190
	Roller lever	VFM350-02-01	VM-01C	Polyacetal roller	270
		VFM350-02-01S	VM-01CS	Hard steel roller	280
	One way roller lever	VFM350-02-02	VM-02C	Polyacetal roller	280
		VFM350-02-02S	VM-02CS	Hard steel roller	290
	Straight plunger	VFM350-02-05	VM-05D	—	380
	Roller plunger	VFM350-02-06	VM-06D	Polyacetal roller	370
VFM350-02-06S		VM-06DS	Hard steel roller	380	
Manual operation	Toggle lever	VFM350-02-08	VM-08D	—	360
	Push button (Mushroom)	VFM350-02-30R	VM-30CR	Red	309
		VFM350-02-30B	VM-30CB	Black	
		VFM350-02-30G	VM-30CG	Green	
		VFM350-02-30Y	VM-30CY	Yellow	
	Push button (Extended)	VFM350-02-32R	VM-32CR	Red	302
		VFM350-02-32B	VM-32CB	Black	
		VFM350-02-32G	VM-32CG	Green	
		VFM350-02-32Y	VM-32CY	Yellow	
	Push button (Flush)	VFM350-02-33	VM-33C	With a set of red, black, green, yellow	307
		VFM350-02-34R	VM-34CR		
	Twist selector (2 position)	VFM350-02-34B	VM-34CB	Black	308
		VFM350-02-34G	VM-34CG	Green	
VFM350-02-34Y		VM-34CY	Yellow		
Key selector (2 position)	VFM350-02-36	VM-36C	—	327	

Note 1) Actuator replacement is available for all types.

Note 2) For push button (mushroom), push button (extended), push button (flush) and a single unit of fastening ring, refer to pages 2347 and 2348. The other parts are not replaceable.

Note 3) The handle of the selector (2 position) cannot be removed or replaced alone.

How to Order

VFM35 0 - 02 - 01 S - -

Made to Order

(Refer to pages 2342 to 2345 for details.)

X207	Alternate type, Mushroom push button
X219	Push-lock turn-reset type, Mushroom push button

Option

F	Foot bracket (Only internal pilot)
----------	---------------------------------------

Port size

02	Rc 1/4
N02	NPT 1/4
F02	G 1/4

Body option

0	Internal pilot type
1	External pilot type

Actuator type

00	Basic
01	Roller lever
02	One way roller lever
05	Straight plunger
06	Roller plunger
08	Toggle lever
30	Push button (Mushroom)
32	Push button (Extended)
33	Push button (Flush) Note 1)
34	Twist selector (2 position)
36	Key selector (2 position)

Note 1) When selecting the flush type, it is not necessary to select the suffix for the actuator.


Suffix for actuator

S	Hard steel roller
R	Red
B	Black
G	Green
Y	Yellow


Color of
push button
selector

Construction

Non-actuated



Actuated



Component Parts

No.	Description	Material	Note
1	Body	ADC	Platinum silver
2	Pilot body	PBT	ZDC only for external pilot type
3	Head cover	ZDC	Black zinc chromated
4	Spool valve assembly		
5	End cover	ADC	Matt-black
6	Piston	POM	
7	Plunger	POM	

No.	Description	Material	Note
8	Valve seat (A)	POM	
9	Valve seat (B)	POM	
10	Valve	NBR	
11	Valve spring	Stainless steel	
12	Return spring	Stainless steel	
13	Spool spring	Stainless steel	

VM

VMG

VR

VR51

VHK

VH

VHS


VHS

Series VFM300


Series VFM300

Basic

VFM350-02-00



Symbol




* 0.5 MPa supply

F.O.F. *	16 N
P.T.	1.0 mm
O.T.	2.0 mm
T.T.	3.0 mm


Roller lever

VFM350-02-01

VFM350-02-01S



Symbol




* 0.5 MPa supply

F.O.F. *	8 N
P.T.	2.2 mm
O.T.	4.0 mm
T.T.	6.2 mm


One way roller lever

VFM350-02-02

VFM350-02-02S



Symbol




* 0.5 MPa supply

F.O.F. *	7 N
P.T.	2.4 mm
O.T.	4.6 mm
T.T.	7.0 mm


5 Port Mechanical Valve Rubber Seal **Series VFM300**

Series VFM300


Straight plunger VFM350-02-05



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F. *	20 N
P.T.	1.5 mm
O.T.	2.0 mm
T.T.	3.5 mm


Roller plunger VFM350-02-06 VFM350-02-06S



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F. *	20 N
P.T.	1.5 mm
O.T.	2.0 mm
T.T.	3.5 mm


Toggle lever VFM350-02-08



Panel mounting hole



Symbol




* 0.5 MPa supply

F.O.F. *	15 N
T.T.	40°


Series VFM300

Series VFM300


Push button (Mushroom) VFM350-02-30R/B/G/Y



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.8 mm
O.T.	1.7 mm
T.T.	6.5 mm


Push button (Extended) VFM350-02-32R/B/G/Y



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.8 mm
O.T.	1.7 mm
T.T.	6.5 mm


Push button (Flush) VFM350-02-33



Panel mounting hole



Symbol




* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.8 mm
O.T.	1.7 mm
T.T.	6.5 mm


5 Port Mechanical Valve Rubber Seal **Series VFM300**

Series VFM300


Twist selector (2 position) VFM350-02-34R/B/G/Y



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F. *	23 N
T.T.	90°


Key selector (2 position) VFM350-02-36



Panel mounting hole



Symbol




* 0.5 MPa supply


F.O.F. *	26 N
T.T.	90°

Key can be removed at the "on" and "off" positions.

External pilot type VFM351 type



With foot bracket VFM350-02-□-F



5 Port Mechanical Valve Metal Seal

Series VFM200

RoHS

**Compact design,
large flow capacity
High cycle rate,
long life/300 c.p.m. or less
Piping possible to any EXH
port.**

Proper countermeasures can be taken for applications in which the noise of the exhaust could cause problems to the surroundings.

**Pilot type is selectable.
(Internal pilot and external
pilot)**



Specifications

Fluid	Air/Inert gas		
Operating pressure	0.1 to 1.0 MPa ⁽¹⁾		
Ambient and fluid temperature	-5 to 60°C (No freezing)		
Flow characteristics	C[dm ³ /(s·bar)]	b	Cv
1(P)→2(B)/4(A)	4.0	0.2	0.9
2(B)/4(A)→4(EB)/5(EA)	3.5	0.32	0.85
Maximum frequency (Mechanical operation type)	300 c.p.m. or less		
Lubrication	Not required (Use turbine oil Class 1 ISO VG32, if lubricated.)		
Port size	Main valve Rc 1/4 Pilot valve (EXH)/M5 x 0.8		
Option	Foot bracket ⁽²⁾		

Note 1) External pilot type Main valve: 0 to 1.0 MPa
Pilot valve: 0.1 to 1.0 MPa

Note 2) The bracket can not be retrofitted later.

Model

	Actuator	Model	Actuator part no.	Application	Weight (g)
Mechanical operation	Basic	VFM250-02-00	—	—	300
	Roller lever	VFM250-02-01	VM-01C	Polyacetal roller	310
		VFM250-02-01S	VM-01CS	Hard steel roller	320
	One way roller lever	VFM250-02-02	VM-02C	Polyacetal roller	320
		VFM250-02-02S	VM-02CS	Hard steel roller	330
	Straight plunger	VFM250-02-05	VM-05D	—	420
Manual operation	Roller plunger	VFM250-02-06	VM-06D	Polyacetal roller	410
		VFM250-02-06S	VM-06DS	Hard steel roller	420
	Toggle lever	VFM250-02-08	VM-08D	—	400
	Push button (Mushroom)	VFM250-02-30R	VM-30CR	Red	349
		VFM250-02-30B	VM-30CB	Black	
		VFM250-02-30G	VM-30CG	Green	
		VFM250-02-30Y	VM-30CY	Yellow	
	Push button (Extended)	VFM250-02-32R	VM-32CR	Red	342
		VFM250-02-32B	VM-32CB	Black	
		VFM250-02-32G	VM-32CG	Green	
		VFM250-02-32Y	VM-32CY	Yellow	
	Push button (Flush)	VFM250-02-33	VM-33C	With a set of red, black, green, yellow	347
	Twist selector (2 position)	VFM250-02-34R	VM-34CR	Red	348
		VFM250-02-34B	VM-34CB	Black	
		VFM250-02-34G	VM-34CG	Green	
		VFM250-02-34Y	VM-34CY	Yellow	
	Key selector (2 position)	VFM250-02-36	VM-36C	—	367

Note 1) Actuator replacement is available for all types.

Note 2) For push button (mushroom), push button (extended), push button (flush) and a single unit of fastening ring, refer to pages 2347 and 2348. The other parts are not replaceable.

Note 3) The handle of the selector (2 position) cannot be removed or replaced alone.

How to Order

VFM25 **0** - **02** - **01** **S** - -

Made to Order

(Refer to pages 2342 to 2345 for details.)

X207	Alternate type, Mushroom push button
X219	Push-lock turn-reset type, Mushroom push button

Option

F	Foot bracket (Only internal pilot)
----------	---------------------------------------

Port size

02	Rc 1/4
-----------	--------

Body option

0	Internal pilot type
1	External pilot type

Actuator type

00	Basic
01	Roller lever
02	One way roller lever
05	Straight plunger
06	Roller plunger
08	Toggle lever
30	Push button (Mushroom)
32	Push button (Extended)
33	Push button (Flush) Note 1)
34	Twist selector (2 position)
36	Key selector (2 position)

Suffix for actuator


S	Hard steel roller
R	Red
B	Black
G	Green
Y	Yellow

Color of push button selector


Note 1) When selecting the flush type, it is not necessary to select the suffix for the actuator.

Construction

Non-actuated



Actuated



Component Parts

No.	Description	Material	Note
1	Body	ADC	Platinum silver
2	Pilot body	ZDC	Platinum silver
3	Head cover	ZDC	Black zinc chromated
4	Spool/sleeve	Stainless steel	
5	End cover	POM	
6	Piston guide	Brass	
7	Piston guide for end cover	Brass	
8	Piston	POM	
9	Piston for end cover	POM	
10	Guide bushing	POM	
11	Cushion	Urethane rubber	


No.	Description	Material	Note
12	Cushion for end cover	Urethane rubber	
13	Plunger	Stainless steel	
14	Valve seat (A)	POM	
15	Valve seat (B)	POM	
16	Valve	NBR	
17	Return spring	Stainless steel	
18	Return spring	Stainless steel	
19	Valve spring	Stainless steel	
20	Mini Y packing	NBR	
21	Mini Y packing	NBR	

Series VFM200


Series VFM200

Basic

VFM250-02-00



Symbol




* 0.5 MPa supply

F.O.F. *	16 N
P.T.	1.0 mm
O.T.	2.0 mm
T.T.	3.0 mm


Roller lever

VFM250-02-01

VFM250-02-01S



Symbol




* 0.5 MPa supply

F.O.F. *	8 N
P.T.	2.2 mm
O.T.	4.0 mm
T.T.	6.2 mm


One way roller lever

VFM250-02-02

VFM250-02-02S




Symbol



* 0.5 MPa supply


F.O.F. *	7 N
P.T.	2.4 mm
O.T.	4.6 mm
T.T.	7.0 mm

VFM250-02-05



F.O.F. *	20 N
P.T.	1.5 mm
O.T.	2.0 mm
T.T.	3.5 mm


VFM250-02-06



Min. 3
Max. 11

F.O.F. *	20 N
P.T.	1.5 mm
O.T.	2.0 mm
T.T.	3.5 mm

VFM250-02-08




Max. 7.5

F.O.F. *	15 N
T.T.	40°


Series VFM200

Series VFM200


Push button (Mushroom) VFM250-02-30R/B/G/Y



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.8 mm
O.T.	1.7 mm
T.T.	6.5 mm


Push button (Extended) VFM250-02-32R/B/G/Y



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.8 mm
O.T.	1.7 mm
T.T.	6.5 mm


Push button (Flush) VFM250-02-33



Panel mounting hole



Symbol




* 0.5 MPa supply

F.O.F. *	21 N
P.T.	4.8 mm
O.T.	1.7 mm
T.T.	6.5 mm


5 Port Mechanical Valve Metal Seal **Series VFM200**

Series VFM200


Twist selector (2 position) VFM250-02-34R/B/G/Y



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F. *	23 N
T.T.	90°


Key selector (2 position) VFM250-02-36



Panel mounting hole



Symbol




* 0.5 MPa supply


F.O.F. *	26 N
T.T.	90°

Key can be removed at the "on" and "off" positions.

External pilot type VFM251 type



With foot bracket VFM250-02-□□-F





Series VM100/200 has been remodeled.
When selecting this model, please consider
the new VM100-A/VM200-A series.


Alternate Type, Mushroom Push Button

X207


Alternate type: When pushing the push button, the valve actuates and will hold its position even after the button is released. Pushing the button again will return the button and valve to their previous position.

VM120-01-30R/B/G/Y-X207


VM130-01-30R/B/G/Y-X207




Panel mounting hole



Symbol
2 port




3 port




F.O.F.*	21 N
T.T.	6.7 mm

VM220-02-30R/B/G/Y-X207


VM230-02-30R/B/G/Y-X207




Panel mounting hole



Symbol
2 port




3 port




F.O.F.*	52 N
T.T.	6.7 mm


VM430-01-30R/B/G/Y-X207



Panel mounting hole



Symbol



* 0.5 MPa supply

F.O.F.*	26 N
T.T.	6.7 mm

Made to Order 2


Please contact SMC for detailed specifications, dimensions and delivery.




Alternate Type, Mushroom Push Button

X207


VZM450-01-30R/B/G/Y-X207



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F.*	16 N
T.T.	6.7 mm


VZM550-01-30R/B/G/Y-X207



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F.*	21 N
TT	6.7 mm


VFM350-02-30R/B/G/Y-X207



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F.*	21 N
T.T.	6.7 mm


VFM250-02-30R/B/G/Y-X207



Panel mounting hole



Symbol



* 0.5 MPa supply

F.O.F.*	21 N
T.T.	6.7 mm



Series VM100/200 has been remodeled.
When selecting this model, please consider
the new VM100-A/VM200-A series.


Push-lock Turn-reset Type, Mushroom Push Button

X219


Push-lock turn-reset type: When pressing the push button, it is locked in this status. Turning the button clockwise will reset it.

VM120-01-30R/B/G/Y-X219

VM130-01-30R/B/G/Y-X219




Panel mounting hole




Symbol

2 port



3 port




* 0.5 MPa supply


F.O.F. *	52 N
T.T.	5.8 mm

VM220-02-30R/B/G/Y-X219

VM230-02-30R/B/G/Y-X219




Panel mounting hole




Symbol

2 port




3 port




* 0.5 MPa supply

F.O.F. *	52 N
T.T.	5.8 mm


VM430-01-30R/B/G/Y-X219



Panel mounting hole



Symbol




* 0.5 MPa supply

F.O.F. *	26 N
T.T.	5.8 mm


Push-lock Turn-reset Type, Mushroom Push Button

X219


VZM450-01-30R/B/G/Y-X219



Panel mounting hole




Symbol




* 0.5 MPa supply

F.O.F. *	21 N
T.T	5.8 mm


VZM550-01-30R/B/G/Y-X219



Panel mounting hole




Symbol



* 0.5 MPa supply

F.O.F. *	21 N
T.T.	5.8 mm


VFM350-02-30R/B/G/Y-X219



Panel mounting hole




Symbol



* 0.5 MPa supply

F.O.F.*	21 N
TT	58 mm


VFM250-02-30R/B/G/Y-X219



Panel mounting hole



Symbol



* 0.5 MPa supply

F.O.F.*	21 N
T.T.	5.8 mm



Series VM Specific Product Precautions 1

Be sure to read before handling.

Refer to front matter 53 for Safety Instructions and pages 3 to 8 for 3/4/5 Port Solenoid Valve Precautions.

Mounting

⚠ Warning

1. Conditions for mechanical operation

Do not move the mechanical operation beyond the operating limit position, as this could damage the mechanical valve itself and lead to equipment malfunction.


• Actuator stroke

Operate the mechanism within the stroke range that has been obtained through the formula given below. (Do not move beyond the operating limit position.)

Operating stroke: $(P.T. + 0.5 \times O.T.)$ to $(P.T. + O.T. - 0.1)$

Series	Actuator	Actuator stroke (mm)
VM1000	Basic T.T. = 4.8 mm (T.T. = 2.5 mm)	3.7 to 4.7 (2.2 to 2.4)
	Roller lever	3.5 to 4.4
	One way roller lever	3.5 to 4.4
	Basic	2.2 to 2.9
VM100	Roller lever	4.3 to 5.3
	One way roller lever	4.3 to 5.3
	Straight plunger	2.7 to 3.4
	Roller plunger	2.7 to 3.4
	Cross roller plunger	2.7 to 3.4
VM200	Basic	4.0 to 4.9
	Roller lever	8.7 to 10.7
	One way roller lever	9.5 to 11.7
	Straight plunger	4.5 to 5.4
	Roller plunger	4.5 to 5.4
VM400	Cross roller plunger	4.5 to 5.4
	Basic	2.5 to 3.4
	Roller lever	6.2 to 8.2
	One way roller lever	6.5 to 8.7
	Straight plunger	4.5 to 5.4
VZM500 VFM400 VFM300 VFM200	Roller plunger	4.5 to 5.4
	Cross roller plunger	4.5 to 5.4
	Basic	2.0 to 2.9
	Roller lever	4.2 to 6.0
	One way roller lever	4.7 to 6.7
	Straight plunger	2.5 to 3.4
	Roller plunger	2.5 to 3.4

For straight and roller plunger types, there is a groove indicating P.T. and T.T. for stroke adjustment.



Pressure Source


⚠ Warning

Operable fluid is either air or inert gas only. It cannot be used for corrosive gas and fluid.

⚠ Caution

When using vacuum pressure for VM100, supply vacuum pressure to P port.

Definition of Symbol



F.O.F. (Full Operating Force) .. Required force to total travel position.

P.T. (Pre-travel) From free position to initial valve operating position.

O.T. (Over Travel) From initial valve operating position to total travel position.

T.T. (Total Travel) From free position to total travel position.

Caution

This product cannot be used for applications in which the pressure must be sealed because there will be a slight leakage. Please consult with SMC for this type of application.



Series VM

Specific Product Precautions 2

Be sure to read before handling.

Refer to front matter 53 for Safety Instructions and pages 3 to 8 for 3/4/5 Port Solenoid Valve Precautions.

Mounting

⚠ Warning

2. Conditions for mechanical operation


- Cam and dog angle and maximum speed

Select the angle and the maximum speed of the operating cam and the dog of the mechanism from within the selection range given in the table below.

If they are operated beyond the selection range, the cam and the dog could apply impact shocks to the actuator, leading to damage.

Series	Actuator	Angle limit switch actuator	Max. speed limit switch actuator (m/s)
VM1000	Roller lever	30°	0.7
	45°	0.3	
	One way roller lever	30°	0.7
VM100 VM200 VM400	45°	0.3	
	Roller lever	30°	0.7
	45°	0.3	
	One way roller lever	30°	0.7
	45°	0.3	
	Straight plunger	—	0.2
VZM500 VZM400 VFM300 VFM200	Roller plunger	30°	0.3
	Cross roller plunger	30°	0.3
	Roller lever	30°	1.5
	45°	0.7	
	One way roller lever	30°	0.7
VM800	45°	0.3	
	Straight plunger	—	0.4
	Roller plunger	30°	0.7
	Roller lever	30°	0.5
	45°	0.2	
	Adjustable roller lever	30°	0.2
	45°	0.1	
	Adjustable rod lever	—	0.2

Avoid abrupt angles on limit switch actuator.



Cam and Dog Material

Roller material	Plunger material	Plunger surface finish
Polyacetal	Steel	▽ Rz6.3
Steel	Steel, Resin	▽ Rz12.5

3. Never perform additional machining such as enlarging the body mounting holes.

As doing so could lead to abnormal conditions such as air leakage.

4. Operate all manual valves such as the push pin types, the selector types, and the flip toggle types with your finger.

If a hammer or other tools are used, or it is operated mechanically through the use of a cylinder or the like, damage could result.

Environments

⚠ Caution

1. Do not operate it in an area in which fluids such as oil, coolant, or water splash on it or dust comes in contact with it. Because it does not have a waterproof or dustproof construction, fluids or dust could enter the valve, leading to malfunction. Therefore, take measures such as providing a protective cover to prevent direct exposure.

Maintenance

⚠ Warning

1. Perform inspections on a regular basis as necessary, such as at the beginning of an operation, to make sure that the mechanical valve operates properly.

Failure to observe this precaution could lead to unsafe operation, such as unintended operation or malfunction.


How to Change the Buttons

⚠ Caution

Replace the button in the following manner to change color of the button.

1. Push button (Flush type)


- Installation Of the four colors, red, green, black, and yellow, select and align the protruding portion of the button with the recessed portion of the body and push in.
- Removal Remove the fastening ring and insert the tip of a small flat screwdriver into the groove of the button to pry it up.



2. Push button (Mushroom and extended types)

At the time of shipment, only 1 button of the color that you specified is attached to the body.

	Mushroom type	Extended type
Mounting	Align the protruding portion of the button with the recessed portion of the body and push in. (Use the mark on the button as a reference to align the protruding part.)	Align the protruding portion of the button with the recessed portion of the body and push in.
Removal	Placing your finger under the collar of the button on the side of the mark, tilt it upward.	Remove the fastening ring and insert the tip of a small flat screwdriver into the groove of the button to pry it up.






Series VM Specific Product Precautions 3

Be sure to read before handling.


Refer to front matter 53 for Safety Instructions and pages 3 to 8 for 3/4/5 Port Solenoid Valve Precautions.

How to remove a mushroom button

How to remove at panel mount



Removing the valve as a unit



Replacement parts

1. Use the part numbers listed below to order individual mushroom head or flat head buttons.

Color	Mushroom button	Extended button
Red	3402186R	3402187R
Black	3402186B	3402187B
Green	3402186G	3402187G
Yellow	3402186Y	3402187Y

Color	Push button (Flush)
Red	3402188R
Black	3402188B
Green	3402188G
Yellow	3402188Y


2. To order single fastening ring, use the part number below.
Fastening ring: 3402184

3. To order a single push button for series VM1000 and a single cover use the part number below.

Color	Push button	Cover for push button
Red	3410701-R	3410703 (White only)
Black	3410701-B	
Green	3410701-G	


Series VM-X219, VZM-X219, VFM-X219 How to Mount Panel

[Task 1] Removal of the push button and fastening ring
Remove them from the body turning them counterclockwise in the order of the pushbutton and fastening ring.



[Task 2] Mounting the valve to the panel

Insert the valve to the panel and fix it with a fastening ring. Remove three spacers attached to the valve depending on the panel thickness.



[Task 3] Mounting the push button

Tighten the push button clockwise by hand and further tighten it until load is applied.

Note) When the push button is not tightened enough, the valve may not output correctly after operating the push button. In other cases, the valve outputs temporarily, but when it is in the holding state, the valve may stop outputting. In this situation, please tighten the push button again.

