Clean Air Filter

Series SFD

RoHS

Hollow Fiber Element

Nominal filtration rating: 0 1 μm (filtration efficiency 99.99%)

■ Initial pressure drop: **0** ■ **03** MPa (at inlet pressure 0.7 MPa, maximum flow)

Maximum operating pressure: 1 0 MPa (at 20°C)



AT

IDF IDU

IDFA

IDFB

IDH

ID

IDG

IDK AMG

AFF

AM

AMD AMH


AME

AMF

ZFC SF

SFD

LLB AD



							1 6		Made to Order ges 303 and 304
Туре		Disposable ty	pe (non-replace	eable element)		Cartr	idge type (rep	laceable element)	
Flow rate L/m	nin (ANR) (at inlet pressure 0.7 MPa)	Up to 60	Up to 80	Up to 100	Up to 300	Up to 400	Up to 500	Up to	100
Dort size	One-touch fitting	ø4	ø6	ø8	ø8	ø10	ø12	_	
Port size	Female thread	-	_	Rc 1/4, G 1/4 NPT 1/4	_	_	Rc 1/4, G 1/4 NPT 1/4	Rc 1/4, G 1	/4, NPT 1/4
Case mat	erial		Resin		Resin			Aluminum	Stainless steel
Fluid		Air (Nitrogen)							
Nominal filtration rating		0.01 μm (filtration efficiency: 99.99%) Note)							
Initial pressure drop		0.03 MPa (at inlet pressure 0.7 MPa, maximum flow)							
Maximum operating pressure (at 20°C)		1.0 MPa (in case of nitrogen: 0.99 MPa)							
Operating temperature		5 to 45°C							
Mana The al	the clean air filter in decigned for the filtration of colid chicago. It is not cuitable for the congration of water and oil								

Note) The clean air filter is designed for the filtration of solid objects. It is not suitable for the separation of water and oil

Integrated production in a clean environment


Under a clean environment, all components have undergone ultrasonic cleaning.


Assembly, inspection and antistatic double packaging processes are conducted in an integrated production system.

Assembly environment

Clean room: Class M5.5 (ISO class 7)*
 Clean bench: Class M3.5 (ISO class 5)*


* Fed. Std. 209E (): based on ISO14644-1.





Hollow fiber membrane

The hollow fiber membrane has a porous construction with numerous fine holes on a straw type fiber membrane wall. The hollow fiber membrane filter traps and filtrates the impurities from the compressed air through the overlapping layered fine holes.



AT IDF

HAA

IDFA

IDFB

IDH

ID IDG

IDK AMG

AFF

AMD

AMH AME

AMF

ZFC SF

SFD LLB

AD 🗆


Series SFD Model Selection

Select the model by using the following procedures involving the inlet pressure and the maximum flow rate. [Example] Inlet pressure: 0.6 MPa

Maximum flow rate: 100 L/min (ANR)

- 1. Obtain the intersection A for the inlet pressure and the maximum flow rate by using the maximum flow rate chart.
- 2. If the obtained intersection A is above the maximum flow rate line, the SFD200-C12, -□02, -C10, or -C08 are selected.

Maximum Flow Rate



Clean Air Filter

Series SFD





SFD 100-C08

Clean air filter

		Size
	Symbol	Max. flow rate
	1	100 L/min (ANR)
	2	500 L/min (ANR)

Caco material

Symbol	Material	
0	Resin	
1	Aluminum	
2	Stainless steel	

Symbol 1 and 2 are made to order. For details, refer to page 303.

Option				
Symbol	Option			
Nil	None			
В	Bracket (SFD100 only)			


* The brackets are provided with the SFD200 series as a standard product. (Nil)

- POIL :			
Symbol		Connection size	Note
C04	ø4		050400
C06	ø6	Clean One-touch fittings (Series KP)	SFD100 only
C08	ø8		SFD100/200
C10	ø10	intango (concerta)	SFD200 only
C12	ø12		
02		Rc 1/4	Female thread
N02		NPT 1/4	SFD100/200
F02		G 1/4	GI D 100/200



Different diameters for IN and OUT ports are Made to Order. For details, refer to page 304.

Relationship between **Operating Temperature and** Max. Operating Pressure



Specifications

Model	SFD10□	SFD20□	
Port size	One-touch fittings ø4, ø6, ø8	One-touch fittings ø8, ø10, ø12	
Port size	Rc, NPT, G 1/4	Rc, NPT, G 1/4	
Fluid	Air (Nitrogen)	Air (Nitrogen)	
Air flow capacity	Up to 100 L/min (ANR)	Up to 500 L/min (ANR)	
Nominal filtration rating Note 1)	0.01 μm (99.99%)		
Operating pressure range Note 2)	– 100 kPa to 1.0 MPa (in case of nitrogen: 0.99 MPa)		
Operating temperature	5 to 45°C		
Initial pressure drop	0.03 MPa (at inlet pressure 0.7 MPa, maximum flow)		
Element proof differential pressure Note 3)	0.5 MPa		
Proof pressure	1.5 MPa		
Element service life	1 year, or when the pressure drop reaches 0.1 MPa.		

Note 1) Measured under SMC's specified conditions.

Note 2) The maximum operating pressure varies depending on temperature. Refer to the graph that shows the relationship between operating temperature and maximum operating pressure on the left.

Note 3) This means that the element does not break at 0.5 MPa. See "Specific Product Precautions".

Model	Port size	Rated flow (L/min (ANR)) Note 1)	Weight		
	ø4 (One-touch fittings)	60	35 g		
050400	ø6 (One-touch fittings)	80	35 g		
SFD100	ø8 (One-touch fittings)	100	35 g		
	Rc, NPT, G 1/4	100	35 g		
SFD101 Note 2)	Rc, NPT, G 1/4	100	60 g		
SFD102 Note 2)	Rc, NPT, G 1/4	100	150 g		
	ø8 (One-touch fittings)	300	190 g		
OFFICE	ø10 (One-touch fittings)	400	190 g		
SFD200	ø12 (One-touch fittings)	500	190 g		
	Rc, NPT, G 1/4	500	260 g		

Note 1) The maximum flow rate when the inlet pressure is 0.7 MPa. Note 2) SFD101 and SFD102 are produced upon receipt of order.



HAW

AT IDF

İĎŪ IDFA

IDFB

IDH ID

IDG

IDK

AMG

AFF AM

AMD

AMH AME

AMF

ZFC

SF


SFD LLB

 $\mathsf{AD}\square$


Series SFD

Flow Characteristics







SFD200-C08




SFD100-C06




SFD200-C10



SFD100-C08, -02, -N02, -F02




SFD200-C12, -02, -N02, -F02



Clean Air Filter Series SFD

Construction

SFD100-C□



Component Parts

No.	Description	Material	Note
1	Element	PC, Polyolefin, PU, PET, ABS	
2	Cover	PBT	
3	Bracket	PBT	
4	O-ring	H-NBR	
5	Cassette	PP, EPDM, Stainless steel	

Replacement Parts

No.	Description	Material	Note
1	Bracket set	SFD-BR100	With 2 countersunk head screws (M3)

No.	Description	Material	Note
1	Bracket set	SFD-BR100	With 2 countersunk head screws (M3)


Component Parts

No.	Description	Material	Note
1	Element	PC, Polyolefin, PU, PET, ABS	
2	Cover	PBT	
3	Bracket	PBT	
4	O-ring	H-NBR	


Replacement Parts

No.	Description	Material	Note
1	Bracket set	SFD-BR100	With 2 countersunk head screws (M3)

SFD100-□02



SFD200-C□




Component Parts			
No.	Description	Material	Note
1	Element	PC, Polyolefin, PU	
2	Cover	Aluminum alloy	
3	Fitting body	PBT	
4	Cassette	PP, EPDM, Stainless steel	
5	Bracket	Stainless steel alloy	
6	O-ring A	H-NBR	
7	O-ring B	H-NBR	
8	Rod cover	Stainless steel alloy	
9	Tie-rod	Stainless steel alloy	
10	Cap nut	Stainless steel alloy	
11	Plain washer	Stainless steel alloy	

Replacement Parts

No.	Description	Material	Note
1 Element set		SFD-EL200	With 3 O-rings

SFD200-□02



Component Parts			
No.	Description	Material	Note
1	Element	PC, Polyolefin, PU	
2	Cover	Aluminum alloy	
3	Fitting body	Stainless steel alloy	
4	Bracket	Stainless steel alloy	
5	O-ring A	H-NBR	
6	O-ring B	H-NBR	
7	Rod cover	Stainless steel alloy	
8	Tie-rod	Stainless steel alloy	
9	Cap nut	Stainless steel alloy	
10	Plain washer	Stainless steel alloy	

Replacement Parts

No.	Description	Material	Note
1	Element set	SFD-EL200	With 3 O-rings

HAA HAW AT IDF IDU

IDFA

IDFB IDH

ID IDG

IDK

AMG

AFF

AM

AMD

AMH AME

AMF

ZFC SF


SFD


LLB AD□

Series SFD

Dimensions

SFD100-C□







SFD100-C□ Dimensions

Model		Α	В
SFD100-	C04	4	81
	C06	6	81
	C08	8	82

Bracket mounting dimensions



SFD100-□02







Hole shape for bracket mounting



SFD200-C□







SFD200-C□ Dimensions


Model		Α	В
	C08	8	125
SFD200-	C10	10	126
	C12	12	126

SFD200-□02





Bracket mounting dimensions




Series SFD **Made to Order Specifications 1**

Contact us for detailed specifications, delivery and prices.



1 Metal Case



Case material

Symbol	Material
1	Aluminum
2	Stainless steel

with a clean One-touch fitting. * The bracket is provided as a standard product.

Metal case suitable for an atmosphere exposed to organic solvents and chemicals

Specifications


The specifications are the same as the standard product. Refer to "Specifications" on page 299.


Flow Characteristics

The flow characteristics are the same as the SFD100-02. Refer to "Flow Characteristics" on page 300.

Construction

SFD101-02






Component Parts

No.	Description	Material	Note
1	Case	Aluminum alloy	
2	Cover	Aluminum alloy	
3	Element	PC, Polyolefin, PU, PET, ABS	
4	O-ring	FKM	

Replacement Parts

No.	Description	Part no.	Note	
1	Element set	SFD-EL101	With O-ring	
2	Bracket	SFD-BR101	Material: Stainless steel 304	

SFD102-02



Component Parts


po		
Description	Material	Note
Case	Stainless steel alloy	
Cover	Stainless steel alloy	
Element	PC, Polyolefin, PU, PET, ABS	
Hex. socket head set screw	Stainless steel alloy	
O-ring	FKM	
	Case Cover Element Hex. socket head set screw	Description Material Case Stainless steel alloy Cover Stainless steel alloy Element PC, Polyolefin, PU, PET, ABS Hex. socket head set screw Stainless steel alloy

Replacement Parts


No.	Description	Part no.	Note	
1	Element set	SFD-EL101	With O-ring	
2	Bracket	SFD-BR101	Material: Stainless steel 304	

Dimensions

SFD101-02



SFD102-02



AT IDF

HAA HAW

İĎŪ

IDFA IDFB

IDH

ID

IDG

IDK

AMG

AFF

AM

AMD AMH

AME

AMF ZFC

SF

SFD LLB


 $\mathsf{AD}\square$

Series SFD **Made to Order Specifications 2**

Contact us for detailed specifications, delivery and prices.



2 Different Diameters for IN and OUT Ports



- in side confidention symbol		
IN side connection symbol	Connection size	
C04	ø4	
C06	ø6	Clean One-touch
C08	ø8	fittings (Series KP)
C10	ø10	intings (ochos rai)
C12	ø12	
02	Rc 1/4	
N02	NPT 1/4	
F02	G 1/4	
* IN/OLIT combina		* IN/OLIT combination

OUT side connection symbol	Connection size		
C04	ø4		
C06	ø6	Clean One-touch	
C08	ø8	fittings (Series KP)	
C10	ø10	Intings (oches rail)	
C12	ø12		
02	Rc 1/4		
N02	NPT 1/4		
F02	G 1/4		

^{*} IN/OUT combination is the below table

SFD100 Different Diameter Combinations

`	<u> </u>		OUT port size				
		C04	C06	C08	02	N02	F02
	C04		•	-	•	•	•
size	C06	•		•	•	•	•
t Si	C08	_	•		•	•	•
IN port	02	•	•	•		_	ı
Z	N02	•	•	•	_		_
	F02	•	•	•	_	_	/

^{*} The symbol "—" stands for unavailable combination. * The symbol "—" stands for unavailable combination.

SFD200 Different Diameter Combinations

	_	OUT port size					
		C08	C10	C12	02	N02	F02
	C08		•	_	•	•	•
size	C10	•		•	•	•	•
t Si	C12	_	•		•	•	•
IN port	02	•	•	•		_	_
Z	N02	•	•	•	_		_
	F02	•	•	•	_	_	

Specifications

The specifications are the same as the standard models.

Refer to "Specifications" on page 299.

Flow Characteristics

When the IN and OUT ports have different diameters, the flow characteristics will be those of the port with the smaller diameter.

Refer to "Flow Characteristics" for the smaller diameter from the chart of standard product on page 300.

Construction


The construction and materials are the same as the standard product.

Refer to "Construction" on page 301.


Dimensions

SFD100 different diameters

One-touch fitting dimensions(A, B) Port size ① Port size (2) α**4** Basic dimension 72 Fitting Fitting dimension A dimension B



SFD200 different diameters



Model	Port size ①	Port size ②	Total length
	C08 (C10)	C10 (C08)	125.5 (A + 114.5 + B)
	C08 (□02)	□02 (C08)	120 (114.5 + A)
SFD200-	C10 (C12)	C12 (C10)	125.5 (A + 114.5 + B)
	C10 (□02)	□02 (C10)	120 (114.5 + A)
	C12 (□02)	□02 (C12)	120 (114.5 + A)

Related Products <Pre><Pre-filters for Series SFD>

Mist Separator Series AM

Refer to pages 201 to 208 for details.



Series AM

Model	AM150C	AM250C
Rated flow (L/min (ANR))	300	750
Port size (Nominal size B)	1/8, 1/4	1/4, 3/8

Specifications	
Fluid	Compressed air
Max. operating pressure	1.0 MPa
Min. operating pressure Note)	0.05 MPa
Proof pressure	1.5 MPa
Ambient temperature	5 to 60°C
Nominal filtration rating	0.3 μm (Filtering efficiency 99.9%)

Note) With auto drain: 0.1 MPa (N.O. type), 0.15 MPa (N.C. type)

HAA HAW AT

IDF IDU IDFA

IDFB

IDH ID

IDG

IDK AMG AFF

Micro Mist Separator Series AMD

Refer to pages 209 to 217 for details.



Spring AMD

CONCO AND			
Model	AMD150C	AMD250C	
Rated flow (L/min (ANR))	200	500	
Port size (Nominal size B)	1/8, 1/4	1/4, 3/8	

Specifications	
Fluid	Compressed air
Max. operating pressure	1.0 MPa
Min. operating pressure Note)	0.05 MPa
Proof pressure	1.5 MPa
Ambient temperature	5 to 60°C
Nominal filtration rating	0.01 µm (Filtering efficiency 99.9%)

Note) With auto drain: 0.1 MPa (N.O. type), 0.15 MPa (N.C. type)

AM AMD

AMH AME

Super Mist Separator Series AME

Odor Removal Filter Series AMF

Refer to pages 227 to 234 for details.



Series AIVIE		
Model	AME150C	AME250C
Rated flow (L/min (ANR))	200	500
Port size (Nominal size B)	1/8, 1/4	1/4, 3/8

Specifications	
Fluid	Compressed air
Max. operating pressure	1.0 MPa
Min. operating pressure	0.05 MPa
Proof pressure	1.5 MPa
Ambient temperature	5 to 60°C
Nominal filtration rating	0.01 um (Filtering efficiency 99.9%

LLB

SFD

 $\mathsf{AD}\square$ GD

Refer to pages 235 to 243 for details.



Series AMF

Model	AMF150C	AMF250C
Rated flow (L/min (ANR))	200	500
Port size (Nominal size B)	1/8, 1/4	1/4, 3/8

Specifications

opeomioanome	
Fluid	Compressed air
Max. operating pressure	1.0 MPa
Min. operating pressure	0.05 MPa
Proof pressure	1.5 MPa
Ambient temperature	5 to 60°C
Nominal filtration rating	0.01 µm (Filtering efficiency 99.9%)

Series SFD Related Products

Ionizer/Bar type Series IZS40/41/42

Refer to Best Pneumatics No. 6 for details.



- Potential amplitude is reduced with Dual AC type.
 25 V or less (Installation height: 300 mm)
- Rapid elimination of static electricity by a feedback sensor
- Reduction of adjustment and maintenance labor by auto balance sensor
- Simple operation: Can be controlled by powering the ionizer ON. (Standard type)
- Setting ionizer with remote controller
- Transition wiring may be used.
- High speed static electricity elimination cartridges and energy saving static electricity elimination cartridges are available.

Series	Туре	Ion generation method	Ion balance	
IZS42	Dual AC type		±30V	
IZS41	Feedback sensor type	Corona discharge type		
IZS40	Standard type			

Clean Regulator Series SRH/SRP

Refer to pages 757 to 777 for details.

Stainless steel regulator controlled for contamination

Series SRH



Series SRP



Series SRH


Port size Rc							
1/8	1/4	3/8	1/2	9/16-18UNF	7/8-14UNF		
. T	T		1	T	1		
	$lue{}$	$lue{}$	-ullet		lacksquare		
	1/8	1/8 1/4					

Series SRP

Series	Port size Rc			
	M5	1/8		
SRP1000		<u> </u>		
C111 1000	∀	Ψ		

Clean Gas Filter Series SF

Refer to pages 273 to 294 for details.







Cartridge Type

Series	Time	Main material			Thread Port size		ort size
Series	Type	Element	Housing	Seal	type	M5	1/4
100 SFA 200 300	Disc	PTFE + Polyester	Stainless steel 316 (Electro- polishing)	Fluoro- rubber	Rc NPT TSJ UOJ		•
SFB100	Straight	PTFE + PFA		(FPM)		•	•

Disposable Type

Series	Type	Main material		Thread	Port size			
Series Type	Element	Housing	Seal	type	1/4	3/8		
SFB300	Straight	PTFE + PFA	Stainless steel 316 (Electro- polishing)	-	Rc TSJ URJ	•		
SFC100	Multiple disc	PTFE + PVDF		(Electro- O-ring LIDI		 	-	



Series SFD Specific Product Precautions 1

Be sure to read before handling. Refer to front matter 43 for Safety Instructions and pages 6 to 8 for Air Preparation Equipment Precautions.

Selection

⚠ Warning

- Thoroughly and carefully confirm the purpose of use, required specifications and operating conditions (fluid, pressure, flow rate, nominal filtration rating and environment) then select a model within the specifications.
- The product is not certified under the High Pressure Gas Safety law, so for nitrogen, its maximum operating pressure will be 0.99 MPa (gauge pressure).
- Contact us beforehand if the product will be used in an application such as a caisson shield, breathing, food and/or medical treatment that affects the human body directly or indirectly.
- If the compressed air includes ozone, do not use it since it may damage the product or cause malfunction. When it includes ozone, use a clean gas filter (SFA/B/C).

Mounting

⚠ Warning

1. Instruction manual

Mount the product after reading and understanding the instruction manual. Keep it in a location where it can easily be found.

2. Flushing

Flush the piping line when the filter is used for the first time or has been replaced. In the event of connecting such as piping, flush (air blow) when using this product for the first time or replacing its elements in order to reduce the affect of the dust generated from the connection, etc. Flushing the line is also required to eliminate contamination resulting from the piping line installation. Therefore, be sure to flush the line before actually running the system. Fix all mounting parts for use.

3. Use fittings with resin threads for the connection of fittings to the IN and OUT ports.

Using fittings with metal threads could damage the IN and $\ensuremath{\mathsf{OUT}}$ ports.

 Connect tubing to the IN and OUT One-touch fittings in accordance with the precautions for One-touch fittings.

⚠ Caution

1. Connect the piping in accordance with the flow direction marked on the case.

If connected in reverse, the element could break.

The mounting orientation does not affect the performance, but if excessive force is applied to the SFD100 series, the body may become disconnected from the bracket.

Therefore, take particular care about the mounting orientation.

Caution on Installation

⚠ Warning

1. The material of the element is polycarbonate.

The material is resistant to wiping with alcohol, but is not suitable for atmospheres or places with organic solvents, chemicals, cutting oils, synthetic oils, ester base compressor oils, alkalis or thread locking agents.

- If the pressure difference (pressure drop) between the inlet and the outlet exceeds 0.1 MPa, it can cause damage to the product.
- Do not install the product in a place where it can be affected by a pulsation (including surge pressure) of over 0.1 MPa.
- Use caution regarding the particles that may be emitted from the outlet side of a pneumatic equipment.

Installation of a pneumatic equipment on the outlet side can deteriorate the cleanliness because a particle will be generated from the equipment.

The mounting position of the pneumatic equipment needs to be considered.

- Set the air flow capacity with an initial pressure drop of 0.03 MPa or less. If the initial pressure drop is set to be high, its service life will be shorten due to clogging.
- 5. Determine the product by the maximum consumption flow rate.

When using compressed air for an air blow application, calculate the maximum volume of air that will be consumed before selecting the SFD series product size.

Generally, the following pollutant particles are contained in compressed air.

[Pollutant particle substances contained in the compressed air]

· Moisture (drainage)

Dusts and particles which are in the surrounding air

Deteriorated oil which is discharged from the compressor
 Solid foreign matter such as rust and/or oil in the piping

 The SFD series is not compatible with compressed air which contains fluids such as water and/or oil.

- Install a dryer (IDF, IDG, ID series), mist separator (AM series), micro mist separator (AMD series), super mist separator (AME series), or odor removal filter (AMF series),
- etc., for the source of the air for the SFD series.

 7. Using with a flow-rate much higher than its specification could lead to exceeding the differential pressure the product can resist.

Use the product within its specifications. Also, take care about the replacement period of the product, taking into consideration that the differential pressure of the filter will increase over time.

HAA HAW

AT

IDFA

IDH ID

IDG

AMG

AFF AM

AMD

AMH

AMF ZFC

SF SFD

LLB

AD□ GD



Series SFD Specific Product Precautions 2

Be sure to read before handling. Refer to front matter 43 for Safety Instructions and pages 6 to 8 for Air Preparation Equipment Precautions.

Piping

1. Unpacking the sealed package

Since the filter is sealed in an antistatic double bag, the inner package should be unpacked in a clean atmosphere (such as a clean room).

- 2. Apply a wrench to 2 chamfered flats or hexagon portion on the IN side or the OUT side to prevent the housing from rotating.
- Always tighten threads with the proper tightening torque.

When attaching fittings to the product, tighten with the proper tightening torque shown below.

Material	Tightening torque (N⋅m)
Resin	2 to 3
Metal	12 to 14

Check the arrow mark on the case which shows the flow direction to connect the IN and OUT ports correctly.

If connected in reverse, the element could break.

Maintenance

- Follow the maintenance procedures in the instruction manual. If handled incorrectly equipment or device can be damaged or cause a malfunction.
- When removing the product, exhaust the air and ensure the air is released to atmosphere before removing it.
- 3. When the element comes to the end of its life, immediately replace it with a new filter or replacement element (cartridge type).

Service life of element

The service life of the element ends when either of the following two conditions occurs.

- 1) After 1 year of usage has elapsed.
- 2) When the pressure drop reaches 0.1 MPa even though the operating period has been less than 1 year.

Operating Environment

⚠ Warning

1. Do not operate under the conditions listed below due to a risk of malfunction.

In locations having corrosive gases, organic solvents, and chemical solutions, or in locations in which these elements are likely to adhere to the equipment.

In locations in which salt water, water, or water vapor could come in contact with the equipment.

In locations that are exposed to direct sunlight. (Shield the equipment from sunlight to prevent its resin material from ultraviolet ray degradation or overheating.)

In locations that have a heat source and poor ventilation. (Shield the equipment from heat sources to protect it from soft-ening degradation due to radiated heat.)

In locations that are exposed to shocks and vibrations.

In locations with high humidity or a large amounts of dust.

When the product is used for blowing, use caution to prevent the work from being damaged by entrained air from the surrounding area.

When the compressed air is used for air blow, the exhausted air from the blow nozzle may have taken in airborne foreign matter (such as solid particle, fluid particle) from the surround air. The foreign matter will be sprayed on the work, and the airborne foreign matter may adhere to it. Therefore, use caution for the surrounding environment.

Other Tube Brands

- When tubing of brands other than SMC's are used, verify that the tubing O.D. satisfies the following accuracy;
 - 1) Polyolefin tube: Within ±0.1 mm
 - 2) Polyurethane tubing: Within +0.15 mm, within -0.2 mm
 - 3) Nylon tubing: Within ±0.1 mm
 - 4) Soft nylon tubing: Within ±0.1 mm

Do not use tubing which does not meet these outside diameter tolerances. It may not be possible to connect them, or they may cause other trouble, such as air leakage or the tube pulling out after connection.

The recommended tube for the clean fitting is polyolefin tube. Other tubes can satisfy the performance in terms of leakage, tensile strength, etc., but impair the cleanliness. Note this point for use

