


Air Preparation Equipment Page 97



Compressor

Air Dryers



- Flow capacity: 65000 L/min (ANR)
- Outlet air pressure dew point: 10°C



- Flow capacity: 780 L/min (ANR)
- Outlet air atmospheric pressure dew point: -30°C

Air Preparation Filters



Micro Mist Separator with Prefilter

- Nominal filtration rating: 0.01 µm
- Odor Removal Filter
- Outlet oil mist concentration: Max. 0.0032 ppm

Detection Conversion Unit Page 74

Pressure Sensors



- Air: -0.1 to 1 MPa
- General fluids: -0.1 to 15 MPa

Flow Sensors



- Air: 0.2 to 12000 L/min (ANR)
- General fluids: 0.5 to 250 L/min (ANR)

Industrial Filters Page 101



- Flow capacity: Max. 3800 L/min (ANR)
- Nominal filtration rating: 0.5 to 120 µm


Pressure Control Equipment Page 37



- Set pressure range: 0.02 to 0.5 MPa
- Set pressure range: 0.005 to 0.8 MPa


Piping Material Page 104

Fittings/S Couplers



- Stainless steel series

Tubing



- Coil tube
- Double-layered tube
- Longer length tube


Operation Unit

Solenoid Valves Page 79

Explosion-proof Specifications



Intrinsically safe explosion proof



Explosion proof (Flameproof)

NAMUR Standards IP67



Accessories Page 52

Relay



Booster relay

Valves



Lock-up valve

Electro-Pneumatic Transducer



Electro-pneumatic transducer

Positioners Page 6



Smart positioner





Electro-pneumatic positioner

Actuators Page 62



- Applicable cylinder size: ø50 to ø300

Industrial process valve Actuator



In principle, SMC products cannot be used outdoors.