Micro Clamp Cylinder

Compact Lightweight High Clamping Force High Holding Force

Compact Width 20 mm

(Base type, Tandem type)

Lightweight 250 g


(Base type)

Maximum clamping force 200 N

(Tandem type) * Operating pressure: 0.6 MPa

Maximum holding force 300 N*Figure

(Base type, Tandem type) * When operating pressure of 0.2 to 0.6 MPa is applied.





Flat clamping characteristics

Outputs constant clamping force for workpiece thickness up to 3.5 mm. * Figure 1

- \cdot Easy adjustment of clamping position during assembly
- · When thickness of workpiece differs, adjustment is not required if within range.

Relationship between reference plane distance and clamping force






External force in unclamping direction

(Welding reaction force, inertial force during transfer, etc.)

External force in und

Reduction of assembly labor by unitization

Arm assembly Mounting assembly added to clamp cylinder.




CKZM16 -X2800 (Base type) -X2900 (Tandem type)

Easy mounting 2 types of mounting possible


Basic mounting

Press the mounting bracket against surface A, and fix it with the work clamping base. Using a bolt to support the mounting bracket is recommended.



Non-rotating mounting

The work clamping base can be used as a parallel key to prevent rotation. Using a bolt to support the mounting bracket is recommended.



Dust resistant construction


Fully closed structure prevents dust from entering easily.


Auto switch mountable



Short pitch (21 mm) mounting is possible.

(D-A9□)





Micro Clamp Cylinder CKZM16-X2800

How to Order



Arm opening angle

X2800 Base type X2900 Tandem type

Auto switch type

Nil Without auto switch For applicable auto switch models, refer to the below table.

Number of auto switches

Nil	2 pcs.				
S	1 pc.				
n	"n" pcs.				

Auto Switch Model/Refer to the WEB catalog or Best Pneumatics No. 3 for further information on auto switches.

Compact auto switch (-X2800 and -X2900 types only)

	e Special function Electrical entry	Flootwicel	Clastrias	ig	\\	L	oad volt	age	Auto swite	ch model	Lead	wir	e ler	igth	[m]	Due sedend	A I:	
Туре		<u>5</u> V	Wiring (Output)		C	AC	Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)		None (N)	Pre-wired connector	Applie loa			
£				3-wire (NPN)		5 V,		M9NV	M9N				0	_	0	IC circuit		
switch				3-wire (PNP)		12 V		M9PV	M9P				0	_	0	IC CIICUII	C Circuit	
				2-wire		12 V		M9BV	M9B				0	_	0			
anto	Diagnostic indication (2-color indication) Grommet		3-wire	3-wire (NPN)		5 V,		M9NWV	M9NW				0	_	0	IC circuit	Dalass	
		ommet Yes	3-wire (PNP)	wire (PNP) 24 V	12 V		M9PWV	M9PW				0	_	0	IC Circuit	Relay, PLC		
state			2-wire		12 V			M9BWV	M9BW				0	_	0	_	1 LC	
	Motor registent	Vater resistant		3-wire (NPN)	5 V,	5 V,			M9NAV	M9NA	0	0		0	_	0	IC circuit	
Solid	(2-color indication)		3-wire (PNP)		12 V		M9PAV	M9PA	0	0		0	_	0	IC Circuit			
	(2-color indication)	(2-color indication)	cation)		2-wire		12 V		M9BAV	M9BA	0	0		0	_	0	_	
witch	Grommet	Yes	3-wire (NPN equivalent)	_	5 V		A96V	A96				_	_	_	IC circuit	_		
o ∞		162	2-wire	24 V	12 V	100 V	A93V*2	A93					_	_	_	Relay,		
윤		N	No	Z-WITE	24 V	5 V,12 V	100 V or less	A90V	A90		_		_	_	_	IC circuit	PLC	

^{*1} Water resistant type auto switches can be mounted on the above models, but in such a case SMC cannot guarantee water resistance.

* Lead wire length symbols: 0.5 m Nil (Example) M9NWV (Example) M9NWVM 3 m L (Example) M9NWVL 5 m Z

* Solid state auto switches marked with "O" are produced upon receipt of order.

(Example) M9NWVZ

Magnetic field resistant auto switch (-X2900 type only)

Type	Auto switch model	Applicable magnetic field	Electrical entry	Indicator light	Wiring (Pin no. in use)	Load voltage	Lead wire length	Applicable load
	D-P3DWASC		Pre-wired connector		2-wire (3 – 4)		0.3 m	
0-11-1-4-4-	D-P3DWASE	AC magnetic field	Fie-wired connector		2-wire (1 - 4)		0.3 111	D-1
Solid state auto switch	D-P3DWA	(Single-phase AC		2-color indication		24 VDC	0.5 m	Relay, PLC
auto Switch	D-P3DWAL	welding magnetic field)	Grommet	indication	2-wire		3 m	
	D-P3DWAZ						5 m	

Specifications

Туре	Base type (-X2800)	Tandem type (-X2900)			
Operating pressure	0.2 to 0.6 MPa				
Appropriate workpiece thickness range	e 3.5 mm or less				
Maximum holding force Note)	300) N			
Cylinder bore size	16 :	mm			
Cylinder stroke	27 mm	25 mm x 2			
Arm length	25 mm				
Arm opening angle	68 de	grees			
Clamping force	Refer to page 3				
Appropriate workpiece insert length	kpiece insert length 8 mm (Refer to page 4) 8 mm (R				
Weight	250 g	330 g			

Note) The maximum holding force is 300 N when a pressure of 0.2 to 0.6 MPa is supplied.

The clamping state is not maintained while operating air is exhausted.




^{*2 1} m type lead wire is only applicable to D-A93.

^{*} For details about auto switches with pre-wired connector, refer to the WEB catalog or Best Pneumatics No. 2.


Clamping Force Characteristics (Reference Plane Distance and Clamping Force)


Arm length: 25 mm

Base type (-X2800)



Tandem type (-X2900)








Note 1) The clamping operating range is 3.5 mm upward from the reference plane, and 0.5 mm downward from the reference plane when the work clamping base is removed.


Note 2) When the height is changed by inserting a shim between the work clamping base and the mounting bracket, the "clamping force characteristics/reference plane distance" becomes narrower only for the height changed.

Dimensions/Base Type (-X2800)










Auto switch groove

Auto switch groove

Work clamping base (Note 3)




Note 1) The hexagon nut is installed to prevent detachment of the work clamping base before the shipment.

Note 3) If the clamping base is used to clamp the workpiece, the torque range is 5.2 to 6.7 [N·m].





Remove the hexagon nut when the product is installed to the equipment.


Dimensions/Tandem Type (-X2900)















Work clamping base (Note 3)



Note 1) The hexagon nut is installed to prevent detachment of the work clamping base before the shipment.

Remove the hexagon nut when the product is installed to the equipment. Note 3) If the clamping base is used to clamp the workpiece, the torque range is 5.2 to 6.7 [N·m].

CKZM16-X2900 Auto Switch Mounting


Auto Switch Proper Mounting Position (Detection at Stroke End) and its Mounting Height


Auto switch mounting position is the most sensitive position for when the arm positions are clamping and unclamping.


The clamp side switch position is when the workpiece thickness 0 mm.

Base type (-X2800)

D-M9□ D-A9□








⚠ Caution

- The auto switch mounting position on the clamp side changes with the workpiece thickness. It cannot be mounted in a position which detects the overall workpiece thickness of 0 to 3.5 mm.
- · 2 switches can not be installed in one switch groove.

| [mm] | Auto switch model | A | B | | D-M9□ | 45 | 18.8 | | D-A9□ | 49 | 22.8 |

Tandem type (-X2900)

D-P3DWA□ **D-M9**□ **D-A9**□



			[mm]
Auto switch model	Α	В	С
D-P3DWA□	98	23.3	8.7
D-M9□	94	18.8	_
D-A9□	98	22.8	_

∧ Caution

 The auto switch mounting position on the clamp side changes with the workpiece thickness. It cannot be mounted in a position which detects the overall workpiece thickness of 0 to 3.5 mm.





Series CKZM **Specific Product Precautions**


Be sure to read this before handling. For Safety Instructions, Actuator and Auto Switch Precautions, refer to "Handling Precautions for SMC Products" and the Operation Manual on SMC website, http://www.smcworld.com

Caution on Handling Auto Switch

⚠ Warning

1. If multiple cylinders are operated adjacent to each other, the magnets that are enclosed in the adjacent cylinders could affect the operation of the auto switches, causing the switches to malfunction. Therefore, make sure that the mounting pitch of the cylinders is at least that indicated in the table below.


Base type (-X2800)



Cylinder minimum mounting pitch

(Cylinder minimum mounting pitch [mm]									
Ī	A. da a. dala	I	_	(d)						
	Auto switch model	With	Without	With	Without					
l		shielding plate	shielding plate	shielding plate	shielding plate					
Ī	D-M9□	25	35	5	15					
	D-A9□	21	21	1	1					

Tandem type (-X2900)



Cylinder minimum mounting pitch

cymiae: minimum meaning piter.									
Auto switch model	l	_	(d)						
	With	Without	With	Without					
model	shielding plate	shielding plate	shielding plate	shielding plate					
D-M9□	25	30	5	10					
D-A9□	21	28	1	8					
D-P3DWA□	21	35	1	15					

Caution on Handling Auto Switch

⚠ Warning

If cylinders are used with a mounting pitch less than that shown on the left, they must be shielded with iron plates or the separately sold magnetic shielding plate (part no.: MU-S025). Please contact SMC for further information.



Material: Ferrite stainless steel Thickness: 0.3 mm Since the back side is treated with adhesive, it is possible to attach to the cylinder.

How to use

In order to not influence the auto switch mounted on cylinder B adjacent to the magnetic force of cylinder A, use a shielding plate to block the magnetic force.


2. The magnetic field resistant auto switch (D-P3DWA) cannot be used in environments with DC magnetic fields.

Even under AC magnetic fields, if a magnetic body structure is placed very close to the cylinder, it will be affected by magnetization. Use the auto switch at a sufficient distance.

How to manually unclamp while the operating air is exhausted.

⚠ Caution

- 1. Absolutely do not release the lock until the safety is ensured.
- 2. Loosen the hexagon socket head cap screw for "manual window cover". And rotate the window.
- 3. Insert a long stick-like object into the "manual window" and push the joint inside down.
- 4. Confirm "manual window" is completely covered with the "manual window cover". Then tighten the hexagon socket head cap screw.
 - * Tightening torque: 0.36 to 0.45 N·m



Note for Loads on End of Arm Assembly (Moving Part)

⚠ Warning

1. Do not attach any load, including a jig, onto the end of the arm assembly (moving part).

A Safety Instructions Be sure to read "Handling Precautions for SMC Products" (M-E03-3) before using.