
Vacuum / Release Unit

VQD1000-V Series

Rubber Seal


- O Response speed Adaptable to 0608 chip (EUK CAR 13 msec (at 500 mm*) / 18.5 msec (at 1000 mm*)
- Smooth detachment of a work piece without over-blow
- No need to adjust the timing when switching between vacuum and positive pressure. (single signal control)
- No need to design a restrictor circuit for release air.
- N.O. (Vacuum absorption type when de-energized) and N.C. (Vacuum shutoff type when de-energized) specifications are available.




SMC

Vacuum / Release Unit

VQD1000-V Series



<N.O. specifications>



Suction filter can be cleaned.

If you energize the VQD1151W, you can clean the suction filter using positive-pressure air blowing.

Suction filter

Recommended: ZFC050-M5X50 (Filtration rating 20 μm)

Details ▶ P.1408



When the distance between work pieces is fluctuated.

Compatible with an atmospheric release pressure circuit

Possible to make it an atmospheric release type by installing a check valve on the connecting port and by setting the release air pressure (P) lower.

(When the release air is running low, the pressure inside the tank changes to vacuum from the positive pressure. In this case, the pressure is rapidly released to the atmosphere due to the check valve.)

Atmospheric pressure

Atmospheric pressure suction port

Recommended check valve AKH04B-M5

When the release pressure is running low.

Additionally a tank can be installed.

Possible to add a tank for charging release air in accordance with the distance (volume) between the unit from the work piece.

Added tank
(using piping materials)

[Example of tank addition]

Tube

Tube cap


KO2C series

KO2H series



<N.O. specifications>

When de-energized Vacuum absorption De-energizing 2 solenoid valves simultaneously Charging release air during absorption of a work piece P2: Release air P1: Suction air V2: Charging release air V2: Charging release air Connection port



<Relationship between pressure and a release air tank>

$$P2 = \frac{(P + 0.1) \times (V1 + V2) - (P1 + 0.1) \times V1}{V2} - 0.1$$

P1: Suction vacuum pressure / Negative pressure (MPa)

P2: Release pressure / Positive pressure (MPa)

P: Detaching (Release) pressure (MPa)

* 0 MPa (atmospheric pressure) is normal.

V1: Total volume from a unit to a work piece (cm³)

V2: Volume of a release air tank (cm3)

 $\left(\begin{matrix} VQD1000\text{-V type: } 0.8 \text{ cm}^3 \\ VQD1000\text{-VL type: } 3.2 \text{ cm}^3 \end{matrix} \right)$

P2: Release Air Guideline

	Distance between the unit and	d the work area (mm)	300	500	1000	2000					
	V1: Total volume from the uni	t to the work area (cm3)	1.67	2.65	5.10	10.01					
	P2: Release pressure (MPa)	VQD1000-V	0.19	0.30	0.58	_					
		VQD1000-VL	_	0.08	0.14	0.28					

(Plug)

<Conditions> • Suction vacuum pressure (P1): –90 kPa (–0.090 MPa)

Piping tube size: ø4 (I.D. ø2.5)

Suction filter: When mounting ZFC050-M5X50 (internal volume: 0.2 cm³)

[How to Adjust]

- 1. Adjust P2 release pressure, using a regulator, in accordance with V1 volume. We recommend that you use our precision type, IR series.
- When V1 volume differs in the same manifold, equalize it by adjusting the length or internal diameter of the piping.Even when the piping length is extended a good response is ensured.
- It is recommended for the electrical control of the valve that the release and switching valves are turned ON or OFF at the same time (single signal control). An overshoot of the release air pressure can also be generated by changing the electrical control.



VV100

VV061

V100


SO70

VOD-V

VK VT

Vacuum / Release Unit VQD1000-V Series






Vacuum / Release Unit VQD1000-V Series

Specifications

	Valve construction			Direct operated poppet valve				
li	Fluid			Air				
, i	Operating Suction (nec		ative pressure)	0 to −100 kPa				
Ë	pressure rang	e Release (pos	itive pressure)	0 to 0.7 MPa				
specifications		N.O.	Suction (OFF)	2 ± 1 msec				
읉	Response	specifications	Release (ON)	4 ± 1 msec				
8	time	N.C.	Suction (ON)	4 ± 1 msec				
ဗ္ဗ	8	specifications	Release (OFF)	2 ± 1 msec				
				16 L/min/0.27 dm ³ /(s·bar)				
Valve	Manual overri	de		Non-locking push type				
-	Impact/Vibration resistance			150/30 m/s ²				
	Mounting position			Unrestricted				
	Enclosure			Dusttight				
တ္က	Coil rated voltage			24 VDC, 12 VDC				
اق ن	Allowable rate	d voltage		±10% of rated voltage				
菠菔	Coil insulation	ı type		Class B or equivalent				
Electric specifications	Power	VQD1151W (fo	r switching)	3.2 W energy saving type (Inrush: 3.2 W, Holding: 2.4 W)				
ш 8	consumption	10-VQ110 (for	release supply)	1 W				
S	Electrical entry			L/M plug connector (with light/surge voltage suppressor)				

Replacement Parts




Product Weight (Formula)


VQD1000-V(C)	W = 80n + 31			
VQD1000-V(C)L	W = 84n + 49			


W: Weight (g)

N: No. of unit (Stations)




For the product with the lead wire, the lead wire length is 300 mm. To extend the lead wire length to 600 mm or more, select the valve without connector and order the connector assembly separately.






Note) Product with specification on pressure charging A port.

If a standard product is used, external leakage may occur.





3.2 cm³ Guideline: 1 m or longer distanced from a work piece

4 Blanking plate assembly

VVQD1000-10A-V

Note) One set includes a blanking plate assembly for the solenoid valve for switching and one for the solenoid valve for charging release air.



VV061

VV100

S070

VQD VOD-V


VK

VT

1405 @

VQD1000-V Series

Dimensions



L: Dimensions (VQD1000-V(C)-□□ / Standard type: Tank volume 0.8 cm³)

11.5 (13.5)

14.5 (16.5)

Ln	1	2	3	4	5	6	7	8	9	10
L1	23	34	45	56	67	78	89	100	111	122
L2	17	28	39	50	61	72	83	94	105	116

Formula: L1 = 11n + 12, L2 = 11n + 6 (Max. 10 stations)

L: Dimen									
n	 2	2	1	-	6	7	Q	٩	10

L	1	2	3	4	5	6	7	8	9	10
L1	25	36	47	58	69	80	91	102	113	124
L2	19	30	41	52	63	74	85	96	107	118

Formula: L1 = 11n + 14, L2 = 11n + 8 (Max. 10 stations)

The dimensions shown in brackets indicate the VQD1000-V(C)L-□□ / tank volume 3.2 cm³.

n x M5

(Output port)



VQD1000-V Series **Specific Product Precautions**


Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions and pages 3 to 9 for 3/4/5 Port Solenoid Valve Precautions.

Manual Override Operation

∕ Warning

Connected actuator is started by manual operation. Use the manual override after confirming that there is no danger.

■ Non-locking push type (Tool required)




override button in the direction the arrow (->) indicates until it stops (approx. 0.5 mm), and release it to turn it OFF

Wiring Specifications


∕ Caution

VQD1151W-□ (For switching)




For the VQD1151W specifications (energy saving type), power consumption at holding is reduced with the above circuit. Refer to electrical power waveform as shown below.

<Energy saving type's electrical power waveform> (Rated voltage: at 24 VDC)



10-VQ110-□-X46 (For charging release air)



Continuous Energization

∕ Warning

Coil temperature may get high due to ambient temperature or energizing duration. Do not touch the valve by hand directly. When there is such a dangerous case to be touched by hand directly, install a protective cover.

∕∖\ Caution

When simultaneously energizing 3 stations or more, make sure to place an energized and non-energized valve alternatively.

However, if 3 stations or more need to be energized simultaneously at the time of installing or adjusting, the energizing time should be less than 30 minutes to achieve an energized status not exceeding 50%.

Valve Mounting

∕ Caution

After confirming the gasket is correctly placed under the valve, securely tighten the bolts with the proper torque shown in the table below.

Proper tightening torque (N·m) 0.18 to 0.25


How to Use Plug Connector

∧ Caution

Attaching and detaching connectors

- To attach a connector, hold the lever and connector unit between your fingers and insert straight onto the pins of the solenoid valve so that the lever's pawl is pushed into the groove and locks.
- To detach a connector, remove the pawl from the groove by pushing the lever downward with your thumb, and pull the connector straight out.

Note) Gently pull the lead wire, otherwise it may cause contact failure or disconnection.



When Piping to a Product

∕**.**∖ Caution

When piping to a product, check the supply port, etc.

connecting pin may be deformed, resulting in malfunction.

Also, when tightening the piping tube, clamp the base unit to avoid any undue force from being applied to the valve. If a force of 120 N or more is applied to the coil especially, the

1407

VV061

VV100

V100

S070

VOD

VOD-V


VK

VT


Related Products

Suction Filter

ZFC050-M5X50



Example of mounting to the manifold base (A port) of the vacuum/release unit VQD1000-V series



Specifications

Filtration degree	20 Mm (Nominal)				
Fluid	Air				
Operating pressure range	-100 to 700 kPa				
Ambient temperature	0 to 60°C (No freezing)				

Replacement element part no. ··· ZFC-EL050-X50

⚠ Caution

- To screw in OUT side port (M5 male thread), tighten by hand before giving it an additional 1/4 turn with a tightening tool.
- 2. When replacing the element, remove the IN side body using the hexagon surface on the IN side, then replace the element. After replacing the element, tighten the IN side body with the tightening torque 0.5 to 0.7 N·m.
- 3. As a rule, replace the element when the pressure drops by 20 kPa.

