Plug-in Top Ported


Compact 5-Port Solenoid Valve

A top-ported type has been added to the JSY3000 series.





Installed image 4(A) and 2(B) port output pressure detection is possible.



JSY3000 Series




Plug-in Top Ported

JSY3000 Series

(E UK ROHS



How to Order Valves





Series

JSY3000

a	Type	οf	acti	ation
	IVDE	UI.	aul	ıauvıı

1	2-position single	
2	2-position double	
3	3-position closed center	
4	3-position exhaust center	
5	3-position pressure center	
Α	Dual 3-port (N.C./N.C.)	
В	B Dual 3-port (N.O./N.O.)	
С	Dual 3-port (N.C./N.O.)	

3 Body option

	Pilot valve
U	exhaust method

4 Coil type

Nil	None	
Т	With power-saving circuit	

5 Rated voltage

24 VDC

6 Light/surge voltage suppressor and common specification

	Symbol	Specifications		
	U	With light /surge voltage suppressor (Non-polar)		
Z With light /surge voltage suppress		With light /surge voltage suppressor (Positive common)		
	NZ	With light /surge voltage suppressor (Negative common)		

Manual override

Nil	Non-locking push type
D	Push-turn locking slotted type
E	Push-turn locking lever type

8 4(A)/2(B) port size Thread piping

R1	D-1/10
RI	Rc1/16

^{*} When ordering a valve individually, the base gasket is not included. The base gaskets are attached to the manifold.


Valve Specifications


Valve type			Rubber seal	
Fluid			Air	
	2-position single		0.15 to 0.7	
Internal pilot operating	2-position double		0.1 to 0.7	
pressure range [MPa]	3-position		0.2 to 0.7	
[w]	4-position dual 3-port valve		0.15 to 0.7	
External pilot	Operating pressure range		-100 kPa to 0.7	
(Made to Order)	Pilot	2-position single		
operating pressure range	pressure	2-position double	0.25 to 0.7	
[MPa]	range	3-position		
Ambient and fluid temperatures [°C]			-10 to 50 (No freezing)	
Max. operating frequency [Hz] 2-position single/double 4-position dual 3-port valve 3-position		2-position single/double	5	
		4-position dual 3-port valve	3	
		3-position	3	
·			Non-locking push type	
Manual override	Manual override		Push-turn locking slotted type	
			Push-turn locking lever type	
Pilot exhaust type	Internal pilot External pilot (Made to Order)		Individual exhaust	
Filot extiaust type			ilidividual extlaust	
Lubrication			Not required	
Mounting orientation*1			Unrestricted	
Impact/Vibration resistance*1 m/s²			150/30	
Coil rated voltage [DC]			24 V	
Allowable voltage fluctuation [V]			±10% of the rated voltage	
Power consumption [W]	Standard		0.4	
Fower consumption [W]	With power-saving circuit (Made to Order)		0.1 [Inrush 0.4, Holding 0.1]	
Surge voltage suppressor			Diode (Varistor for non-polar type)	
Indicator light			LED	

^{*1} Impact resistance: No malfunction occurred when tested in the axial direction and at a right angle to the main valve and armature in both an energized and a de-energized state, once in each condition. (Value in the initial state)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz in the axial direction and at a right angle to the main valve and armature in both an energized and a de-energized state, once in each condition. (Value in the initial state)

Dimensions







↑ Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use. SMC Corporation https://www.smcworld.com