Circulating Fluid Temperature Controller



Air-cooled refrigeration





Thermo-chiller Low-temperature Type

Supports low temperatures of as low as -10°C

Compact:

Equivalent in size to the HRS040

■ Cooling capacity: 1 kW*¹

■ Temperature stability: ±0.1°C


Set temperature range:

-10°C to 40°C



377 mm

How to Order



592 mm


HRS040-A-20-T1-X158/X164


Specifications

	Model		X158	X164		
Cooling method			Air-cooled r	Air-cooled refrigeration		
Temperature control method			PID c	PID control		
Set temperature range/Temperature stability °C			-10 to 40/	-10 to 40/±0.1*1, *4		
Cooling capacity (50/60 Hz) W			1000/1	1000/1000*3		
゠゠	Ambient temperature	°C	5 to 4	5 to 40*1		
불	Ambient humidity	%RH	30 to 70 (No co	30 to 70 (No condensation)*1		
들등	Altitude	m	1000 c	1000 or less		
Installation environment	Atmosphere		No corrosive or flammable gases			
	Autiosphere		For other precautions, refer to the	e catalog and operation manual.		
Refrigerant			R410A (HFC), 0.53 kg			
Circulating	Fluid type			50% ethylene glycol aqueous solution*2		
를	Pump capacity (50/60 Hz)	MPa		0.11 (15 L/min)/0.36 (15 L/min)* ⁵		
ວັ	Rated flow (50/60 Hz)	L/min	15/15	15/15* ⁵ , * ⁶		
Tank capacity L			Approx. 5			
Operation display panel				7-segment digital display		
Communication functions				Contact input/output, Serial RS-485/RS-232C (D-sub9 female)		
supply	Voltage	V		Single-phase 200 to 230 VAC (50/60 Hz)		
			Allowable voltag	0		
าร	Breaker	Α		20		
Power	Rated operating current	Α	2.0.	8.8/11.2*3		
ŏ	Applicable earth leakage breaker capacity	Α		20*7		
4	Rated power consumption	kVA		1.7/2.2*3		
Circ	Circulating fluid contact material		Stainless steel, Copper brazing (Heat exchanger), Brass, Carbon, SiC PP, PE, POM, FKM, EPDM, PVC, NBR			
			, EPDM, PVC, NBR			
Weight (dry state) kg		64				
Coating color			White Net compliant			
UL standard		Compliant	Not compliant			

- *1 No condensation should be present.
- *2 Dilute pure ethylene glycol with tap water to create the solution. Additives such as preservatives cannot be used.
- *3 ① Ambient temperature: 32°C, ② Circulating fluid temperature: -10°C, ③ Circulating fluid at the rated flow, ④ Circulating fluid: 50% ethylene glycol aqueous solution
- *4 The temperature at the thermo-chiller outlet when the circulating fluid flow is at the rated flow and the circulating fluid outlet and return port are directly connected When the installation environment and power supply are within the specification range and stable
- *5 The capacity at the circulating fluid outlet when the circulating fluid temperature is -10°C
- *6 The required flow rate for maintaining the cooling capacity or temperature stability.
- The cooling capacity and the temperature stability specifications may not be satisfied if the flow rate is lower than the rated flow.
- *7 Use an earth leakage breaker with a sensitivity of 30 mA and a 200 V power supply (to be prepared by the customer).

Cooling Capacity






Pump Capacity

1

HRS040-A-20-T1-X158/X164 (Single-phase 200 to 230 VAC)


Circulating fluid temperature [°C]



SMC

Dimensions

HRS040-A-20-T1-X158/X164



Power Cable Specifications

	Rated value for thermo-chiller			Power cable examples		
Applicable model	Power supply	Applicable breaker rated current	Terminal block screw diameter	Cable size	Recommended crimped terminal	Optional accessories
HRS040-A-20-T1-X158/164	Single-phase 200 to 230 VAC (50/60 Hz)	20 A	M4	3 cores x 3.5 mm² (3 cores x AWG12) * Including grounding cable	R5.5.4	HRS-CA004



Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.

SMC Corporation

Akihabara UDX 15F,
4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN
Phone: 03-5207-8249 Fax: 03-5298-5362
https://www.smcworld.com

© 2023 SMC Corporation All Rights Reserved