Pilot Operated 2-Port Solenoid Valve



Max. operating pressure differential

4.0 MPa

Fluid Compressed air, Nitrogen, Argon, Oxygen*1




Low particle generation

Oil-free

IP67*2

*2 The DIN terminal is IP65.


Application Examples




Nitrogen filling unit

JSXH-X1





Easy maintenance



Improved environmental resistance

- · Dustproof/waterproof IP67 structure
- · With a stainless steel coil cover

Passed 1000 hours Accelerated weathering test ISO 4892-3 (JIS K 7350-3) compliant

Passed 1000 hours Ozone-proof exposure test ISO 1431 (JIS K 6259) compliant

Passed 960 hours

Combined cycle test ISO 14993 (JIS H 8502: 1999) compliant



* Please contact your local sales representative for more details.

Electrical Entry Variations

Grommet



Grommet with PCB



Conduit



DIN terminal



M12 connector



Specifications

Model	Port size	C [dm³/(s · bar)]	Orifice diameter [mmø]	Fluid	Body material	Valve type	Seal material	Electrical entry	Standards
JSXH20 Series	3/8	15	16	Compressed air Nitrogen	Brass	N.C.	PUR (Main valve)	Grommet DIN terminal	C€
	1/2	17.7	16	Argon Oxygen ^{*1}	Diass	N.C.	HNBR (Pilot valve)	Conduit M12 connector	UK CA

^{*1} When using oxygen, please refer to "Fluid Supply" on page 4.

Related Equipment

	Description	Max. operating pressure	Series				Port size	Э			Web
	Description	pressure [MPa]	Series	1/4	1/2	3/8	3/4	1	1 1/4	1 1/2	Catalog
To make the later of the later	High pressure electro-pneumatic	5.0	ітvх			•					
G	regulator	3.0	ІТУН	•		•					
111 - 111 -	Pilot operated 3-port solenoid valve	5.0	VCH410		•		•	•			
	Direct operated regulator	Inlet pressure 6.0	VCHR30				•	•			
	(Relieving type)	Set pressure 0.5 to 5.0	VCHR40					•			
	Silencer	5.0 (Relief valve release	VCHN3				•	•			
	Silericer	pressure: 1.8 MPa)	VCHN4					•	•	•	
	Check valve	5.0	VCHC40				•	•			
000	Pressure switch	5.0 (ISE76G) 10.0 (ISE77G) 16.0 (ISE78G) 50.0 (ISE79S)	ISE70□G/79S	•							




Pilot Operated 2-Port Solenoid Valve







How to Order



1 Series

Symbol	Series		
Н	High-pressure/ Pilot operated		

2 Size

Symbol	Size
2	20

3 Valve type

Symbol		Valve type
1	N.C.	2 (OUT) 1 (IN)

4 Main valve construction

Symbol	Main valve construction
D	Diaphragm

6 Body material

Symbol	Body material
С	Brass

6 Seal material

Symbol	Seal material			
Symbol	Main valve	Pilot valve		
Н	PUR	HNBR		

Port size and orifice diameter

Symbol	Port size	Orifice diameter [mmø]
03	3/8	16
04	1/2	10

8 Thread type

Symbol	Thread type
R	Rc
N	NPT
F	G

Pated voltage

AC

Symbol	Rated voltage	Symbol	Rated voltage
1	100 VAC	7	240 VAC
2	200 VAC	8	48 VAC
3	120 (110) VAC	В	24 VAC
4	220 VAC	J	230 VAC

DC

Symbol	Rated voltage
5	24 VDC
6	12 VDC

Option

Symbol	Option
Nil	None
D	Oil-free

2 Pressure type

Symbol	Specifications
	Operating pressure: 0.15 to 4.0 MPa Fluid: Air, Nitrogen, Oxygen, Argon

Electrical entry

Symbol	Electrical entry	CE/UKCA- compliant	
G	Grommet*1	0	24 VDC
G	aronimet		12 VDC
	Grommet with PCB		100 VAC 24 VDC
GS			12 VDC
	(With surge voltage suppressor)		48 VAC
			24 VAC
cs	Conduit (With surge voltage suppressor)		
DS	DIN terminal (With surge voltage suppressor)		All voltages
DZ	DIN terminal with light (With surge voltage suppressor)		All voltages
DN	Without DIN connector (With surge voltage suppressor)		All voltages
WN	M12 connector/Without connector cable (With surge voltage suppressor)*2		All voltages

^{*1} DC voltage only

^{*2} A cable for the M12 connector is not included with the product.



Specifications



Size			20	
			20	
	Valve construction		Pilot operated diaphragm Normally closed (N.C.)	
	Valve type		·	
	Fluid		Compressed air, Nitrogen, Argon, Oxygen	
	Orifice diameter		16 mmø	
	Port size		3/8"	1/2"
	Flow rate characteristics*1	C [dm³/(s·bar)]	15	17.7
		b	0.36	0.22
		Cv	3.9	4.3
"	Max. operating pressure differential		4.0 MPa	
Valve specifications	Min. operating pressure differential		0.15 MPa	
	Fluid temperature		−10 to 50°C	
	Ambient temperature		−10 to 50°C	
eci	Leakage*1	Internal leakage	1 cm ³ /min or less	
g		External leakage		
Valve	Thread type		G, Rc, NPT	
	Max. system pressure		4.0 MPa	
	Proof pressure		6.0 MPa	
	Body material		Brass	
	Degrees of protection		IP67 (IP65 for the DIN terminal)	
	Seal material	Main valve	PUR	
		Pilot valve	HNBR	
	Impact/Vibration resistance*2		150/30 m/s ²	
	Mounting orientation		Unrestricted	
	Weight*6	Grommet	3/8"	1/2"
			713 g	671 g
	Rated voltage	AC	24 V, 48 V, 100 V, 110 V, 120 V	
		AC	200 V, 220 V, 230 V, 240 V	
"		DC	12 V, 24 V	
ő	Allowable voltage fluctuation		±10% of the rated voltage	
ati	Allowable leakage	AC	5% or less of the rated voltage	
ijį	voltage	DC	2% or less of the rated voltage	
ec	Apparent power*3, *4	AC	8 VA	
sb	Power consumption*3	DC	6 W	
Coil specifications	Temperature rise*5	AC	70°C	
		DC	65°C	
	Electrical entry		Grommet type, Conduit terminal DIN terminal, M12 connector	

- *1 The value for air at a differential pressure of 0.15 MPa or higher and an ambient temperature of 20°C
- *2 Impact resistance: No malfunction occurred when tested with a drop tester in the axial direction and at a right angle to the main valve and armature in both an energized and a deenergized state, once in each condition. (Value in the initial state)
 - Vibration resistance: No malfunction occurred in a one-sweep test between 5 and 2000 Hz. The test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Value in the initial state)
- *3 Power consumption/Apparent power: The value at an ambient temperature of 20°C and when the rated voltage is applied (Variation: ±10%)
- *4 There is no difference in the frequency and the inrush and energized apparent power, since a rectifying circuit is used in the AC.
- *5 Temperature rise: The value at an ambient temperature of 20°C and when the rated voltage is applied. Use this value as a reference as the actual value varies depending on the ambient environment
- *6 The values are for the grommet type. Add 20 g for the grommet type with PCB, 70 g for the conduit type, 50 g for the DIN terminal type, and 15 g for the type without a DIN connector and the M12 connector type.

Fluid Supply

.Marning


- 1. Compressed air, nitrogen, argon or oxygen can be used as a fluid.
- Do not use compressed air which includes chemicals, synthetic oils containing organic solvents, salt, or corrosive gases, etc., as this can cause damage or malfunction.
- 3. If oxygen is used as the fluid, it can lead to serious and unforeseen risks. However, it is possible to manage and control the risk of hazards and economic loss. In order to use the product safely, it should only be handled by personnel with appropriate knowledge, with support from a suitably qualified specialist.
- 4. Oxygen gas increases the susceptibility of substances to burning; Oxygen gas can be ignited by frictional heat and static electricity. If oxygen is ignited, the metal and seal materials burn. Therefore, flush the piping thoroughly and mount a suitable filter to prevent foreign matter such as metal powder and dust from entering the product.
- Take safety measures by installing safety devices (e.g. a circuit that stops the supply of oxygen gas) to prevent fire and explosion in the event of failure, taking flameproof safety standards into consideration.




JSXH-X1

Dimensions

G: Grommet







GS: Grommet with PCB

S. 88


CS: Conduit




DS: DIN terminal DZ: DIN terminal with light



DN: Without DIN connector



WN: M12 connector/
Without connector cable



⚠ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)*1), and other safety regulations.

⚠ Danger: Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

⚠ Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

⚠ Caution: Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

*1) ISO 4414: Pneumatic fluid power - General rules and safety requirements for systems and their components ISO 4413: Hydraulic fluid power - General rules and safety requirements for systems and their components IEC 60204-1: Safety of machinery - Electrical equipment of machines - Part 1: General requirements ISO 10218-1: Robots and robotic devices - Safety requirements for industrial robots - Part 1:Robots

⚠Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

- 3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.
 - 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
 - 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
 - 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
- 4. Our products cannot be used beyond their specifications. Our products are not developed, designed, and manufactured to be used under the following conditions or environments. Use under such conditions or environments is not covered.
 - 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
 - 2. Use for nuclear power, railways, aviation, space equipment, ships, vehicles, military application, equipment affecting human life, body, and property, fuel equipment, entertainment equipment, emergency shut-off circuits, press clutches, brake circuits, safety equipment, etc., and use for applications that do not conform to standard specifications such as catalogs and operation manuals.
 - 3. Use for interlock circuits, except for use with double interlock such as installing a mechanical protection function in case of failure. Please periodically inspect the product to confirm that the product is operating properly.

⚠ Caution

We develop, design, and manufacture our products to be used for automatic control equipment, and provide them for peaceful use in manufacturing industries.

Use in non-manufacturing industries is not covered.

Products we manufacture and sell cannot be used for the purpose of transactions or certification specified in the Measurement Act.

The new Measurement Act prohibits use of any unit other than SI units in

Limited warranty and Disclaimer/ Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.*2) Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.
 - *2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

↑ Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.

SMC Corporation

Akihabara UDX 15F,

4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN

Phone: 03-5207-8249 Fax: 03-5298-5362

https://www.smcworld.com

© 2024 SMC Corporation All Rights Reserved