Multi Hand Adapter

Multi hand adapter

Allows for the handling of various workpieces by a single robot

Allows for the simultaneous transfer of multiple workpieces


Up to 3 grippers can be mounted.
 Reduces tool changing time






Mounting and removal are possible using the 2 clamper bolts.





Gripper Mounting Example



RMMA Series



New

RoHS

Multi Hand Adapter

RMMA Series







How to Order



Gripper mounting angle




2Changer specification



* E and F are equipped with a collar assembly.

3 Option



RMMA1-20T090-E-01 is the set part number, which includes an RMMA1-20T090-E multihand adapter (90° mounting angle) and an RMMA-A11-01 (option replacement parts). For details, refer to page 6.



180°

- * For the connector cable to be used when two or more grippers are mounted, refer to page 8.
 - * This product is shipped as parts (in an unassembled state). Therefore, the user needs to assemble them into the product.

Specifications

| Mounting angle | | 90° | 120° |
|-----------------------|-----------------------------------|---------------------------------|------|
| Max. work load | | 20 kg*1 | |
| Moment r | Moment resistance Mp, Mr 60 N·m*1 | | ·m*1 |
| Torque resistance My | | 60 N·m*¹ | |
| Standards | Robot side | Equivalent to ISO9409-1-50-4-M6 | |
| | Gripper mounting side | Equivalent to ISO9409-1-50-4-M6 | |
| Operating temperature | | −10 to 60°C*1 | |


*1 Use the product at the minimum tolerances of the robot and peripheral devices to be connected.


In addition, be sure to perform a verification test to confirm the absence of problems before use.


Weight

| weight | | [9] |
|--------------------------------|--------------------|---------------------|
| Item | Mounting angle 90° | Mounting angle 120° |
| With main plate and tool plate | 520* ² | 550* ² |
| With tool plate | 400*2 | 430*2 |
| Without tool plate | 340 | 370 |

- *2 The weight of the M6 x 10 hexagon socket thin head cap screws (4 pcs.) and the Ø6 x 10 parallel pin (1 pc.) is included in the weight.
- The weight of the multi-hand adapter body is included in the weights above.










Be sure to read this before handling the products. Refer to the back cover for safety instructions.


I For air gripper precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the I
 I SMC website: https://www.smcworld.com

Component Parts



■ Main plate (for mounting the robot)





Replacement Parts

| No. | Description | Replacement part no. | Quantity |
|--------------|-----------------|----------------------|----------|
| 1 | Main plate | RMTM2-4M1 | 1 |
| 2 Tool plate | | RMTM2-4T1*1 | 1 |
| 3 | Collar assembly | RMMA-A00-01 | 1 |

^{*1} The tool plate includes the following accessories. Hexagon socket thin head cap screw (4 pcs.) and parallel pin ø6 x 10 (1 pc.)




Dimensions: Mounting Angle 90°



RMMA1-20T090-E: With main plate and tool plate (E)

* The dimensions of the model with tool plate (F) are the same as those of the model with main plate/tool plate (E) except for the detailed portions.




Multi Hand Adapter **RMMA** Series

Dimensions: Mounting Angle 120°

0


RMMA1-20T120-E: With main plate and tool plate (E)

* The dimensions of the model with tool plate (F) are the same as those of the model with main plate/tool plate (E) except for the detailed portions.





Dimensions: Multi Hand Adapter Single Unit (90°/120° mounting angle)


RMMA1-20T090-N: Mounting Angle 90°





RMMA1-20T120-N: Mounting Angle 120°


















RMMA Series Option

Mounting Angle 180° Parts Set/RMMA1-20T090-E-01




- RMMA1-20T090-E-01 (180° mounting angle) is the set part number, which includes an RMMA1-20T090-E multi-hand adapter (90° mounting angle) and an RMMA-A11-01 (option replacement parts).
- * Only an additional 90° mounting angle can be used in combination.

Mounting example




Gripper Mounting Examples





Dimensions: Mounting Angle 180° Parts Set

RMMA1-20T090-E-01









RMMA Series Connector Cable


A cable to connect grippers and an additional I/O terminal when performing electrical wiring with 2 or more grippers

Part name: Connector cable Order no.: RMH-A00-18A




Specifications


| Standards | IEC61076-2-104 compliant | |
|-----------------------------|--------------------------|--|
| Connector type | M8 socket | |
| Number of poles | 8 | |
| Keying | A | |
| Rated voltage | 30 VDC | |
| Rated current | 1A | |
| Conductor | AWG26 | |
| Terminal processing | Half-stripped | |
| Operating temperature range | −10 to +60°C | |



Dimensions



A (Pin no.) (5:1)



Wiring

| Connector | Pin no. | Wiring color |
|--|---------|--------------|
| M8-8 pin Angled connector (Socket) | 1 | White |
| | 2 | Brown |
| | 3 | Green |
| | 4 | Yellow |
| | 5 | Gray |
| | 6 | Black |
| | 7 | Blue |
| | 8 | Red |

⚠ Caution

The pin arrangement varies depending on the robot manufacturer.

Refer to the operation manuals of the grippers and robots to be used for details.



Related Product



Air Grippers for **Collaborative Robots**

RMH□ Series

Unitization of the peripheral devices required for gripper driving

Operation is possible simply by connecting 1 air supply tube and 1 electrical cable.

Built-in

Solenoid valve

Exhaust throttle valve with silencer

Auto switch

Fitting



* The attachment should be ordered separately by the customer.

3 types of grippers available for use with a variety of workpieces

Standard Type



RMHZ2 Series

3-Finger Type



RMHS3 Series

Long Stroke Type



RMHF2 Series

Can be used with the collaborative robots of 12 companies

UNIVERSAL ROBOTS, OMRON/TECHMAN ROBOT, FANUC, YASKAWA Electric, Mitsubishi Electric, HAN'S ROBOT, KUKA, DOOSAN ROBOTICS, SIASUN, JAKA, AUBO, ABB

9

⚠ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)*1, and other safety regulations.

⚠ Danger: Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

⚠ Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

⚠ Caution: Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

*1) ISO 4414: Pneumatic fluid power - General rules and safety requirements for systems and their components ISO 4413: Hydraulic fluid power - General rules and safety requirements for systems and their components IEC 60204-1: Safety of machinery - Electrical equipment of machines - Part 1: General requirements ISO 10218-1: Robots and robotic devices - Safety requirements for industrial robots - Part 1:Robots

⚠Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

- 3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.
 - 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
 - 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
 - 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
- 4. Our products cannot be used beyond their specifications. Our products are not developed, designed, and manufactured to be used under the following conditions or environments. Use under such conditions or environments is not covered.
 - 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
 - 2. Use for nuclear power, railways, aviation, space equipment, ships, vehicles, military application, equipment affecting human life, body, and property, fuel equipment, entertainment equipment, emergency shut-off circuits, press clutches, brake circuits, safety equipment, etc., and use for applications that do not conform to standard specifications such as catalogs and operation manuals.
 - 3. Use for interlock circuits, except for use with double interlock such as installing a mechanical protection function in case of failure. Please periodically inspect the product to confirm that the product is operating properly.

⚠ Caution

We develop, design, and manufacture our products to be used for automatic control equipment, and provide them for peaceful use in manufacturing industries.

Use in non-manufacturing industries is not covered.

Products we manufacture and sell cannot be used for the purpose of transactions or certification specified in the Measurement Act.

The new Measurement Act prohibits use of any unit other than SI units in

Limited warranty and Disclaimer/ Compliance Requirements

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.*2) Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.
 - *2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

↑ Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.

SMC Corporation

https://www.smcworld.com © 2024 SMC Corporation All Rights Reserved