

ø20, ø25, ø35, ø50

Good for film packaging applications



■ **Uses a material compliant with the FDA (U.S. Food and Drug Administration) dissolution test as well as Japan Food Sanitation Act standards**

■ **Blue colored pad**

Easy to distinguish the vacuum pad by color during contamination inspection

■ **Reduced leakage**

Sealing skirt design, better sealing performance even for thin films




■ **Reduction of wrinkles made on thin workpieces (film, vinyl, etc.) during adsorption**

Wrinkle prevention with the stopper in the center of the vacuum pad



Variations

Form	Pad diameter				Vacuum inlet/Mounting	Buffer stroke	Page
	ø20	ø25	ø35	ø50			
Pad Unit					—	—	267
With Adapter	Male thread				M5 x 0.8, M12 x 1.75 G1/8, G1/4, G3/8	—	268
	Female thread				M5 x 0.8 M8 x 1.25	—	
With Buffer	Female thread				Vacuum inlet: M5 x 0.8, Rc1/8 Mounting: M10 x 1, M14 x 1	10 mm/20 mm	271



Vacuum Pad

Symbol/Form

Pad diameter $\phi 20, \phi 25, \phi 35, \phi 50$

How to Order

Pad unit **ZP3P-20PTSF**

Mounting Bracket Part Nos.

Adapter Assembly	p. 275
Buffer Assembly	p. 275

Pad diameter

Symbol	Pad diameter
20	$\phi 20$
25	$\phi 25$
35	$\phi 35$
50	$\phi 50$

Pad material


Symbol	Material
SF	Silicone rubber*1, *2

*1 Uses a material compliant with a dissolution test of the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use."


*2 Uses a material compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Japanese Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Japanese Ministry of Health and Welfare Notification No. 370, 1959)

Dimensions: Pad Unit


ZP3P-20PTSF [Weight: 1.8 g]




ZP3P-25PTSF [Weight: 2.2 g]



ZP3P-35PTSF [Weight: 4.7 g]




ZP3P-50PTSF [Weight: 12.4 g]




Pad Mounting Dimensions

If an adapter will be made by the customer, design the adapter with the dimensions shown below.

Applicable pad 20PT/25PT



Applicable pad 35PT/50PT



* The R part has to be smooth with no corners.

How to Order

Vertical vacuum inlet
With adapter

ZP3P **- T 20 PT SF - A5**

Adapter material

Symbol	Material
Nil	Aluminum
S	Stainless steel (Stainless steel 304)

Pad diameter

Symbol	Pad diameter
20	ø20
25	ø25
35	ø35
50	ø50

Pad material

Symbol	Material
SF	Silicone rubber*1, *2

*1 Uses a material compliant with a dissolution test of the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use."

*2 Uses a material compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Japanese Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Japanese Ministry of Health and Welfare Notification No. 370, 1959)

Mounting thread size

Type	Symbol	Size	ø20	ø25	ø35	ø50
Male thread	A5	M5 x 0.8	●	●	—	—
	A12	M12 x 1.75	—	—	●	●
	AG1	G1/8	●	●	—	—
	AG2	G1/4	—	—	●	●
Female thread	B5	M5 x 0.8	●	●	—	—
	B8	M8 x 1.25	—	—	●	●

* The pad is shipped together but does not come assembled.


Mounting

When mounting the male thread adapter, be sure to tighten using the recommended tightening torque in the chart on the right. Tightening outside of the recommended tightening torque range may result in sealing failure or loosening of the thread.


Product part number	Connection thread size	Proper tightening torque [N·m]
ZP3P□-T□PTSF-A5	M5 x 0.8	1.2 to 1.6
ZP3P□-T□PTSF-A12	M12 x 1.75	3 to 5
ZP3P□-T□PTSF-AG1	G1/8	3 to 5
ZP3P□-T□PTSF-AG2	G1/4	8 to 12
ZP3P□-T□PTSF-AG3	G3/8	15 to 20

Dimensions: With Male Thread Adapter


ZP3P-T20PTSF-A5 [Weight: 3.9 g]
ZP3PS-T20PTSF-A5 [Weight: 7.6 g]




ZP3P-T25PTSF-A5 [Weight: 4.3 g]
ZP3PS-T25PTSF-A5 [Weight: 8.0 g]



ZP3P-T20PTSF-AG1 [Weight: 5.9 g]
ZP3PS-T20PTSF-AG1 [Weight: 13.1 g]




ZP3P-T25PTSF-AG1 [Weight: 6.3 g]
ZP3PS-T25PTSF-AG1 [Weight: 13.5 g]



Dimensions: With Male Thread Adapter


ZP3P-T35PTSF-A12 [Weight: 20.7 g]

ZP3PS-T35PTSF-A12 [Weight: 48.3 g]




ZP3P-T35PTSF-AG2 [Weight: 14.5 g]

ZP3PS-T35PTSF-AG2 [Weight: 32.1 g]




ZP3P-T35PTSF-AG3 [Weight: 21.1 g]

ZP3PS-T35PTSF-AG3 [Weight: 48.8 g]




ZP3P-T50PTSF-A12 [Weight: 28.4 g]

ZP3PS-T50PTSF-A12 [Weight: 56.0 g]




ZP3P-T50PTSF-AG2 [Weight: 22.2 g]

ZP3PS-T50PTSF-AG2 [Weight: 39.8 g]




ZP3P-T50PTSF-AG3 [Weight: 28.8 g]

ZP3PS-T50PTSF-AG3 [Weight: 56.5 g]




Dimensions: With Female Thread Adapter


ZP3P-T20PTSF-B5 [Weight: 4.9 g]
ZP3PS-T20PTSF-B5 [Weight: 10.5 g]




ZP3P-T25PTSF-B5 [Weight: 5.3 g]
ZP3PS-T25PTSF-B5 [Weight: 10.9 g]



ZP3P-T35PTSF-B8 [Weight: 13.2 g]
ZP3PS-T35PTSF-B8 [Weight: 28.7 g]



ZP3P-T50PTSF-B8 [Weight: 20.9 g]
ZP3PS-T50PTSF-B8 [Weight: 36.4 g]



Model
Selection

For Special
Applications

Mark-free

For Film
Adsorption

Multistage

Flat

Nozzle

Sponge

For Disk
Adsorption

For Panel
Holding

Ball Spline
Buffer

Construction

Mounting
Bracket
Assembly

Precautions

How to Order

Vertical vacuum inlet
With buffer

ZP3P-T 20 PT SF J 10-B5

Pad diameter	
Symbol	Pad diameter
20	ø20
25	ø25
35	ø35
50	ø50

Pad material

Symbol	Material
SF	Silicone rubber*1, *2

- *1 Uses a material compliant with a dissolution test of the FDA (U.S. Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use."
 *2 Uses a material compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Japanese Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Japan Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Japanese Ministry of Health and Welfare Notification No. 370, 1959)

Vacuum inlet

Type	Symbol	Size	ø20, ø25	ø35, ø50
Female thread	B5	M5 x 0.8	●	—
	B01	Rc1/8	—	●

Stroke (■)

Buffer specification	
Symbol	Stroke
J	Rotating
K	Non-rotating

Symbol	Stroke	ø20, ø25	ø35, ø50
10	10 mm	●	●
20	20 mm	●	●

Specifications

Pad diameter	Buffer specification	Stroke [mm]	Tightening torque [N·m]	Connection thread	Spring reactive force [N]	
					At 0 stroke	At full stroke
ø20, ø25	J/K	10, 20	2.5 to 3.5	M10 x 1	1.0	3.0
ø35, ø50	J/K	10, 20	6.5 to 7.5	M14 x 1	2.0	5.0

* The buffer and mounting nut are shipped together with the product (unassembled).

⚠ Specific Product Precautions

Be sure to read this before handling the products. For safety instructions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: <https://www.smcworld.com>

Operating Precautions


⚠ Caution

1. When selecting a buffer


Buffers come with general industrial grease applied to them and are therefore not compliant with FDA regulations. Metal wear particles will be generated due to the sliding motion of the buffer. Please take this into consideration when deciding whether this pad is suitable for your application.

Dimensions: With Buffer

ZP3P-T20PTSFJ■-B5



ZP3P-T20PTSFK■-B5





Dimensions

Part no.	A	B	D	Weight [g]
ZP3P-T20PTSFJ10-B5	32.5	68.5	23	26.7
ZP3P-T20PTSFJ20-B5	42.5	106.5	51	40.8

Dimensions

Part no.	A	B	D	Weight [g]
ZP3P-T20PTSFK10-B5	32.5	68.5	23	28.5
ZP3P-T20PTSFK20-B5	42.5	106.5	51	41.8

Dimensions: With Buffer



ZP3P-T25PTSFJ■-B5

ZP3P-T25PTSFK■-B5


Dimensions

Part no.	A	B	D	Weight [g]
ZP3P-T25PTSFJ10-B5	33	69	23	27.1
ZP3P-T25PTSFJ20-B5	43	107	51	41.2

Dimensions

Part no.	A	B	D	Weight [g]
ZP3P-T25PTSFK10-B5	33	69	23	28.5
ZP3P-T25PTSFK20-B5	43	107	51	42.2

ZP3P-T35PTSFJ■-B01
ZP3P-T35PTSFJ10-B01
ZP3P-T35PTSFJ20-B01

ZP3P-T35PTSFK■-B01
ZP3P-T35PTSFK10-B01
ZP3P-T35PTSFK20-B01



Dimensions

Part no.	A	B	Weight [g]
ZP3P-T35PTSFJ10-B01	37.5	104	93.6
ZP3P-T35PTSFJ20-B01	47.5	109.5	94.6

Dimensions


Part no.	A	B	Weight [g]
ZP3P-T35PTSFK10-B01	37.5	104	93.0
ZP3P-T35PTSFK20-B01	47.5	109.5	94.1

Dimensions: With Buffer



Dimensions

Part no.	A	B	Weight [g]
ZP3P-T50PTSFJ10-B01	40.5	107	101.3
ZP3P-T50PTSFJ20-B01	50.5	112.5	102.3



Dimensions


Part no.	A	B	Weight [g]
ZP3P-T50PTSFK10-B01	40.5	107	100.7
ZP3P-T50PTSFK20-B01	50.5	112.5	101.8

Vacuum Pad **ZP3P-PT Series**


Construction

Pad with Adapter

Male thread




Female thread



Component Parts

No.	Description	Material (Surface treatment)	Note
1	Vacuum pad	Silicone rubber	
2	Adapter	Aluminum alloy (Clear anodized)	ZP3P-T□
		Stainless steel	ZP3PS-T□
3	Gasket	Stainless steel/NBR	ZP3P-□- (A5/AG1/AG2/AG3) ZP3PS-□- (AG1/AG2/AG3)
		Stainless steel/FKM	ZP3PS-□-A5
	Seal washer	Structural steel/NBR	ZP3P-□-A12
		Stainless steel/FKM	ZP3PS-□-A12

Pad with Buffer



Component Parts

No.	Description	Material (Surface treatment)
1	Vacuum pad	Silicone rubber
2	Adapter	Aluminum alloy (Clear anodized)
3	Piston rod	Stainless steel
4	Buffer body	Brass (Electroless nickel plating)
5	Return spring	Stainless steel
6	Buffer adapter	Brass (Electroless nickel plating)
7	Nut	Steel (Zinc chromated)
8	Gasket	Stainless steel/NBR


Vacuum Pad ZP3P-PT Series

Parts Structure

With T Type Adapter

ZP3P□-T (20 to 50) PTSF-(A5/AG1/A12/AG2/AG3)

ZP3P□-T (20 to 50) PTSF-(B5/B8)



With Buffer

