







2-Color Display Digital Flow Switch

Series PFM

-  Flow rate range: 10, 25, 50, 100 L/min.
-  Minimum unit setting: 0.01 L/min.
(0.1 L/min when the flow rate range is 25, 50, 100 L/min.)
-  Repeatability: $\pm 1\%$ F.S.
-  Grease-free
-  Flow adjustment valve is integrated.
(Reduced piping and space saving)
-  Response time:
Either 50 ms, 0.5 s, 1 s
or 2 s can be chosen.



RoHS

Fluid

Air, N₂, Ar, CO₂

2-color display

See abnormal values at a glance.



PFM

PFMV




PF2A

PF3W


PF2D

IF

2-Color Display Digital Flow Switch




Connectors
Connection and removal of wiring is easy.



Support for vertical and horizontal secure mounting (panel mount)

A single panel opening is sufficient.
Reduces panel fitting labor and enables space-savings.



Measurement flow range (L/min)	Integrated type	Remote type	
	Model	Sensor unit	Monitor unit
0.2 to 10 (0.2 to 5)	PFM710	PFM510	PFM3□□
0.5 to 25 (0.5 to 12.5)	PFM725	PFM525	
1 to 50 (1 to 25)	PFM750	PFM550	
2 to 100 (2 to 50)	PFM711	PFM511	

() : Fluid: CO₂



Compact

Same size even when the model with different flow rate range (10, 25, 50, 100 L/min) is chosen.

Lightweight: 55 g (PFM711)

(With One-touch fitting, without flow adjustment valve)

Existing model PF2A711: 290 g




Comparison with the existing model PF2A711 (10 to 100 L/min)

Reduced piping space

Mountable in a narrow location since the straight piping length* is not required.

* A straight piping length of 8 times the piping diameter is required for the existing model.




Comparison with the existing model PF2A711 (10 to 100 L/min) when $\phi 6$ One-touch fittings are attached.

Piping Variations

	One-touch fitting: $\phi 4$, $\phi 6$, $\phi 8$, $\phi 1/4$		Female thread: Rc 1/8, 1/4 • NPT 1/8, 1/4 • G 1/8, 1/4	
	Straight	Bottom	Straight	Bottom
Without flow adjustment				
With flow adjustment				

Mounting



Main Functions

● Selection of fluid

Air, Nitrogen (N₂), Argon (Ar) or Carbon dioxide (CO₂) can be selected using the buttons.


● Secret code setting function

The user must input a secret code to cancel the keylock mode. This ensures that only authorized persons can operate the switch.

For details and other functions, refer to page 995.

● Power-saving mode

Turning off the display can save power consumption.



Flashing



Flashing

The decimal point indicators flash in power-saving mode.

■ Selection of indication unit

User can select between ANR and NL/min for each fluid.

[ANR] Indicates the flow rate converted to a volume under standard conditions: 20°C, 1 atm (atmosphere), 65%RH

[NL/min] Indicates the flow rate converted to a volume under normal conditions: 0°C, 1 atm (atmosphere).

■ External input

Can be selected from accumulated value external reset, auto-shift and auto-shift zero.


■ Indication resolution

Minimum unit setting can be selected from 1 L/min, 0.1 L/min and 0.01 L/min. Depends on the model. Refer to the specifications (P. 966, 992) for details.

Several Combinations

Depending on the installation conditions, it is possible to add or remove the **flow adjustment valve**, change the **fitting type** and the **piping direction** as desired.


Refer to page 990 for details.



The accuracy may fluctuate by 2 to 3% just after replacement.
(Repeatability does not change.)

Recommended Air Circuits

Compressed air line



Dryer

Air filter

Regulator

Micro mist separator

Flow switch

IDF
IDU


AF

AR
IR


AMD
AFD

PFM


Applications




● Digital display




● Not subject to pressure variations




● Free mounting orientation



● With switch output and analog output



● Accumulated flow display



PFM
PFMV
PF2A
PF3W
PF2D
IF

● 2-Color Display Digital Flow Switch

Series PFM7 Integrated Display



Series PFM5 Remote Sensor Unit



Series PFM7, PFM5 Common Specifications

Series PFM3 Flow Sensor Monitor



Made to Order

Features	P. 958 to 961
How to Order	P. 964
Specifications	P. 966
Piping Specifications/Weight	P. 967
Analog Output	P. 967
Dimensions	P. 968
How to Order	P. 976
Specifications	P. 978
Piping Specifications/Weight	P. 979
Analog Output	P. 979
Dimensions	P. 980
Pressure Loss/Flow Characteristics	P. 988
Parts Description	P. 989
Wetted parts construction	P. 989
Detection Principle	P. 989
Component Parts	P. 990
How to Order	P. 991
Specifications	P. 992
Analog Output	P. 992
Dimensions	P. 993
Function Details	P. 995
Changing the piping entry direction	P. 996
combination for IN and OUT side	
Compatible with argon (Ar) and carbon	P. 998
dioxide (CO ₂) mixed gas	

PFM
PFMV
PF2A
PF3W
PF2D
IF

2-Color Display Digital Flow Switch Series PFM7

Integrated
display



How to Order

Integrated
display

PFM7 **10** **C4** **A** **M**

Type

7 Integrated display

Rated flow range (Flow rate range)

10	0.2 to 10 (5) L/min
25	0.5 to 25 (12.5) L/min
50	1 to 50 (25) L/min
11	2 to 100 (50) L/min

* (): Fluid: CO₂

Flow adjustment valve

Nil	None
S	Yes

Port size

Symbol	Description	Flow rate range			
		10	25	50	11
01	Rc 1/8	●	●	●	●
02	Rc 1/4	●	●	●	●
N01	NPT 1/8	●	●	●	●
N02	NPT 1/4	●	●	●	●
F01	G 1/8 *	●	●	●	●
F02	G 1/4 *	●	●	●	●
C4	ø4 (5/32") One-touch fitting	●	●	●	●
C6	ø6 One-touch fitting	●	●	●	●
C8	ø8 (5/16") One-touch fitting	●	●	●	●
N7	ø1/4" One-touch fitting	●	●	●	●

* Conforming to ISO228-1.

Piping entry direction

Nil	Straight
L	Bottom

* Different combinations of piping entry directions for IN and OUT side are available as made-to-order. (Refer to page 996.)

• Made to Order
(Refer to pages 965 and 996.)

• Option 2
(Refer to page 965.)

• Option 1
(Refer to page 965.)

• Calibration certificate

Nil	None
A	With calibration certificate

* The certificate is written in English and Japanese. Other languages are available as specials.

• Operation manual

Nil	With operation manual (Japanese and English)
N	None

• Unit specifications

M	Fixed SI unit (Note1)
Nil	With unit switching function (Note2)

Note1) Fixed unit: Instantaneous flow rate: L/min
Accumulated flow: L

Note2) Since the unit for Japan is fixed to SI due to new measurement law, this option is for overseas.

• Output specifications



A	2 NPN outputs
B	2 PNP outputs
C	1 NPN output + Analog (1 to 5 V)
D	1 NPN output + Analog (4 to 20 mA)
E	1 PNP output + Analog (1 to 5 V)
F	1 PNP output + Analog (4 to 20 mA)
G	1 NPN output + External input (Note3)
H	1 PNP output + External input (Note3)

Note3) User can select from accumulated value external reset, auto-shift and auto-shift zero.





Piping Variations

	With One-touch fittings (C4, C6, C8, N7)		Female thread (01, 02, N01, N02, F01, F02)	
	Straight (Nil)	Bottom (L)	Straight (Nil)	Bottom (L)
Without flow adjustment valve (Nil)				
With flow adjustment valve (S)				

Option 1

NII	W	Z
With lead wire with connector (2 m)	With lead wire with connector (2 m) + Rubber cover for connector (silicon rubber)	Without lead wire with connector
 ZS-33-D Lead wire length 2 m	 ZS-33-F ZS-33-D Lead wire length 2 m	

Option 2

NII	R	S	T
None	Bracket (For without flow adjustment valve) ZS-33-M	Bracket (For with flow adjustment valve) ZS-33-MS	Panel mount adapter (For without flow adjustment valve) ZS-33-J
	 Mounting screw (accessory)	 Mounting screw (accessory) Piping direction: Cannot be mounted with bottom piping type.	 Panel mount adapter A Panel mount adapter B Panel Mounting bracket
V			
Panel mount adapter (For with flow adjustment valve) ZS-33-JS			
 Panel mount adapter A Panel mount adapter B Panel Mounting bracket			

Each option is not assembled with the product, but shipped together.

Made to Order

Symbol	Specification/Description
X693	Change of piping entry direction
X694	combination
X731	Compatible with argon (Ar) and carbon dioxide (CO ₂) mixed gas


For details, refer to page 996 through to 998.

DIN Rail Mounting Bracket (Order Separately)

ZS-33-R

Stations

1	1 station
2	2 stations
3	3 stations
4	4 stations
5	5 stations



- DIN rail (supplied by customers)
- Port size F02: G 1/4 cannot be mounted on the DIN rail.

For details about the Flow Switch Precautions, refer to pages 952 and 953. For details about the Specific Product Precautions, refer to the Operation Manual at SMC website.

Specifications

Model		PFM710	PFM725	PFM750	PFM711
Applicable fluid		Dry air, N ₂ , Ar, CO ₂ (Air quality grade is JIS B8392.1-1, 1.2 to 1.6.2 and ISO 8573.1-1, 1.2 to 1.6.2.)			
Rated flow range (Flow rate range)	Dry air, N ₂ , Ar	0.2 to 10 L/min	0.5 to 25 L/min	1 to 50 L/min	2 to 100 L/min
	CO ₂	0.2 to 5 L/min	0.5 to 12.5 L/min	1 to 25 L/min	2 to 50 L/min
Displayable range (Note 1)	Dry air, N ₂ , Ar	0.2 to 10.5 L/min	0.5 to 26.3 L/min	1 to 52.5 L/min	2 to 105 L/min
	CO ₂	0.2 to 5.2 L/min	0.5 to 13.1 L/min	1 to 26.2 L/min	2 to 52 L/min
Settable range (Note 1)	Dry air, N ₂ , Ar	0 to 10.5 L/min	0 to 26.3 L/min	0 to 52.5 L/min	0 to 105 L/min
	CO ₂	0 to 5.2 L/min	0 to 13.1 L/min	0 to 26.2 L/min	0 to 52 L/min
Minimum unit setting (Note 2)		0.01 L/min	0.1 L/min	0.1 L/min	0.1 L/min
Accumulated pulse flow rate exchange value		0.1 L/pulse	0.1 L/pulse	0.1 L/pulse	1 L/pulse
Indication unit (Note 3)		Instantaneous flow rate L/min, CFM x 10 ⁻² Accumulated flow L, ft ³ x 10 ⁻¹			
Linearity		Display accuracy: ±3%F.S. (Fluid: Dry air) Analog output accuracy: ±5%F.S. (Fluid: Dry air)			
Repeatability		±1%F.S. Analog output accuracy: ±3%F.S. (Fluid: Dry air)			
Pressure characteristics		±5%F.S. (0.35 MPa reference)			
Temperature characteristics		±2%F.S. (15 to 35°C) ±5%F.S. (0 to 50°C)			
Operating pressure range		-100 kPa to 750 kPa			
Rated pressure range		-70 kPa to 750 kPa			
Proof pressure		1 MPa			
Accumulated flow range		Max. 999999 L (Note 4)			
Switch output		NPN or PNP open collector output			
	Maximum load current	80 mA			
	Maximum applied voltage	28 VDC (at NPN output)			
	Internal voltage drop	NPN output: 1 V or less (at 80 mA) PNP output: 1.5 V or less (at 80 mA)			
	Response time	1 s (50 ms, 0.5 s, 2 s can be selected.)			
	Output protection	Short-circuit protection			
Accumulated pulse output		NPN or PNP open collector output (Same as switch output)			
Analog output (Note 5)	Response time	1.5 s or less (90% response)			
	Voltage output	Voltage output: 1 to 5 V Output impedance: 1 kΩ			
	Current output	Current output: 4 to 20 mA Max. load impedance: 600 Ω, Min. load impedance: 50 Ω			
Hysteresis (Note 6)	Hysteresis mode	Variable			
	Window comparator mode	Variable			
External input		No-voltage input (Reed or Solid state) Input 30 ms or more			
Display method		3-digit, 7-segment LED 2-color display (Red/Green) Renewed cycle: 10 times/sec			
Status LED's		OUT1: Lights up when output is turned ON (Green). OUT2: Lights up when output is turned ON (Red).			
Power supply voltage		24 VDC ±10%			
Current consumption		55 mA or less			
Environment	Enclosure	IP40			
	Operating fluid temperature	0 to 50°C (with no freezing and condensation)			
	Operating temperature range	Operating: 0 to 50°C Stored: -10 to 60°C (with no freezing and condensation)			
	Operating humidity range	Operating, Stored: 35 to 85%R.H. (with no condensation)			
	Withstand voltage	1000 VAC for 1 minute between terminals and housing			
Insulation resistance		50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing			
Standards		CE UL, CSA RoHS			

- Note 1) When the minimum unit setting 0.01 L/min is selected for 10 L/min type, the indication upper limit will be [9.99 L/min].
When the minimum unit setting 0.1 L/min is selected for 100 L/min type, the indication upper limit will be [99.9 L/min].
- Note 2) User can select between 0.01 L/min and 0.1 L/min for the PFM710, and between 0.1 L/min and 1 L/min for the PFM711 respectively.
If the indication unit is selected to "CFM", the minimum unit setting cannot be changed.
- Note 3) At the time of shipment from the factory, the minimum unit setting is set to 0.1 L/min for the PFM710 and 1 L/min for the PFM711 respectively.
"ANR" is used for standard conditions: 20°C, 1 atm and 65%R.H.
"NL/min" is used for normal conditions: 0°C and 1 atm.
When equipped with a unit switching function, (The SI unit (L/min or L) is fixed for types with no unit switching function.)
- Note 4) Cleared when the power supply is turned off. Hold function can be selected. (Interval of 2 min or 5 min can be selected).
If the 5 min interval is selected, the life of the memory element (electronic part) is limited to 1 million cycles. (If energized for 24 hours, life is calculated as 5 min x 1 million = 5 million min = 9.5 years). Therefore, if using the hold function, calculate the memory life for your operating conditions, and use within this life.
- Note 5) Set to 1.5 s (90%), can be changed to 100 ms.
- Note 6) Set to hysteresis mode at the time of shipment from the factory. Can be changed to window comparator mode using push-buttons.
- Note 7) For details about wiring and thread type, refer to the Operation Manual that can be downloaded from SMC website (<http://www.smcworld.com>).

Settable Range and Rated Flow Range

Set the flow rate within the rated flow range.




The settable rate range is the range of flow rate that can be set in the switch.

The rated flow range is the range that satisfies the switch specifications (accuracy, linearity etc.).

It is possible to set a value outside of the rated flow range if it is within the settable range, however, the specification is not be guaranteed.

The flow range if using CO₂ is given in brackets.

Sensor	Flow range							
	0.2 L/min	0.5 L/min	1 L/min	2 L/min	10 L/min	25 L/min	50 L/min	100 L/min
PFM710 PFM510	0.2 L/min				10 L/min (5 L/min)			
	0.2 L/min				10.5 L/min (5.2 L/min)			
	0				10.5 L/min (5.2 L/min)			
PFM725 PFM525	0.5 L/min				25 L/min (12.5 L/min)			
	0.5 L/min				26.3 L/min (13.1 L/min)			
	0				26.3 L/min (13.1 L/min)			
PFM750 PFM550	1 L/min				50 L/min (25 L/min)			
	1 L/min				52.5 L/min (26.2 L/min)			
	0				52.5 L/min (26.2 L/min)			
PFM711 PFM511	2 L/min				100 L/min (50 L/min)			
	2 L/min				105 L/min (52 L/min)			
	0				105 L/min (52 L/min)			

 Rated flow range
 Displayable range
 Settable range


In the case of the PFM5 series, the displayable and settable ranges are the same as the PFM3 series flow monitor.

Piping Specifications/Weight

Part no.	01	02	N01	N02	F01	F02	C4	C6	C8	N7
Port size	Rc 1/8	Rc 1/4	NPT 1/8	NPT 1/4	G 1/8	G 1/4	ø4 (5/32") One-touch fitting	ø6 One-touch fitting	ø8 (5/16") One-touch fitting	ø1/4" One-touch fitting
Weight	Straight Bottom Straight With orifice: 135 g Bottom With orifice: 145 g	Without orifice: 95 g Without orifice: 105 g Straight With orifice: 135 g Bottom With orifice: 145 g	Without orifice: 95 g Without orifice: 105 g Straight With orifice: 135 g Bottom With orifice: 145 g	Without orifice: 95 g Without orifice: 105 g Straight With orifice: 135 g Bottom With orifice: 145 g	Without orifice: 95 g Without orifice: 105 g Straight With orifice: 135 g Bottom With orifice: 145 g	Straight Bottom Straight With orifice: 165 g Bottom With orifice: 175 g	Straight Bottom Straight With orifice: 165 g Bottom With orifice: 175 g	Straight Bottom Straight With orifice: 95 g Bottom With orifice: 105 g	Without orifice: 55 g Without orifice: 65 g Straight With orifice: 95 g Bottom With orifice: 105 g	Without orifice: 55 g Without orifice: 65 g Straight With orifice: 95 g Bottom With orifice: 105 g
Wetted parts material	LCP, PBT, Brass (Electroless nickel plating), HNBZ (+ Fluoro coated), FKM (+ Fluoro coated), Silicon, Au, Stainless steel 304									

Analog Output


Note) Analog output at maximum rated flow rate when CO₂ is selected is 3 [V] for the voltage output type and 12 [mA] for the current output type.



Analog Voltage Output (1 to 5 V)

Model	Max. rated flow value [L/min]
PFM710 -□-C/E	10 (5)
PFM725 -□-C/E	25 (12.5)
PFM750 -□-C/E	50 (25)
PFM711 -□-C/E	100 (50)

* (): Fluid: CO₂



Analog Current Output (4 to 20 mA)



Model	Max. rated flow value [L/min]
PFM710 -□-D/F	10 (5)
PFM725 -□-D/F	25 (12.5)
PFM750 -□-D/F	50 (25)
PFM711 -□-D/F	100 (50)

* (): Fluid: CO₂


Series **PFM7**

Dimensions

PFM7□□-C4/C6/C8/N7





(mm)	
One-touch fitting Applicable tube O.D.	A
ø4 (5/32")	64.2
ø6	64.6
ø8 (5/16")	68
ø1/4"	64.6



With rubber cover
for connector



PFM7□□-C4L/C6L/C8L/N7L





(mm)	
One-touch fitting Applicable tube O.D.	A
ø4 (5/32")	10.1
ø6	10.3
ø8 (5/16")	12
ø1/4"	10.3

Dimensions

PFM7□□-(N)01/(N)02/F01



PFM7□□-(N)01L/(N)02L/F01L



PFM

PFMV

PF2A

PF3W


PF2D

IF


Series PFM7

Dimensions

PFM7□□-F02




PFM7□□-F02L




Dimensions

PFM7□S-C4/C6/C8/N7



PFM7□S-C4L/C6L/C8L/N8L



PFM

PFMV

PF2A

PF3W


PF2D

IF


Series **PFM7**

Dimensions

PFM7□S-(N)01/(N)02/F01




PFM7□S-(N)01L/(N)02L/F01L




Dimensions

PFM7□S-F02



PFM7□S-F02L



PFM

PFMV

PF2A


PF3W

PF2D


IF

Dimensions


**Panel mount adapter/
Without flow adjustment valve/Straight**



**Panel mount adapter/
Without flow adjustment valve**




Panel Fitting Dimensions




Panel thickness 1 to 3.2 mm

Note) Piping entry direction: Minimum dimensions for bottom side piping. If using straight piping, the piping material and tubing need to be taken into consideration when designing the system. If a bend (R) is used, limit it to R3 or less.


**Panel mount adapter/
With flow adjustment valve/Straight**



**Panel mount adapter/
With flow adjustment valve**



Panel Fitting Dimensions




Panel thickness 1 to 3.2 mm


Note) Piping entry direction: Minimum dimensions for bottom side piping. If using straight piping, the piping material and tubing need to be taken into consideration when designing the system. If a bend (R) is used, limit it to R3 or less.

Dimensions


With bracket/Without flow adjustment valve




With bracket/With flow adjustment valve



DIN rail mounting



Lead wire with connector ZS-33-D



Cable Specifications of Lead Wire with Connector

Conductor	Nominal cross section area	AWG26
	External diameter	Approx. 0.50 mm
Insulation	External diameter	Approx. 1.00 mm
	Colors	Brown, White, Black, Blue
Sheath	Material	Oil-resistant PVC
Finished external diameter		ø3.5

- DIN rail (supplied by customers)
- Port size, F02: G 1/4 cannot be mounted on the DIN rail.

PFM

PFMV

PF2A

PF3W

PF2D

IF

2-Color Display Digital Flow Switch Series PFM5

Remote
sensor unit



How to Order

Remote sensor unit

PFM5 **10** **C4** **1**

Type

5 Remote sensor unit

Rated flow range (Flow rate range)

10	0.2 to 10 (5) L/min
25	0.5 to 25 (12.5) L/min
50	1 to 50 (25) L/min
11	2 to 100 (50) L/min

* (): Fluid: CO₂

Flow adjustment valve

Nil	None
S	Yes

Port size

Symbol	Description	Flow rate range			
		10	25	50	11
01	Rc1/8	●	●	●	●
02	Rc1/4	●	●	●	●
N01	NPT1/8	●	●	●	●
N02	NPT1/4	●	●	●	●
F01	G1/8 *	●	●	●	●
F02	G1/4 *	●	●	●	●
C4	ø4 (5/32") One-touch fitting	●	●	●	●
C6	ø6 One-touch fitting	●	●	●	●
C8	ø8 (5/16") One-touch fitting	●	●	●	●
N7	ø1/4" One-touch fitting	●	●	●	●

* Conforming to ISO228-1.

Piping entry direction

Nil	Straight
L	Bottom

* Different combinations of piping entry directions for IN and OUT side are available as made-to-order. (Refer to page 996.)

• **Made to Order**
(Refer to pages 977 and 996.)

• **Option 2**
(Refer to page 977.)

• **Option 1**
(Refer to page 977.)

Calibration certificate

Nil	None
A	With calibration certificate

* The certificate is written in English and Japanese. Other languages are available as specials.

Operation manual

Nil	With operation manual (Japanese and English)
N	None



Output specification

No.	Description	Applicable display unit
1	Analog output (1 to 5 V)	PFM30□
2	Analog output (4 to 20 mA)	PFM31□





Piping Variations

	With One-touch fittings (C4, C6, C8, N7)		Female thread (01, 02, N01, N02, F01, F02)	
	Straight (Nil)	Bottom (L)	Straight (Nil)	Bottom (L)
Without flow adjustment valve (Nil)				
With flow adjustment valve (S)				

Option 1

NII	W	Z
With lead wire with connector (2 m)	With lead wire with connector (2 m) + Rubber cover for connector (silicon rubber)	Without lead wire with connector
		

Option 2

NII	R	S	T
None	Bracket (For without flow adjustment valve) ZS-33-M	Bracket (For with flow adjustment valve) ZS-33-MS	Panel mount adapter (For without flow adjustment valve) ZS-33-J
			
		Piping direction: Cannot be mounted with bottom piping type.	
V			
Panel mount adapter (For with flow adjustment valve) ZS-33-JS			
			

Each option is not assembled with the product, but shipped together.

Made to Order

Symbol	Specification/Description
X693	Change of piping entry direction combination
X694	


For details, refer to pages 996 and 997.

DIN Rail Mounting Bracket (Order Separately)

ZS-33-R

Stations

1	1 station
2	2 stations
3	3 stations
4	4 stations
5	5 stations



- DIN rail (supplied by customers)
- Port size F02: G1/4 cannot be mounted on the DIN rail.

For details about the Flow Switch Precautions, refer to pages 952 and 953. For details about the Specific Product Precautions, refer to the Operation Manual at SMC website.

Specifications

Model		PFM510	PFM525	PFM550	PFM511
Applicable fluid		Dry air, N ₂ , Ar, CO ₂ (Air quality grade is JIS B8392.1-1, 1.2 to 1.6.2 and ISO 8573.1-1, 1.2 to 1.6.2.)			
Rated flow range (Flow rate range) <small>Note 1)</small>	Dry air, N ₂ , Ar	0.2 to 10 L/min	0.5 to 25 L/min	1 to 50 L/min	2 to 100 L/min
	CO ₂	0.2 to 5 L/min	0.5 to 12.5 L/min	1 to 25 L/min	2 to 50 L/min
Accuracy		±3%F.S. (Fluid: Dry air)			
Repeatability		±1%F.S. (Fluid: Dry air)			
Pressure characteristics		±5%F.S. (0.35 MPa reference)			
Temperature characteristics		±2%F.S. (15 to 35°C) ±5%F.S. (0 to 50°C)			
Operating pressure range		-100 kPa to 750 kPa			
Rated pressure range		-70 kPa to 750 kPa			
Proof pressure		1 MPa			
Analog output	Response time	50 msec or 1 s (with response time selection function: 1 s at no-voltage input)			
	Voltage output	Voltage output: 1 to 5 V Output impedance: 1 kΩ			
	Current output	Current output: 4 to 20 mA Max. load impedance: 600 Ω, Min. load impedance: 50 Ω			
Status LED's		Power ON indicator: Lights when power is turned on (Green). Flow rate indicator: Flashes when flow is applied (Green).			
Power supply voltage		24 VDC ±10%			
Current consumption		35 mA or less			
Environment	Enclosure	IP40			
	Operating fluid temperature	0 to 50°C (with no freezing and condensation)			
	Operating temperature range	Operating: 0 to 50°C Stored: -10 to 60°C (with no freezing and condensation)			
	Operating humidity range	Operating, Stored: 35 to 85%R.H. (with no condensation)			
	Withstand voltage	1000 VAC for 1 minute between terminals and housing			
	Insulation resistance	50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing			
Standards		CE UL, CSA RoHS			

Note 1) Flow rate unit is based on standard conditions (20°C, 1 atm, 65% RH).


Note 2) For details about wiring and thread type, refer to the Operation Manual that can be downloaded from SMC website (<http://www.smworld.com>).

Piping Specifications/Weight

Part no.	01	02	N01	N02	F01	F02	C4	C6	C6	N7
Port size	Rc 1/8	Rc 1/4	NPT 1/8	NPT 1/4	G1/8	G1/4	ø4 (5/32") One-touch fitting	ø6 One-touch fitting	ø8 (5/16") One-touch fitting	ø1/4" One-touch fitting
Weight	Straight Bottom Straight Bottom	Straight Bottom Straight Bottom	Without orifice: 95 g Without orifice: 105 g With orifice: 135 g With orifice: 145 g	Without orifice: 95 g Without orifice: 105 g With orifice: 135 g With orifice: 145 g	Straight Bottom Straight Bottom	Straight Bottom Straight Bottom	Without orifice: 125 g Without orifice: 135 g With orifice: 165 g With orifice: 175 g	Straight Bottom Straight Bottom	Without orifice: 55 g Without orifice: 65 g With orifice: 95 g With orifice: 105 g	Without orifice: 55 g Without orifice: 65 g With orifice: 95 g With orifice: 105 g
Wetted parts material	LCP, PBT, Brass (Electroless nickel plating), HNBR (+ Fluoro coated), FKM (+ Fluoro coated), Silicon, Au, Stainless steel 304									

Analog Output


Note) Analog output at maximum rated flow rate when CO₂ is selected is 4.57 [V]
for the voltage output type and 18.28 [mA] for the current output type.



Analog Voltage Output (1 to 5 V)

Model	Max. rated flow value [L/min]
PFM510-□-1	10 (5)
PFM525-□-1	25 (12.5)
PFM550-□-1	50 (25)
PFM511-□-1	100 (50)

* () : Fluid: CO₂



Analog Current Output (4 to 20 mA)

Model	Max. rated flow value [L/min]
PFM510-□-2	10 (5)
PFM525-□-2	25 (12.5)
PFM550-□-2	50 (25)
PFM511-□-2	100 (50)

* () : Fluid: CO₂

PFM

PFMV

PF2A

PF3W



PF2D

IF


Series PFM5

Dimensions

PFM5□□-C4/C6/C8/N7





(mm)	
One-touch fitting Applicable tube O.D.	A
ø4 (5/32")	64.2
ø6	64.6
ø8 (5/16")	68
ø1/4"	64.6



With rubber cover for connector



PFM5□□-C4L/C6L/C8L/N7L





(mm)	
One-touch fitting Applicable tube O.D.	A
ø4 (5/32")	10.1
ø6	10.3
ø8 (5/16")	12
ø1/4"	10.3

Dimensions

PFM5□□-(N)01/(N)02/F01



PFM5□□-(N)01L/(N)02L/F01L



PFM

PFMV

PF2A

PF3W


PF2D

IF


Series PFM5

Dimensions

PFM5□□-F02




PFM5□□-F02L




Dimensions

PFM5□S-C4/C6/C8/N7



PFM5□S-C4L/C6L/C8L/N8L



PFM

PFMW

PF2A


PF3W

PF2D


IF

Dimensions

PFM5□S-(N)01/(N)02/F01




PFM5□S-(N)01L/(N)02L/F01L




Dimensions

PFM5□S-F02



PFM5□S-F02L



PFM

PFMV

PF2A


PF3W

PF2D


IF

Dimensions


Panel mount adapter/Without flow adjustment valve/Straight



Panel mount adapter/Without flow adjustment valve




Panel Fitting Dimensions




Panel thickness 1 to 3.2 mm

Note) Piping entry direction: Minimum dimensions for bottom side piping. If using straight piping, the piping material and tubing need to be taken into consideration when designing the system. If a bend (R) is used, limit it to R3 or less.


Panel mount adapter/With flow adjustment valve/Straight



Panel mount adapter/With flow adjustment valve



Panel Fitting Dimensions




Panel thickness 1 to 3.2 mm


Note) Piping entry direction: Minimum dimensions for bottom side piping. If using straight piping, the piping material and tubing need to be taken into consideration when designing the system. If a bend (R) is used, limit it to R3 or less.

Dimensions

With bracket/Without flow adjustment valve




DIN rail mounting




- DIN rail (supplied by customers)
- Port size, F02: G1/4 cannot be mounted on the DIN rail.

With bracket/With flow adjustment valve



**Lead wire with connector
ZS-33-D**



Cable Specifications of Lead Wire with Connector

Conductor	Nominal cross section area	AWG26
	External diameter	Approx. 0.50 mm
Insulation	External diameter	Approx. 1.00 mm
	Colors	Brown, White, Black, Blue
Sheath	Material	Oil-resistant PVC
Finished external diameter		ø3.5

* Connects to the PFM3□□ series.

PFM

PFMV

PF2A

PF3W

PF2D


IF

Series PFM7/PFM5


Common Specifications

Pressure Loss (Pressure: 0.35 [MPa])


PFM710, 510 / For 10 (L/min)




PFM725, 525 / For 25 (L/min)



PFM750, 550 / For 50 (L/min)




PFM711, 511 / For 100 (L/min)




Flow Characteristics


PFM710, 510 / For 10 (L/min)




PFM725, 525 / For 25 (L/min)




PFM750, 550 / For 50 (L/min)



PFM711, 511 / For 100 (L/min)



Wetted parts construction



Component Parts


No.	Description	Material	Note
1	Fitting for piping	Brass	Electroless nickel plating
2	O-ring	FKM	Fluoro coated
3	O-ring	HNBR	Fluoro coated
4	Rectifying module	Stainless steel 304	
5	Body	PBT	
6	Sensor housing	LCP	
7	Sensor chip	Silicon	
8	Orifice	Brass	Electroless nickel plating
9	Seal	FKM	Fluoro coated
10	Mesh	Stainless steel 304	
11	Bottom piping adapter	PBT	
12	O-ring	HNBR	Fluoro coated
13	Flow adjustment valve assembly	PBT	
14	Body B	Brass	Electroless nickel plating
15	Needle	Brass	Electroless nickel plating
16	O-ring	HNBR	Fluoro coated
17	O-ring	HNBR	Fluoro coated

Detection Principle

This MEMS sensor chip consists of upstream temperature measuring sensor (Ru) and downstream temperature measuring sensor (Rd), which are placed symmetrically from the center of a platinum thin film coated heater (Rh) mounted on a membrane, and an ambient temperature sensor (Ra) for measuring gas temperature.


The principle is shown as the diagram on the right. (a) When the gas is static, the temperature distribution of heated gas centered around Rh is uniform, and Ru and Rd have the same resistance. (b) When the gas flows from the left side, it upsets the balance of the temperature distribution of heated gas, and the resistance of Rd becomes greater than that of Ru.

The difference in resistance between Ru and Rd is proportional to the flow velocity, so measurement and analysis of the resistance can show the flow direction and velocity of the gas. Ra is used to compensate the gas and/or ambient temperature.


PFM
PFMV
PF2A
PF3W
PF2D
IF

Component Parts

No.	Description	Model
1	Body	
2	Lead wire with connector (2 m)	ZS-33-D
3	Rubber cover for connector (silicon rubber)	ZS-33-F
4	IN side Bottom piping adapter (with pin)	ZS-33-P1L
5	OUT side Bottom piping adapter (with pin)	ZS-33-P2L
6	For straight piping Flow adjustment valve assembly (with pin)	For 10 L/min ZS-33-10N
		For 25 L/min ZS-33-25N
		For 50 L/min ZS-33-50N
		For 100 L/min ZS-33-11N
7	For bottom piping Flow adjustment valve assembly (with pin)	For 10 L/min ZS-33-10NL
		For 25 L/min ZS-33-25NL
		For 50 L/min ZS-33-50NL
		For 100 L/min ZS-33-11NL
8	One-touch fitting	ø4 (5/32") ZS-33-C4
		ø6 ZS-33-C6
		ø8 (5/16") ZS-33-C8
		ø1/4" ZS-33-N7
9	Female thread	Rc 1/8 ZS-33-01
		NPT 1/8 ZS-33-N01
		G 1/8 ZS-33-F01
		Rc 1/4 ZS-33-02
		NPT 1/4 ZS-33-N02
		G 1/4 ZS-33-F02



⚠ Caution

- ① The accuracy could change by 2 to 3% when the piping is removed or replaced.

The repeatability accuracy is $\pm 1\%$ F.S. when piping is replaced with piping of the same size. However, the accuracy could change by 2 to 3% if the size is different or when changing from straight to elbow or from elbow to straight piping.

Flow Sensor Monitor Series PFM3



How to Order



Output specification

0	2 NPN outputs + 1 to 5 V output
1	2 NPN outputs + 4 to 20 mA output
2	2 NPN outputs + External input ^{Note)}
3	2 PNP outputs + 1 to 5 V output
4	2 PNP outputs + 4 to 20 mA output
5	2 PNP outputs + External input ^{Note)}

Note) User can select from accumulated value external reset, auto-shift and auto-shift zero.

PFM3 0 0 - M L

Type

3	Remote display unit
---	---------------------

Input specification

Symbol	Content	Applicable remote type sensor unit
0	Voltage input	PFM5□□(S)-□-1-□
1	Current input	PFM5□□(S)-□-2-□


Unit specification

Nil	With unit switching function
M	Fixed SI unit ^{Note)}

Note) Fixed unit: Instantaneous flow rate: L/min
Accumulated flow: L

Option 1

Nil	None
L	Power supply/Output connector



Note) Cable is not connected, but shipped together.

Operation manual

Nil	With operation manual (Japanese and English)
N	None


Calibration certificate

Nil	None
A	With calibration certificate

* The certificate is written in English and Japanese.
Other languages are available as specials.

Option 3




Nil	None
F	With sensor connector



Note) Connector is not connected, but shipped together.

Option 2

Nil	None
E	Bracket
B	Panel mount adapter
D	Panel mount adapter + Front protective cover



Note) Options are not assembled, but shipped together.

Option/Part No.

Description	Part no.	Note
Power supply/Output connector (2 m)	ZS-28-A	
Bracket	ZS-28-B	With M3 x 5 L (2 pcs.)
Sensor connector	ZS-28-C-1	1 pc.
Panel mount adapter	ZS-27-C	With M3 x 8 L (2 pcs.)
Panel mount adapter + Front protective cover	ZS-27-D	With M3 x 8 L (2 pcs.)

PFM
PFMV
PF2A
PF3W
PF2D
IF

For details about the Flow Switch Precautions, refer to pages 952 and 953. For details about the Specific Product Precautions, refer to the Operation Manual at SMC website.

Specifications

Model		PFM3□□			
Rated flow range (Flow rate range)	Dry air, N ₂ , Ar	0.2 to 10 L/min	0.5 to 25 L/min	1 to 50 L/min	2 to 100 L/min
	CO ₂	0.2 to 5 L/min	0.5 to 12.5 L/min	1 to 25 L/min	2 to 50 L/min
Displayable range <small>Note 1)</small>	Dry air, N ₂ , Ar	0.2 to 10.5 L/min	0.5 to 26.3 L/min	1 to 52.5 L/min	2 to 105 L/min
	CO ₂	0.2 to 5.2 L/min	0.5 to 13.1 L/min	1 to 26.2 L/min	2 to 52 L/min
Settable range <small>Note 1)</small>	Dry air, N ₂ , Ar	0 to 10.5 L/min	0 to 26.3 L/min	0 to 52.5 L/min	0 to 105 L/min
	CO ₂	0 to 5.2 L/min	0 to 13.1 L/min	0 to 26.2 L/min	0 to 52 L/min
Minimum unit setting <small>Note 2)</small>		0.01 L/min	0.1 L/min	0.1 L/min	0.1 L/min
Accumulated pulse flow rate exchange value		0.1 L/pulse	0.1 L/pulse	0.1 L/pulse	1 L/pulse
Indication unit <small>Note 3)</small>		Instantaneous flow rate L/min, CFM x 10 ⁻² Accumulated flow L, ft ³ x 10 ⁻¹			
Accumulated flow range <small>Note 4)</small>		1999999 L			
Power supply voltage		24 VDC ±10% (With polarity protection)			
Current consumption		50 mA or less			
Sensor input		PFM30□: Voltage input 1 to 5 VDC (input impedance: 1 MΩ)			
Number of inputs: 1		PFM31□: Current input 4 to 20 mA DC (input impedance: 250 Ω)			
Hysteresis <small>Note 5)</small>		Hysteresis mode: Variable, Window comparator mode: Variable			
Switch output		NPN or PNP open collector output: 2 outputs Maximum load current: 80 mA, max. load voltage 30 VDC (at NPN output), Residual voltage 1 V or less (at load current 80 mA), With short-circuit protection			
Accumulated pulse output		NPN or PNP open collector output (Same as switch output)			
Response time		1 s (50 ms, 0.5 s, 2 s can be selected.)			
Repeatability		±0.1%F.S., Analog output accuracy: ±0.3%F.S.			
Analog output		Voltage output: 1 to 5 VDC (0 L/min to max. rated flow rate value) Output impedance: Approx. 1 kΩ, Accuracy: ±1%F.S. (relative to display value) Current output: 4 to 20 mA DC (0 L/min to max. rated flow rate value) Max. load impedance: 600 Ω (at 24 VDC), Min. load impedance: 50 Ω Accuracy: ±1%F.S. (relative to display value)			
Display accuracy		±0.5%F.S. ±1 digit			
Display method		3+1/2-digit, 7-segment LED 2-color display (Red/Green) Sampling cycle: 10 times/sec			
Status LED's		OUT1: Lights up when output is turned ON (Green). OUT2: Lights up when output is turned ON (Red).			
External input <small>Note 6)</small>		No-voltage input (Reed or Solid state), LOW level input 30 msec or more, LOW level 0.4 V or less			
Enclosure		IP40			
Operating temperature range		Operating: 0 to 50°C Stored: -10 to 60°C (with no freezing and condensation)			
Operating humidity range		Operating, Stored: 35 to 85%R.H. (with no condensation)			
Withstand voltage		1000 VAC for 1 minute between terminals and housing			
Insulation resistance		50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing			
Temperature characteristics		±0.5%F.S. (25°C reference)			
Standards		CE UL, CSA RoHS			
Connection		Power supply/Output connection: 5P connector, Sensor connection: 4P connector			
Material		Front case, Rear case: PBT			
Weight		30 g (Without cable) 85 g (With cable)			

Note 1) Select the sensor to connect in the initial setting. If CO₂ is selected as the operating fluid, the value is 1/2 on the maximum side.

Note 2) When 10 L/min with a minimum unit setting of 0.01 L/min is selected for the connected sensor, the upper limit of the display range is 10.50 L/min.

When 100 L/min with a minimum unit setting of 0.1 L/min is selected for the connected sensor, the upper limit of the display range is 105.0 L/min.

The setting at the time of shipment is 10 L/min with a minimum unit setting of 0.1 L/min for the connected sensor.

Note 3) When equipped with a unit switching function. (The SI unit (L/min or L) is fixed for types with no unit switching function.)

Note 4) The accumulated flow value is cleared to 0 when power is turned off. It is possible to select function that holds the accumulated flow value so it is not cleared. (The accumulated flow value can be held at 2- or 5-minute intervals.) The service life of the memory element (electronic component) is limited to 1 million overwrite cycles (assuming 24-hour operation, 5 minutes x 1 million cycles = 9.5 years) when 5-minute intervals are selected. Therefore, when using the holding function, calculate the service life based on the usage conditions, and use the switch within the service life. Applies to models equipped with a unit switching function. (The SI unit (L/min or L) is fixed for types with no unit switching function.)

Note 5) Set to hysteresis mode at the time of shipment from the factory. Can be changed to window comparator mode using push-buttons.


Note 6) Accumulated external reset function at the time of shipment from the factory. Auto-shift or auto-shift zero function can be selected using push-buttons.

Note 7) For details about wiring and thread type, refer to the Operation Manual that can be downloaded from SMC website (<http://www.smworld.com>).


Analog Output

Note: Analog output at maximum rated flow rate when CO₂ is selected is 3 [V] for the voltage output type and 12 [mA] for the current output type.

1 to 5 VDC




4 to 20 mA DC



Rated flow range	Max. rated flow value [L/min]
0.2 to 10 L/min	10 (5)
0.5 to 25 L/min	25 (12.5)
1 to 50 L/min	50 (25)
2 to 100 L/min	100 (50)


* () : Fluid: CO₂

Dimensions




Sensor connector (ZS-28-C-1)

Pin no.	Terminal name
1	DC (+)
2	N.C.
3	DC (-)
4	IN*



* 1 to 5 V or 4 to 20 mA

With bracket



PFM

PFMV


PF2A

PF3W


PF2D

IF

With panel mount adapter




With panel mount adapter + Front protective cover




Dimensions

Panel fitting dimensions

Secure mounting of n (2 or more) switches (horizontal)




Secure mounting of n (2 or more) switches (vertical)



Note) If a bend (R) is used, limit it to R2 or less.

Power supply/Output connector (ZS-28-A)



Cable Specifications

Conductor	Nominal cross section area	0.2 mm ²
	External diameter	0.58 mm
Insulation	External diameter	Approx. 1.12 mm
	Colors	Brown, Black, White, Gray, Blue
Sheath	Material	Oil-resistant PVC
Finished external diameter		ø4.1

Series PFM

Function Details

■ Output operation

The output operation can be selected from the following:
Output (hysteresis mode and window comparator mode)
corresponding to instantaneous flow rate,
Output corresponding to accumulated flow,
Accumulated output pulse output

At the time of shipment from the factory, it is set to hysteresis mode and normal output.

■ Indication color

The indication color can be selected for each output condition. The selection of the indication color provides visual identification of abnormal values. (The indication color depends on OUT1 setting.)

Green for ON, Red for OFF
Red for ON, Green for OFF
Red all the time
Green all the time

■ Selection of operating fluid

The fluid can be selected. If argon (Ar) or carbon dioxide (CO₂) is used, the setting needs to be changed.

Dry air, N ₂
Argon
CO ₂

(Note) When CO₂ is selected, the upper limit of the measured flow rate range will be 1/2 of that for other fluids.

■ Selection of indication unit reference

The indication unit reference can be selected between standard conditions and normal conditions.

Standard conditions: Flow rate converted to a volume at 20°C and 1atm (atmosphere)
Normal conditions: Flow rate converted to a volume at 0°C and 1atm (atmosphere)

■ Setting of response time

The flow rate may change momentarily during transition between ON (open) and OFF (closed) of the valve. It can be set so that this momentary change is not detected.

0.05 sec.
0.5 sec.
1 sec.
2 sec.

<Principle>

When the switch has been in ON area for a set period of time, the output will turn on (or off).

■ Indication mode

The indication mode can be selected between instantaneous flow rate and accumulated flow.

Instantaneous flow rate display
Accumulated flow display

■ External input function

The external input function can be selected from accumulated value external reset, auto-shift and auto-shift zero.

(Input signal: Connect input line to GND for 30 ms or more.)

External reset: This function resets the accumulated value to "0" when an input signal is applied.

Auto-shift: This function generates an output corresponding to the change in relation to instantaneous flow rate when an input signal is applied.


Auto-shift zero: This function displays instantaneous flow rate as "0" when a positive input signal is applied in the auto shift function described above.

Set values and flow rates that are relatively on the negative side are expressed by illumination of the decimal point on the far left.

■ External input wiring example


PFM3□2

NPN open collector output with external input: 2 outputs



PFM3□5

PNP open collector output with external input: 2 outputs



■ Indication resolution

The indication resolution of the PFM710 and 711 series can be changed to enable values to be indicated in smaller steps.

100 resolution	PFM710 PFM711	by 0.1 L/min by 1 L/min
1000 resolution	PFM710 PFM711	by 0.01 L/min by 0.1 L/min

■ Accumulated value hold

Accumulated value is not cleared even when the power supply is turned off.

The accumulated value is memorized every 2 or 5 min. during measurement, and continues from the last memorized value when the power supply is turned on again.

The life time of the memory element is 1 million access cycles. Take this into consideration before using this function.

■ Selection of analog output filter

This selection is available when using a product with an analog output. A signal with fast response speed can be generated by turning off the analog output filter.

■ Selection of power-saving mode

The power-saving mode can be selected.

With this function, if no buttons are pressed for 30 sec., it shifts to power-saving mode.

At the time of shipment from the factory, the product is set to the normal mode (the power-saving mode is turned off).

(When power-saving mode is activated, the decimal point flashes.)

■ Setting of secret code

The user can select whether a secret code must be entered to release key lock.

At the time of shipment from the factory, it is set such that the secret code is not required.

■ Peak/Bottom value indication

The maximum (minimum) flow rate is detected and updated from when the power supply is turned on. In peak (bottom) value indication mode, this maximum (minimum) flow rate is displayed.

■ Keylock function

Prevents operation errors such as accidentally changing setting values.

■ Zero-clear function

Allows the user to adjust the measured flow rate indication to zero. The adjustment range is $\pm 7\%$ F.S. of the initial factory setting.

■ Error indication function

When an error or abnormality arises, the location and contents are displayed.

Description	Contents	Action
Flow rate error	The flow rate exceeds the upper limit of indicated flow rate range.	Decrease the flow rate.
	There is a reverse flow equivalent to -5% or more.	Turn the flow to correct direction.
Overcurrent error	Load current of 80 mA or more is applied to the switch output (OUT1).	Eliminate the cause of the overcurrent by turning off the power supply and then turn on it again.
	Load current of 80 mA or more is applied to the switch output (OUT2).	
System error	Possibility of internal circuit damage before factory adjustment.	Stop operation immediately and contact SMC.
	System error. Possibility of data memorizing failure or internal circuit damage.	Reset the unit, and carry out all settings again.
Zero-clear error	If zero-clear is performed (by holding down and buttons simultaneously for 1 sec.) while there is some flow, "Err4" will be displayed for 1 sec.	Perform zero-clear of accumulated flow rate when there is no flow.
Flow rate error	The flow rate exceeds the accumulated flow rate range.	Clear the accumulated flow rate. (This error does not matter when the accumulated flow rate is not being used.)

If the failure cannot be solved after the above instructions are performed, please contact SMC for investigation.

Please contact SMC for detailed specifications, lead times and prices.



X693, X694

- **Type**

5	Remote sensor unit
7	Integrated display

- **Piping entry direction**


Note) No symbol is entered.

- **Changing the piping entry direction combination**


X693	IN side: Straight/OUT side: Bottom
X694	IN side: Bottom/OUT side: Straight

For details of How to Order, refer to pages 964 and 976.

PFM₅⁷□□-C4/C6/C8/N7-□-X693




PFM₅⁷□□-C4/C6/C8/N7-□-X694




One-touch fitting Applicable tube O.D.		A	B
C4	ø4 (5/32")	10.1	8.1
C6	ø6	10.3	8.3
C8	ø8 (5/16")	12	10
N7	ø1/4	10.3	8.3

PFM⁷₅□□-□01/02-□-X693



PFM⁷₅□□-□01/02-□-X694



Port size	A	B	C (Width across flats)
Rc 1/8, 1/4 NPT 1/8, 1/4 G 1/8	13	11	17
G 1/4	17	15	21

Series PFM7/PFM5


Made to Order 2

Please contact SMC for detailed specifications, lead times and prices.




Dimensions

PFM₅□□S-C4/C6/C8/N7-□-X693




One-touch fitting Applicable tube O.D.	A	B
ø4 (5/32")	10.1	8.1
ø6	10.3	8.3
ø8 (5/16")	12	10
ø1/4	10.3	8.3

PFM₇□□S-C4/C6/C8/N7-□-X694




One-touch fitting Applicable tube O.D.	A	B
ø4 (5/32")	10.1	36.1
ø6	10.3	36.3
ø8 (5/16")	12	37
ø1/4	10.3	36.3

PFM₅□□S-□01/02-□-X693



Port size	A	B	C (Width across flats)
Rc 1/8, 1/4 NPT 1/8, 1/4 G 1/8	13	11	17
G 1/4	17	15	21

PFM₇□□S-□01/02-□-X694



Port size	A	B	C (Width across flats)
Rc 1/8, 1/4 NPT 1/8, 1/4 G 1/8	13	39	17
G 1/4	17	43	21

PFM

PFMV

PF2A

PF3W

PF2D

IF

Series PFM7/PFM5

Made to Order 3

Please contact SMC for detailed specifications, lead times and prices.



Symbol

2 Compatibility with Argon (Ar) and Carbon Dioxide (CO₂) Mixed Gas

X731

The argon-carbon dioxide gas ratio (Ar: CO₂) can be selected using the push-buttons from among the following: 92 : 8, 90 : 10, 80 : 20, 70 : 30, and 60 : 40. Dimensions are same as those of standard models.

PFM 7 ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ -X731


7 Integrated display

For details of How to Order, refer to pages 964 and 976.

Model	Gas ratio		Rated flow range	Displayable range	Settable range	Max. analog output	
	Ar	CO ₂				Voltage (Vmax)	Current (Imax)
PFM710	92%	8%	0.2 to 7.0 L/min	0.2 to 7.4 L/min	0 to 7.4 L/min	3.80 V	15.2 mA
	90%	10%					
	80%	20%					
	70%	30%					
	60%	40%					
PFM725	92%	8%	0.5 to 25.0 L/min	0.5 to 26.3 L/min	0 to 26.3 L/min	5.00 V	20.0 mA
	90%	10%	0.5 to 20.0 L/min	0.5 to 21.0 L/min	0 to 21.0 L/min	4.20 V	16.8 mA
	80%	20%					
	70%	30%					
	60%	40%					
PFM750	92%	8%	1.0 to 50.0 L/min	1.0 to 52.5 L/min	0 to 52.5 L/min	5.00 V	20.0 mA
	90%	10%	1.0 to 40.0 L/min	1.0 to 42.0 L/min	0 to 42.0 L/min	4.20 V	16.8 mA
	80%	20%					
	70%	30%					
	60%	40%					
PFM711	92%	8%	2 to 100 L/min	2 to 105 L/min	0 to 105 L/min	5.00 V	20.0 mA
	90%	10%	2 to 90 L/min	2 to 95 L/min	0 to 95 L/min	4.60 V	18.4 mA
	80%	20%					
	70%	30%	2 to 80 L/min	2 to 84 L/min	0 to 84 L/min	4.20 V	16.8 mA
	60%	40%					

Output characteristics using mixed gas

Analog voltage output (1 to 5 V)



Analog current output (4 to 20 mA)

