

3 Port Solenoid Valve


Series **VQZ100/200/300**

Metal Seal

Rubber Seal




Power consumption: **0.35 w / 0.9 w**
 (Standard)
 (High pressure type,
 High speed response type)



Compact, High Flow

Series	Valve width (mm)	Flow characteristics	
		Metal seal C [dm ³ /(s·bar)]	Rubber seal C [dm ³ /(s·bar)]
Body ported	VQZ100	10	—
	VQZ200	15	1.3
	VQZ300	18	2.4
Base mounted	VQZ100	10	—
	VQZ200	15	2.0
	VQZ300	18	3.2












- SYJ**
- VQZ**
- VP**
- VG**
- VP3**

Metal Seal / Rubber Seal 3 Port Solenoid Valve


VQZ100/200/300

Solenoid Valve Variations

		Sonic conductance C [dm ² /(s·bar)]		Type of actuation	Voltage	Electrical entry	Light/Surge voltage suppressor	Manual override
Body ported	3 port	VQZ100	Metal — Rubber (Poppet) 0.56					
		 P.1792						
		VQZ200	1.3 1.7			Grommet (G)		
Base mounted	3 port	VQZ300	2.4 3.0	 N.C.	(Standard) 12 VDC 24 VDC	L-type plug connector (L)	With light/surge voltage suppressor	Non-locking push type (Tool required)
		 P.1793						
		VQZ100	Metal — Rubber (Poppet) 1.0	 N.O. (Except VQZ100)	(Option) 100 VAC 200 VAC 110 VAC 220 VAC	M-type plug connector (M)	L-type plug connector (L)	
Base mounted	3 port	VQZ200	2.0 3.0				M-type plug connector (M)	Locking type (Tool required)
		 P.1809				DIN terminal (Y)	DIN terminal (YZ) (Except VQZ100)	
		VQZ300	3.2 4.1			 (Except VQZ100)		
		 P.1809						

Manifold


Body Ported



P.1799

Series	Base model	Piping specifications			Applicable solenoid valve	Applicable stations
		Piping direction	Bore size			
			1(P), 3(R)	2(A)		
VQZ100	VV3QZ12-□□□	Top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations
VQZ200	VV3QZ22-□□□	Top	Rc 1/8	C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ2□2	2 to 20 stations
VQZ300	VV3QZ32-□□□	Top	Rc 1/4	C6 (for ø6) C8 (for ø8) C10 (for ø10) Rc 1/4	VQZ3□2	2 to 20 stations

Base Mounted




P.1815

Series	Base model	Piping specifications			Applicable solenoid valve	Applicable stations
		Piping direction	Bore size			
			1(P), 3(R)	2(A)		
VQZ100	VV3QZ15-□□□	Side/top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations
VQZ200	VV3QZ25-□□□	Side	Rc 1/4	C4 (for ø4) C6 (for ø6) C8 (for ø8) Rc 1/8	VQZ2□5	2 to 20 stations
VQZ300	VV3QZ35-□□□	Side	1(P) port Rc 3/8 3(R) port Rc 1/4	C6 (for ø6) C8 (for ø8) C10 (for ø10) Rc 1/4	VQZ3□5	2 to 20 stations

Manifold Options

Body Ported


Blanking plate assembly
VVQZ100-10A-5
(for VQZ100)
VVQZ200-10A-2
(for VQZ200)
VVQZ300-10A-2
(for VQZ300)



P.1805

Blanking plug


KQ2P-23
KQ2P-04
KQ2P-06
KQ2P-08
KQ2P-10



P.1805


DIN rail

AXT100-DR-□



P.1805


Silencer
(for EXH port)



P.1805

Base Mounted


Blanking plate assembly
VVQZ100-10A-5
(for VQZ100)
VVQZ200-10A-5
(for VQZ200)
VVQZ300-10A-5
(for VQZ300)



P.1822

Blanking plug


KQ2P-23
KQ2P-04
KQ2P-06
KQ2P-08
KQ2P-10



P.1822


DIN rail

AXT100-DR-□



P.1822

Silencer
(for EXH port)



P.1822

Port plug
VVQZ100-CP (for VQZ100)



P.1822

SYJ

VQZ

VP

VG

VP3

Body Ported

Plug Lead Unit

3 Port Solenoid Valve

Series VQZ100/200/300

Single Unit



[Option]

Note) CE-compliant:DC type only.


VQZ100 / How to Order Valve

VQZ 1 1 5 - 5 M 1 - C6 - PR -

Series

1 VQZ100 body width 10 mm

Type of actuation



Body type

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) Note 3)	Note 3)
K Note 1)	High pressure type	(0.9 W)	—
R Note 1, 2)	External pilot type		
KR Note 1, 2)	High pressure/External pilot type	(0.9 W)	—

Note 1) Semi-standard

Note 2) For details on external pilot type, refer to page 1806.

Note 3) For AC specification power consumption, refer to page 1794.



Caution
Use standard (DC) specification for continuous duty.

Coil voltage

		CE-compliant
1	100 VAC (50/60 Hz)	—
2	200 VAC (50/60 Hz)	—
3	110 VAC (115 VAC) (50/60 Hz)	—
4	220 VAC (230 VAC) (50/60 Hz)	—
5	24 VDC	●
6	12 VDC	●


CE-compliant

Nil	—
Q	CE-compliant

Note) DC type only.

Option

Nil: None
F: With bracket




Port size [2(A) port]

C3	ø3.2 One-touch fitting
C4	ø4 One-touch fitting
C6	ø6 One-touch fitting
M5	M5 thread (Replaceable type)

Note) For inch size One-touch fittings, refer to page 1806.

Manual override

Nil: Non-locking push type
B: Locking type (Tool required)



Electrical entry

G: Grommet (DC specification)	L: L-type plug connector with lead wire	LO: L-type plug connector without connector	M: M-type plug connector with lead wire	MO: M-type plug connector without connector
	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor

Note) Standard lead wire length: 300 mm

Note) For applicable One-touch fitting and silencer models for this valve series, refer to page 1828.

VQZ200/300 / How to Order Valve



Made to Order

(For details, refer to pages 1794 and 1825.)

Note) AC-type models that are CE-compliant have DIN terminals only.



VQZ 2 1 2 - 5 M 1 - C6 - -

Series

2	VQZ200 body width 15 mm
3	VQZ300 body width 18 mm

Type of actuation

	N.C.	2(A)	
1		(R)3 1(P)	Metal seal
2		(R)3 1(P)	Metal seal
3		(R)3 1(P)	Rubber seal
4		(R)3 1(P)	Rubber seal

Body type

2	Body ported
---	-------------

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) Note 3)	○
B Note 1)	High speed response type	(0.9 W)	—
K Note 1)	High pressure type (Metal seal type only)	(0.9 W)	—
R Note 1, 2)	External pilot type	○	○
BR Note 1, 2)	High speed response/External pilot type	(0.9 W)	—
KR Note 1, 2)	High pressure/External pilot type (Metal seal type only)	(0.9 W)	—

Note 1) Semi-standard

Note 2) For details on external pilot type, refer to page 1806.

Note 3) For AC specification power consumption, refer to page 1794.



Caution
Use standard (DC) specification for continuous duty.

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

Note) For applicable One-touch fitting and silencer models for this valve series, refer to back page 1828.

IP65 compliant

Nil	—
W Note)	Compliant

Note) VQZ200/300 DIN terminal rubber seal only (except external pilot). For details on IP65 enclosure, refer to page 1806.


CE-compliant

Nil	—
Q	CE-compliant

Note) AC-type models that are CE-compliant have DIN terminals only.

Option

Nil: None
F: With bracket



Port size [2(A) port]

Symbol	Port size	VQZ200	VQZ300
C4	ø4 One-touch fitting	○	—
C6	ø6 One-touch fitting	○	○
C8	ø8 One-touch fitting	—	○
C10	ø10 One-touch fitting	—	○
M5	M5 thread	○	—
O2	Rc 1/4	—	○

Note) For inch size One-touch fittings and option thread type, refer to page 1806.

Manual override

Nil: Non-locking push type (Tool required)	B: Locking type (Tool required)

Electrical entry

	G: Grommet (DC specification)	L: L-type plug connector with lead wire	LO: L-type plug connector without connector	M: M-type plug connector with lead wire	MO: M-type plug connector without connector
	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor
CE-compliant	AC	—	—	—	—
	DC	●	●	●	●
	Y: DIN terminal	YO: DIN terminal without connector	YZ: DIN terminal	YOS: DIN terminal without connector (DC specification)	YS: DIN terminal (DC specification)
	With surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor
CE-compliant	AC	●	●	—	—
	DC	●	●	●	●

Note 1) Standard lead wire length: 300 mm

Note 2) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.

SYJ


VQZ

VP

VG

VP3

Specifications



Valve construction	Metal seal	Rubber seal	VQZ100 (Poppet seal)
Fluid	Air, Inert gas		
Max. operating pressure (MPa)	0.7 (High pressure type: 1.0)	0.7	0.7 (High pressure type: 1.0)
Min. operating pressure (MPa)	0.1	0.15	0.15
Ambient and fluid temperature (°C)	-10 to 50 (No freezing)		
Max. operating frequency (Hz)	20	5	20
Pilot exhaust method	Individual exhaust		Common exhaust ^{Note 1)}
Lubrication	Not required		
Manual override	Push type, Locking type (Tool required)		
Mounting orientation	Free		
Impact/Vibration resistance (m/s²) ^{Note 2)}	150/30		
Enclosure*	Dustproof (DIN terminal: IP65 ^{Note 3)})		

* Based on IEC60529

Note 1) When using body ported type as a single unit, the individual exhaust is used.

Note 2) Impact resistance: No malfunction occurred when it is tested with a drop tester in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Value in the initial state)

Vibration resistance: No malfunction occurred in one sweep test between 45 and 2000 Hz. Test was performed to axis and right angle directions of the main valve and armature when pilot signal is ON and OFF. (Value in the initial state)

Note 3) When IP65 compliant DIN terminals are selected: VQZ²□□-□Y□□W1-□□

Solenoid Specifications

Semi-standard Specifications

High speed response type
High pressure type (Metal seal type only)
External pilot type*

* For details on external pilot type, refer to page 1806.



Made to Order
(For details, refer to page 1825.)

Symbol	Description
X30	Pilot valve common exhaust
X90	Main valve fluororubber
X113	All fluororubber

Electrical entry		Grommet (G)		M-type plug connector (M)	
		L-type plug connector (L)		DIN terminal (Y)	
		G, L, M		Y	
Coil rated voltage (V)	DC	24, 12			
	AC 50/60 Hz	100, 110, 200, 220*			
Allowable voltage fluctuation		±10% of rated voltage*			
Power consumption (W)	DC	Standard	0.35 [(With light: 0.4 (DIN terminal with light: 0.45))]		
		High speed response, high pressure	0.9 [(With light: 0.95 (DIN terminal with light: 1.0))]		
Apparent power (VA) ⁺	AC	100 V	0.78 (With light: 0.81)	0.78 (With light: 0.87)	
		110 V	0.86 (With light: 0.89)	0.86 (With light: 0.87)	
		[115 V]	[0.94 (With light: 0.97)]	[0.94 (With light: 1.07)]	
		200 V	1.18 (With light: 1.22)	1.15 (With light: 1.30)	
		220 V	1.30 (With light: 1.34)	1.27 (With light: 1.46)	
		[230 V]	[1.42 (With light: 1.46)]	[1.39 (With light: 1.60)]	
Surge voltage suppressor		Varistor			
Indicator light		LED (Neon light when AC with DIN terminal)			

* In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC.

* For 115 VAC and 230 VAC, the allowable voltage is -15% to +5% of rated voltage.

Flow Characteristics

Series	Valve construction	Model		Flow characteristics						Response time (ms) ^{Note 1)}				Weight (g) ^{Note 2)}
				1 → 2 (P → A)			2 → 3 (A → R)			Standard: 0.35 W	High speed response: 0.9 W	High pressure: 0.9 W	AC	
				C [dm³/(s·bar)]	b	Cv	C [dm³/(s·bar)]	b	Cv					
VQZ100	N.C. valve	Poppet	VQZ115	0.59	0.44	0.17	0.56	0.30	0.14	10 or less	—	13 or less	22 or less	24
VQZ200	N.C. valve	Metal seal	VQZ212	1.2	0.21	0.30	1.3	0.24	0.33	22 or less	14 or less	18 or less	34 or less	57
	N.C. valve	Rubber seal	VQZ232	1.6	0.33	0.39	1.7	0.37	0.45	22 or less	15 or less	—	36 or less	
	N.O. valve	Metal seal	VQZ222	1.2	0.25	0.31	1.3	0.20	0.31	22 or less	14 or less	18 or less	34 or less	
	N.O. valve	Rubber seal	VQZ242	1.6	0.36	0.40	1.7	0.36	0.45	22 or less	15 or less	—	36 or less	
VQZ300	N.C. valve	Metal seal	VQZ312	2.7	0.18	0.62	2.4	0.28	0.56	22 or less	17 or less	22 or less	34 or less	93
	N.C. valve	Rubber seal	VQZ332	3.5	0.34	0.87	3.0	0.33	0.72	33 or less	25 or less	—	57 or less	
	N.O. valve	Metal seal	VQZ322	2.6	0.21	0.59	2.2	0.16	0.49	22 or less	17 or less	22 or less	34 or less	
	N.O. valve	Rubber seal	VQZ342	3.5	0.38	0.88	2.9	0.27	0.69	33 or less	25 or less	—	57 or less	

Note 1) Based on JIS B 8374-1981 (Supply pressure: 0.5 MPa; with light/surge voltage suppressor; clean air)



Response time values will change depending on pressure and air quality.

Note 2) Weight for threaded connection

Construction

VQZ100

Poppet type







Component Parts

No.	Description	Material	Note
1	Body	Resin	
2	Spool valve	Aluminum/HNBR	
3	Pilot valve assembly	—	
4	P. R plate	Resin/Aluminum	VQZ100-12A (Standard) VQZ100-12B (External pilot type) ^{Note)}





Note) It is not possible to change the standard product to external pilot type, and vice versa.

VQZ200/300

Metal seal type



Rubber seal type



Component Parts

No.	Description	Material	Note
1	Body	Aluminum die-casted	
2	Spool, Sleeve	Stainless steel	Metal seal
	Spool valve	Aluminum/HNBR	Rubber seal
3	Piston	Resin	
4	Pilot valve assembly	—	

Note) For "How to Order Pilot Valve Assembly", refer to page 1807.

SYJ

VQZ

VP

VG



VP3

Series VQZ100/200/300


Dimensions: VQZ100

Single Unit


Grommet (G): VQZ115□-□G□1-C3, C4, C6-PR



Note) For bracket assembly part no., refer to page 1807.




VQZ115□-□G□1-M5-PR




Note) For One-touch fittings for P/R port and silencer part no., refer to page 1828.

L-type plug connector (L): VQZ115□-□L□1-C3, C4, C6-PR

M-type plug connector (M): VQZ115□-□M□1-C3, C4, C6-PR



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC





Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

Dimensions: VQZ200

Single Unit


Grommet (G): VQZ2□□-□G□1-C4, C6




Note) For bracket assembly part no., refer to page 1807.

Note) For One-touch fittings for P/R port and silencer part no., refer to page 1828.

VQZ2□□-□G□1-M5




L-type plug connector (L): VQZ2□□-□L□1-C4, C6




Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

M-type plug connector (M): VQZ2□□-□M□1-C4, C6



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

DIN terminal (Y): VQZ2□□-□Y□□1-C4, C6





Unless otherwise indicated, dimensions are the same as Grommet (G).

Series VQZ100/200/300

Dimensions: VQZ300


Single Unit

Grommet (G): VQZ3□2□-□G□1-C6, C8, C10




Note) For bracket assembly part no., refer to page 1807.

VQZ3□2□-□G□1-02




L-type plug connector (L): VQZ3□2□-□L□1-C6, C8, C10




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

DIN terminal (Y): VQZ3□2□-□Y□1-C6, C8, C10



Unless otherwise indicated, dimensions are the same as Grommet (G).

M-type plug connector (M): VQZ3□2□-□M□1-C6, C8, C10



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

Body Ported
Plug Lead Unit

3 Port Solenoid Valve

Series VQZ100/200/300

Manifold Connector Kit



[Option]
Note) For CE-compliant models, DC type only.

VQZ100 / How to Order Manifold

VV3QZ 1 2 - 08 C - D -

Series
1 VQZ100

Manifold type
2 Body ported

Stations
02 2 stations
20 20 stations

Kit type
C Connector

CE-compliant
Nil —
Q CE-compliant

Option
Nil None
D DIN rail mounting (With standard DIN rail length)
D0 Note 1) DIN rail mounting (Without DIN rail)
R Note 2) External pilot type

Note 1) Order DIN rail separately.
For DIN rail part no., refer to page 1805.
Note 2) When two or more symbols are specified, indicate them alphabetically.

Note) For 1(P), 3(R) of optional thread type, refer to page 1806.

VQZ100 / How to Order Valve

VQZ 1 1 5 - 5 M 1 - C3 -

Series
1 VQZ100 body width 10 mm

Type of actuation
1 N.C.

Body type

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W)	Note 3)
K Note 1)	High pressure type	(0.9 W)	—
R Note 1, 2)	External pilot type		
KR Note 1, 2)	High pressure/External pilot type	(0.9 W)	—

Note 1) Semi-standard
Note 2) For details on external pilot type, refer to page 1806.
Note 3) For AC specification power consumption, refer to page 1794.

Manual override
Nil Non-locking push type
B Locking type (Tool required)

CE-compliant
Nil —
Q CE-compliant

Note) For CE-compliant models, DC type only.

Port size [2(A) port]
C3 ø3.2 One-touch fitting
C4 ø4 One-touch fitting
C6 ø6 One-touch fitting
M5 M5 thread (Replaceable type)

Note) For inch size One-touch fittings, refer to page 1806.

Electrical entry

Symbol	Electrical entry	With light/surge voltage suppressor
G	Grommet (DC specification)	None
L	L-type plug connector with lead wire	Yes
LO	L-type plug connector without connector	
M	M-type plug connector with lead wire	
MO	M-type plug connector without connector	

Note) Standard lead wire length: 300 mm

Coil voltage

	CE-compliant
1 100 VAC (50/60 Hz)	—
2 200 VAC (50/60 Hz)	—
3 110 VAC [115 VAC] (50/60 Hz)	—
4 220 VAC [230 VAC] (50/60 Hz)	—
5 24 VDC	●
6 12 VDC	●

Caution
Use standard (DC) specification for continuous duty.

Series VQZ100/200/300

VQZ200/300 / How to Order Manifold



Made to Order
(For details, refer to page 1825.)

Note) AC-type models that
are CE-compliant have
DIN terminals only.



[Option]

VV3QZ **2** **2** - **08** **C** - -

Series

2	VQZ200
3	VQZ300

Manifold type

2	Body ported
---	-------------

Stations

02	2 stations
:	:
20	20 stations

Kit type

C	Connector
---	-----------

CE-compliant

Nil	—
Q	CE-compliant

Option

Nil	None
D	DIN rail mounting (With standard DIN rail length)
D0 <small>Note)</small>	DIN rail mounting (Without DIN rail)

Note) Order DIN rail separately.
For DIN rail part no., refer to page 1805.

Note) For 1(P), 3(R) of optional thread
type, refer to page 1806.

VQZ200/300 / How to Order Valve

VQZ **2** **1** **2** - **5** **M** - **1** - -

Series

2	VQZ200 body width 15 mm
3	VQZ300 body width 18 mm

Type of actuation

1	N.C. Metal seal
2	N.O. Metal seal
3	N.C. Rubber seal
4	N.O. Rubber seal

Body type

2	Body ported
---	-------------

Function

Symbol	Specifications	DC (0.35 W)	AC (Note 3)
Nil	Standard	○	○
B <small>Note 1)</small>	High speed response type	○	—
K <small>Note 1)</small>	High pressure type (Metal seal type only)	○	—
R <small>Note 1, 2)</small>	External pilot type	○	○
BR <small>Note 1, 2)</small>	High speed response/External pilot type	○	—
KR <small>Note 1, 2)</small>	High pressure/External pilot type (Metal seal type only)	○	—

Note 1) Semi-standard
Note 2) For details on external pilot type, refer to page 1806.
Note 3) For AC specification power consumption, refer to page 1794.



Caution
Use standard (DC) specification for
continuous duty.

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

IP65 compliant

Nil	—
W <small>Note)</small>	Compliant

Note) VQZ200/300 DIN
terminal rubber
seal only (except
external pilot). For
details on IP65
enclosure, refer to
page 1806.

CE-compliant

Nil	—
Q	CE-compliant

Note) AC-type models
that are
CE-compliant
have DIN
terminals only.

Port size [2(A) port]

Symbol	Port size	VQZ200	VQZ300
C4	ø4 One-touch fitting	○	—
C6	ø6 One-touch fitting	○	○
C8	ø8 One-touch fitting	—	○
C10	ø10 One-touch fitting	—	○
M5	M5 thread	○	—
02	Rc 1/4	—	○

Note) For inch size One-touch fittings and optional thread
type, refer to page 1806.

Manual override

Nil	Non-locking push type (Tool required)
B	Locking type (Tool required)


Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor	CE-compliant	
			AC	DC
G	Grommet (DC specification)	None	—	●
L	L-type plug connector with lead wire	Yes	—	●
LO	L-type plug connector without connector		—	●
M	M-type plug connector with lead wire		—	●
MO	M-type plug connector without connector		—	●
Y	DIN terminal	None	●	●
YO	DIN terminal without connector		●	●
YZ	DIN terminal		●	●
YS <small>Note 2)</small>	DIN terminal (DC specification)	Yes (Without light)	—	—
YOS <small>Note 2)</small>	DIN terminal without connector (DC specification)		—	●

Note 1) Standard lead wire length: 300 mm


Note 2) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.

Manifold Specifications



Series	Base model	Piping specifications		Applicable solenoid valve	Applicable stations	Manifold base weight (g)
		Piping direction	Port size			
			1(P), 3(R)	2(A)		
VQZ100	VV3QZ12-□□□	Top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 stations: 83 Addition per station: 19
VQZ200	VV3QZ22-□□□	Top	Rc 1/8	C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ2□2	2 stations: 68 Addition per station: 20
VQZ300	VV3QZ32-□□□	Top	Rc 1/4	C6 (for ø6) C8 (for ø8) C10 (for ø10) Rc 1/4	VQZ3□2	2 stations: 114 Addition per station: 37

How to Order Manifold Assembly (Example)



VV3QZ22-05C 1 set (C kit 5-station manifold base part no.)
 * VVQZ200-10A-2 ... 1 set (Blanking plate assembly part no.)
 * VQZ212-5M1-C6 ... 4 sets (N.C. type part no.)

→ The asterisk denotes the symbol for assembly.
 Prefix it to the part nos. of the solenoid valve, etc.

→ Enter in order starting from the first station on the D side.

Add the valve and option part number under the manifold base part number.
 When entry of part numbers becomes complicated, indicate by the manifold specification sheet.

SYJ

VQZ

VP


VG

VP3


Series **VQZ100/200/300**

Dimensions: **VQZ100**

VV3QZ12- Stations **C**




L-type plug connector (L)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

Dimensions


n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	85.5	98	110.5	123	135.5	148	148	160.5	173	185.5	198	210.5	210.5	223	235.5	248	260.5	273
L2	75	75	87.5	100	112.5	125	137.5	137.5	150	162.5	175	187.5	200	200	212.5	225	237.5	250	262.5
L3	43.5	54	64.5	75	85.5	96	106.5	117	127.5	138	148.5	159	169.5	180	190.5	201	211.5	222	232.5
L4	21	16	17	18	19	20	21	15.5	16.5	17.5	18.5	19.5	20.5	15.5	16.5	17.5	18.5	19.5	20.5
L5	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5

n: Stations (Max. 20 stations)

Dimensions: VQZ200


VV3QZ22- [Stations] C

Grommet (G)




The dashed lines indicate the DIN rail mounting [-D].

L-type plug connector (L)




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

DIN terminal (Y)



Unless otherwise indicated, dimensions are the same as Grommet (G).

Dimensions



n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	110.5	123	135.5	148	173	185.5	198	223	235.5	248	260.5	285.5	298	310.5	335.5	348	360.5	373
L2	75	100	112.5	125	137.5	162.5	175	187.5	212.5	225	237.5	250	275	287.5	300	325	337.5	350	362.5
L3	54	70	86	102	118	134	150	166	182	198	214	230	246	262	278	294	310	326	342
L4	16	20.5	18.5	17	15	19.5	18	16	20.5	19	17	15.5	20	18	16.5	21	19	17.5	15.5
L5	43	59	75	91	107	123	139	155	171	187	203	219	235	251	267	283	299	315	331

n: Stations (Max. 20 stations)


Series VQZ100/200/300

Dimensions: VQZ300


VV3QZ32- Stations C




L-type plug connector (L)



M-type plug connector (M)



DIN terminal (Y)



Dimensions

L \ n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	98	110.5	135.5	148	173	198	210.5	235.5	248	273	285.5	310.5	323	348	360.5	385.5	398	423	435.5
L2	87.5	100	125	137.5	162.5	187.5	200	225	237.5	262.5	275	300	312.5	337.5	350	375	387.5	412.5	425
L3	61	80	99	118	137	156	175	194	213	232	251	270	289	308	327	346	365	384	403
L4	18.5	15.5	18.5	15	18	21	18	21	17.5	20.5	17.5	20.5	17	20	17	20	16.5	19.5	16.5
L5	49	68	87	106	125	144	163	182	201	220	239	258	277	296	315	334	353	372	391

Manifold Options


Blanking plate assembly

VVQZ100-10A-5 (for VQZ100)

VVQZ200-10A-2 (for VQZ200)

VVQZ300-10A-2 (for VQZ300)

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.



Blanking plug



KQ2P-23

KQ2P-04

KQ2P-06

KQ2P-08

KQ2P-10



Dimensions

Applicable fitting size ød	Model	A	L	D
3.2	KQ2P-23	16	31.5	5
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12

DIN rail


AXT100-DR-□

* As for □, enter the number from the DIN rail dimensions table.
For L dimension, refer to the dimensions of each kit.

Each manifold can be mounted on a DIN rail.

Insert "D" at the end of the manifold part number.

The DIN rail is approximately 30 mm longer than the length of manifold.





L Dimension

No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L dimension	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
L dimension	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5

Silencer

(for manifold EXH port)

Silencer is installed in the manifold EXH port.



Dimensions

Model	Silencer part no.
VQZ100	AN110-01
VQZ200	AN110-01
VQZ300	AN20-02

For a silencer to be mounted in a single valve unit, refer to page 1828.

SYJ

VQZ

VP

VG

VP3

Replacement Parts

One-touch Fitting Assembly (for Cylinder port)

Fitting size	C3	C4	C6	C8	C10	M5 (VQZ100 only)
Model						
VQZ100/200	VVQ1000-50A-C3	VVQ1000-50A-C4	VVQ1000-50A-C6	—	—	VVQ1000-50A-M5
VQZ300	—	—	VVQ1000-51A-C6	VVQ1000-51A-C8	VVQ1000-51A-C10	—

(Note) Purchasing order is available in units of 10 pieces.

<Plug connector assembly>

DC: SY100-30-4A-□

100 VAC: SY100-30-1A-□

200 VAC: SY100-30-2A-□

Other AC voltages: SY100-30-3A-□

Without lead wire: **SY100-30-A**
(with connector and 2 sockets only)

Lead wire length

Nil	300 mm
6	600 mm
10	1000 mm
15	1500 mm
20	2000 mm
25	2500 mm
30	3000 mm
50	5000 mm

How to Order

Include the connector assembly part number together with the part number for the plug connector's solenoid valve without connector.

(Example) In case of 2000 mm of lead wire

DC	AC
VQZ115-5LO1-M5-PR	VQZ115-1LO1-M5-PR
SY100-30-4A-20	SY100-30-1A-20

<Gasket and screw assembly>

Model	Part no.
VQZ200	VQZ200-GS-2
VQZ300	VQZ300-GS-2

Note 1) The above part numbers are for 10 valves (a set of 10 gaskets and 20 screws).

Note 2) When changing the single unit to the manifold in VQZ100, refer to the base mounted type (page 1824).



<Pilot valve assembly>

V111 □ □ — 5 G □

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) □	□
B (Note)	High speed response type (Applicable to VQZ200/300)	(0.9 W) □	—
K (Note)	High pressure type (Applicable to Metal seal type, Poppet seal type)	(0.9 W) □	—

(Note) Semi-standard

Manual override

Nil	None (Applicable to VQZ200/300)
M	Yes (Applicable to VQZ100)

Manual override (Applicable to the VQZ100)

Nil	Non-locking push type
B	Locking slotted type

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC (50/60 Hz)
4	220 VAC (50/60 Hz)
5	24 VDC
6	12 VDC

Electrical entry

Symbol	Specifications	Electrical entry	Light/surge voltage suppressor
DC	AC		
G	—	Grommet (DC specification)	None
LU	LZ	L-type plug connector with lead wire	Yes
LOU	LOZ	L-type plug connector without connector	
MU	MZ	M-type plug connector with lead wire	
MOU	MOZ	M-type plug connector without connector	

(Note) VQZ pilot valve electrical entry (L, M) is the opposite of the how to order of valve body.

Valve model	Pilot valve model
VQZ115□□□□□1	V111□□□□□□□□
VQZ115□□□□□□□1	V111□□□□□□□□

<DIN terminal type (Applicable to the VQZ200/300)>

V115 □ □ — 5 Y — X110

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) □	□
B (Note)	High speed response type	(0.9 W) □	—
K (Note)	High pressure type (Metal seal type only)	(0.9 W) □	—

(Note) Semi-standard

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC (50/60 Hz)
4	220 VAC (50/60 Hz)
5	24 VDC
6	12 VDC

Electrical entry

Symbol	Specifications	Electrical entry	Light/surge voltage suppressor
Y	DIN terminal		None
YO	DIN terminal without connector		
YZ	DIN terminal with light/surge voltage suppressor		Yes
YS (Note)	DIN terminal with surge voltage suppressor (DC specification)		Yes
YOS (Note)	DIN terminal with surge voltage suppressor, without connector (DC specification)		Yes (Without light)

(Note) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.

<Bracket assembly>

Model	Part no.	Tightening torque (N·m) (Note)
VQZ100	VQZ100-FB	0.25 to 0.35
VQZ200	VQZ200-FB	
VQZ300	VQZ300-FB	

(Note) Tightening torque when mounting a bracket on the valve.

⚠ Caution

When replacing only the pilot valve assembly, use caution because it is not possible to convert to a V115 (DIN terminal) from a V111 (Grommet, L-type, M-type), or vice versa.

Base Mounted

Plug Lead Unit

3 Port Solenoid Valve

Series VQZ100/200/300

Single Unit



[Option]

Note) For CE-compliant models, DC type only.


VQZ100 / How to Order Valve

VQZ 1 1 5 - 5 M 1 - 01 -

Series

1 VQZ100 body width 10 mm

Type of actuation



Body type

5 Base mounted

Function

Symbol	Specifications	DC (0.35 W)	AC (Note 3)
Nil	Standard	○	○
K Note 1)	High pressure type	○	—
R Note 1, 2)	External pilot type	○	○
KR Note 1, 2)	High pressure/External pilot type	○	—

Note 1) Semi-standard

Note 2) For details on external pilot type, refer to page 1823.

Note 3) For AC specification power consumption, refer to page 1810.



Caution

Use standard (DC) specification for continuous duty.

CE-compliant

Nil	—
Q	CE-compliant

Note) For CE-compliant models, DC type only.

Port size

CP	Without sub-plate
01	Rc 1/8

Note) For optional thread type, refer to page 1823.

Manual override

Nil: Non-locking push type



B: Locking type (Tool required)



Electrical entry

G: Grommet (DC specification)	L: L-type plug connector with lead wire	LO: L-type plug connector without connector	M: M-type plug connector with lead wire	MO: M-type plug connector without connector
	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor

Note) Standard lead wire length: 300 mm

Coil voltage

		CE-compliant
1	100 VAC (50/60 Hz)	—
2	200 VAC (50/60 Hz)	—
3	110 VAC [115 VAC] (50/60 Hz)	—
4	220 VAC [230 VAC] (50/60 Hz)	—
5	24 VDC	●
6	12 VDC	●

Note) For sub-plate part no., refer to page 1824.

VQZ200/300 / How to Order Valve



Made to Order

(For details, refer to pages 1810 and 1825.)

Note) AC-type models that are CE-compliant have DIN terminals only.







VQZ **2** **1** **5** **5** **M** **1**

Series

2	VQZ200 body width 15 mm
3	VQZ300 body width 18 mm

Type of actuation

1	N.C.	2(A)	Metal seal
		(R)3 1(P)	
2	N.O.	2(A)	Metal seal
		(R)3 1(P)	
3	N.C.	2(A)	Rubber seal
		(R)3 1(P)	
4	N.O.	2(A)	Rubber seal
		(R)3 1(P)	

Body type

5	Body mounted
---	--------------

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W)	Note 3)
B Note 1)	High speed response type	(0.9 W)	—
K Note 1)	High pressure type (Metal seal type only)	(0.9 W)	—
R Note 1, 2)	External pilot type	—	—
BR Note 1, 2)	High speed response/External pilot type	(0.9 W)	—
KR Note 1, 2)	High pressure/External pilot type (Metal seal type only)	(0.9 W)	—

Note 1) Semi-standard

Note 2) For details on external pilot type, refer to page 1823.

Note 3) For AC specification power consumption, refer to page 1810.



Caution
Use standard (DC) specification for continuous duty.

IP65 compliant

Nil	—
W	Compliant

Note) VQZ200/300 DIN terminal rubber seal only (except external pilot). For details on IP65 enclosure, refer to page 1823.

CE-compliant

Nil	—
Q	CE-compliant

Note) AC-type models that are CE-compliant have DIN terminals only.

Port size

Symbol	Port size	VQZ200	VQZ300
Nil	Without sub-plate	○	○
01	Rc 1/8	○	—
02	Rc 1/4	○	○
03	Rc 3/8	—	○

Note) For optional thread type, refer to page 1823.

Manual override

Nil : Non-locking push type (Tool required)	B : Locking type (Tool required)
--	---

Electrical entry

	G: Grommet (DC specification)	L: L-type plug connector with lead wire	LO: L-type plug connector without connector	M: M-type plug connector with lead wire	MO: M-type plug connector without connector
	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor
CE- mark	—	—	—	—	—
AC	—	—	—	—	—
DC	—	—	—	—	—
Y: DIN terminal	YO: DIN terminal without connector	YZ: DIN terminal	YOS: DIN terminal without connector (DC specification)	YS: DIN terminal (DC specification)	
	With light/surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor	
CE- mark	—	—	—	—	—
AC	—	—	—	—	—
DC	—	—	—	—	—

Note 1) Standard lead wire length: 300 mm


Note 2) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

Note) For sub-plate part no., refer to page 1824.

Specifications



Valve construction	Metal seal	Rubber seal	VQZ100 (Poppet seal)
Fluid	Air, Inert gas		
Max. operating pressure (MPa)	0.7 (High pressure type: 1.0)	0.7	0.7 (High pressure type: 1.0)
Min. operating pressure (MPa)	0.1	0.15	0.15
Ambient and fluid temperature (°C)	-10 to 50 (No freezing)		
Max. operating frequency (Hz)	20	5	20
Pilot exhaust method	Individual exhaust		Common exhaust
Lubrication	Not required		
Manual override	Push type, Locking type (Tool required)		
Mounting orientation	Free		
Impact/Vibration resistance (m/s²) <small>Note 1)</small>	150/30		
Enclosure*	Dustproof (DIN terminal: IP65 <small>Note 2)</small>)		

* Based on IEC60529

Note 1) Impact resistance: No malfunction occurred when it is tested with a drop tester in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Value in the initial state)

Vibration resistance: No malfunction occurred in one sweep test between 45 and 2000 Hz. Test was performed to axis and right angle directions of the main valve and armature when pilot signal is ON and OFF. (Value in the initial state)

Note 2) When IP65 compliant DIN terminals are selected: VQZ²□5□-□Y□□W1-□-□

Solenoid Specifications

Semi-standard Specifications

High speed response type
High pressure type (Metal seal type only)
External pilot type*

* For details on external pilot type, refer to page 1823.



Made to Order
(For details, refer to page 1825.)

Symbol	Description
X30	Pilot valve common exhaust
X90	Main valve fluororubber
X113	All fluororubber

Electrical entry		Grommet (G)		M-type plug connector (M)	
		L-type plug connector (L)		DIN terminal (Y)	
		G, L, M		Y	
Coil rated voltage (V)	DC	24, 12			
	AC 50/60 Hz	100, 110, 200, 220*			
Allowable voltage fluctuation		±10% of rated voltage*			
Power consumption (W)	DC	Standard	0.35 [(With light: 0.4 (DIN terminal with light: 0.45))]		
		High speed response, high pressure	0.9 [(With light: 0.95 (DIN terminal with light: 1.0))]		
Apparent power (VA)	AC	100 V	0.78 (With light: 0.81)	0.78 (With light: 0.87)	
		110 V	0.86 (With light: 0.89)	0.86 (With light: 0.87)	
		[115 V]	[0.94 (With light: 0.97)]	[0.94 (With light: 1.07)]	
		200 V	1.18 (With light: 1.22)	1.15 (With light: 1.30)	
		220 V	1.30 (With light: 1.34)	1.27 (With light: 1.46)	
		[230 V]	[1.42 (With light: 1.46)]	[1.39 (With light: 1.60)]	
Surge voltage suppressor		Varistor			
Indicator light		LED (Neon light when AC with DIN terminal)			

* In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC.

* For 115 VAC and 230 VAC, the allowable voltage is -15% to +5% of rated voltage.

Flow Characteristics

Series	Valve construction	Model		Flow characteristics						Response time (ms) ^{Note 1)}				Note 2) Weight (g)
				1 → 2 (P → A)			2 → 3 (A → R)			Standard: 0.35 W	High speed response: 0.9 W	High pressure: 0.9 W	AC	
				C [dm³/(s·bar)]	b	Cv	C [dm³/(s·bar)]	b	Cv					
VQZ100	N.C. valve	Poppet	VQZ115	0.87	0.46	0.23	1.0	0.35	0.25	10 or less	—	13 or less	22 or less	24
VQZ200	N.C. valve	Metal seal	VQZ215	1.7	0.17	0.38	2.0	0.20	0.45	22 or less	14 or less	18 or less	34 or less	52
	N.C. valve	Rubber seal	VQZ235	2.3	0.46	0.65	3.0	0.40	0.80	22 or less	15 or less	—	36 or less	
	N.O. valve	Metal seal	VQZ225	1.7	0.18	0.38	1.8	0.21	0.39	22 or less	14 or less	18 or less	34 or less	
	N.O. valve	Rubber seal	VQZ245	2.5	0.43	0.67	3.0	0.30	0.74	22 or less	15 or less	—	36 or less	
VQZ300	N.C. valve	Metal seal	VQZ315	3.0	0.21	0.70	3.2	0.27	0.80	22 or less	17 or less	22 or less	34 or less	78
	N.C. valve	Rubber seal	VQZ335	4.5	0.42	1.3	4.1	0.36	1.0	33 or less	25 or less	—	57 or less	
	N.O. valve	Metal seal	VQZ325	2.9	0.21	0.72	2.9	0.16	0.69	22 or less	17 or less	22 or less	34 or less	
	N.O. valve	Rubber seal	VQZ345	4.4	0.45	1.2	4.5	0.38	1.2	33 or less	25 or less	—	57 or less	

Note 1) Based on JIS B 8374-1981 (Supply pressure: 0.5 MPa: with light/surge voltage suppressor: clean air)



Response time values will change depending on pressure and air quality.

Note 2) Weight without sub-plate.

Construction

VQZ100

Poppet type





Component Parts







No.	Description	Material	Note
1	Body	Resin	
2	Spool valve	Aluminum/HNBR	
3	Pilot valve assembly	—	
4	Port plug	Resin/HNBR	VVQZ100-CP

VQZ200/300

Metal seal type



Rubber seal type



Component Parts

No.	Description	Material	Note
1	Body	Aluminum die-casted	
2	Spool, Sleeve	Stainless steel	Metal seal
2	Spool valve	Aluminum/HNBR	Rubber seal
3	Piston	Resin	
4	Pilot valve assembly	—	


Note) For "How to Order Pilot Valve Assembly", refer to page 1824.

Series **VQZ100/200/300**


Dimensions: VQZ100

Single Unit

Grommet (G): VQZ115□-□G□1-01




L-type plug connector (L): VQZ115□-□L□1-01



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M): VQZ115□-□M□1-01




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

Dimensions: VQZ200


Single Unit

Grommet (G): VQZ2□5□-□G□1-⁰¹₀₂




(): VQZ215-□G□1-01

L-type plug connector (L): VQZ2□5□-□L□1-⁰¹₀₂




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M): VQZ2□5□-□M□1-⁰¹₀₂



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

DIN terminal (Y): VQZ2□5□-□Y□□1-⁰¹₀₂



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC


SYJ
VQZ
VP
VG
VP3

Series VQZ100/200/300

Dimensions: VQZ300


Single Unit

Grommet (G): VQZ3□5□-□G□1-⁰²₀₃




() : VQZ315-□G□1-01

L-type plug connector (L): VQZ3□5□-□L□1-⁰²₀₃




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M): VQZ3□5□-□M□1-⁰²₀₃



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

DIN terminal (Y): VQZ3□5□-□Y□□1-⁰²₀₃



Unless otherwise indicated, dimensions are the same as Grommet (G).

Base Mounted
Plug Lead Unit

3 Port Solenoid Valve

Series VQZ100/200/300

Manifold Connector Kit



[Option]
Note) For CE-compliant models, DC-type only.

VQZ100 / How to Order Manifold

VV3QZ 1 5 - 08 C6 C - -

Series
1 VQZ100

Manifold type
5 Base mounted

Stations
02 2 stations
20 20 stations

Port size [2(A) port]

C3	ø3.2 One-touch fitting	For side ported
C4	ø4 One-touch fitting	
C6	ø6 One-touch fitting	
M5	M5 thread (Replaceable type)	For top ported
CP Note 1)	With port plug	
CM Note 2)	Mixed port sizes	—

Note 1) When CP port plug is attached on all 2(A) port. Valve on manifold is top ported.
Note 2) Specify the mixture port (including top and side piping) by the manifold specification sheet.
Note 3) For inch size One-touch fittings, refer to page 1823.

CE-compliant
Nil —
Q CE-compliant

Option

Nil	None
D	DIN rail mounting (With standard DIN rail length)
D0 Note)	DIN rail mounting (Without DIN rail)
R	External pilot type

Note 1) Order DIN rail separately.
For DIN rail part no., refer to page 1822.
Note 2) When two or more symbols are specified, indicate them alphabetically.

Kit type
C Connector

VQZ100 / How to Order Valve

VQZ 1 1 5 - 5 M 1 - C4 -

Series
1 VQZ100 body width 10 mm

Type of actuation
1 N.C.

Body type
5 Base mounted

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) Note 3)	—
K Note 1)	High pressure type	—	—
R Note 1, 2)	External pilot type	—	—
KR Note 1, 2)	High pressure/External pilot type	—	—

Note 1) Semi-standard
Note 2) For details on external pilot type, refer to page 1823.
Note 3) For AC specification power consumption, refer to page 1810.

CE-compliant
Nil —
Q CE-compliant
Note) For CE-compliant models, DC type only.

Port size

CP	With port plug	For side ported
C3	ø3.2 One-touch fitting	For top ported
C4	ø4 One-touch fitting	
C6	ø6 One-touch fitting	
M5	M5 thread	—

Note) For inch size One-touch fittings, refer to page 1823.

Manual override

Nil	Non-locking push type (Tool required)
B	Locking type (Tool required)

Coil voltage

	CE-compliant
1 100 VAC (50/60 Hz)	—
2 200 VAC (50/60 Hz)	—
3 110 VAC [115 VAC] (50/60 Hz)	—
4 220 VAC [230 VAC] (50/60 Hz)	—
5 24 VDC	●
6 12 VDC	●

Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor
G	Grommet (DC specification)	None
L	L-plug plug connector with lead wire	Yes
LO	L-plug plug connector without connector	
M	M-plug plug connector with lead wire	
MO	M-plug plug connector without connector	

Note) Standard lead wire length: 300 mm

Caution
Use standard (DC) specification for continuous duty.

Series VQZ100/200/300

VQZ200/300 / How to Order Manifold



Made to Order
(For details, refer to page 1825.)

Note) AC-type models that are CE-compliant have DIN terminals only.



VV3QZ **2** **5** - **08** **C6** **C** - **□** - **□**

Series

2	VQZ200
3	VQZ300

Manifold type

5	Base mounted
---	--------------

Stations

02	2 stations
⋮	⋮
20	20 stations

Port size [2(A) port]

Symbol	Port size	VQZ200	VQZ300
C4	ø4 One-touch fitting	○	—
C6	ø6 One-touch fitting	○	○
C8	ø8 One-touch fitting	○	○
C10	ø10 One-touch fitting	—	○
01	Rc 1/8	○	—
02	Rc 1/4	—	○
CM	Mixed port sizes	○	○

CE-compliant

Nil	—
Q	CE-compliant

Option

Nil	None
D	DIN rail mounting (With standard DIN rail length)
D0	DIN rail mounting (Without DIN rail)
R	External pilot type

Kit type

C	Connector
---	-----------

Note 1) Specify port mixture/with port plug by means of the manifold specification sheet. Port mixture and port plug are available only for one-touch fitting type.
Note 2) For inch size One-touch fittings, refer to page 1823.

VQZ200/300 / How to Order Valve

VQZ **2** **1** **5** - **5** **M** - **1** - **□**

Series

2	VQZ200 body width 15 mm
3	VQZ300 body width 18 mm

Type of actuation

1	N.C. Metal seal
2	N.O. Metal seal
3	N.C. Rubber seal
4	N.O. Rubber seal

Body type

5	Base mouned
---	-------------

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) ○	(Note 3) ○
B	High speed response type	(0.9 W) ○	—
K	High pressure type (Metal seal type only)	(0.9 W) ○	—
R	External pilot type	○	○
BR	High speed response/External pilot type	(0.9 W) ○	—
KR	High pressure/External pilot type (Metal seal type only)	(0.9 W) ○	—

CE-compliant

Nil	—
Q	CE-compliant

Note) AC-type models that are CE-compliant have DIN terminals only.

IP65 compliant

Nil	—
W	Compliant

Note) VQZ200/300 DIN terminal rubber seal only (except external pilot). For details on IP65 enclosure, refer to page 1823.

Manual override

Nil	Non-locking push type (Tool required)
B	Locking type (Tool required)

Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor	CE-compliant
G	Grommet (DC specification)	None	— ●
L	L-type plug connector with lead wire	Yes	— ●
LO	L-type plug connector without connector		— ●
M	M-type plug connector with lead wire		— ●
MO	M-type plug connector without connector		— ●
Y	DIN terminal	None	— ●
YO	DIN terminal without connector		— ●
YZ	DIN terminal		— ●
YS	DIN terminal (DC specification)	Yes	— ●
YOS	DIN terminal without connector (DC specification)	Yes (Without light)	— ●

Note 1) Standard lead wire length: 300 mm.
Note 2) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.


Note 1) Semi-standard
Note 2) For details on external pilot type, refer to page 1823.
Note 3) For AC specification power consumption, refer to page 1810.

Caution
Use standard (DC) specification for continuous duty.

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC


Manifold Specifications



Series	Base model	Piping specifications			Applicable solenoid valve	Applicable stations	Manifold base weight (g) <small>(Note)</small>
		Piping direction	Port size				
			1(P), 3(R)	2(A)			
VQZ100	VV3QZ15-□□□	Side/Top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations	2 stations: 83 Addition per station: 19
VQZ200	VV3QZ25-□□□	Side	Rc 1/4	C4 (for ø4) C6 (for ø6) C8 (for ø8) Rc 1/8	VQZ2□5	2 to 20 stations	2 stations: 126 Addition per station: 38
VQZ300	VV3QZ35-□□□	Side	1(P) port Rc 3/8 3(R) port Rc 1/4	C6 (for ø6) C8 (for ø8) C10 (for ø10) Rc 1/4	VQZ3□5	2 to 20 stations	2 stations: 209 Addition per station: 60

Note) Weight for threaded connection.

How to Order Manifold Assembly (Example)



VV3QZ25-05C6C ····· 1 set (C kit 5-station manifold base part no.)

VVQZ200-10A-5 ····· 1 set (Blanking plate assembly part no.)

VQZ215-5L1 ····· 4 sets (N.C. type part no.)

The asterisk denotes the symbol for assembly.
Prefix it to the part nos. of the solenoid valve, etc.

Enter in order starting from the first station on the D side.

Add the valve and option part number under the manifold base part number.
When entry of part numbers becomes complicated, indicate by the manifold specification sheet.


- SYJ
- VQZ
- VP
- VG
- VP3

Series **VQZ100/200/300**

Dimensions: **VQZ100: Top Ported**


VV3QZ15- Stations Port size **C**

Grommet (G)



The dashed lines indicate the DIN rail mounting [-D].

M5




Dimensions

n: Stations (Max. 20 stations)

n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	85.5	98	110.5	123	135.5	148	148	160.5	173	185.5	198	210.5	210.5	223	235.5	248	260.5	273
L2	75	75	87.5	100	112.5	125	137.5	137.5	150	162.5	175	187.5	200	200	212.5	225	237.5	250	262.5
L3	43.5	54	64.5	75	85.5	96	106.5	117	127.5	138	148.5	159	169.5	180	190.5	201	211.5	222	232.5
L4	21	16	17	18	19	20	21	15.5	16.5	17.5	18.5	19.5	20.5	15	16.5	17.5	18.5	19.5	20.5
L5	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5


Dimensions: VQZ100: Side Ported

VV3QZ15- Stations Port size **C**




The dashed lines indicate the DIN rail mounting [-D].

L-type plug connector (L)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC


Dimensions

L	n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	85.5	98	110.5	123	135.5	148	148	160.5	173	185.5	198	210.5	210.5	223	235.5	248	260.5	273	
L2	75	75	87.5	100	112.5	125	137.5	137.5	150	162.5	175	187.5	200	200	212.5	225	237.5	250	262.5	
L3	43.5	54	64.5	75	85.5	96	106.5	117	127.5	138	148.5	159	169.5	180	190.5	201	211.5	222	232.5	
L4	21	16	17	18	19	20	21	15.5	16.5	17.5	18.5	19.5	20.5	16.5	17.5	18.5	18.5	19.5	20.5	
L5	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5	

Series **VQZ100/200/300**


Dimensions: **VQZ200**

VV3QZ25- Stations Port size C




The dashed lines indicate the DIN rail mounting [-D].

L-type plug connector (L)




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

DIN terminal (Y)



Unless otherwise indicated, dimensions are the same as Grommet (G).

Dimensions





n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	98	123	135.5	148	173	185.5	198	210.5	235.5	248	260.5	285.5	298	310.5	323	348	360.5	373
L2	75	87.5	112.5	125	137.5	162.5	175	187.5	200	225	237.5	250	275	287.5	300	312.5	337.5	350	362.5
L3	52	68	84	100	116	132	148	164	180	196	212	228	244	260	276	292	308	324	340
L4	17	15	19.5	18	16	20.5	19	17	15.5	20	18	16.5	21	19	17.5	15.5	20	18.5	16.5
L5	42	58	74	90	106	122	138	154	170	186	202	218	234	250	266	282	298	314	330

n: Stations (Max. 20 stations)

Dimensions: VQZ300


VV3QZ35- Stations Port size C

Grommet (G)




The dashed lines indicate the DIN rail mounting [-D].

L-type plug connector (L)




Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

DIN terminal (Y)



Unless otherwise indicated, dimensions are the same as Grommet (G).

Dimensions


n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	98	123	148	160.5	185.5	198	223	248	260.5	285.5	298	323	348	360.5	385.5	398	423	448	460.5
L2	87.5	112.5	137.5	150	175	187.5	212.5	237.5	250	275	287.5	312.5	337.5	350	375	387.5	412.5	437.5	450
L3	66	86	106	126	146	166	186	206	226	246	266	286	306	326	346	366	386	406	426
L4	16	18.5	21	17.5	20	16	18.5	21	17.5	20	16	18.5	21	17.5	20	16	18.5	21	17.5
L5	48	68	88	108	128	148	168	188	208	228	248	268	288	308	328	348	368	388	408

n: Stations (Max. 20 stations)

Manifold Options



Blanking plate assembly
VVQZ100-10A-5 (for VQZ100)
VVQZ200-10A-5 (for VQZ200)
VVQZ300-10A-5 (for VQZ300)

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.



Blanking plug

KQ2P-23
KQ2P-04
KQ2P-06
KQ2P-08
KQ2P-10




Dimensions (mm)				
Applicable fitting size ød	Model	A	L	D
3.2	KQ2P-23	16	31.5	5
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12

DIN rail
AXT100-DR-□

□ As for □, enter the number from the DIN rail dimensions table.
For L dimension, refer to the dimensions of each kit.

Each manifold can be mounted on a DIN rail.
Insert "D" at the end of the manifold part number.
The DIN rail is approximately 30 mm longer than the length of manifold.





L Dimension

No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L dimension	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
L dimension	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5

Silencer
(for manifold EXH port)

Silencer is installed in the manifold EXH port.



Dimensions	
Model	Silencer part no.
VQZ100	AN110-01
VQZ200	AN20-02
VQZ300	AN20-02

Port plug
VVQZ100-CP (for VQZ100)

This is used when changing piping location. (Side or Top)



Semi-standard Specifications



External Pilot Specification

The external pilot specification is used when the operating pressure is below the minimum operating pressure 0.1 to 0.15 MPa or when valve is used for a vacuum application. Order a valve by adding the external pilot specification [R] to the part number.

Valve Part No.


VQZ 5R — 1 —

• Entry is the same as standard products.

Manifold Part No.

VV3QZ 5 — C — R —

• Entry is the same as standard products.



CE-compliant

Nil	—
Q	CE-compliant

Pressure Specifications

Series		VQZ100 <small>Note 2)</small>	VQZ200/300
External pilot pressure range <small>Note 1)</small>	Metal seal	—	0.1 to 0.7 MPa
	Rubber seal (VQZ100: poppet)	0.2 to 0.7 MPa	0.15 to 0.7 MPa
Operating pressure range <small>Note 1)</small>		-100 kPa to 0.7 MPa	

Note 1) In case of the high pressure type, upper limit of max. operating pressure and external pilot pressure range is 1 MPa.

Note 2) When using the VQZ100 series for a vacuum application, vacuum air through its 1(P) port. When supplying vacuum-release air, supply it through its 3(R) port. But do not supply vacuum-release air exceeding 50% for the external pilot pressure.

In addition, when the VQZ100 is to be used at an operating pressure greater than 0.2 MPa, please assure that the operating pressure is set to equal to or less than the external pilot pressure.

Inch Size One-touch Fittings and Optional Threads

Inch size One-touch fittings and NPT, NPTF and G thread are available.

Manifold Part No.

VV3QZ 5 — N7 T C —

• Entry is the same as standard products.

• Cylinder port

CE-compliant

Nil	—
Q	CE-compliant

• Thread type (Cylinder port and 1(P), 3(R) ports)

Symbol	N1	N3	N7	N9	N11	NM <small>Note 1)</small>	M5	01	02
Applicable tubing O.D.	ø1/8"	ø5/32"	ø1/4"	ø5/16"	ø3/8"	Mixed	M5 thread	1/8 thread	1/4 thread
Cylinder port	VQZ100	●	●	—	—	●	●	—	—
	VQZ200	—	●	●	—	●	—	●	—
	VQZ300	—	—	●	●	●	—	—	●

Note 1) Except VQZ100, mixing One-touch fittings and thread types is impossible.

Note 2) Metric size One-touch fittings (C□) are also available.

Nil	Rc
N	NPT
T	NPTF
F	G

Optional Threads Other than Rc

Rc specifications are standard for all ports, however, NPT, NPTF and G are available for overseas markets. Add the appropriate symbol following the port size in the standard part number.

Valve Part No.

VQZ 5 — 1 — T

• Entry is the same as standard products.

CE-compliant

Nil	—
Q	CE-compliant

• Thread type (Cylinder port and 1(P), 3(R) ports of sub-plate)

Nil	Rc
N	NPT
T	NPTF
F	G

IP65 Enclosure (Based on IEC60529)

DIN terminal is available with IP65 enclosure.

Valve Part No.

(Applicable to the VQZ200/300 rubber seal with the exception of the external pilot type)

VQZ ²/₃ 5 — Y W1 —

• Entry is the same as standard products.

Note) The pilot exhaust IP65 valves is common with main valve exhaust. (The standard valve has an individual exhaust for the pilot valve.)

CE-compliant

Nil	—
Q	CE-compliant

Replacement Parts

One-touch Fitting Assembly (for Cylinder port)

Fitting size	C3	C4	C6	C8	C10	M5 (VQZ100 only)
Model						
VQZ100	VVQ1000-50A-C3	VVQ1000-50A-C4	VVQ1000-50A-C6	—	—	VVQ1000-50A-M5
VQZ200	—	VVQ1000-51A-C4	VVQ1000-51A-C6	VVQ1000-51A-C8	—	—
VQZ300	—	—	VVQ2000-51A-C6	VVQ2000-51A-C8	VVQ2000-51A-C10	—

(Note) Purchasing order is available in units of 10 pieces.

<Plug connector assembly>

DC: SY100-30-4A-□

100 VAC: SY100-30-1A-□

200 VAC: SY100-30-2A-□

Other AC voltages: SY100-30-3A-□

Without lead wire: SY100-30-A
(with connector and 2 sockets only)

Lead wire length

Nil	300 mm
6	600 mm
10	1000 mm
15	1500 mm
20	2000 mm
25	2500 mm
30	3000 mm
50	5000 mm

How to Order

Include the connector assembly part number together with the part number for the plug connector's solenoid valve without connector.

(Example) In case of 2000 mm of lead wire

DC	AC
VQZ115-5LO1-M5	VQZ115-1LO1-M5
SY100-30-4A-20	SY100-30-1A-20

<Gasket and screw assembly>

Model	Part no.
VQZ100	VQZ100-GS-5
VQZ200	VQZ200-GS-5
VQZ300	VQZ300-GS-5

(Note) The above part numbers are for 10 valves (a set of 10 gaskets and 20 screws).



<Sub-plate>

Model	Sub-plate part no.	
	For internal pilot	For external pilot
VQZ100	VQZ100-S-01□(-Q)	VQZ100-S-01□(-R(-Q)
VQZ200	VQZ200-S-01□(-Q)	VQZ200-S-01□(-R(-Q)
VQZ300	VQZ300-S-02□(-Q)	VQZ300-S-02□(-R(-Q)

* Thread type

<Pilot valve assembly>

V111 □ □ — 5 G □ □

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) ○	○
B (Note)	High speed response type (Applicable to VQZ200/300)	(0.9 W) ○	—
K (Note)	High pressure type (Applicable to Metal seal type, Poppet seal type)	(0.9 W) ○	—

(Note) Semi-standard

Manual override

Nil	None (Applicable to VQZ200/300)
M	Yes (Applicable to VQZ100)

Manual override (Applicable to the VQZ100)

Nil	Non-locking push type
B	Locking slotted type

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC (50/60 Hz)
4	220 VAC (50/60 Hz)
5	24 VDC
6	12 VDC

Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor
DC AC		
G	—	None
LU LZ	Grommet (DC specification)	
LOU LOZ	L-type plug connector with lead wire	
MU MOZ	L-type plug connector without connector	Yes
MU MOZ	M-type plug connector with lead wire	
MOU MOZ	M-type plug connector without connector	

(Note) The electrical entry (L, M) for the VQZ100 pilot valve is different from that of the main valve model number.

Valve model	Pilot valve model
VQZ115□□□L□1	V111□□M□□□
VQZ115□□□M□1	V111□□M□□□

<DIN terminal type (Applicable to the VQZ200/300)>

V115 □ □ — 5 Y — X110

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) ○	○
B (Note)	High speed response type	(0.9 W) ○	—
K (Note)	High pressure type (Metal seal type only)	(0.9 W) ○	—

(Note) Semi-standard

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC (50/60 Hz)
4	220 VAC (50/60 Hz)
5	24 VDC
6	12 VDC

Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor
Y	DIN terminal	
YO	DIN terminal without connector	None
YZ	DIN terminal with light/surge voltage suppressor	Yes
YS (Note)	DIN terminal with surge voltage suppressor (DC specification)	Yes
YOS (Note)	DIN terminal with surge voltage suppressor, without connector (DC specification)	Yes (Without light)

(Note) For AC voltage valves there is no "S" option. It is already built-in to the rectifier circuit.

⚠ Caution

When replacing only the pilot valve assembly, use caution because it is not possible to convert to a V115 (DIN terminal) from a V111 (Grommet, L-type, M-type), or vice versa.

Series VQZ200/300

Made to Order

Please contact SMC for detailed dimensions, specifications, and lead times.



1 Pilot Valve Common Exhaust Specification

Pilot exhaust is exhausted through the main R port.


* Not designed to prevent leakage to outside.

* A combination of external pilots is not available.

* "How to Order Manifold" is the same as standard products. Please specify this to "How to Order Valve."

Applicable solenoid valve series: VQZ200/300

How to Order




2 Main Valve Fluororubber Specification

The seal material, the part of the main valve in contact with fluid, is made of fluororubber.

* "How to Order Manifold" is the same as standard products. Please specify this to "How to Order Valve."

Applicable solenoid valve series: VQZ200/300

How to Order




3 All Fluororubber Specification

The rubber material of the part in contact with fluid, is made of fluororubber.

* "How to Order Manifold" is the same as standard products. Please specify this to "How to Order Valve."

Applicable solenoid valve series: VQZ200/300

How to Order





Series VQZ Specific Product Precautions 1

Be sure to read before handling.

Refer to front matter 53 for Safety Instructions and pages 3 to 8 for 3/4/5 Port Solenoid Valve Precautions.


Manual Override

⚠ Caution

Without an electric signal for the solenoid valve the manual override is used for switching the main valve. Push type is standard. Locking type (Tool required) is available as an option.


1. VQZ100

Push type



Press in the direction of the arrow.


Locking type (Tool required)



Turn 90° in the direction of arrow.


2. VQZ200/300

Push type (Tool required)




Push down on the manual override button with a small screwdriver until it stops. Release the screwdriver and the manual override will return.

Locking type (Tool required)



Push down completely on the manual override button with a small screwdriver. While down, turn clockwise 90° to lock it. Turn it counterclockwise to release it.

Locked position



Precautions


When operating with a screwdriver, turn it gently using a watchmaker's screwdriver. (Torque: less than 0.1 N·m)
Press and rotate to lock the manual operation of VQZ200/300. If rotate without pressing, manual breakage and air leakage could be occurred.

How to Use L/M-Type Plug Connector

⚠ Caution

1. Attaching and detaching connectors

To attach a connector, hold the lever and connector unit between your fingers and insert straight onto the pins of the solenoid valve and remove the pawl from the groove by pushing the lever downward with your thumb, and pull the connector straight out.




Light/Surge Voltage Suppressor


⚠ Caution

1. L/M-type plug connector

<DC>




<AC>




2. DIN terminal

<DC>

With surge voltage suppressor (YS, YOS)




Light/surge voltage suppressor (YZ)



<AC>

With light (YZ)



Note) Surge voltage suppressor of varistor has residual voltage corresponding to the protective element and rated voltage; therefore, protect the controller side from the surge.



Series VQZ

Specific Product Precautions 2

Be sure to read before handling.

Refer to front matter 53 for Safety Instructions and pages 3 to 8 for 3/4/5 Port Solenoid Valve Precautions.


Lead Wire Connection

⚠ Caution

1. Crimping of lead wires and sockets

Not necessary if ordering the lead wire pre-connected model. Strip 3.2 to 3.7 mm at the end of the lead wires, insert the ends of the core wires evenly into the sockets, and then crimp with a crimping tool. When this is done, take care that the coverings of the lead wires do not enter the core wire crimping area.

(Please contact SMC for the crimping tools.)




2. Attaching and detaching sockets with lead wires

Attaching

Insert the sockets into the square holes of the connector (⊙, ⊖ indication), and continue to push the sockets all the way in until they lock by hooking into the seats in the connector. (When they are pushed in, their hooks open and they are locked automatically.) Then, confirm that they are locked by pulling lightly on the lead wires.

Detaching

To detach a socket from a connector, pull out the lead wire while pressing the socket's hook with a stick having a thin tip (approx. 1 mm). If the socket will be used again, first spread the hook outward.




Pilot Valve Replacement

⚠ Caution


1. When replacing a conventional type valve with a new type for maintenance or other reasons, a "conversion connector assembly" is necessary to convert the connector from 3 terminals to 2 terminals and must be ordered separately. (When ordering, refer to the below part nos.)

For pilot valves, there is no compatibility between the conventional type and new type. When replacing a pilot valve, be sure to confirm whether it is the new type or the conventional type.

[Conventional]



[New]



SYJ

VQZ

VP

VG

VP3



Series VQZ

Specific Product Precautions 3

Be sure to read before handling.

Refer to front matter 53 for Safety Instructions and pages 3 to 8 for 3/4/5 Port Solenoid Valve Precautions.

How to Use DIN Terminal

1. EN-175301-803C (Former DIN 43650C) (8 mm between pins)

The DIN terminal type with an IP65 enclosure is protected against dust and water, however, it must not be used in water.

2. Connection

- 1) Loosen the holding screw and pull the connector out of the solenoid valve terminal block.
- 2) After removing the holding screw, insert a flat head screwdriver, etc. into the notch on the bottom of the terminal block and pry it open, separating the terminal block and the housing.
- 3) Loosen the terminal screws (slotted screws) on the terminal block, insert the cores of the lead wires into the terminals according to the connection method, and fasten them securely with the terminal screws.
- 4) Secure the cord by fastening the ground nut.

3. Changing the entry direction

After separating the terminal block and housing, the cord entry can be changed by attaching the housing in the desired direction (4 directions at 90° intervals).


* When equipped with a light, be careful not to damage the light with the cord's lead wires.

4. Precautions

Plug in and pull out the connector vertically without tilting to one side.

5. Compatible cable

Cable O.D.: $\phi 3.5$ to $\phi 7$
(Reference) 0.5 mm², 2-core or 3-core, equivalent to JIS C 3306



DIN Connector Part No.


Without light

Rated voltage	Voltage symbol	Part no.
All voltages	None	SY100-82-1

With light

Rated voltage	Voltage symbol	Part no.
24 VDC	24 V	SY100-82-3-05
12 VDC	12 V	SY100-82-3-06
100 VAC	100 V	SY100-82-2-01
200 VAC	200 V	SY100-82-2-02
110 VAC (115 VAC)	110 V	SY100-82-2-03
220 VAC (230 VAC)	220 V	SY100-82-2-04

Circuit diagram with light




Fitting and Silencer Part No. for P, R Ports When Using Valve as an Individual Unit

Part no. for one-touch fitting for 1(P) port and silencer/one-touch fitting for 3(R) port

Series	(1) One-touch fitting for 1(P) port	(2) For 3(R) port	
		Silencer	One-touch fitting
VQZ100	KQ2H06-M5A	AN120-M5	KJS04-M5A
VQZ200	KQ2S06-01AS	INA-25-46	IN-457-32L (for $\phi 6$)
VQZ300	KQ2H08-02AS	AN101-01	KQ2H06-01AS

The diameter of the above fitting and silencer is the maximum diameter to in the EXH port.





Series VQZ

Specific Product Precautions 4

Be sure to read before handling.


Refer to front matter 53 for Safety Instructions and pages 3 to 8 for 3/4/5 Port Solenoid Valve Precautions.

One-touch Fittings Replacement

⚠ Caution


The built-in fittings on the manifold can be changed easily. Simply remove the corresponding valve and take out the fitting clip underneath.

Take out the clip with a screwdriver, etc., then replace the fittings. About mounting the fittings, after inserting the fitting until it stops, then put the clip into the prescribed position.



VQZ200: Horizontally clipped to the valve body

VQZ100/300: Vertically clipped to the valve body



Precautions

When pulling the fitting assembly away from the valve base, remove the clip, then connect a tube or plug (KQ2P-□□) with the One-touch fitting and pull it out holding the tube or plug. Do not hold the release bushing to avoid damage.

DIN Rail Removal/Mounting


⚠ Caution

1. Removing

- 1) Loosen the clamp screw on the (a) side of both ends of the manifold.
- 2) Lift the (a) side of the manifold off the DIN rail and slide it in the direction of the (b) side.

2. Mounting

- 1) Catch the hook of the DIN rail bracket on the (b) side on the DIN rail.
- 2) Push side (a) onto the DIN rail and tighten the clamp screw. The proper tightening torque for screws is 0.3 to 0.4 N·m.




Valve Mounting

⚠ Caution

1. After confirming the gasket is correctly placed under the valve, securely tighten the bolts with the proper torque shown in the table below.

Model	Proper tightening torque
VQZ100	0.13 to 0.19 N·m
VQZ200	0.25 to 0.35 N·m
VQZ300	0.5 to 0.7 N·m




VQZ100 Piping Direction Replacement

⚠ Caution

1. How to replace the port direction

Fitting and port plug are modules. After removing the clip with a flat head screwdriver, take out the fitting and port plug. The piping direction (side or top) can be altered by exchanging the fitting and port plug. During exchange, insert the fitting and the port plug until they contact the wall, then, insert the clip to specified position.




Precautions

The clip length for the valve and the base are different. Fitting may detach if the incorrect clip is used.

2. Valve piped on top can be operated independently by using PR plate.

(Refer to the below part numbers when placing an order.)



VQZ100-12A (Standard)
VQZ100-12B (External pilot type)
* 2 set screws are included.

SYJ

VQZ

VP

VG

VP3