EB /**ES** Series Bronze/Stainless Steel



Product Configurations of Sintered Metal Elements

| Configuration | Bronz | e elements | (BC) | Stainless s | Stainless steel elements (SUS) | | |
|----------------------------|--|--|---|---|--|---|--|
| Disc | | EBD Series (P.108) | With outside diam- eter cutting finish Without outside di- ameter cutting fin- ish | | ESD Series (P.111) | With outside diam- eter cutting finish Without outside di- ameter cutting fin- ish | |
| Square sheet | | EBS Series (P.108) | With external shear- ing finish With external ma- chining finish | | ESS Series (P.112) | With external shear- ing finish With external ma- chining finish | |
| Cylinder | | EBP Series (P.109) | _ | Welding Welding | ESP Series (P.113) | Seamless finish (molded product) With seams (welded product) | |
| Cylinder with bottom | | EBW Series (P.109) | _ | Welding Welding | ESW Series (P.114) | Seamless finish (molded product) With seams (welded product) | |
| Cone with flange | | EBF Series (P.110) | _ | _ | _ | - | |
| Element with fitting | A Hex width across flats C | P.110 | - With fitting (M3, M5, R1/8, R1/4, R3/8, R1/2) | A A Hex width across flats C A Hex width across flats C | P.115 | • With fitting (M3, M5, R1/8, R1/4, R3/8, R1/2) | |
| Features | Sintered material: CAC4 (Metal material of eleme • Produces 2CuCO3·Cu(viding good corrosion re | nts with fitting: br OH)2 (patina) in | | Sintered material: SUS3 (Metal material of eleme · Austenite stainless ste acids, alkaline substar | nts with fitting: st eel with good co | rrosion resistance to | |

SMC sintered metal elements are suitable

- High mechanical strength and withstand pressure
- Anti-corrosion
- Suitable for high-accuracy filtration
- Suitable for machining, crimping, brazing, welding, and simultaneous sintering
- Washing allows repeated use

Specifications

| Item | Bronze | Stainless steel | |
|--|---|------------------------|--|
| Material | CAC403 equivalent | SUS316L equivalent | |
| Sintering density (g/cm ³) | 5.0 to 6.5 | 4.2 to 5.2 | |
| Void ratio (%) | 25 to 43 | 36 to 48 | |
| Operating temperature range (°C) Note 4) | -160 to 200 | -250 to 550 | |
| Thermal expansion coefficient (/°C) | 1.8 x 10 ^{−5} | 1.6 x 10 ⁻⁵ | |
| Tensile strength (MPa) | 9.8 to 83.4 | | |
| Nominal filtration accuracy (μ m) | (1), 2, 5, 10, 20, 40, 70, 100, 120 | | |
| Typical configurations | Disc, square sheet, cylinder, cylinder with bottom, cone with flange, element with fitting, etc | | |

Note 1) Sintering density, void ratio, and tensile strength differ according to nominal filtration accuracy. Note 2) Thermal expansion coefficient applies to stainless steel or bronze material, not to sintered metal elements.

Note 3) Nominal filtration accuracy of 1 μ m is an optional value.

Note 4) For operating temperature range of the element with fitting (standard product), refer to pages 110 and 115.

Raw material categories and nominal filtration accuracy (µm)

| Sieve (mesh) | 20 | 24 | 32 | 2 4 | 2 | 60 | 80 | 120 | 200 | 5 | 250 |
|----------------------------------|-----|-----|-----|-----|---|-----|-----|-----|------|---|-----|
| Opening (µm) | 850 | 710 | 500 | 35 | 5 | 250 | 180 | 125 | 5 75 | 5 | 63 |
| Nominal filtration accuracy (µm) | 120 | 5 | 100 | 70 | | 40 | 20 | 10 | 5 | | 2 |

Note 1) Sieve (mesh) and opening values apply to metal mesh separating raw material, not to elements. Note 2) Nominal filtration accuracy: Refers to value used to categorize raw material, not to filtration rating, (Refer to the page 118 for "11 Nominal filtration accuracy").

Raw Material Powder and Sintered Metal Element

<Bronze powder>



<Sintered bronze>



<Stainless steel powder>



<Sintered stainless steel>



A sintered metal element consists of countless interconnected capillary tubes, making it suitable for a wide range of uses. For detailed information on purpose-specific applications, please contact

1. Filtration

SMC

Applications

Sintered metal elements are widely used for removing foreign particles from many different kinds of flow media.

Major application fields: General gases, water, various kinds of oils

Normally, filtration makes use of the so-called bridge effect where foreign particles are blocked because they form a bridge-like accumulation.

The size and distribution of particles to be filtered can be controlled through parameters such as the diameter of the capillary tubes. Particles may be blocked completely or selectively.



2. High-viscosity filtration

This is used to remove foreign matter or gel from raw materials for fibers or films.

3. Sound absorption

The porous quality of sintered metal elements allows them to absorb sound energy, providing a muffling or silencing effect.

4. Gas removal

Sintered metal elements are used for degassing purposes in forming and molding processes.



5. Foaming

Sintered metal elements positioned in various kinds of fluids are used to introduce gases, for stirring and other purposes.



6. Flow control

Because a sintered metal element consists of countless interconnected capillary tubes, it can be used to control the flow of fluids. Cylindrical bronze elements are especially suited for this type of application.



7. Other applications

Various other applications make use of the fluidpassing functionality of sintered metal elements.

∕⊘SMC

for a wide range of industrial applications.



Flow Rate Characteristics

Note) Flow rate characteristics for stainless steel elements ESP-ESW (diameter 120 mm or less, no ESD seams) are different.

<Simplified formula for calculating pressure drop>

The state equation of an ideal gas (PV/T = constant) and the pressure drop are proportional to element thickness and viscosity. Based on this, the pressure drop under conditions that are different from those used in the flow rate characteristics chart can be calculated roughly for reference, using the following simplified procedure.

(1) Pressure drop ∆P kPa when flow medium is air, temperature T1°C, pressurization P1 kPa:

(2) Element thickness dependent pressure drop ΔP kPa when flow medium is air and water, element thickness t1 mm, and element thickness in flow rate characteristics chart differs: ΔPo: Pressure drop kPa obtained from flow rate characteristics chart or from (1)

$$\Delta P = \Delta P_0 \times \frac{t_1}{t_0 (2.3 \text{ or } 3)}$$

- to: Element thickness in flow rate characteristics chart (BC element = 3 mm/ SUS element = 2.3 mm)
- (3) Pressure drop ΔP kPa when viscosity η₁ of flow medium differs from that of air or water: ΔP=ΔPo x <u>η₁</u>

 ΔP_0 : Pressure drop kPa obtained from flow rate characteristics chart η_1 : Viscosity of flow medium Pa·s

 η_0 : Viscosity of flow rate characteristics chart (air = 1.8 x 10⁻⁵ Pa·s, water = 1 x 10⁻³ Pa·s)



Bronze (BC)



RoHS

Standard dimensions product (no cutting finish)

| øD | 6 | 8 | 10 | 12 | 15 | 20 |
|------------|----------|---|----|----|----|----|
| t | 2 | 2 | 2 | 3 | 3 | 3 |
| μ m | 2 to 120 | | | | | |

Note) For products with non-standard dimensions, sintering mold is required. Please contact SMC.

Manufacturing range for product without

2 to 20

| cutting finish | | | | | |
|----------------|---------|------|----|--|--|
| | 2 to 30 | | | | |
| 1 | 1.5 | 2 to | 10 | | |

2 to 40

| Tolerance | | | | |
|-----------|--|----|-------|--|
| | | øD | ± 0.3 | |
| | | t | ± 0.3 | |
| | | | | |

2 to 120 Note) Smallest unit for specifying diameter D values is 1 mm, and 0.5 mm for t values.

Manufacturing range for product with cutting finish

| øD | 30 to 200 | 30 to 300 | 30 to 400 | |
|------------|-----------|-----------|-----------|--|
| t | 1 | 1.5 | 2 to 10 | |
| μ m | 2 to 20 | 2 to 40 | 2 to 120 | |

Tolerance

øD

t

um

| | ± 0.3 | 30 D 120 | | |
|---------|-------|--------------------------|--|--|
| øD | ± 0.5 | 120 < D 315 | | |
| | ± 0.8 | 315 < D 400 | | |
| | ± 0.3 | | | |
| t ± 0.5 | | t: 5 to 10 (exceeds 300) | | |
| | | | | |

Note 1) Smallest unit for specifying diameter D and t values is 0.5 mm.

Note 2) Edge sections of products with a nominal filtration accuracy of 70 µm and higher may exhibit particle chipping and other machining problems

In Minimum order quantity is 10 pieces. (Excluding EBD-□M)

2. Square Sheet

How to Order EBS - 20 5 w Nominal filtration accuracy (um) 2 5 10 20 40 70 100 120 Circumference finish category Nil Product with shirring finish М Product with machining finish ≥

Manufacturing range for product with shearing finish

| W (Width) | 10 to 200 | 10 to 300 | 10 to 300 | | |
|------------|-----------|-----------|-----------|--|--|
| L (Length) | 20 to 200 | 20 to 300 | 20 to 500 | | |
| t | 1 | 1.5 | 2 to 3 | | |
| μ m | 2 to 20 | 2 to 40 | 2 to 120 | | |

Tolerance

| W, L | ± 1 | 10 W, L 120 |
|-------|-------|----------------|
| vv, ∟ | ± 2 | 120 < W, L 500 |
| t | ± 0.3 | |

Note 1) Smallest unit for specifying W and L values is 1 mm, and 0.5 mm for t values.

- Note 2) When shearing is used, the cut section is a break surface which will have shear drops and cracks. To remove these, process at least 5 mm on one side.
- Note 3) Edge sections of products with a nominal filtration accuracy of 70 µm and higher may exhibit particle chipping and other machining problems

Manufacturing range for product with machining finish

| W (Width) | 5 to 200 | 5 to 30 | 30 to 300 | 5 to 30 | 30 to 300 |
|------------|----------|----------|-----------|----------|-----------|
| L (Length) | 5 to 200 | 5 to 200 | 30 to 300 | 5 to 200 | 30 to 500 |
| t | 1 | 1.5 | | 2 to | 10 |
| μ m | 2 to 20 | 2 to | 40 | 2 to | 120 |

Tolerance

| W, L | ±0.3 | 5 W, L 30 | | | |
|------|-------|---------------------------|--|--|--|
| | ±0.5 | 30 < W, L 120 | | | |
| | ±1 | 120 < W, L 315 | | | |
| | ± 1.5 | 315 < W, L 500 | | | |
| | ±0.3 | | | | |
| τ | ±0.5 | t: 5 to 10 (exceeds L300) | | | |

Note 1) Smallest unit for specifying W, L, and t values is 0.5 mm.

Note 2) Edge sections of products with a nominal filtration accuracy of 70 um and higher may exhibit particle chipping and other machining problems.

Standard Configurations and Dimensions (Unit: mm)

Bronze (BC)

RoHS





| tanda | rd d | imensi | ons pro | oduct | | | | |
|------------|-------|----------|-----------|---|------------|--------|------------|-----|
| øD | 10 |) 20 | 30 | 40 | 45 | 50 | 6 | 5 |
| L | 20 | 0 200 | 200 | 200 | 200 | 250 | 250 | 500 |
| t | 2 | 2 | 2 | 2 | 2.5 | 3 | | 3 |
| μ m | | | | 2 | to 120 | | | |
| lanufa | ictu | ring rar | nge | | | | | |
| øD | | | - | | L | | | |
| 10 D | 20 | 10 to 50 | 10 to 200 | | | | | |
| 20 < D | 35 | 20 to 80 | 20 to 200 | 20 to | 300 | | | |
| 35 < D | 45 | | 35 to 200 | 35 to | 400 | | | |
| 45 < D | 65 | | | 45 to | 500 | | | |
| 65 < D | 130 | | | | 65 to 500 | | | |
| 130 < D | 200 | | | | 130 to 500 | 1 | 30 to 300 | 1 |
| 200 < D | 250 | | | | | 2 | 200 to 300 | 1 |
| t | | 1.5 | 2 | 2.5 | 3 | 4 | 5 | 6 |
| μ m | | 2 to 40 | | | 2 to | 120 | | |
| olerar | nce (| for sta | ndard a | and cu | stom p | roduct | s) | |
| | 1 | 0.3 | 1 | 0 D 3 | 0 | | | |
| øD | 1 | 0.5 | 30 |) <d 12<="" td=""><td>0</td><td></td><td></td><td></td></d> | 0 | | | |
| | ÷ | : 1 | 120 |) < D 25 | 0 | | | |
| | 1 | 0.3 | 1 | 0 L 30 | о — | | | |
| | 1 | 0.5 | 30 | 0 <l 12<="" td=""><td>0</td><td></td><td></td><td></td></l> | 0 | | | |
| | | | | | | | | |

FGD FGE FGA FGA FGF FGH FQ1 FN

õ

| Note 1) | For a 200 mm length, there is a draft taper of | of about 1 mm across. There- |
|---------|--|------------------------------|
| | fore the diameter D tolerance refers to the v | alue at the center of L. |

120 < L 315

315 < L 500

Note 3) End surfaces are created by cutting. Edge sections of products with a nominal filtration accuracy of 70 µm and higher may exhibit particle chipping and other machining problems.
Note 3) Smallest unit for specifying diameter D and L values is 0.5 mm. Small-

Note 3) Smallest unit for specifying diameter D and L values is 0.5 mm. Smallest unit for specifying t values is as noted in the table. Note 4) For products with non-standard dimensions, sintering mold is required.

Note 4) For products with non-standard dimensions, sintering mold is required. Please contact SMC.

4. Cylinder with Bottom



Standard dimensions product (no cutting finish)

| øD | 8 | 10 | 20 |
|------------|---|----------|----|
| L | 2 | 0 | 40 |
| t | | | |
| μ m | | 2 to 120 | |
| | | | |

± 1 ± 1.5

+0.3

Manufacturing range for product without cutting finish

| øD | 7 ≤ D ≤ 10 | | 10 < D ≤ 20 | | | | |
|------------|------------|----------|-------------|----------|----------|---|--|
| L | 7 to | o 10 | | 10 t | 10 to 50 | | |
| t | 1.5 | 2 | 1.5 | 2 2.5 3 | | 3 | |
| μ m | 2 to 40 | 2 to 120 | 2 to 40 | 2 to 120 | | | |
| | | | | | | | |

Manufacturing range for product with cutting finish

| øD | | 20 < | D ≤ 30 | $30 < D \le 40$ | | | | |
|------------|---------|----------|--------|-----------------|---|----------|---|--|
| L | | 20 to 80 | | | | 30 to 80 | | |
| t | 1.5 | 2 2.5 3 | | | 2 | 2.5 | 3 | |
| μ m | 2 to 40 | 2 to 120 | | | | 2 to 120 | | |

Tolerance (for standard and custom products)

| ٥D | ± 0.3 | $7 \le D \le 30$ |
|-----|-------|------------------|
| 00 | ± 0.5 | $30 < D \leq 40$ |
| | ± 0.3 | 7 ≤ L ≤ 30 |
| L L | ± 0.5 | $30 < L \leq 80$ |
| t | +03 | • |

Note 1) There is a draft taper of about 1 mm across.

Note 2) Opening side end surface is created by cutting. Edge sections of products with a nominal filtration accuracy of 70 μm and higher may exhibit particle chipping and other machining problems.

Note 3) Smallest unit for specifying diameter D and L values is 0.5 mm. Smallest unit for specifying t values is as noted in the table.Note 4) For products with non-standard dimensions, sintering mold is required.

Note 4) For products with non-standard dimensions, sintering mold is required. Please contact SMC.



Standard Configurations and Dimensions (Unit: mm)

Bronze (BC)

5. Cone with Flange How to Order EBF - 9 10 5 ♦t1 ∮øD1 Nominal filtration accuracy (µm) 2 5 10 20 40 70 100 120

Standard dimensions product

| ø D1 (± 0.5) | 9 | 10 | 12 | 15 | 20 |
|---------------------|---------|---------|----|----------|----|
| ø D2 (± 0.5) | 7 | 8 | 9 | 11 | 15 |
| L (± 0.5) | 10 | | 11 | 13 | 14 |
| t1 (± 0.3) | 1 | 1.5 | | 2 | 3 |
| t2 (± 0.3) | 2 | 2 | 2 | 2 | 3 |
| μm | 2 to 20 | 2 to 40 | | 2 to 120 | |

Note) Figures in brackets indicate tolerance.





RoHS

6. Element with Fitting (Standard product)

EBKX model number

| Connection | Model number | | 0 | | |
|------------|--------------|------|----|----|---------------|
| thread | wodel number | Α | В | С | Configuratior |
| M3 | EBKX-X9007- | 9.7 | 8 | 12 | 1 |
| M5 | EBKX-X9008- | 9.7 | 8 | 12 | 1 |
| R1/8 | EBKX-L7004- | 13.5 | 8 | 11 | 1 |
| B1/4 | EBKX-J2001- | 47.3 | 17 | 21 | 2 |
| n1/4 | EBKX-L7005- | 19 | 19 | 21 | 1 |
| D0/0 | EBKX-J2002- | 48.3 | 17 | 21 | 2 |
| R3/8 | EBKX-L7006- | 20 | 19 | 21 | 1 |
| R1/2 | EBKX-J2003- | 51.3 | 17 | 21 | 2 |
| R1/2 | EBKX-L7007- | 23 | 19 | 21 | 1 |

Model number suffix (nominal filtration accuracy) definition Example: Nominal filtration accuracy 2 µm

EBKX-J2001-002

| symbol | Nominal filtration accuracy |
|--------|-----------------------------|
| 002 | 2 µm |
| 005 | 5 µm |
| 010 | 10 µm |
| 020 | 20 µm |
| 040 | 40 µm |
| 070 | 70 µm |
| 100 | 100 µm |
| 120 | 120 µm |

Operating temperature: -160 to 100°C

m Hex width







1 Crimping

2 Crimping







| øD | 2 D < 4 | 4 D 30 |
|----|---------|---------|
| t | 1 to 4 | 1 to 10 |

Note 1) For products with non-standard dimensions, sintering mold is required. Please contact SMC. Note 2) Smallest unit for specifying diameter D values is 0.1 mm, and 0.5 mm for t values.

Manufacturing range for product with cutting finish (no welding)

| øD | 20 to 220 | 220.5 to 350 |
|----|--------------|--------------|
| t | 1 to 3, 4, 5 | (3), 4, 5 |

Note 1) Smallest unit for specifying diameter D values is 0.5 mm, and 0.5 mm for t values of 3 mm or less.

Note 2) Figures in brackets manufacturing range for nominal filtration accuracy 2 μm

Manufacturing range for product with cutting finish (with welding)

| øD | Welding pattern | t |
|--------------|--------------------|-----------|
| 221 D 440 | 1 | 2 to 3 |
| 440 < D 500 | 2 | 2 to 3 |
| 500 < D 660 | (4) | 3 |
| 660 < D 880 | (5) | 3 |
| 880 < D 1000 | 6 | 3 |
| 350 < D 700 | 3 | (3), 4, 5 |

Note 1) Smallest unit for specifying diameter D values is 0.5 mm, and 0.5 mm for t values of 3 mm or less. Note 2) Products with t = 2 to 3 and D \ge 221, or t = (3), 4, 5 and D \ge 350 have welded seams.

Products with t ≥ 3 have dual-sided welding. Figures in brackets indicate manufacturing range for nominal filtration accuracy 2 µm.

Note 3) Products with outside diameter D \geq 800 are finished by manual grinding.

Welded sections are wire brushed to remove oxide scales. (Oxide bath cleaning is not performed.)



* Minimum order quantity is 10 pieces. (Excluding ESD-□M)



Tolorance

t

| Tolerar | ice | |
|---------|-------|-------------|
| | ± 0.3 | 20 D 120 |
| øD | ± 0.5 | 120 < D 315 |
| | ± 0.8 | 315 < D 350 |
| t | ± 0.2 | |

± 0.2

Tolerance

| | ± 0.5 | 221 D 315 |
|----|------------|-------------------------|
| øD | ± 0.8 | 315 < D 800 |
| | ± 2 | 800 < D 1000 |
| t | ± 0.2 (exc | luding welded sections) |

Stainless steel (SUS) RoHS 2. Square Sheet How to Order ESS - 20 50 5 Nominal filtration accuracy (µm) Outside finish category No symbol Product with shearing finish 2 Product with machining finish М 5 10 20 40 70 ≥ 100 120 Manufacturing range for product with

| - | snearing tinis | sn (no weidin | g) | | weided prod | uct | | Iolerar | ice | |
|---|----------------|---------------|-----------|---|-------------|------------|-------------|--------------|-----------|--------------------------|
| [| W (Width) | 10 to 220 | 10 to 220 |] | W (Width) | 221 to 500 | 20 to 1000 | W.L | ±1 | 10 ≤ W, L ≤ 120 |
| [| L (Length) | 20 to 220 | 20 to 500 | | L (Length) | 221 to 500 | 501 to 1000 | ₩ , L | ±2 | $120 < W, L \le 1000$ |
| [| t | 1, 1.5 | 2 to 3 |] | t | 2 to 3 | 3 | t | ± 0.2 (ex | cluding welded sections) |

Welded was doned

Note 1) Smallest unit for specifying W and L values is 1 mm, and 0.5 mm for t values. Note 2) When shearing is used, the cut section is a break surface which will have shear drops and cracks. To remove these, process at least 5 mm on one side.

Manufacturing range for product with machining finish (no walding)

| manufacturing range for product with machining minsh (no weiging) | | | | | | | | | |
|---|-----------------|-------------------|-------------------|-------------------|----------------------|--|--|--|--|
| W (Width) | $5 \le W < 221$ | $5 \le W \le 30$ | $30 \le W < 221$ | $5 \le W \le 30$ | $30 \le W \le 350$ | | | | |
| L (Length) | $5 \le L < 221$ | $5 \le L \le 200$ | $30 \leq L < 501$ | $5 \le L \le 200$ | $30 \leq L \leq 350$ | | | | |
| t | 1, 1.5 | 2 t | o 3 | (3), | 4, 5 | | | | |

Note 1) Smallest unit for specifying W and L values is 0.5 mm, and 0.5 mm for t values of 3 mm or less. Note 2) Figures in brackets indicate manufacturing range for nominal filtration accuracy 2 µm.

Manufacturing range for product with machining finish (with welding)

| W (Width) | 221 ≤ W ≤ 450 | $40 \le W \le 450$ | $40 \le W \le 1000$ |
|------------|--------------------|----------------------|------------------------|
| L (Length) | $221 \leq L < 501$ | $501 \le L \le 1000$ | $351 \leq L \leq 1000$ |
| t | 2 to 3 | 3 | (3), 4, 5 |

Note 1) Smallest unit for specifying W and L values is 0.5 mm, and 0.5 mm for t values of 3 mm or less. Note 2) Products with W > 450 are cut sheets welded together which may have a slight shift or uneven height. Note 3) Figures in brackets indicate manufacturing range for nominal filtration accuracy 2 µm.

Welding pattern (t= 2 to 3, common to shearing/machining finish)

| W (Width) | (Longth) | L (Length) Configuration | | of sheets | | | |
|---------------------|----------------------|---|----------------------------|-----------|--|--|--|
| W (Widili) | Lengin) | Configuration 1 3 2 4 4 4 4 2 4 4 4 5 5 5 5 5 5 5 | W | L | | | |
| $20 \le W < 221$ | 501 ≤ L ≤ 1000 | 1 1 | | 2 | | | |
| | 221 ≤ L ≤ 441 | | 1 | 2 | | | |
| $221 \le W \le 441$ | 441 < L < 501 | | 2 | 1 | | | |
| | 501 ≤ L ≤ 1000 | 3 | 2 | 2 | | | |
| 441 < W < 501 | 441 < L < 662 | 2 | 1 | 3 | | | |
| 441 < W < 501 | 662 ≤ L ≤ 1000 | (4) | 2 1 3 2 | 2 | | | |
| 501 ≤ W < 662 | 501 ≤ L < 662 | (4) | 2 | 3 | | | |
| 501 S W < 002 | $662 \le L \le 1000$ | (4) | 1 1 2 2 1 3 | 2 | | | |
| 662 ≤ W ≤ 882 | 662 ≤ L ≤ 882 | 6 | 2 | 4 | | | |
| 002 > W 5 882 | 882 < L ≤ 1000 ⑥ | 4 | 2 | | | | |
| $882 < W \le 1000$ | 882 < L ≤ 1000 | 7 | 2 | 5 | | | |
| | | | | | | | |

Welding pattern (t = (3), 4, 5)

| W (Width) | L (Length) | Configuration | Number of sheets | | | | | |
|----------------|----------------|---------------|------------------|---|--|--|--|--|
| VV (VVIdiri) | Lengin) | Coniguration | w | L | | | | |
| 40 < 10 . 051 | 351 ≤ L < 701 | 1 | 1 | 2 | | | | |
| 40 ≤ W < 351 | 701 ≤ L ≤ 1000 | 2 | 1 | 3 | | | | |
| 351 ≤ W < 701 | 351 ≤ L < 701 | 3 | 2 | 2 | | | | |
| 351≤W< 701 | 701 < 1 < 1000 | (4) | 2 | 3 | | | | |
| 701 ≤ W ≤ 1000 | 701 ≤ L ≤ 1000 | 5 | 3 | 3 | | | | |

Note 1) Products with t = 2 to 3 and W \ge 221, L \ge 501 or t = (3), 4, 5 and W, L \ge 350 have welded searns. Products with t \ge 3 have dual-sided welding. Note 2) Welded sections of products with W, L ≥ 800 are wire brushed to remove oxide scales. (Oxide bath cleaning is not performed.)

(Welding patterns)



Tolerance

- . .

| | ± 0.3 | 5 ≤ W, L ≤ 30 |
|-------|-------|------------------|
| W.L | ± 0.5 | 30 < W, L ≤ 120 |
| VV, L | ± 1 | 120 < W, L ≤ 315 |
| | ± 1.5 | 315 < W, L < 501 |
| t | ± 0.2 | |

Tolerance

| 1 Olorun | | | | | | |
|----------|------------|-----------------------------------|--|--|--|--|
| | ± 0.5 | 40 ≤ W, L ≤ 120 | | | | |
| W.L | ± 1 | $120 < W, L \le 315$ | | | | |
| VV, L | ± 1.5 | 315 < W, L < 1000 | | | | |
| | ± 5 | t ≥ 4 (W < 450) | | | | |
| t | ± 0.2 (exc | ± 0.2 (excluding welded sections) | | | | |



5

ő

Tolerance

 $26 \le D \le 30$

t

| | ± 0.3 | $4 \le D \le 20$ |] |
|----|-------|------------------|--|
| øD | ± 0.5 | $20 < D \leq 30$ | Note 1) For products with non-standard dimensions, sintering mold is required. |
| | ± 1 | *: 2 weld seams | Please contact SMC. |
| | ± 0.3 | $5 \le L \le 30$ | Note 2) Smallest unit for specifying diameter D and L values is 0.5 mm. Smallest |
| L | ± 0.5 | $30 < L \le 60$ | unit for specifying t values is as noted in the table. Products with 2 weld |
| | ± 2 | *: 2 weld seams | seams are only available in the dimensions indicated in the table. Note 3) Products with 2 weld seams may have some curvature or uneven height. |
| t | ± 0.2 | | Note 4) End finish: no cutting (for 2 μ m or less, and L > 40, cutting finish is provided) |

1.5 2 2.5

Standard dimensions product (with seams)

| øD | 30 | | 40 | | 5 | 0 | 65 | |
|----|-----|-----|-----|-----|-----|-----|-----|-----|
| L | 250 | 500 | 250 | 500 | 250 | 500 | 250 | 500 |
| t | | | 2 | 2 | | | 2 | .3 |

Manufacturing range for product with seams

| øD | 10 to 14 | 15 to 19 | 20 to 29 | 30 to 39 | 40 to 49 | 50 to 73 | 74 to 150 |
|-----------------------------------|----------|----------|----------|-----------|------------|----------|-----------------------|
| L (*: 2 weld seams dimensions) | 10 to | 500 | | 10 to 500 | 0 (1000 *) | | 50 to 500 (1000 *) |
| t | 1 | 1 to 1.5 | 1 to 2 | 1.5 to 2 | 1.5 to 2.5 | 1.5 to 3 | 2 to 3 |

Tolerance

| øD | ± 1.5 | 10 to 73 | 1 | | |
|----|-------|--------------------|------|--|--|
| | ± 2 | 74 to 150 |] | | |
| L | ± 0.3 | 10 ≤ L ≤ 30 |] No | | |
| | ± 0.5 | 30 < L ≤ 120 | 1 | | |
| | ± 1 | 120 < L ≤ 315 | 1 | | |
| | ± 1.5 | 315 < L ≤ 500 | | | |
| | ± 3 | $500 < L \le 1000$ | | | |
| t | ± 0.2 | | No | | |

ote 1) Smallest unit for specifying diameter D and L values is 1mm, and 0.5mm for t values. Dimension in brackets for 2-seam products refer to maximum length.

ote 2) Products with D ≥ 74 have 2 seams in lengthwise direction. **SMC**

ote 3) End finish: with cutting.

10 to 60 (120 *)

3 3.5 4 4.5





L

Welding

 $10 \le \emptyset \mathbf{D} \le 73$

Standard Configurations and Dimensions (Unit: mm)

Stainless steel (SUS)

4. Cylinder with Bottom

How to Order



Nominal filtration accuracy (µm)



Cylinder outside diameter finish category







RoHS

Standard dimensions product (seamless)

| øD | 8 | 10 | 12 | 15 | 20 | 30 |
|----|----|----|----|----|----|----|
| L | 10 | 20 | 20 | 20 | 40 | 50 |
| t | | 3 | | | | |

Manufacturing range for seamless product

| øD | | | | | L | | | | |
|-------------------|------|---------|---------|---------|---|----------|---|-----|---|
| 5≤D< 8 | 5 to | 20 | | | | | | | |
| $8 \le D < 11$ | | 5 to 30 | | | | | | | |
| 11 ≤ D < 15 | | | 5 to 40 | | | | | | |
| $15 \leq D < 18$ | | | 5 to | 40 | | | | | |
| 18 ≤ D < 21 | | | 5 to | 50 | | | | | |
| $21 \le D < 26$ | | | | 5 to 50 | | | | | |
| $26 \le D \le 30$ | | | | | | 10 to 60 | | | |
| t | 1 | 1.5 | 2 | 2.5 | 3 | 3.5 | 4 | 4.5 | 5 |

Tolerance

| øD | ± 0.3 | $5 \le D \le 20$ | No |
|----|-------|------------------|-------------|
| øD | ± 0.5 | 20 < D ≤ 30 | |
| | ± 0.3 | 5 ≤ L ≤ 30 | No |
| L | ± 0.5 | 30 < L ≤ 60 | 1 |
| t | ± 0.2 | | \neg_{No} |
| | | | _ |

Note 1) For products with non-standard dimensions, sintering mold is required. Please contact SMC.

is required. Prease contact SMC.
tet 2) Smallest unit for specifying diameter D and L values is 0.5 mm. Smallest unit for specifying t values is as noted in the table.

table. bte 3) End finish: no cutting (For 2 μm or less, and L > 40, cutting finish is provided.)

ő

Standard dimensions product (with seams)

| øD | 3 | 0 | 4 | 0 | 5 | 0 | 6 | 5 |
|----|-----|-----|-----|-----|-----|-----|-----|-----|
| L | 250 | 500 | 250 | 500 | 250 | 500 | 250 | 500 |
| t | 2 | | | | | 2 | .3 | |

Manufacturing range for product with seams

| øD | 10 to 14 | 15 to 19 | 20 to 29 | 30 to 39 | 40 to 49 | 50 to 73 | 74 to 150 |
|------------------------------|----------|----------|----------|-----------|------------|----------|-----------|
| L | 10 # | 500 | | 10 to 500 |) (1000 *) | | 50 to 500 |
| (*: 2 weld seams dimensions) | 10 10 | 500 | | | (1000 *) | | |
| t | 1 | 1 to 1.5 | 1 to 2 | 1.5 to 2 | 1.5 to 2.5 | 1.5 to 3 | 2 to 3 |

\mathbf{L} $\mathbf{Welding}$ $\mathbf{Velding}$ $\mathbf{Velding}$ $\mathbf{Velding}$

Welding

Tolerance

| øD | ± 1.5 | 10 to 73 | | | | |
|----|-------|----------------|----|--|--|--|
| | ± 2 | 74 to 150 | | | | |
| | ± 1.0 | 10 ≤ L ≤ 30 | | | | |
| | ± 1.0 | 30 < L ≤ 120 | | | | |
| L | ± 2 | 120 < L ≤ 315 | | | | |
| | ± 2.5 | 315 < L ≤ 500 | | | | |
| | ± 3 | 500 < L ≤ 1000 | | | | |
| t | ± 0.2 | | No | | | |
| | - | | _ | | | |

ote 1) Smallest unit for specifying diameter D and L values is 1 mm, and 0.5 mm for t values. Dimensions in brackets for 2-seam products refer to maximum length.
ote 2) Products with D ≥ 74 have 2 seams in length-

e 2) Products with D ≥ 74 have 2 seams in lengthwise direction.

SMC

ote 3) End finish: with cutting.



Standard Configurations and Dimensions (Unit: mm)

Stainless steel (SUS)

5. Element with Fitting (Standard product)

ESKA model number

| Connection | Model number | I | Dimensions | 3 | Configuration |
|------------|--------------|------|------------|--------|---------------|
| thread | woder number | Α | В | С | Coninguration |
| | ESKA-Z2701- | 9 | 6 | N/A *1 | 1 |
| M3 | ESKA-Z2711- | 9.7 | 8 | 14 | 2 |
| | ESKA-Z2702- | 17 | 8 | N/A *1 | 1 |
| M5 | ESKA-Z2712- | 9.7 | 8 | 14 | 2 |
| | ESKA-Z2801- | 38 | 13 | N/A *2 | 3 |
| R1/8 | ESKA-Z2811- | 13.5 | 8 | 14 | 2 |
| D4/4 | ESKA-Z2802- | 52 | 17 | 17 | 3 |
| R1/4 | ESKA-Z2812- | 19 | 19 | 21 | 2 |
| D0/0 | ESKA-Z2803- | 53 | 17 | 17 | 3 |
| R3/8 | ESKA-Z2813- | 20 | 19 | 21 | 2 |
| D1/0 | ESKA-Z2804- | 58 | 17 | 22 | 3 |
| R1/2 | ESKA-Z2814- | 23 | 19 | 21 | 2 |

Model number suffix (nominal filtration accuracy) definition symbol Nominal filtration accuracy Example: Nominal filtration accuracy 2 μm

ESKA-Z2701-002

| symbol | Nominal filtration accuracy | Example: | | | |
|--------------------------------------|-----------------------------|----------|--|--|--|
| 002 | 2 µm | | | | |
| 005 | 5 µm | | | | |
| 010 | 10 µm | | | | |
| 020 | 20 µm | | | | |
| 040 | 40 µm | | | | |
| 070 | 70 µm | | | | |
| 100 | 100 µm | | | | |
| 120 | 120 µm | | | | |
| Operating temperature: -196 to 150°C | | | | | |

(1) Simultaneous sintering (*1)

| A |
|--------------------------|
| Hex width across flats C |
| |

2 Crimping



(*2)



RoHS

Cleaning Method

According to the clogged material and clogging condition, select an appropriate cleaning method from those shown below. A combination of both methods may yield greater results.





Sintered Metal Element Specific Product Precautions 1

Be sure to read this before handling the products.

Precautions on Design

≜Caution

1. Strength

The elements are made of porous material with voids inside. Therefore their tensile strength compared to conventional stainless steel or bronze products is lower by a factor of one or two magnitudes. Depending on the application conditions, reinforcing material may be required. Use punched metal or similar for reinforcement.

2. Operating temperature

The operating temperature range given in the specifications (page 106) is the range in which material strength does not deteriorate significantly.

In an oxidizing atmosphere (atmospheric air), the temperature point where oxidization and discoloring begins is 100°C for bronze elements and 250°C for stainless steel elements.

3. Fatigue breakdown

Fatigue breakdown may occur under the following conditions: 1) Element is subject to vibrations

 Element is subject to cyclic thermal expansion and contraction

In such cases, use suitable countermeasures such as vibration dampers or punched metal reinforcements to support the element, or employ a construction that absorbs thermal expansion and contraction.

4. End configuration

For information on end configurations of cylinder elements (open or with bottom), check the notes and configuration information on the page for the respective product in this catalog. When devising applications, make sure that there are no problems such as improper sealing or leaks due to the end configurations.

5. Particle separation

When cutting is performed, particle chipping will occur at edge sections. This is especially noticeable with products rated for high nominal filtration accuracy (µm) values. Particle chipping and other machining problems may also occur at edges of products that are not finished by cutting. Carefully check sealing properties before use.

6. Welded products (Stainless steel elements)

Welded stainless steel elements are produced by argon welding. Consequently, problems such as uneven height, distortion, warping, raised beads etc. may be present.

Discoloration of sections exposed to heat may not be completely removed by cleaning.

7. Cleaning

The products of sintered metal elements in the table are cleaned before shipping, but not to clean room standards. Before use in a clean room, elements must be cleaned and flushed by the customer, and application suitability must be verified.

| Bronze element | Oxide bath cleaning | Note) |
|-----------------|--|---------------------------------|
| Stainless steel | $\begin{array}{l} \text{Oxide bath} \\ \text{cleaning} \rightarrow \begin{array}{l} \text{Passivation} \\ (\text{Nitric acid bath}) \end{array}$ | Welded products |
| element | Passivation (Nitric acid bath) | Non-welded finished products |

Note) Products with nominal filtration accuracy of 2 to 10 micron and 5 t or higher may exhibit discoloration by oxide bath cleaning.

≜Caution

8. Corrosion

Note that corrosion will occur, depending on usage and ambient conditions. Major corrosive substances and corrosion conditions are listed below. Be sure to check this information.

Bronze elements

| Category | Corrosive substances and corrosion conditions | | | | |
|-------------|--|--|--|--|--|
| Acid, | Use in solutions with ferric or cupric ion content or am- monium content not possible, due to corrosion | | | | |
| alkali | Use in nitric acid, sulfur, and hydrochloric acid not possible, due to corrosion | | | | |
| Atmosphere | Corrosion caused by hydrogen sulfide (H_2S) and sulfurous acid (SO ₂) | | | | |
| Sea water | Products have some resistance but long-term use will cause corrosion | | | | |
| Fresh water | Corrosion caused by presence of carbonic acid (carbonation) | | | | |

Stainless steel elements

| Stanliess steer elements | | | | |
|-------------------------------|---|--|--|--|
| Category | Corrosive substances and corrosion conditions | | | |
| Acid, alkali, etc. | Sulfur, hydrochloric acid, etc. Corrosion may be accelerated by density, tempera- ture, halogen (especially chlorine) ion content, etc. | | | |
| | Nitric acid Compared to sulfur, hydrochloric acid etc., resistance is better due to passivity, but under certain conditions, corrosion may occur. | | | |
| | Corrosion due to sodium hydroxide and potassium hydroxide Corrosion will be intensified by introduction of dissolved oxygen | | | |
| | Sodium chloride, sodium bromide etc. | | | |
| Atmosphere | Corrosion caused by CO ₂ , SO ₂ , NH ₃ etc. in the atmosphere, and by temperature and other atmospheric conditions | | | |
| Sea water | Corrosion depending on chlorine ion content, dissolved oxygen content, and organic matter | | | |
| Fresh water | Corrosion caused by halogen (especially chlorine) ion content, deposits, etc. | | | |
| | Corrosion caused by presence of carbonic acid (carbonation) | | | |
| High- temperature water | Corrosion is accelerated at higher temperatures | | | |
| Steam | Corrosion is accelerated at higher temperatures | | | |

9. Discoloration

1) Elements can be discolored by foreign matter deposits, oxidization by flow medium, and other conditions. In particular, as for the bronze element, a dark red CuO film is formed by the moisture included in the atmosphere and the product may be discolored when unpacked. However, this does not affect the product characteristics. If the discoloration of the bronze element is pointed out as appearance problem, Ni plating treatment is available. For details, contact SMC.

 A portion that may be seen as black point may rarely occur on the element surface.

This is caused by raw materials included in the raw material powder and does not adversely affect the product performance.



Sintered Metal Element Specific Product Precautions 2

Be sure to read this before handling the products.

Precautions on Design

11.Nominal filtration accuracy

Nominal filtration accuracy of sintered metal elements is a classification rating using the particle size of the raw material. (This is different from the filtration rating with regard to the flow medium.) For reference, particle sizes that can be removed with an efficiency of 95% (in air and water) at different nominal filtration accuracy ratings are listed below.

Nominal filtration accuracy and 95% removable particle sizes (reference)

| Nominal filtration accuracy (µm) | 95% removable particle size (μm) | | | |
|---|----------------------------------|-----------------------|--------------------|-----------------------|
| | Flow medium: Air | | Flow medium: Water | |
| | Bronze (BC) | Stainless steel (SUS) | Bronze (BC) | Stainless steel (SUS) |
| 120 | — | _ | 244 | 110 |
| 100 | _ | _ | 177 | 87 |
| 70 | — | — | 104 | 66 |
| 40 | 3.6 | 2.5 | 90 | 45 |
| 20 | 2.8 | 2 | 59 | 31 |
| 10 | 2.1 | 1.5 | 32 | 20 |
| 5 | 1.5 | 1.1 | 20 | 15 |
| 2 | 1 | 0.7 | 17 | 10 |

Installation

▲Caution

1. Installation of standard elements with fitting

When the element is held with a tool directly, this may cause damage to the element, resulting in breakage.

1) Connection thread M3

First tighten by hand and then use a suitable wrench on the hex sleeve of the fitting to tighten further by about 1/4 turn.

Tighten the ESKA-Z2701- \Box by hand. Do not grip the sintered part with pliers or other tools.

2) Connection thread M5

First tighten by hand and then use a suitable wrench on the hex sleeve of the fitting to tighten further by about 1/6 turn.

Tighten the ESKA-Z2702- by hand. Do not grip the sintered part with pliers or other tools.

- 3) Connection thread R (pipe taper thread)
- First tighten by hand and then use a suitable wrench on the hex sleeve of the fitting to tighten further.

| Connection thread | Suitable tightening torque (N·m) |
|-------------------|----------------------------------|
| R1/8 | 7 to 9 * |
| R1/4 | 12 to 14 |
| R3/8 | 22 to 24 |
| R1/2 | 28 to 30 |

* Tighten the ESKA-Z2801-□ by hand. Do not grip the sintered part with pliers or other tools.

Operating Environment

≜Caution

- Discoloration and material degradation may occur if used in a corrosive atmospheric environment. Severe corrosion will cause the product to lose its filtering functionality.
- 2. When the product is subject to vibrations or shock, fatigue breakdown may occur. Provide suitable reinforcement to avoid such conditions.

Storage

▲Caution

1. Keep the product indoors and in its packing until use.

Protect the product from water, humidity, and high temperatures, to avoid discoloration and corrosion.

2. Do not place any objects on top of the product. Otherwise there is a risk of deformation or breakage.

Maintenance

 Pressure drop ∆P will change depending on operating conditions.

Pressure drop ΔP is one of the performance parameters of the element. Establish suitable management standards for this parameter.

2. Be aware of individual product warranty conditions and exclusions.

In the case of sintered metal products, conditions such as filter performance degradation due to clogging and discoloration are not covered by the warranty, even during the warranty period.