Slider Type/Ball Bushing Bearing

CY1L Series

ø6, ø10, ø15, ø20, ø25, ø32, ø40





CY1L Series **Model Selection**



Caution on Design (1)

ST: Stroke (mm)

How to Find σ when Selecting the Allowable Load Mass

Since the maximum load mass with respect to the cylinder stroke changes as shown in the table below, σ should be considered as a coefficient determined in accordance with each stroke. Example) CY1L25D-650

- (1) Maximum load mass = 20 kg(2) Load mass for 650 st = 13.6 kg
- (3) $\sigma = \frac{13.6}{20} = 0.68$ is the result

Calculation Formula for σ ($\sigma \leq 1$)

50

Model	CY1L6	CY1L10	CY1L15
σ=	1	10 ^(0.86 - 1.3 x 10⁻³ x ST)	10 ^(1.5 - 1.3 x 10⁻³ x ST)
0-		3	7
Model	CY1L20	CY1L25	CY1L32
σ=	10 ^(1.71 - 1.3 x 10⁻³ x ST)	10 ^(1.98 - 1.3 x 10⁻³ x ST)	10 ^(2.26 - 1.3 x 10⁻³ x ST)
0 =	12	20	30
Model	CY1L40		
σ=	10 ^(2.48 - 1.3 x 10⁻³ x ST)		

Note) Calculate with σ = 1 for all applications up to σ 10 – 300 mmST, σ 15 – 500 mmST, σ 20 – 500 mmST, σ 25 – 500 mmST, σ 32 – 600 mmST and σ 40 – 600 mmST.



Examples of Allowable Load Mass Calculation Based on Cylinder Mounting Orientation

1. Horizontal Operation (Floor mounting)



Maximum Load Mass (Center of slide block)

Bore size (mm)	6	10	15	20	25	32	40
Max. load mass (kg)	1.8	3	7	12	20	30	50
Stroke (Max)	Up to 300 st	Up to 300 st	Up to 500 st	Up to 500 st	Up to 500 st	Up to 600 st	Up to 600 st

The above maximum load mass values will change with the stroke length for each cylinder size, due to limitation from warping of the guide shafts. (Take note of the coefficient $\sigma_{\rm J}$)

Moreover, depending on the operating direction, the allowable load mass may be different from the maximum load mass.

2. Horizontal Operation (Wall mounting)



Lo: Distance from mounting surface to load center of gravity (cm)

(mm)	Allowable load mass (WA) (kg)
6	<u></u> σ⋅6.48
0	6.8 + 2 Lo
10	<u>σ.15.0</u>
10	8.9 + 2 Lo
15	σ·45.5
15	11.3 + 2 Lo
20	σ ⋅101
20	13.6 + 2 Lo
25	σ.180
25	15.2 + 2 Lo
32	σ ⋅330
32	18.9 + 2 Lo
40	σ·624
40	22.5 + 2 Lo

(ka)

3. Vertical Operation



Lo: Distance from mounting surface to load center of gravity (cm) Note) Operating pressure should be equal to or less than the maximum operating pressure in the article, "Vertical Operation" listed on page



CYP

CY3B

D-🗆
-X□
Technical Data

1510



1515.

Caution on Design (2)

Example of Allowable Load Mass Calculation Based on Cylinder Mounting Orientation

4. Inclined Operation (In operating direction)



Lo: Distance from mounting surface to load center of gravity (cm)

5. Inclined Operation (At a right angle to operating direction)



Lo: Distance from mounting surface

to load center of gravity (cm)

Bore siz Allowable load mass (WA) (kg) **σ**.6.48 6 3.6 + 2 (1.6 + Lo) sin0 **σ**⋅15 10 5 + 2 (1.95 + Lo) sin0 σ.45.5 15 6.5 + 2 (2.4 + Lo) sinθ σ.115 20 2 (2.8 + Lo) sinθ 8+ **σ**.180 25 9 + 2 (3.1 + Lo) sin0 σ.330 32 11 + 2 (3.95 + Lo) sinθ **σ**.624 40 13 + 2 (4.75 + Lo) sinθ

6. Load Center Offset in Operating Direction (Lo)



Bore size (mm)	Allowable load mass (WA) (kg)
6	$\frac{\sigma \cdot 2}{Lo + 1.7}$
10	$\frac{\sigma \cdot 5.6}{\text{Lo} + 2.8}$
15	<u> </u>
20	<u> </u>
25	<u>σ.46.15</u> Lo + 3.55
32	<u> </u>
40	<u>σ·188.1</u> Lo + 5.7

7. Horizontal Operation (Pushing load, Pusher)



F: Drive (from slide block to position Lo) resistance force W x μ (kg) Lo: Distance from mounting surface to load center of gravity (cm) μ : Friction coefficient

Bore size (mm)	6	10	15	20
Allowable drive resisting force (Fa) (kg)	<u>σ.2.72</u> 1.6 + Lo	$\frac{\sigma \cdot 5.55}{1.95 + \text{Lo}}$	<u>σ.15.96</u> 2.4 + Lo	<u>σ.41.7</u> 2.8 + Lo
Bore size (mm)	25	32	40	

8. Horizontal Operation (Load, Lateral offset Lo)



Lo: Distance from center of side block to load's center of gravity (cm)

Bore size (mm)	6	10	15	20
Allowable load mass (WA) (kg)	$\frac{\sigma{\cdot}6.48}{3.6 + \text{Lo}}$	<u>σ.15</u> 5 + Lo	$\frac{\sigma \cdot 45.5}{6.5 + \text{Lo}}$	<u>σ.80.7</u> 8 + Lo
Bore size (mm)	25	32	40	

@SMC

Caution on Design (3)

Vertical Operation

When operating a load vertically, it should be operated within the allowable load mass and maximum operating pressures shown in the table below. Use caution, as operating above the prescribed values may lead to dropping of the load.

When the cylinder is mounted vertically or sidelong, sliders may move downwards due to the self-weight or workpiece mass. If an accurate stopping position is required at the stroke end or the middle-stroke, use an external stopper to secure accurate positioning.

Bore size (mm)	Model	Allowable load mass (Wv) (kg)	Maximum operating pressure (Pv) (MPa)		
6	CY1L 6H	1.0	0.55		
10	CY1L10H	2.7	0.55		
15	CY1L15H	7.0	0.65		
15	CY1L15L	4.1	0.40		
20	CY1L20H	11.0	0.65		
20	CY1L20L	7.0	0.40		
25	CY1L25H	18.5	0.65		
25	CY1L25L	11.2	0.40		
32	CY1L32H	30.0	0.65		
32	CY1L32L	18.2	0.40		
40	CY1L40H	47.0	0.65		
40	CY1L40L	29.0	0.40		

Note 1) Use caution, since the magnetic coupling may be dislocated if it is used over the maximum operating pressure.

Note 2) Allowable load mass above indicates the maximum load mass when loaded. The actual loadable mass must be determined referring to the flow chart in the Model Selection 1.

Intermediate Stop

1. Intermediate stopping of load with an external stopper, etc.

When stopping a load in mid-stroke using an external stopper (adjusting bolt, etc.), operate within the operating pressure limits shown in the table below. Use caution, as operation at a pressure exceeding these limits can result in breaking of the magnetic coupling.

Bore size (mm)	Model	Operating pressure limit for intermediate stop (Ps) (MPa)					
6	CY1L 6H	0.55					
10	CY1L10H	0.55					
15	CY1L15H	0.65					
15	CY1L15L	0.40					
20	CY1L20H	0.65					
20	CY1L20L	0.40					
25	CY1L25H	0.65					
25	CY1L25L	0.40					
32	CY1L32H	0.65					
32	CY1L32L	0.40					
40	CY1L40H	0.65					
40	CY1L40L	0.40					

2. Intermediate stopping of load with an air pressure circuit

When stopping a load using an air pressure circuit, operate at or below the kinetic energy shown in the table below. Use caution, as operation when exceeding the allowable value can result in breaking of the magnetic coupling.

		(Ticlcrenec values)	
Bore size (mm)	Model	Allowable kinetic energy for intermediate stop (Es) (J)	
6	CY1L 6H	0.007	
10	CY1L10H	0.03	
15	CY1L15H	0.13	CY3B
15	CY1L15L	0.076	CY3R
20	CY1L20H	0.24	CY1S
20	CY1L20L	0.16	0110
25	CY1L25H	0.45	CY1L
25	CY1L25L	0.27	
32	CY1L32H	0.88	CY1H
32	CY1L32L	0.53	01/4 5
40	CY1L40H	1.53	CY1F
40	CY1L40L	0.95	CYP
			UIF

(Reference values)

Magnetically Coupled Rodless Cylinder Slider Type: Ball Bushing Bearing **CY1L Series** 06, 010, 015, 020, 025, 032, 040

How to Order Ball Bushing Bearing CY1L 25 30 J79W Refer to page 1517 Slider type for details (Ball bushing bearing) Auto switch Number of auto switches Bore size Without auto switch Nil 2 pcs Nil (Built-in magnet) S 6 6 mm 25 25 mm 1 pc For the applicable auto switch 10 n "n" pcs. 10 mm 32 32 mm model, refer to the table below. 15 15 mm 40 40 mm Adjustment type 20 20 mm Nil With adjusting bolt R With shock absorbers (2 pcs.) Port thread type With shock absorber (With plate A) Symbol Туре Bore size BS * Installed on side A at time of shipment M thread ø6, ø10, ø15 Nil Rc ø20, ø25. Shock Absorbers ΤN NPT ø32 ø40 Bore size (mm) TF G Type 6 10.15 20 25 32.40 Standard (shock absorber Magnetic holding force **BB0805 BB1006 BB1411 BB2015** RB series) Refer to page 1517 for specifications. Shock absorber soft type RJ0805 RJ0806H RJ1007H RJ1412H

Standard stroke

Refer to "Standard Stroke" on page 1517.

The shock absorber service life is different from that of the CY1L cylinder. Refer to "Specific Product Precautions" for each shock absorber for the replacement

Heter t period.

RJ series type (-XB22)

The shock absorber soft type RJ series type (-XB22) is a made to order specification.
 For details, refer to page 1752.

* Solid state auto switches marked with "O" are produced upon receipt of order.

Applicable Auto Switches/Refer to pages 1575 to 1701 for further information on auto switches.

			light	Wiring	Load volta		tage	Auto swite	h model	Lead wire length (m) *															
Туре	pe Special function El		ndicator light	(Output)	DC		AC			0.5	0.5 3 5 (Nil) (L) (Z)		None												
			Pu					Perpendicular	In-line	(Nil)	(L)	(Z)	(N)												
				3-wire (NPN)		5 V, 12 V		F7NV	F79			0	-	0	IC										
£		Grommet		3-wire (PNP)]	5 V, 12 V		F7PV	F7P	•	•	0	-	0	circuit										
switch				2-wire]	10.11		F7BV	J79		•	0	-	0											
sv		Connector		2-wire		12 V		J79C	_	•	۲	٠	•	-	-	Deleu									
auto	Discuss stills in discation		1	3-wire (NPN)	1		_	F7NWV	F79W	•	•	0	-	0	IC	Relay, PLC									
al	Diagnostic indication (2-color indicator)		Yes	3-wire (PNP)	24 V	24 V 5 V, 1	24 V 5 V, 12	24 V	24 V	24 V	24 V	24 V	24 V	24 V	5 V, 12 V		_	F7PW	•	٠	0	-	0	circuit	PLC
state					1	12 V]	F7BWV	J79W	•	•	0	-	0											
Solid st	Water resistant (2-color indicator)	Grommet		2-wire	1			F7BAV**	F7BA**	-	•	0	-	0	-										
Š	With diagnostic output (2-color indicator)]		4-wire (NPN))		5 V, 12 V	1	-	F79F	•	•	0	-	0	IC circuit	1								
switch			Yes	3-wire (NPN equivalent)	—	5 V	—	—	A76H	•	•	-	-	-	IC circuit	—									
s		Grommet	rommet 🎽 🗌		_	_	200 V	A72	A72H		•	-	-	-											
f						12 V	100 V	A73	A73H	•	۲	•	-	-	-										
a			٩	2-wire	24 V	5 V, 12 V	100 V or less	A80	A80H		•	-	-	-	IC circuit	Relay,									
Reed		Connector	No Yes]	24 V	12 V		A73C	_	•	٠	•	•	-	-	PLC									
ñ		Connector	۶	1		5 V, 12 V	_	A80C	_		۲	•		-	IC circuit	1									

** Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.

* Lead wire length symbols: 0.5 m Nil

- 3 m------ L 5 m------ Z
- (Example) J79W (Example) J79WL (Example) J79WZ

None------ N (Example) J79CN

· Since there are other applicable auto switches than listed, refer to page 1520 for details.

· For details about auto switches with pre-wired connector, refer to pages 1648 and 1649.

*Auto switches are shipped together, (but not assembled).



Symbol

Rubber bumper (Magnet type)



Easy piping and wiring

Hollow shafts are used, and centralization of ports on one side makes piping easy. Auto switches can be mounted through the use of special switch rails.

Shock absorbers and adjusting bolt are standard equipment

Impacts at stroke end due to high speed use can be absorbed, and fine adjustment of the stroke is possible.



Made to Order: Individual Specifications (For details, refer to pages 1538 and 1539.)

	(i oi details, refer to pages 1500 and 1505.)
Symbol	Specifications
-X116	Hydro specifications
-X168	Helical insert thread specifications
-X322	Outside of cylinder tube with hard chrome plated
-X431	Auto switch rails on both side faces (with 2 pcs.)

Made to Order Specifications

Click ne	Click here for details										
Symbol	Specifications										
-XB9	Low speed cylinder (15 to 50 mm/s)										
-XB13	Low speed cylinder (7 to 50 mm/s)										
-XB22	Shock absorber soft type RJ series type										

Amount of Adjustment by Adjusting Bolt



Bore size	Amount of adjustment b	y adjusting bolt: R(mm)
(mm)	Single side	Both sides
6	6	12
10	5.5	11
15	3.5	7
20	5.5	11
25	5	10
32	5.5	11
40	4.5	9

* Since the cylinder is in an intermediate stop condition when stroke adjustment is performed, use caution regarding the operating pressure and the kinetic energy of the load.

The amount of adjustment for adjustment bolts is the total amount when adjusted on both plate ends. For the adjustment on a single plate end, the amount of adjustment is half of the figures in the table above.

 Adjust the stroke adjustment with an adjustment bolt. It cannot be adjusted by a shock absorber.

Specifications

Bore size (mm)	6	10	15	20	25	32	40			
Fluid		Air									
Proof pressure					1.05 MPa						
Maximum operating	g pressure				0.7 MPa						
Minimum operating	g pressure			(0.18 MPa						
Ambient and fluid f	emperature			-10 to 6	0°C (No f	reezing)					
Piston speed *		50 to 500 mm/s									
Cushion		Rubber bumper/Shock absorber									
Lubrication		Not required (Non-lube)									
Stroke length tole	rance (mm)	0 to	250 st: +1 0	^{.0} , 251 to	1000 st: +	^{1.4} , 1001 ៖	st and up:	+1.8 0			
	Туре Н	19.6 53.9 137 231 363 588									
Holding force (N)	Type L	81.4 154 221 358 569									
Standard equipm	ent	Auto switch mounting rail									

* In the case of setting an auto switch at the intermediate position, the maximum piston speed is subject to restrict for detection upon the response time of a load (Relays, Sequence controller, etc.).

Standard Stroke

Bore size (mm)	Standard stroke (mm)	Maximum available stroke (mm)
6	50, 100, 150, 200	300
10	50, 100, 150, 200, 250, 300	500
15	50, 100, 150, 200, 250, 300, 350 400, 450, 500	750
20	100 150 000 050 000 050	1000
25 32	100, 150, 200, 250, 300, 350 400, 450, 500, 600, 700, 800	1500
40	100, 150, 200, 250, 300, 350 400, 450, 500, 600, 700, 800 900, 1000	1500

Note) Intermediate stroke is available in 1 mm increments.

Weight

								(kg)
Number of magne	Bore size (mm)	6	10	15	20	25	32	40
Basic weight	CY1L⊟H	0.324	0.580	1.10	1.85	2.21	4.36	4.83
Dasic weigin	CY1LDL	—	—	1.02	1.66	2.04	4.18	4.61
	eight per each of stroke	0.044	0.077	0.104	0.138	0.172	0.267	0.406

Calculation (Example) CY1L32H-500

 Characteristic
 Additional weight
 Classic weight
 Cylinder stroke
 Store
 Store

Shock Absorber Specifications

Refer to the RB series in Best Pneumatics No. 2-3 for the details on shock absorbers.

Applicable rodles	ss cylinder	6 CY1L10 15	CY1L20	CY1L25	CY1L ³² 40					
Shock absorber r	nodel	RB0805	RB1006	RB1411	RB2015					
Maximum energy al	osorption: (J)	0.98	3.92	14.7	58.8					
Stroke absorption	n: (mm)	5	5 6 11							
Collision speed: ((m/s)	0.05 to 5								
Max. operating frequen	cy: (cycle/min) *	80	80 70 45							
Ambient tempera	ture range		-10 to	80 °C						
Carries forest (NI)	Extended	1.96	4.22	6.86	8.34					
Spring force: (N)	Retracted	3.83	6.18	15.3	20.50					
* It denotes the v	alues at the	maximum energy	, absorption per (ne cycle Therefr	ore the operating					

It denotes the values at the maximum energy absorption per one cycle. Therefore, the operat frequency can be increased according to the energy absorption.

The shock absorber service life is different from that of the CY1L cylinder. Refer to the Specific Product Precautions for the replacement period.

CYP

D-

-X

Technical

Data



CY1L Series

Construction

Slider type/Ball bushing bearing



Component Parts

No.	Description	Material	Note
1	Slide block	Aluminum alloy	Anodized
2	Plate A	Aluminum alloy	Anodized
3	Plate B	Aluminum alloy	Anodized
4	Cylinder tube	Stainless steel	
5	Guide shaft A	Carbon steel	Hard chrome plated
6	Guide shaft B	Carbon steel	Hard chrome plated
7	Piston	Aluminum alloy Note 1)	Chromated
8	Shaft	Stainless steel	
9	Piston side yoke	Rolled steel	Zinc chromated
10	External slider side yoke	Rolled steel	Zinc chromated
11	Magnet A		
12	Magnet B		
13	Piston nut	Carbon steel	Zinc chromated ø25 to ø40
14	Retaining ring	Carbon tool steel	Phosphate coated
15	Retaining ring	Carbon tool steel	Phosphate coated
16	External slider tube	Aluminum alloy	
17	Slider spacer	Rolled steel	Nickel plated
18	Spacer	Rolled steel	Nickel plated
19	Ball bushing		
20	Plug	Brass	Nickel plated ø25 to ø40 only
21	Adjusting bolt A	Chromium molybdenum steel	Nickel plated
22	Adjusting bolt B	Chromium molybdenum steel	Nickel plated
23	Shock absorber		
24	Hexagon nut	Carbon steel	Nickel plated
25	Hexagon nut	Carbon steel	Nickel plated
26	Hexagon socket head cap screw	Chromium molybdenum steel	Nickel plated
27	Hexagon socket head cap screw	Chromium molybdenum steel	Nickel plated
28	Hexagon socket head cap screw	Chromium molybdenum steel	Nickel plated
Note 1) Broop for a6		

Note 1) Brass for ø6

No.	Description	Material	Note
29	Hexagon socket head cap screw	Chromium molybdenum steel	Nickel plated
30	Switch mounting rail	Aluminum alloy	
31	Auto switch		
32	Magnet for auto switch		
33	Steel ball		ø6, ø10, ø15 only
34	Side cover	Carbon steel	ø6 only
35	Grease cup	Carbon steel	ø15 or larger
36 *	Wear ring A	Special resin	
37*	Wear ring	Special resin	
38 *	Wear ring B	Special resin	
39*	Cylinder tube gasket	NBR	
40 *	Guide shaft gasket	NBR	
41 *	Piston seal	NBR	
42 *	Scraper	NBR	

Replacement Parts: Seal Kit

Bore size (mm)	Kit no.	Contents
6	CY1S6-PS-N	Set of nos. above 38, 39, 40, 41
10	CY1L10-PS-N	Set of nos. above 38, 39, 40, 41, 42
15	CY1L15-PS-N	
20	CY1L20-PS-N	Set of nos. above
25	CY1L25-PS-N	36, 37, 38, 39, 40,
32	CY1L32-PS-N	(4), (42)
40	CY1L40-PS-N]

Note 1) Seal kit includes 3, 3, 4, 4 for ø6. 3, 3 to 4 are for ø10, ø15. 3 to 4 are for ø20 to ø40. Order the seal kit, based on each bore size.

Note 2) 66: Same for CY1S6 Note 3) For replacement of the ${\it o10}$ wear ring A, contact SMC or your near-

est sales representative. Seal kit includes a grease pack (o6, o10: 5 and 10 g, ø15 to ø40: 10 g). Order with the following part number when only the grease pack is needed. Grease pack part no. for o6, o10: GR+F-005 (5 g) for external sliding parts, GR-S-5010 (10 g) for tube interior

Grease pack part no. for ø15 to ø40: GR-S-010 (10 g)

Dimensions





																							(mm)
Model	Α	В	С	D	d	EA	EB	FA	FB	G	GP	н	HA	HE	3 Н	GН	I HO) н	PHS	; НТ	•	J	JK
CY1L6	7	6.5	3	7.6	8	—	—	—	_	6	36	27	5	10	11	9	25	5 26	6 14	16	M4	x 0.7	6.5
CY1L10	8.5	8	4	12	10	6	12	3	5	7.5	50	34	6	17.	5 14	.5 13	5 33	3 33	21.	5 18	M5	x 0.8	9.5
Model	L	LD	М	M	N	(N)	(NA)	(NB)		NN	!	PA*	PB	PW	Q	QW	RW	Т	TT	ta	tb	w	z
CY1L6	40	3.5	6	M4 x	0.7	11	30	24	N	//8 x 1	.0	24	40	60	54	20	12	10	16	_	—	56	68
CY1L10	68	4.3	8	M4 x	0.7	10.5	27	19	N	//8 x 1.	.0	30	60	80	85	26	17.5	12.5	20.5	0.5	1.0	77	103

* PA dimensions are for split from center.



Model	Α	в	С	D	d	EA	EB	FA	FB	G	GP	н	HA	ΗВ	HG	HI	но	HP	HS	нт		J		JK	L	LD
CY1L15	7.5	9.5	5	16.6	12	6	13	3	6	6.5	65	40	6.5	4	16	14	38	39	25	16		M6 x 1	.0	9.5	75	5.6
CY1L20	9.5	9.5	5.2	21.6	16	_	Ι	Ι	Ι	8.5	80	46	9	10	18	16	44	45	31	20		M6 x 1	.0	10	86	5.6
CY1L25	9.5	11	6.5	26.4	16	8	14	4	7	8.5	90	54	9	18	23	21	52	53	39	20	N	//8 x 1.	25	10	86	7
CY1L32	10.5	14	8	33.6	20	8	16	5	7	9.5	110	66	12	26.5	26.5	5 24.5	5 64	64	47.5	25	N	/10 x 1	.5	15	100	9.2
CY1L40	11.5	14	8	41.6	25	10	20	5	10	10.5	130	78	12	35	30.5	28.5	5 76	74	56	30	Ν	/10 x 1	.5	15	136	9.2
Model	м	M	N	(N)	(NA)	(NB))	NN	I		Р	PA ³	P	BF	PW	Q	QW	RW	т	ta	tb	TT	w	z	Shock a	ibsorber
CY1L15	8	M5 x	0.8	8.5	27	17	N	18 x	1.0	M5	x 0.8	45	7	70	95	90	30	15	12.5	0.5	1.0	22.5	92	112	RB0	805
CY1L20	10	M6 x	1.0	10.5	29	20	M	10 x	1.0	Ro	; 1/8	50	9	90 1	20	105	40	28	16.5	_	—	25.5	117	130	RB1	006
CY1L25	10	M6 x	1.0	12.5	49	40	M	14 x	1.5	Ro	; 1/8	60	10	00 1	30	105	50	22	16.5	0.5	1.0	25.5	127	130	RB1	411
CY1L32	12	M8 x	1.25	13.5	52	42	M	20 x	1.5	Ro	; 1/8	70	12	20 1	60	121	60	33	18.5	0.5	1.0	28.5	157	149	-RB2	015
CY1L40	12	M8 x	1.25	12.5	51	36	M	20 x	1.5	Ro	; 1/4	90	14	10 1	90	159	84	35	20.5	1.0	1.0	35.5	187	194		.015

* PA dimensions are for split from center.

D-

CY3B CY3R

CY1S

CY1L CY1H

CY1F Cyp

CY1L Series Auto Switch Mounting

Proper Auto Switch Mounting Position (Detection at stroke end)



			Applicable	auto switch	I					
Bore size (mm)	D-A7:	3/A80	D-A72 D-A70H D-A73C D-F70/ D-F70V D-F70V D-F70V D-F7BA D-F79F	/A80C J79 /J79C //J79C //J79W /V	D-F7NT					
	Α	В	Α	в	Α	В				
6	23	45	23.5	44.5	28.5	39.5				
10	58	45	58.5	44.5	63.5	39.5				
15	65	47	65.5	46.5	70.5	41.5				
20	76	54	76.5	53.5	81.5	48.5				
25	76	54	76.5	53.5	81.5	48.5				
32	92	57	92.5	56.5	97.5	51.5				
40	130	64	130.5	58.5						

Note 1) 50 mm is the minimum stroke available with 2 auto switches mounted. In the case of a stroke less than this, please contact SMC.

Note 2) Adjust the auto switch after confirming the operating conditions in the actual setting.

Mounting of Auto Switch

When mounting an auto switch, the auto switch mounting screw should be screwed into a hexagon nut (M3 x 0.5) which has been inserted into the groove of the switch mounting rail. (Tightening torque: Approx. 0.5 to 0.7 N •m)



Operating Range

							(mm)			
Auto switch model		Bore size								
	6	10	15	20	25	32	40			
D-A7[]/A8[]	6	6	6	6	6	6	6			
D-F7□/J7□	3	3	4	3	3	3	3.5			
D-F79F	4.5	4.5	4.5	4.5	4.5	4.5	4.5			

Since this is a guideline including hysteresis, not meant to be guaranteed. (Assuming approximately $\pm 30\%$ dispersion) There may be the case it will vary substantially depending on an ambient environment.

Other than the models listed in "How to Order", the following auto switches are applicable.

For detailed specifications refer to page 1627

Туре	Model	Electrical entry (Fetching direction)	Features					
Solid state auto switch	D-F7NT	Grommet (In-line)	With timer					
* With pre-wired connector is available for D-F7NT type, too. For details, refer to pages 1648 and 1649.								



CY1L Series Specific Product Precautions

Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions and pages 3 to 12 for Actuator and Auto Switch Precautions.

Operation

Warning

1. Be aware of the space between the plates and the slide block.

Take sufficient care to avoid getting your hands or fingers caught when the cylinder is operated.

2. Do not apply a load to a cylinder which is greater than the allowable value stated in the "Model Selection" pages.

This may cause malfunctions.

- 3. Do not use the cylinder in an environment where the cylinder is expose to moisture, adhesive foreign matter, dust or liquid such as water or cutting fluid. If the cylinder is used in an environment where the lubrication of the cylinders sliding parts is compromised, please consult SMC.
- 4. When applying grease to the cylinder, use the grease that has already been applied to the product. Contact SMC for available grease packs.

Mounting

ACaution

1. Avoid operation with the external slider fixed to the mounting surface.

The cylinder should be operated with the plates fixed to the mounting surface.

2. Make sure that the cylinder mounting surface is a flatness of 0.2 mm or less.

If the flatness of the cylinder mounting surface is not appropriate, 2 guide shafts may be twisted. This may adversely affect the operating conditions and shorten the service life due to the increase of sliding resistance and the early abrasion of bearings.

The cylinder mounting surface must be a flatness of 0.2 mm or less, and the cylinder must be mounted as it smoothly operates through the full stroke at the minimum operating pressure (0.18 MPa or less).

Service Life and Replacement Period of Shock Absorber

ACaution

1. Allowable operating cycle under the specifications set in this catalog is shown below.

1.2 million times RB08

2 million times RB10 to RB2725

- Note) Specified service life (suitable replacement period) is the value at room temperature (20 to 25°C).
 - The period may vary depending on the temperature and other conditions. In some cases the absorber may need to be replaced before the allowable operating cycle above.

Disassembly and Maintenance

A Warning

1. Use caution as the attractive power of the magnets is very strong.

When removing the external slider and piston slider from the cylinder tube for maintenance, etc., handle with caution, since the magnets installed in each slider have a very strong attractive force.

▲ Caution

1. Use caution when removing the external slider, as the piston slider will be directly attracted to it.

When removing the external slider or piston slider from the cylinder tube, first force the sliders out of their magnetically coupled positions, and then remove them individually when there is no longer any holding force. If they are removed while slill magnetically coupled, they will be directly attracted to one another and will not come apart.

- 2. Since the magnetic holding force can be changed (for example, from CY1L25L to CY1L25H), please contact SMC if this is necessary.
- 3. Do not disassemble the magnetic components (piston slider, external slider).

This can cause a loss of holding force and malfunction.

- When disassembling to replace the seals and wear ring, refer to the separate disassembly instructions.
- 5. Use caution to the direction of the external slider and the piston slider.

Since the external slider and piston slider are directional for σ 6, σ 10 and holding force type L, refer to the figures below when performing disassembly or maintenance. Put the external slider and piston slider together, and insert the piston slider into the cylinder tube so that they will have the correct positional relationship as shown in Fig. (1). If they align as shown in Fig. (2), insert the piston slider after turning it around 180°. If the direction is not correct, it will be impossible to obtain the specified holding force.





Fig. (1) Correct position

Fig. (2) Incorrect position

Example of ø15 with holding force type L

D--X Technical Data

CY3B CY3R

CY1S

CY1L CY1H

CY1F

CYP



Linear Guide Type

CY1H Series

Single Axis Type: Ø10, Ø15, Ø20, Ø25/Double Axis Type: Ø25, Ø32





CY1H Series Model Selection



Model Selection CY1H Series

Caution on Design (1)

The maximum load mass and allowable moment will differ depending on the workpiece mounting method, cylinder mounting orientation and piston speed. A determination of usability is performed based on the operating limit values in the graphs with respect to operating conditions, but the total ($\Sigma \alpha n$) of the load factors (αn) for each mass and moment should not exceed 1.



Wmax, Mmax and Me max values are according to graph (1), (2) and (3) below.



@SMC

1525

CY3B

CY3R

CY1S

CY1L

CY1H

CY1F

CYP

D-

-X□

Technical

Data

CY1H Series

Selection Calculation -

The selection calculation finds the load factors (α n) of the items below, where the total ($\Sigma \alpha$ n) does not exceed 1.

∑Ωn = Ω	$\lambda_1 + \alpha_2 + \alpha_3 \le 1$	
Item	Load factor $lpha$ n	Note
1. Max. load mass	Cℓ1 = W/Wmax	Examine W. Wmax is the max. load mass for Va.
2. Static moment	CL2 = M/Mmax	Examine M1, M2, M3. Mmax is the allowable moment for Va.
3. Dynamic moment	013 = Me/Memax	Examine Me1, Me3. Memax is the allowable moment for V.
		V: Collision speed Va : Average speed

Calculation Example

Operating Conditions
 Operating Conditions
 Cylinder: CYIHI5
 Cushion: Standard (Adjusting bolt)
 Mounting: Horizontal wall mounting
 Speed (average): Va = 300 [mm/s]
 Load mass: W = 1 [kg] (excluding mass of arm section)
 LI = 50 [mm]



Item	Load factor Qn	Note
Maximum load mass	α1 = W/Wmax = 1/9 = 0.111	Examine W. Find the value of Wmax when Va = 300 mm/s from Graph (1).
Static moment		Examine M2. Since M1 & M3 are not generated, investigation is unnecessary. Find the value M2 max when Va = 300 mm/s from Graph (3).
BDynamic moment We Guide central axis Guide central axis Met	From V = 1.4 Va We = $\delta \cdot W \cdot V$ = 4/100 · 10 · 1.4 · 300 = 168 [N] Mes = 1/3 · We (L ₂ - A) = 1/3 · 168 · 0.032 = 1.8 [N-m] C(3 = Mes/Mes max = 1.8/7.2 = 0.250	Examine Mes. Find the load equivalent to impact We. Damper coefficient $\delta = 4/100$ (urethane damper) Find the value of Mes max when V = 1.4 and $Va = 420$ mm/s from Graph (2).
	Me1 = 1/3 · We · L1 = 1/3 · 168 · 0.05 = 2.8 [N·m] 0/4 = Me1/Me1 max = 2.8/7.2 = 0.389	Examine Me 1. From above, We = 168 Find the value of Mes max when V = 1.4 and Va = 420 mm/s from Graph (2).

$$\begin{split} \Sigma \Omega n &= \Omega 1 + \Omega 2 + \Omega 3 + \Omega 4 \\ &= 0.111 + 0.031 + 0.250 + 0.389 \end{split}$$

= 0.781

Can be used based on $\Sigma \Omega n = 0.781 \le 1$

Model Selection CY1H Series



Vertical Operation

When using in vertical operation, prevention of workpiece dropping due to breaking of the magnetic coupling should be considered. The allowable load mass and maximum operating pressure should be as shown in the table below. When the cylinder is mounted vertically or sidelong, sliders may move downwards due to the self-weight or workpiece mass. If an accurate stopping position is required at the stroke end or the middle-stroke, use an external stopper to secure accurate positioning.

Model	Allowable load mass (Wv) (kg)	Maximum operating pressure Pv (MPa)
CY1H10	2.7	0.55
CY1H15	7.0	0.65
CY1H20	11.0	0.65
CY1H25	18.5	0.65
CY1HT25	18.5	0.65
CY1HT32	30.0	0.65

Intermediate Stop (1) Intermediate Stopping of Load with External Stopper, etc.

When stopping a load in mid-stroke using an external stopper, etc.,operate within the operating pressure limits shown in the table below. The magnetic coupling will break if operated at a

	pressure exceeding these limits.						
]	Model	Operating pressure limit for intermediate stop Ps (MPa)					
1	CY1H10	0.55					
	CY1H15	0.65					
1	CY1H20	0.65					
1	CY1H25	0.65					
	CY1HT25	0.65					
]	CY1HT32	0.65					

(2) Intermediate Stopping of Load with Air Pressure Circuit

When stopping a load using an air pressure circuit, operate at or below the kinetic energy shown in the table below. The magnetic coupling will break if the allowable value is exceeded.

Model	Allowable kinetic energy for intermediate stop Es (J)	
CY1H10	0.03	D-🗆
CY1H15	0.13	
CY1H20	0.24	- ¥⊓
CY1H25	0.45	
CY1HT25	0.45	Technical
CY1HT32	0.88	Data



1527

Magnetically Coupled Rodless Cylinder Linear Guide Type **CY1H** Series

Single axis: Ø10, Ø15, Ø20, Ø25/Double axis: Ø25, Ø32



Refer to "Standard Stroke" on page 1529

Shook Abcorborg

Shock Absolucia									
Model	Turne	Bore size (mm)							
woder	Туре	10	15	20	25	32			
СҮ1Н	Standard (shock absorber RB series)	RB0805	RB0806	RB1006	RB1411	-			
CTIN	Shock absorber soft type RJ series type (-XB22)	RJ0806H		RJ1007H	RJ1412H	-			
OVIUT	Standard (shock absorber RB series)	_	_	_	RB1411	RB2015			
CY1HT -	Shock absorber soft type RJ series type (-XB22)	_	_	_	RJ1412H	_			

* The shock absorber service life is different from that of the CY1H cylinder.

Befer to "Specific Product Precautions" for each shock absorber for the replacement period. * The shock absorber soft type RJ series type (-XB22) is a made to order specification. For details, refer to page 1752

Applicable Auto Switches/Refer to pages 1575 to 1701 for further information on auto switches.

	ight				Load voltage		Auto switch model		Lead wire length (m)*												
Туре	Type Special function			Wiring (Output)	(C , S)				E F		try direction		3	5	Pre-wired connector	Applic	cable load				
		entry	Indicator	(Output)		DC	AC	Perpendicular	In-line	(Nil)	(L)	(Z)	CONNECTOR								
				3-wire (NPN)		5 V. 12 V		Y69A	Y59A	•	۰	0	0	IC							
ہ ج	_			3-wire (PNP)		5 V, 12 V		Y7PV	Y7P	•	۰	$\left \circ \right $	0	circuit							
Solid state auto switch	itoti				2-wire	12 V		12 V			Y69B	Y59B	•	•	$ \circ $		—	Deleu			
S S S	Diagnostic indication Grommet	ation	Yes	3-wire (NPN)	PN) 24 V	24 V	5 V. 12 V	—	Y7NWV	Y7NW	•	•	$ \circ $		IC	Relay, PLC					
등육	(2-color indicator)							3-wire (PNP)	5 V, 12 V	5 V, 12 V	Y7PWV	Y7PW	٠	٠	$\left \circ \right $	0	circuit	PLC			
a v				2-wire	1011	12 V		Y7BWV	Y7BW	•	•	$ \circ $		_							
	Water resistant (2-color indicator)	1	1]]]	1			2-wire		12 V			Y7BA**		•	$ \circ $			
Reed auto switch		Grommet	Yes	3-wire (NPN equivalent)	_	5 V	-	-	Z76	•	•	-	-	IC circuit	-						
lo s		_ Gronner					2-wire	24 V	12 V	100 V	_	Z73	•	•	•	-	—				
art		_	2-wire	24 V	5 V, 12 V	100 V or less	_	Z80	•	۲	-	-	IC circuit	Relay, PLC							

** Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.

Consult with SMC regarding water resistant types with the above model numbers.

* Lead wire length symbols: 0.5 m----- Nil (Example) Y7BW * Solid state auto switches marked with "O" are produced upon receipt of order. (Example) Y7BWL 3 m L 5 m..... Z

(Example) Y7BWZ

For details about auto switches with pre-wired connector, refer to pages 1648 and 1649.
 Normally closed (NC = b contact) solid state auto switches (D-Y7G/Y7H types) are also available. Refer to page 1595 for details.

* Auto switches are shipped together, (but not assembled).



Magnetically Coupled Rodless Cylinder Linear Guide Type CY1H Series

Symbol

Rubber bumper (Magnet type)





Made to Order: Individual Specifications (For details, refer to pages 1538.)

 Symbol
 Specifications

 -X168
 Helical insert thread specifications

Made to Order Specifications

Click here for details						
Symbol	Specifications					
-XB10	Intermediate stroke (Using exclusive body)					
-XB11	Long stroke					
-XB22	Shock absorber soft type RJ series type					

Theoretical Output

							(N)
Bore size	Piston area	O	oerati	ng pre	essur	e (MF	Pa)
(mm)	(mm ²)	0.2	0.3	0.4	0.5	0.6	0.7
10	78	15	23	31	39	46	54
15	176	35	52	70	88	105	123
20	314	62	94	125	157	188	219
25	490	98	147	196	245	294	343
32	804	161	241	322	402	483	563

Note) Theoretical output (N) = Pressure (MPa) x Piston area (mm²)

Amount of Adjustment by Adjusting Bolt

Stroke adjustment on one side of 15 mm (CY1H10/15/20) or 30 mm (CY1H25, CY1HT25, CY1HT32) can be performed with the adjustment bolt, but when the amount of adjustment exceeds 3 mm, the magnetic coupling may be broken depending on the operating conditions. Therefore, operation should conform to the intermediate stop conditions on page 1527.

Do not adjust strokes by moving the stopper, as this can cause cylinder damage.

Adjusting both	

	(1111)	
Model	Stroke adjustment range L	
CY1H10, CY1H15,	0 to 15	
CY1H20		
CY1H25, CY1HT25,	0.1- 00	
CY1HT32	0 to 30	

Specifications

					,	
Bore size (mm)	10	15	20	25	32	
Fluid	Air					
Action		Double acting				
Maximum operating pressure			0.7 MPa			
Minimum operating pressure	0.2 MPa					
Proof pressure	1.05 MPa					
Ambient and fluid temperature	-10 to 60°C (No freezing)					
Piston speed	70 to 500 mm/s					
Cushion (External stopper)	Urethane bumpers on both ends (Standard), Shock absorber (Option				orber (Option)	
Lubrication	Not required (Non-lube)					
Stroke length tolerance	0 to 1.8 mm					
Holding force (N)	53.9	137	231	363	588	
Piping	Centralized piping type					
Piping port size	M5 >	¢ 0.8		Rc ¹ /8		

Standard Stroke

Bore size (mm)	Number of axes	Standard stroke (mm) Note)	Maximum available stroke (mm)
10		100, 200, 300	500
15	1 axis	100, 200, 300, 400, 500	750
20		100, 200, 300, 400, 500, 600	1000
25		100, 200, 300, 400, 500, 600, 800	1000
25	2 axis	100, 200, 300, 400, 500,	1200
32	2 0/13	600, 800, 1000	1500

Note) Strokes are manufacturable in 1 mm increments up to the maximum strokes. Suffix "-XB10" to the end of the part number for intermediate strokes excluding standard strokes and "XB11" for strokes exceeding standard strokes up to the manufacturable maximum strokes.

Weight

....

								(KG)
				Standard s	troke (mm)			
Model	100	200	300	400	500	600	800	1000
CY1H10	1.0	1.3	1.6	—	—	—	—	—
CY1H15	2.2	2.7	3.2	3.6	4.1	—	—	—
CY1H20	3.0	3.5	4.0	4.4	4.9	5.4	—	—
CY1H25	4.6	5.3	6.0	6.6	7.3	8.0	9.4	—
CY1HT25	5.1	6.2	7.3	8.3	9.4	10.4	12.5	14.6
CY1HT32	8.4	9.6	10.7	11.9	13.0	14.2	16.5	18.8

Shock Absorber Specifications

Applicable cylinde	r size (mm)	10	15	20	25	32
Shock absorber mod	lel	RB0805	RB0806	RB1006	RB1411	RB2015
Maximum energy absorption (J)		0.98	2.94	3.92	14.7	58.8
Stroke absorption (mm)		5	6	6	11	15
Collision speed (m/s) *		0.05 to 5				
Max. operating frequency (cycle/min)		80		70	45	25
Spring force (N)	Extended	1.	96	4.22	6.86	8.34
Spring lorce (N)	Retracted	3.83	22	6.18	15.30	20.50
Weight (g)		1	5	25	65	150

frequency can be increased according to the energy absorption. The shock absorber service life is different from that of the CY1H cylinder. Refer to the Specific Product Precautions for the replacement period. CY1F

CYP



CY1H Series

Construction Note)

Single axis type / CY1H



Component Parts

No.	Description	Material	Note
1	Body	Aluminum alloy	Anodized
2	Plate A	Aluminum alloy	Anodized
3	Plate B	Aluminum alloy	Anodized
4	Cylinder tube	Stainless steel	
5	Piston	Aluminum alloy	Chromated
6	Piston nut	Carbon steel	Zinc chromated (Except CY1H10/15)
7	Shaft	Stainless steel	
8	Piston side yoke	Rolled steel plate	Zinc chromated
9	External slider side yoke	Rolled steel plate	Zinc chromated
10	Magnet A	—	
11	Magnet B	—	
12	External slider tube	Aluminum alloy	
13	Spacer	Rolled steel plate	Nickel plated
14	Space ring	Aluminum alloy	Chromated (Except CY1H10)
15	Slide table	Aluminum alloy	Anodized
16	Side plate A	Aluminum alloy	Anodized
17	Side plate B	Aluminum alloy	Anodized
18	Internal stopper	Aluminum alloy	Anodized
19	Stopper	Aluminum alloy	Anodized
20	Shock absorber	—	RB series
21	Adjusting bolt	Chrome molybdenum steel	Nickel plated
22	Adjusting bumper	Urethane rubber	
23	Linear guide	—	
24	Top cover	Aluminum alloy	Anodized
25	Dust cover	Special resin	
26	Magnet (For auto switch)	—	
	/		

No.	Description	Material	Note
27	Parallel pin	Carbon steel	Nickel plated
28	Square nut for body mounting	Carbon steel	Nickel plated
29*	Wear ring A	Special resin	
30*	Wear ring B	Special resin	
31*	Piston seal	NBR	
32*	Scraper	NBR	
33*	O-ring	NBR	
34*	O-ring	NBR	

Note) 4 square nuts for body mounting are included regardless of strokes.

Replacement Parts: Seal Kit

Bore size (mm)	Kit no.	Contents
10	CY1H10-PS	Set of the above nos. 30, 31, 32, 33, 34
15	CY1H15-PS	Set of the above nos.
20	CY1H20-PS	29, 30, 31, 32, 33, 34
25	CY1H25-PS	23, 30, 31, 32, 33, 34

Note 1) Seal kit includes 20 to 30. Order the seal kit, based on each bore size. Note 2) For replacement of the o10 wear ring A, contact SMC or your nearest sales representative.

* Seal kit includes a grease pack (e10: 5 and 10 g, e15 to e25: 10 g). Order with the following part number when only the grease pack is needed. Grease pack part no. for e10: GR-F-005 (5 g) for external sliding parts, GR-S-010 (10 g) for tube interior

Grease pack part no. for ø15 to ø25: GR-S-010 (10 g)



Magnetically Coupled Rodless Cylinder Linear Guide Type CY1H Series

Construction

Double axis type / CY1HT



Component Parts

No.	Description	Material	Material
1	Body	Aluminum alloy	Anodized
2	Plate	Aluminum alloy	Anodized
3	Cylinder tube	Stainless steel	
4	Piston	Aluminum alloy	Chromated
5	Piston nut	Carbon steel	Zinc chromated
6	Shaft	Stainless steel	
7	Piston side yoke	Rolled steel plate	Zinc chromated
8	External slider side yoke	Rolled steel plate	Zinc chromated
9	Magnet A	-	
10	Magnet B	-	
11	External slider tube	Aluminum alloy	
12	Spacer	Rolled steel plate	Nickel plated
13	Space ring	Aluminum alloy	Chromated (Except CY1HT32)
14	Slide table	Aluminum alloy	Anodized
15	Side plate	Aluminum alloy	Anodized (Except CY1HT32)
16	Internal stopper	Aluminum alloy	Anodized
17	Stopper	Aluminum alloy	Anodized
18	Shock absorber	-	RB series
19	Adjusting bolt	Chrome molybdenum steel	Nickel plated
20	Adjusting bumper	Urethane rubber	
21	Linear guide	_	
22	Top cover	Aluminum alloy	Anodized
23	Dust cover	Special resin	
24	Magnet (For auto switch)	_	
25	Parallel pin	Stainless steel	

No.	Description	Material	Material	CY3B
26	Square nut for body mounting	Carbon steel	Nickel plated	CY3R
27	Hexagon socket head taper plug	Carbon steel	Nickel plated	eren
28*	Wear ring A	Special resin		CY1S
29*	Wear ring B	Special resin		•
30*	Piston seal	NBR		CY1L
31*	Scraper	NBR		ULL
32*	O-ring	NBR		01/411
33*	O-ring	NBR		CY1H

Note) 4 square nuts for body mounting are included regardless of strokes.

Replacement Parts: Seal Kit

inopiaconiterit i arte		
Bore size (mm)	Kit no.	Contents
25	CY1HT25-PS	Set of the above nos.
32	CY1HT32-PS	28, 29, 30, 31, 32, 33

* Seal kit includes 28 to 33. Order the seal kit, based on each bore size.

* Seal kit includes a grease pack (10 g).

Order with the following part number when only the grease pack is needed. Grease pack part no.: GR-S-010 (10 g)

D-🗆
-X□
Technical
Data
Data

CY1F

CYP

CY1H Series

Dimensions

Single axis type / Ø 10

CY1H10







Single axis type / Ø15, Ø20, Ø25 CY1H15/20/25







				I																		CY3B CY3R
																-					(mm)	CY1S
	Model	A	EA	\ EI	В Н	I H	A HE	3 H	с но	3 HF	• нт	Γ	J	L	LL	LW	M	MM	N	NL	NT	
	CY1H15	97	26.	5 2 [.]	1 46	3 33	.5 33.	5 45	17	42	19	N	/15 x 0.8	106	44	71.5	M5 x 0.8	8	16.5	15	8	CY1L
	CY1H20	102.5	26.	5 22	2 54	1 42	.5 41.	5 53	16	50	23.	5 N	//5 x 0.8	108	48.5	75.5	M5 x 0.8	8	18	15	8	
	CY1H25	125	29	24	4 63	3 46	46	61	.5 25	58.	5 28	N	/16 x 1.0	138	56	86	M6 x 1.0	10	20.5	18	9	CY1H
_		Р		DA	PB	PP	S	T14/	14/	XA	ХВ	7	ZZ									
	Model	P		PA	РВ	PP	5	TW	W	XA	хв	2										
	CY1H15	M5 x	0.8	50	62	21	161	65	88.5	—	-	194	17.5									CY1F
	CY1H20	Rc1/	/8	50	65	23	169	70	92.5	—	-	205	19.5									
_	CY1H25	Rc1/	/8	65	75	27	209	75	103	11.3	9.5	250	23.5									CYP



Dimensions

Double axis type: $/\emptyset 25, \emptyset 32$ CY1HT25/32











																			(mm)
Model	Α	EA	EB	Н	HA	HB	HC	HG	HP	HT	ſ	LL	LW	M	MM	N	NL	NT	PA
CY1HT25	125	28.5	79	63	46	46	61.5	19.5	58.5	35	M6 x 1.0	56	119	M6 x 1.0	10	20.5	18	9	65
CY1HT32	132.5	30	90	75	52.5	57.5	72.5	25	69.5	43	M8 x 1.25	63.5	130	M8 x 1.25	12	23	22.5	12	66
Model	PB	PP	PS	6	TW	w	XA	ХВ	7										
	FD	FF	гə	3	1 44	VV	N A	VD	2										
CY1HT25	108	18	51	209	110	136	11.3	9.5	250										
CY1HT32	115	14	61	219	124	150	9.7	2	265										

SMC

CY1H Series Auto Switch Mounting

Proper Auto Switch Mounting Position (Detection at stroke end)

Piping port surface



	Applicable auto switch						
Cylinder model	D-Z7 🗆 / Z80/ Y5 🗆 / Y6 🗆 / Y7 🗆						
	Α	В					
CY1H10	65.5	59.5					
CY1H15	72	122					
CY1H20	77.5	127.5					
CY1H25	86	164					
CY1HT25	86	164					
CY1HT32	82	183					

 \ast 50 mm is the minimum stroke available with 2 auto switches mounted. Please contact SMC in the case of a stroke less than this.

Note) Adjust the auto switch after confirming the operating conditions in the actual setting.

Mounting of Auto Switch



Note) Use a watchmaker's screwdriver with a grip diameter of 5 to 6 mm to tighten the auto switch mounting screws (attached to the auto switch).

The tightening torque should be 0.05 to 0.1 N•m.

Auto Switch Lead Wire Containment Groove

On models CY1H20 and CY1H25 a groove is provided on the side of the body (one side only) to contain auto switch lead wires. This should be used for management of wiring.



Operating Range

						(mm)
Cylinder model	Auto switch model		B	ore siz	ze	
Cylinder model	Auto switch model	10	15	20	25	32
CY1H	D-Z7□/ Z80	8	6	6	6	-
	D-Y5□/ Y6□/ Y7□	6	5	5	5	-
OVAUT	D-Z7□/ Z80	-	-	-	6	9
CY1HT	D-Y5□/ Y6□/ Y7□	—	—	—	5	6

* Some auto switches cannot be mounted.

 Since this is a guideline including hysteresis, not meant to be guaranteed. (Assuming approximately ±30% dispersion)

There may be the case it will vary substantially depending on an ambient environment.

CY3B CY3R
CY1S
CY1L
CY1H
CY1F
CYP

D- □
-X□
Technical Data



CY1H Series Specific Product Precautions 1

Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions and pages 3 to 12 for Actuator and Auto Switch Precautions.

Operation

M Warning

1. Be aware of the space between the plates and the slide block.

Take sufficient care to avoid getting your hands or fingers caught when the cylinder is operated.

2. Do not apply a load to a cylinder which is greater than the allowable value stated in the "Model Selection" pages.

This may cause malfunctions.

- When the cylinder is used in a place where water or cutting oil may splash or the lubrication condition on the cylinder sliding parts would be deteriorated, please consult with SMC.
- 4. When applying grease to the cylinder, use the grease that has already been applied to the product. Contact SMC for available grease packs.

ACaution

 The unit can be used with a direct load within the allowable range, but when connecting to a load which has an external guide mechanism, careful alignment is necessary.

Since variation of the shaft center increases as the stroke becomes longer, a connection method should be devised which allows for this displacement.

- Since the guide is adjusted at the time of shipment, unintentional movement of the adjustment setting should be avoided.
- 3. This unit can be operated without lubrication. If lubrication is performed, use turbine oil Class 1 (with no additives), ISO VG32. (Machine oil and spindle oil cannot be used.)
- 4. Do not use the cylinder in an environment where the cylinder is expose to moisture, adhesive foreign matter, dust or liquid such as water or cutting fluid. If the cylinder is used in an environment where the lubrication of the cylinders sliding parts is compromised, please consult SMC.
- 5. Do not operate with the magnetic coupling out of position.

In case the magnetic coupling is out of position, push the external slider back into the correct position by hand at the end of the stroke (or correct the piston slider with air pressure).

6. Do not disassemble the magnetic components (piston slider, external slider).

This can cause a loss of holding power and malfunction.

Mounting

A Caution

- The interior is protected to a certain extent by the top cover, however, when performing maintenance, etc., take care not to cause scratches or other damage to the cylinder tube, slide table or linear guide by striking them or placing objects on them. Cylinder bores are manufactured to precise tolerances, so that even a slight deformation may cause faulty operation.
- Because the slider is supported by precision bearings, take care not to apply strong impacts or excessive moments to the table when loading a workpiece.

3. Mounting of the cylinder body

The body is mounted using the square nuts, which are included, in the two T-slots on the bottom of the body. Refer to the table below for mounting bolt dimensions and tightening torque.

Model		CY1H10	CY1H15	CY1H20	CY1H25	CY1HT32	
	Thread size	M4 x 0.7	M5 >	ĸ 0.8	M6 x	< 1.0	M8 x 1.25
Bolt dimensions	Dimension t	L-7	L-8	L-8	Ŀ	-9	L-12
Tightening torque	N · m	1.37	2.0	65	4	.4	13.2



Service Life and Replacement Period of Shock Absorber

▲Caution

1. Allowable operating cycle under the specifications set in this catalog is shown below.

1.2 million times RB08

2 million times RB10 III to RB2725

Note) Specified service life (suitable replacement period) is the value at room temperature (20 to 25°C).

The period may vary depending on the temperature and other conditions. In some cases the absorber may need to be replaced before the allowable operating cycle above.





CY1H Series Specific Product Precautions 2

Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions and pages 3 to 12 for Actuator and Auto Switch Precautions.



Loosen the hexagon nut, adjust the stroke with a hexagon wrench from the plate side, and secure by retightening the hexagon nut. When there is a shock absorber, loosenthe hexagon nut, adjust the stroke, and then retighten the hexagon nut.

Adjustment should be performed to make effective use of the shock absorber's absorption capacity, with its position relative to the adjustment bolt as shown in the figure to the right.

ACaution

 If the effective stroke of the shock absorber is shortened by the stroke adjustment, its absorption capacity will be drastically reduced. Therefore, the adjusting bolt should be secured at a position where it projects about 0.5 mm farther than the shock absorber.

Lock Nut Tig	Lock Nut Tightening Torque										
Model	For shock absorber For adjusting bo										
CY1H10	4.07										
CY1H15	1.67	1.67									
CY1H20	3.14										
CY1H25	10.0										
CY1HT25	10.8	3.14									
CY1HT32	23.5										



After completing the above adjustment, replace the top cover and dust covers back into place.

The round head Phillips screws for securing the top cover should be tightened with a torque of 0.58 N m.

CY3B CY3R
CY1S
CY1L
CY1H
CY1F
CYP

OVOD



CY1L/H Series Made to Order: Individual Specifications



Please contact SMC for detailed dimensions, specifications and lead times.

Applicable Series

No.	Symbol	Specifications/Description	Slider type					
NO.	Symbol	Specifications/Description	Ball bushing type CY1L	High precision guide type CY1H				
1	-X116	Hydro specifications	●(ø25 to ø40)	—				
2	-X168	Helical insert thread specifications	●(ø20 to ø40)	●(ø20 to ø32)				
3	-X322	Outside of cylinder tube with hard chrome plated	●(ø15 to ø40)	—				
4	-X431	Auto switch rails on both side faces (With 2 pcs.)	●(ø6 to ø40)	—				

1 Hydro Specifications



This type is applicable for precision constant speed feed, intermediate stop and skip feed.

[Slider type]



Hydro specifications

Specifications

Туре	Slider type				
Bore size	Slider type CY1L25 to 40				
Fluid	Turbine oil				
Piston speed	15 to 300 mm/s				

Note) Piping is from each plate on both sides.

Dimensions



				(mm)
Model	HTA	HTB	Р	Throttle dia.
CY1L25	20	23	Rc ¹ /8	8.2
CY1L32	24	26.5	Rc 1/8	8.2
CY1L40	25	30.5	Rc ¹ ⁄4	11

* Dimensions other than the above are the same as the standard type.



Specifications

opeomoutions	
Applicable Series	CY1L/CY1H
Bore size	CY1L : ø20 to ø40 CY1H: ø20 to ø32
	Symbol



Outside of cylinder tube with hard chrome plated

The cylinder tube outer circumference is plated with hard chrome, which further reduces bearing abrasion. Note) The slider type (slide block) is provided with a greasing port.

Specifications

Applicable Series	Bore size (mm)
CY1L	ø15 to ø40

Construction/Dimensions

CY1L (Slider type)



		(mm)
Bore size	CY1L	
(mm)	NA	HW
15	33.0	37.5
20	38.0	43.0
25	43.0	43.0
32	50.0	50.0
40	61.0	68.0



Made to Order: Individual Specifications CY1L/H Series



SMC

Bore size (mm)	Applicable stroke (mm)
6	20 to
10 15 20 25	25 to
32 40	35 to

CY3B CY3R
CY1S
CY1L
CY1H
CY1F
CYP

