

3 Port Solenoid Valve


VQZ100/200/300 Series

Metal Seal

Rubber Seal




Power consumption: **0.35 w / 0.9 w**
 (Standard)
 (High pressure type,
 High speed response type)



Compact, High Flow







Series	Valve width (mm)	Flow rate characteristics	
		Metal seal C [dm ³ /(s·bar)]	Rubber seal C [dm ³ /(s·bar)]
Body ported	VQZ100	10	—
	VQZ200	15	1.3
	VQZ300	18	2.4
Base mounted	VQZ100	10	—
	VQZ200	15	2.0
	VQZ300	18	3.2



Metal Seal / Rubber Seal 3 Port Solenoid Valve


VQZ100/200/300

Solenoid Valve Variations

		Sonic conductance C [dm ² /(s·bar)]		Type of actuation	Voltage	Electrical entry	Light/Surge voltage suppressor	Manual override
Body ported	3 port	VQZ100	Metal — Rubber (Poppet) 0.56					
		 P.1014						
		VQZ200	1.3 1.7			Grommet (G)		
Base mounted	3 port	VQZ300	2.4 3.0	 N.C.	(Standard) 12 VDC 24 VDC	L-type plug connector (L)	With light/surge voltage suppressor	Non-locking push type (Tool required)
		 P.1015			(Option) 100 VAC 200 VAC 110 VAC 220 VAC	M-type plug connector (M)	L-type plug connector (L) M-type plug connector (M)	
		VQZ100	Metal — Rubber (Poppet) 1.0	 N.O. (Except VQZ100)		DIN terminal (Y)	DIN terminal (YZ) (Except VQZ100)	Locking type (Tool required)
Base mounted	3 port	VQZ200	2.0 3.0			 P.1031		
		VQZ300	3.2 4.1			 P.1031		

Manifold


Body Ported



P.1021

Series	Base model	Piping specifications			Applicable solenoid valve	Applicable stations
		Piping direction	Bore size			
			1(P), 3(R)	2(A)		
VQZ100	VV3QZ12-□□□	Top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations
VQZ200	VV3QZ22-□□□	Top	Rc 1/8	C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ2□2	2 to 20 stations
VQZ300	VV3QZ32-□□□	Top	Rc 1/4	C6 (for ø6) C8 (for ø8) C10 (for ø10) Rc 1/4	VQZ3□2	2 to 20 stations

Base Mounted




P.1037

Series	Base model	Piping specifications			Applicable solenoid valve	Applicable stations
		Piping direction	Bore size			
			1(P), 3(R)	2(A)		
VQZ100	VV3QZ15-□□□	Side/top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations
VQZ200	VV3QZ25-□□□	Side	Rc 1/4	C4 (for ø4) C6 (for ø6) C8 (for ø8) Rc 1/8	VQZ2□5	2 to 20 stations
VQZ300	VV3QZ35-□□□	Side	1(P) port Rc 3/8 3(R) port Rc 1/4	C6 (for ø6) C8 (for ø8) C10 (for ø10) Rc 1/4	VQZ3□5	2 to 20 stations

Manifold Options

Body Ported


Blanking plate assembly
VVQZ100-10A-5
(for VQZ100)
VVQZ200-10A-2
(for VQZ200)
VVQZ300-10A-2
(for VQZ300)



P.1027

Blanking plug


KQ2P-23
KQ2P-04
KQ2P-06
KQ2P-08
KQ2P-10



P.1027


DIN rail

AXT100-DR-□



P.1027


Silencer
(for EXH port)



P.1027

Base Mounted


Blanking plate assembly
VVQZ100-10A-5
(for VQZ100)
VVQZ200-10A-5
(for VQZ200)
VVQZ300-10A-5
(for VQZ300)



P.1044

Blanking plug


KQ2P-23
KQ2P-04
KQ2P-06
KQ2P-08
KQ2P-10



P.1044


DIN rail

AXT100-DR-□



P.1044

Silencer
(for EXH port)



P.1044

Port plug
VVQZ100-CP (for VQZ100)



P.1044

Body Ported

Plug Lead Unit

3 Port Solenoid Valve

VQZ100/200/300 Series

Single Unit



[Option]

Note) CE/UKCA-compliant:DC type only.


VQZ100 / How to Order Valve

VQZ 1 1 5 - 5 M 1 - C6 - PR -

Series

1 VQZ100 body width 10 mm

Type of actuation



Body type

Function

Symbol	Specifications	DC	AC
Nil	Standard	○ (0.35 W)	○ Note 3)
K Note 1)	High pressure type	○ (0.9 W)	—
R Note 1, 2)	External pilot type	○	○
KR Note 1, 2)	High pressure/External pilot type	○ (0.9 W)	—

Note 1) Semi-standard

Note 2) For details on external pilot type, refer to page 1028.

Note 3) For AC specification power consumption, refer to page 1016.



Caution
Use standard (DC) specification for continuous duty.

Coil voltage

		CE/UKCA-compliant
1	100 VAC (50/60 Hz)	—
2	200 VAC (50/60 Hz)	—
3	110 VAC [115 VAC] (50/60 Hz)	—
4	220 VAC [230 VAC] (50/60 Hz)	—
5	24 VDC	●
6	12 VDC	●


CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

Note) DC type only.

Option

Nil: None
F: With bracket




Port size [2(A) port]

C3	ø3.2 One-touch fitting
C4	ø4 One-touch fitting
C6	ø6 One-touch fitting
M5	M5 thread (Replaceable type)

Note) For inch size One-touch fittings, refer to page 1028.

Manual override



Electrical entry

G: Grommet (DC specification)	L: L-type plug connector with lead wire	LO: L-type plug connector without connector	M: M-type plug connector with lead wire	MO: M-type plug connector without connector
	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor

Note) Standard lead wire length: 300 mm

Note) For applicable One-touch fitting and silencer models for this valve series, refer to page 1050.

Note) Manifold mounting screws and gaskets are included with the manifold, but they are not included when ordering a body ported solenoid valve as a single unit. Order them separately if necessary. (For details, refer to page 1029.)

VQZ200/300 / How to Order Valve



Made to Order

(For details, refer to pages 1016 and 1047.)

Note) AC-type models that are CE/UKCA-compliant have DIN terminals only.



[Option]

VQZ 2 1 2 - 5 M 1 - C6 - -

Series

2	VQZ200 body width 15 mm
3	VQZ300 body width 18 mm

Type of actuation

	N.C.	2(A)	
1			Metal seal
2			Metal seal
3			Rubber seal
4			Rubber seal

Body type

2	Body ported
---	-------------

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) Note 3)	(0.9 W)
B Note 1)	High speed response type	(0.9 W)	—
K Note 1)	High pressure type (Metal seal type only)	(0.9 W)	—
R Note 1, 2)	External pilot type	○	○
BR Note 1, 2)	High speed response/External pilot type	(0.9 W)	—
KR Note 1, 2)	High pressure/External pilot type (Metal seal type only)	(0.9 W)	—

Note 1) Semi-standard

Note 2) For details on external pilot type, refer to page 1028.

Note 3) For AC specification power consumption, refer to page 1016.

Caution

Use standard (DC) specification for continuous duty.

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

IP65 compliant

Nil	—
W Note)	Compliant

Note) VQZ200/300 DIN terminal rubber seal only (except external pilot). For details on IP65 enclosure, refer to page 1028.


CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

Note) AC-type models that are CE/UKCA-compliant have DIN terminals only.

Option

Nil: None
F: With bracket



Port size [2(A) port]

Symbol	Port size	VQZ200	VQZ300
C4	ø4 One-touch fitting	○	—
C6	ø6 One-touch fitting	○	○
C8	ø8 One-touch fitting	—	○
C10	ø10 One-touch fitting	—	○
M5	M5 thread	○	—
O2	Rc 1/4	—	○

Note) For inch size One-touch fittings and option thread type, refer to page 1028.

Manual override

Nil: Non-locking push type (Tool required)	B: Locking type (Tool required)
--	---------------------------------

Electrical entry

	G: Grommet (DC specification)	L: L-type plug connector with lead wire	LO: L-type plug connector without connector	M: M-type plug connector with lead wire	MO: M-type plug connector without connector
	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor
CE/UKCA compliant	AC	—	—	—	—
	DC	●	●	●	●
	Y: DIN terminal	YO: DIN terminal without connector	YZ: DIN terminal	YOS: DIN terminal without connector (DC specification)	YS: DIN terminal (DC specification)
	With surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor
CE/UKCA compliant	AC	●	●	●	●
	DC	●	●	●	●

Note 1) Standard lead wire length: 300 mm



Note 2) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.

VQZ100/200/300 Series

Construction

VQZ100

Poppet type







Component Parts

No.	Description	Material	Note
1	Body	Resin	
2	Spool valve	Aluminum/HNBR	
3	Pilot valve assembly	—	
4	P. R plate	Resin/Aluminum	VQZ100-12A (Standard) VQZ100-12B (External pilot type) <small>Note)</small>





Note) It is not possible to change the standard product to external pilot type, and vice versa.

VQZ200/300

Metal seal type



Rubber seal type



Component Parts



No.	Description	Material	Note
1	Body	Aluminum die-casted	
2	Spool, Sleeve	Stainless steel	Metal seal
2	Spool valve	Aluminum/HNBR	Rubber seal
3	Piston	Resin	
4	Pilot valve assembly	—	

Note) For "How to Order Pilot Valve Assembly", refer to page 1029.

Dimensions: **VQZ200**

Single Unit


Grommet (G): VQZ2□□-□G□1-C4, C6




Note) For bracket assembly part no., refer to page 1029.

Note) For One-touch fittings for P/R port and silencer part no., refer to page 1050.

VQZ2□□-□G□1-M5




L-type plug connector (L): VQZ2□□-□L□1-C4, C6




Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

DIN terminal (Y): VQZ2□□-□Y□1-C4, C6



Unless otherwise indicated, dimensions are the same as Grommet (G).

M-type plug connector (M): VQZ2□□-□M□1-C4, C6





Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

VQZ100/200/300 Series

Dimensions: VQZ300


Single Unit

Grommet (G): VQZ3□2□-□G□1-C6, C8, C10




Note) For bracket assembly part no., refer to page 1029.

VQZ3□2□-□G□1-02




L-type plug connector (L): VQZ3□2□-□L□1-C6, C8, C10




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M): VQZ3□2□-□M□1-C6, C8, C10



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

DIN terminal (Y): VQZ3□2□-□Y□1-C6, C8, C10



Unless otherwise indicated, dimensions are the same as Grommet (G).

Body Ported
Plug Lead Unit

3 Port Solenoid Valve

VQZ100/200/300 Series

Manifold Connector Kit



[Option]
Note) For CE/UKCA-compliant models, DC type only.

VQZ100 / How to Order Manifold

VV3QZ 1 2 - 08 C - D -

Series
1 VQZ100

Manifold type
2 Body ported

Stations
02 2 stations
20 20 stations

Kit type
C Connector

CE/UKCA-compliant
Nil —
Q CE/UKCA-compliant

Option
Nil None
D DIN rail mounting (With standard DIN rail length)
D0 Note 1) DIN rail mounting (Without DIN rail)
R Note 2) External pilot type

Note 1) Order DIN rail separately.
For DIN rail part no., refer to page 1027.
Note 2) When two or more symbols are specified, indicate them alphabetically.

Note) For 1(P), 3(R) of optional thread type, refer to page 1028.

VQZ100 / How to Order Valve

VQZ 1 1 5 - 5 M 1 - C3 -

Series
1 VQZ100 body width 10 mm

Type of actuation
1 N.C.

Body type

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) ○	Note 3) ○
K Note 1)	High pressure type	(0.9 W) ○	—
R Note 1, 2)	External pilot type	○	○
KR Note 1, 2)	High pressure/External pilot type	(0.9 W) ○	—

Note 1) Semi-standard
Note 2) For details on external pilot type, refer to page 1028.
Note 3) For AC specification power consumption, refer to page 1016.

Manual override
Nil Non-locking push type
B Locking type (Tool required)

CE/UKCA-compliant
Nil —
Q CE/UKCA-compliant

Note) For CE/UKCA-compliant models, DC type only.

Port size [2(A) port]
C3 ø3.2 One-touch fitting
C4 ø4 One-touch fitting
C6 ø6 One-touch fitting
M5 M5 thread (Replaceable type)

Note) For inch size One-touch fittings, refer to page 1028.

Electrical entry

Symbol	Electrical entry	With light/surge voltage suppressor
G	Grommet (DC specification)	None
L	L-type plug connector with lead wire	Yes
LO	L-type plug connector without connector	
M	M-type plug connector with lead wire	
MO	M-type plug connector without connector	

Note) Standard lead wire length: 300 mm

Coil voltage

	CE/UKCA-compliant
1 100 VAC (50/60 Hz)	—
2 200 VAC (50/60 Hz)	—
3 110 VAC [115 VAC] (50/60 Hz)	—
4 220 VAC [230 VAC] (50/60 Hz)	—
5 24 VDC	●
6 12 VDC	●

Caution
Use standard (DC) specification for continuous duty.

VQZ100/200/300 Series

VQZ200/300 / How to Order Manifold



Made to Order
(For details, refer to page 1047.)

Note) AC-type models that are
CE/UKCA-compliant
have DIN terminals only.



VV3QZ 2 2 - 08 C - -

Series

2	VQZ200
3	VQZ300

Manifold type

2	Body ported
---	-------------

Stations

02	2 stations
:	:
20	20 stations

CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

Option

Nil	None
D	DIN rail mounting (With standard DIN rail length)
D0 Note)	DIN rail mounting (Without DIN rail)

Note) Order DIN rail separately.
For DIN rail part no., refer to page 1027.

Kit type

C	Connector
---	-----------

Note) For 1(P), 3(R) of optional thread
type, refer to page 1028.

VQZ200/300 / How to Order Valve

VQZ 2 1 2 - 5 M - - 1 - -

Series

2	VQZ200 body width 15 mm
3	VQZ300 body width 18 mm

Type of actuation

1	N.C. Metal seal
2	N.O. Metal seal
3	N.C. Rubber seal
4	N.O. Rubber seal

Body type

2	Body ported
---	-------------

Function

Symbol	Specifications	DC (0.35 W)	AC (Note 3)
Nil	Standard	○	○
B Note 1)	High speed response type	(0.9 W) —	—
K Note 1)	High pressure type (Metal seal type only)	(0.9 W) ○	—
R Note 1, 2)	External pilot type	○	○
BR Note 1, 2)	High speed response/External pilot type	(0.9 W) ○	—
KR Note 1, 2)	High pressure/External pilot type (Metal seal type only)	(0.9 W) ○	—

Note 1) Semi-standard
Note 2) For details on external pilot type, refer to page 1028.
Note 3) For AC specification power consumption, refer to page 1016.



Caution
Use standard (DC) specification for
continuous duty.

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

IP65 compliant

Nil	—
W Note)	Compliant

Note) VQZ200/300 DIN
terminal rubber
seal only (except
external pilot). For
details on IP65
enclosure, refer to
page 1028.

CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

Note) AC-type models that are
CE/UKCA-compliant have
DIN terminals only.

Port size [2(A) port]

Symbol	Port size	VQZ200	VQZ300
C4	ø4 One-touch fitting	○	—
C6	ø6 One-touch fitting	○	○
C8	ø8 One-touch fitting	—	○
C10	ø10 One-touch fitting	—	○
M5	M5 thread	○	—
O2	Rc 1/4	—	○

Note) For inch size One-touch fittings and optional thread
type, refer to page 1028.

Manual override

Nil	Non-locking push type (Tool required)
B	Locking type (Tool required)


Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor	CE/UKCA-compliant	
			AC	DC
G	Grommet (DC specification)	None	—	●
L	L-type plug connector with lead wire	Yes	—	●
LO	L-type plug connector without connector		—	●
M	M-type plug connector with lead wire		—	●
MO	M-type plug connector without connector		—	●
Y	DIN terminal	None	●	●
YO	DIN terminal without connector		●	●
YZ	DIN terminal		●	●
YS Note 2)	DIN terminal (DC specification)	Yes (Without light)	—	●
YOS Note 2)	DIN terminal without connector (DC specification)		—	●

Note 1) Standard lead wire length: 300 mm
Note 2) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.


Note) Manifold mounting screws and gaskets are included with
the manifold, but they are not included when ordering a
body ported solenoid valve as a single unit. Order them
separately if necessary. (For details, refer to page 1029.)

Manifold Specifications



Series	Base model	Piping specifications			Applicable solenoid valve	Applicable stations	Manifold base weight (g)
		Piping direction	Port size				
			1(P), 3(R)	2(A)			
VQZ100	VV3QZ12-□□□	Top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations	2 stations: 83 Addition per station: 19
VQZ200	VV3QZ22-□□□	Top	Rc 1/8	C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ2□2	2 to 20 stations	2 stations: 68 Addition per station: 20
VQZ300	VV3QZ32-□□□	Top	Rc 1/4	C6 (for ø6) C8 (for ø8) C10 (for ø10) Rc 1/4	VQZ3□2	2 to 20 stations	2 stations: 114 Addition per station: 37

How to Order Manifold Assembly (Example)



VV3QZ22-05C 1 set (C kit 5-station manifold base part no.)

* **VVQZ200-10A-2** ... 1 set (Blanking plate assembly part no.)

* **VQZ212-5M1-C6** ... 4 sets (N.C. type part no.)

→ The asterisk denotes the symbol for assembly. Prefix it to the part nos. of the solenoid valve, etc.

→ Enter in order starting from the first station on the D side.



Add the valve and option part number under the manifold base part number.

When entry of part numbers becomes complicated, indicate by the manifold specification sheet.


VQZ100/200/300 Series

Dimensions: VQZ100


VV3QZ12- Stations C



The dashed lines indicate the DIN rail mounting [-D].




L-type plug connector (L)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC


Dimensions

n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	85.5	98	110.5	123	135.5	148	148	160.5	173	185.5	198	210.5	210.5	223	235.5	248	260.5	273
L2	75	75	87.5	100	112.5	125	137.5	137.5	150	162.5	175	187.5	200	200	212.5	225	237.5	250	262.5
L3	43.5	54	64.5	75	85.5	96	106.5	117	127.5	138	148.5	159	169.5	180	190.5	201	211.5	222	232.5
L4	21	16	17	18	19	20	21	15.5	16.5	17.5	18.5	19.5	20.5	15.5	16.5	17.5	18.5	19.5	20.5
L5	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5

Dimensions: VQZ200


VV3QZ22- Stations C

Grommet (G)




The dashed lines indicate the DIN rail mounting [-D].

L-type plug connector (L)




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

DIN terminal (Y)



Unless otherwise indicated, dimensions are the same as Grommet (G).

Dimensions


n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	110.5	123	135.5	148	173	185.5	198	223	235.5	248	260.5	285.5	298	310.5	335.5	348	360.5	373
L2	75	100	112.5	125	137.5	162.5	175	187.5	212.5	225	237.5	250	275	287.5	300	325	337.5	350	362.5
L3	54	70	86	102	118	134	150	166	182	198	214	230	246	262	278	294	310	326	342
L4	16	20.5	18.5	17	15	19.5	18	16	20.5	19	17	15.5	20	18	16.5	21	19	17.5	15.5
L5	43	59	75	91	107	123	139	155	171	187	203	219	235	251	267	283	299	315	331

n: Stations (Max. 20 stations)


VQZ100/200/300 Series

Dimensions: VQZ300

VV3QZ32- Stations C




L-type plug connector (L)




Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

DIN terminal (Y)



Unless otherwise indicated, dimensions are the same as Grommet (G).

Dimensions

n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	98	110.5	135.5	148	173	198	210.5	235.5	248	273	285.5	310.5	323	348	360.5	385.5	398	423	435.5
L2	87.5	100	125	137.5	162.5	187.5	200	225	237.5	262.5	275	300	312.5	337.5	350	375	387.5	412.5	425
L3	61	80	99	118	137	156	175	194	213	232	251	270	289	308	327	346	365	384	403
L4	18.5	15.5	18.5	15	18	21	18	21	17.5	20.5	17.5	20.5	17	20	17	20	16.5	19.5	16.5
L5	49	68	87	106	125	144	163	182	201	220	239	258	277	296	315	334	353	372	391

Manifold Options


Blanking plate assembly

VVQZ100-10A-5 (for VQZ100)

VVQZ200-10A-2 (for VQZ200)

VVQZ300-10A-2 (for VQZ300)

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.



Blanking plug



KQ2P-23

KQ2P-04

KQ2P-06

KQ2P-08

KQ2P-10



Dimensions


(mm)

Applicable fitting size ød	Model	A	L	D
3.2	KQ2P-23	16	31.5	5
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12

DIN rail

AXT100-DR-□

* As for □, enter the number from the DIN rail dimensions table.
For L dimension, refer to the dimensions of each kit.



Each manifold can be mounted on a DIN rail.

Insert "D" at the end of the manifold part number.

The DIN rail is approximately 30 mm longer than the length of manifold.



L Dimension

No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L dimension	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
L dimension	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5

Silencer

(for manifold EXH port)

Silencer is installed in the manifold EXH port.



Dimensions

Model	Silencer part no.
VQZ100	AN110-01
VQZ200	AN110-01
VQZ300	AN20-02

For a silencer to be mounted in a single valve unit, refer to page 1050.

Semi-standard Specifications



Replacement Parts

One-touch Fitting Assembly (for Cylinder port)

Fitting size	C3	C4	C6	C8	C10	M5 (VQZ100 only)
Model						
VQZ100/200	VVQ1000-50A-C3	VVQ1000-50A-C4	VVQ1000-50A-C6	—	—	VVQ1000-50A-M5
VQZ300	—	—	VVQ1000-51A-C6	VVQ1000-51A-C8	VVQ1000-51A-C10	—

Note) Purchasing order is available in units of 10 pieces.

<Plug connector assembly>

DC: SY100-30-4A-□

100 VAC: SY100-30-1A-□

200 VAC: SY100-30-2A-□

Other AC voltages: SY100-30-3A-□

Without lead wire: **SY100-30-A**
(with connector and 2 sockets only)

Lead wire length

Nil	300 mm
6	600 mm
10	1000 mm
15	1500 mm
20	2000 mm
25	2500 mm
30	3000 mm
50	5000 mm

How to Order

Include the connector assembly part number together with the part number for the plug connector's solenoid valve without connector.

Example) In case of 2000 mm of lead wire

DC	AC
VQZ115-5LO1-M5-PR	VQZ115-1LO1-M5-PR
SY100-30-4A-20	SY100-30-1A-20

<Gasket and screw assembly>

Model	Part no.
VQZ100	VQZ100-GS-5
VQZ200	VQZ200-GS-2
VQZ300	VQZ300-GS-2

Note 1) The above part numbers are for 10 valves
(a set of 10 gaskets and 20 screws).

Note 2) VQZ100 is common to the body ported type and base mounted type.

<Bracket assembly>

Model	Part no.	Tightening torque (N·m) <small>Note)</small>
VQZ100	VQZ100-FB	0.25 to 0.35
VQZ200	VQZ200-FB	
VQZ300	VQZ300-FB	

Note) Tightening torque when mounting a bracket on the valve.

<Pilot valve assembly>

V111 □ □ — 5 G □ □

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) <input type="radio"/>	<input type="radio"/>
B <small>Note)</small>	High speed response type (Applicable to VQZ200/300)	(0.9 W) <input type="radio"/>	—
K <small>Note)</small>	High pressure type (Applicable to Metal seal type, Poppet seal type)	(0.9 W) <input type="radio"/>	—

Note) Semi-standard

Manual override

Nil	None (Applicable to VQZ200/300)
M	Yes (Applicable to VQZ100)

Manual override (Applicable to the VQZ100)

Nil	Non-locking push type
B	Locking slotted type

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor
DC AC		
G —	Grommet (DC specification)	None
LU LZ	L-type plug connector with lead wire	Yes
LOU LOZ	L-type plug connector without connector	
MU MZ	M-type plug connector with lead wire	
MOU MOZ	M-type plug connector without connector	

Note) VQZ pilot valve electrical entry (L, M) is the opposite of the how to order of valve body.

Valve model	Pilot valve model
VQZ115 □ □ □ □ □ 1	V111 □ □ □ □ □ □
VQZ115 □ □ □ □ □ 1	V111 □ □ □ □ □ □

<DIN terminal type (Applicable to the VQZ200/300)>

V115 □ □ — 5 Y — X110

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) <input type="radio"/>	<input type="radio"/>
B <small>Note)</small>	High speed response type	(0.9 W) <input type="radio"/>	—
K <small>Note)</small>	High pressure type (Metal seal type only)	(0.9 W) <input type="radio"/>	—

Note) Semi-standard

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor
Y	DIN terminal	None
YO	DIN terminal without connector	
YZ	DIN terminal with light/surge voltage suppressor	
YS <small>Note)</small>	DIN terminal with surge voltage suppressor (DC specification)	Yes
YOS <small>Note)</small>	DIN terminal with surge voltage suppressor, without connector (DC specification)	Yes (Without light)

Note) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.

⚠ Caution

When replacing only the pilot valve assembly, use caution because it is not possible to convert to a V115 (DIN terminal) from a V111 (Grommet, L-type, M-type), or vice versa.

Base Mounted
Plug Lead Unit

3 Port Solenoid Valve

VQZ100/200/300 Series

Single Unit



[Option]

Note) For CE/UKCA-compliant models, DC type only.


VQZ100 / How to Order Valve

VQZ 1 1 5 - 5 M 1 - 01 -

Series

1 VQZ100 body width 10 mm

Type of actuation



Body type

5 Base mounted

Function

Symbol	Specifications	DC (0.35 W)	AC (Note 3)
Nil	Standard	○	○
K Note 1)	High pressure type	○	—
R Note 1, 2)	External pilot type	○	○
KR Note 1, 2)	High pressure/External pilot type	○	—

Note 1) Semi-standard
Note 2) For details on external pilot type, refer to page 1045.
Note 3) For AC specification power consumption, refer to page 1032.



Caution
Use standard (DC) specification for continuous duty.

CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant


Note) For CE/UKCA-compliant models, DC type only.

Port size

CP	Without sub-plate
01	Rc 1/8

Note) For optional thread type, refer to page 1045.

Manual override



Electrical entry

G: Grommet (DC specification)	L: L-type plug connector with lead wire	LO: L-type plug connector without connector	M: M-type plug connector with lead wire	MO: M-type plug connector without connector
	With light/ surge voltage suppressor	With light/ surge voltage suppressor	With light/ surge voltage suppressor	With light/ surge voltage suppressor

Note) Standard lead wire length: 300 mm

Coil voltage

	CE/UKCA-compliant
1 100 VAC (50/60 Hz)	—
2 200 VAC (50/60 Hz)	—
3 110 VAC [115 VAC] (50/60 Hz)	—
4 220 VAC [230 VAC] (50/60 Hz)	—
5 24 VDC	●
6 12 VDC	●

Note) For sub-plate part no., refer to page 1046.
Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included.

VQZ200/300 / How to Order Valve



Made to Order

(For details, refer to pages 1032 and 1047.)

Note) AC-type models that are CE/UKCA-compliant have DIN terminals only.



[Option]

VQZ 2 1 5 - 5 M 1 -

Series

2	VQZ200 body width 15 mm
3	VQZ300 body width 18 mm

Type of actuation

	N.C.	2(A)	
1			Metal seal
	(R)S 1(P)		
2			Metal seal
	(R)S 1(P)		
3			Rubber seal
	(R)S 1(P)		
4			Rubber seal
	(R)S 1(P)		

Body type

5	Body mounted
---	--------------

Function

Symbol	Specifications	DC	AC
NII	Standard	(0.35 W)	
B Note 1)	High speed response type	(0.9 W)	
K Note 1)	High pressure type (Metal seal type only)	(0.9 W)	
R Note 1, 2)	External pilot type		
BR Note 1, 2)	High speed response/External pilot type	(0.9 W)	
KR Note 1, 2)	High pressure/External pilot type (Metal seal type only)	(0.9 W)	

Note 1) Semi-standard

Note 2) For details on external pilot type, refer to page 1045.

Note 3) For AC specification power consumption, refer to page 1032.



Caution
Use standard (DC) specification for continuous duty.

IP65 compliant

NII	—
W Note)	Compliant

Note) VQZ200/300 DIN terminal rubber seal only (except external pilot). For details on IP65 enclosure, refer to page 1045.

CE/UKCA-compliant

NII	—
Q	CE/UKCA-compliant

Note) AC-type models that are CE/UKCA-compliant have DIN terminals only.

Port size

Symbol	Port size	VQZ200	VQZ300
NII	Without sub-plate		
01	Rc 1/8		—
02	Rc 1/4		
03	Rc 3/8	—	

Note) For optional thread type, refer to page 1045.

Manual override

NII: Non-locking push type (Tool required)	B: Locking type (Tool required)

Electrical entry

	G: Grommet (DC specification)	L: L-type plug connector with lead wire	LO: L-type plug connector without connector	M: M-type plug connector with lead wire	MO: M-type plug connector without connector
	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor	With light/surge voltage suppressor
CE/UKCA-compliant	—	—	—	—	—
AC	—	—	—	—	—
DC	—	—	—	—	—
	Y: DIN terminal	YO: DIN terminal without connector	YZ: DIN terminal	YOS: DIN terminal without connector (DC specification)	YS: DIN terminal (DC specification)
	With light/surge voltage suppressor	With light/surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor	With surge voltage suppressor
CE/UKCA-compliant	—	—	—	—	—
AC	—	—	—	—	—
DC	—	—	—	—	—

Note 1) Standard lead wire length: 300 mm

Note 2) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.

Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC



Note) For sub-plate part no., refer to page 1046.

Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included.

Construction

VQZ100

Poppet type







Component Parts





No.	Description	Material	Note
1	Body	Resin	
2	Spool valve	Aluminum/HNBR	
3	Pilot valve assembly	—	
4	Port plug	Resin/HNBR	VVQZ100-CP

VQZ200/300

Metal seal type



Rubber seal type



Component Parts

No.	Description	Material	Note
1	Body	Aluminum die-casted	
2	Spool, Sleeve	Stainless steel	Metal seal
2	Spool valve	Aluminum/HNBR	Rubber seal
3	Piston	Resin	
4	Pilot valve assembly	—	


Note) For "How to Order Pilot Valve Assembly", refer to page 1046.

VQZ100/200/300 Series


Dimensions: VQZ100

Single Unit


Grommet (G): VQZ115□-□G□1-01



L-type plug connector (L): VQZ115□-□L□1-01



M-type plug connector (M): VQZ115□-□M□1-01




Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

Dimensions: VQZ200


Single Unit

Grommet (G): VQZ2□5□-□G□1-⁰¹₀₂




(): VQZ215-□G□1-01

L-type plug connector (L): VQZ2□5□-□L□1-⁰¹₀₂




Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

M-type plug connector (M): VQZ2□5□-□M□1-⁰¹/₀₂



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

DIN terminal (Y): VQZ2□5□-□Y□□1-⁰¹₀₂




Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

VQZ100/200/300 Series

Dimensions: VQZ300


Single Unit

Grommet (G): VQZ3□5□-□G□1-⁰²₀₃




() : VQZ315-□G□1-02

L-type plug connector (L): VQZ3□5□-□L□1-⁰²₀₃




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M): VQZ3□5□-□M□1-⁰²₀₃



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

DIN terminal (Y): VQZ3□5□-□Y□□1-⁰²₀₃



Unless otherwise indicated, dimensions are the same as Grommet (G).

Base Mounted
Plug Lead Unit

3 Port Solenoid Valve

VQZ100/200/300 Series

Manifold Connector Kit



[Option]

Note) For CE/UKCA-compliant models, DC-type only.

VQZ100 / How to Order Manifold

VV3QZ 1 5 - 08 C6 C - -

Series
1 VQZ100

Manifold type
5 Base mounted

Stations
02 2 stations
20 20 stations

Port size [2(A) port]

C3	ø3.2 One-touch fitting	For side ported
C4	ø4 One-touch fitting	
C6	ø6 One-touch fitting	
M5	M5 thread (Replaceable type)	For top ported
CP	With port plug	
CM	Mixed port sizes	—

Note 1) When CP port plug is attached on all 2(A) port. Valve on manifold is top ported.
Note 2) Specify the mixture port (including top and side piping) by the manifold specification sheet.
Note 3) For inch size One-touch fittings, refer to page 1045.

CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

Option

Nil	None
D	DIN rail mounting (With standard DIN rail length)
D0	DIN rail mounting (Without DIN rail)
R	External pilot type

Note 1) Order DIN rail separately.
For DIN rail part no., refer to page 1044.
Note 2) When two or more symbols are specified, indicate them alphabetically.

Kit type
C Connector

VQZ100 / How to Order Valve

VQZ 1 1 5 - 5 M 1 - C4 -

Series
1 VQZ100 body width 10 mm

Type of actuation
1 N.C.

Body type
5 Base mounted

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W)	(Note 3)
K	High pressure type	(0.9 W)	—
R	External pilot type	—	—
KR	High pressure/External pilot type	(0.9 W)	—

Note 1) Semi-standard
Note 2) For details on external pilot type, refer to page 1045.
Note 3) For AC specification power consumption, refer to page 1032.

Coil voltage

	CE/UKCA-compliant
1 100 VAC (50/60 Hz)	—
2 200 VAC (50/60 Hz)	—
3 110 VAC [115 VAC] (50/60 Hz)	—
4 220 VAC [230 VAC] (50/60 Hz)	—
5 24 VDC	●
6 12 VDC	●

CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

Note) For CE/UKCA-compliant models, DC type only.

Port size

CP	With port plug	For side ported
C3	ø3.2 One-touch fitting	For top ported
C4	ø4 One-touch fitting	
C6	ø6 One-touch fitting	
M5	M5 thread	—

Note) For inch size One-touch fittings, refer to page 1045.

Manual override

Nil	Non-locking push type (Tool required)
B	Locking type (Tool required)

Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor
G	Grommet (DC specification)	None
L	L-plug plug connector with lead wire	Yes
LO	L-plug plug connector without connector	
M	M-plug plug connector with lead wire	
MO	M-plug plug connector without connector	—

Note) Standard lead wire length: 300 mm
Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included.

Caution
Use standard (DC) specification for continuous duty.

VQZ100/200/300 Series

VQZ200/300 / How to Order Manifold



Made to Order
(For details, refer to page 1047.)

Note) AC-type models that are CE/UKCA-compliant have DIN terminals only.



VV3QZ **2** **5** - **08** **C6** **C** - **□** - **□**

Series

2	VQZ200
3	VQZ300

Manifold type

5	Base mounted
---	--------------

Stations

02	2 stations
...	...
20	20 stations

Port size [2(A) port]

Symbol	Port size	VQZ200	VQZ300
C4	ø4 One-touch fitting	○	—
C6	ø6 One-touch fitting	○	○
C8	ø8 One-touch fitting	○	○
C10	ø10 One-touch fitting	—	○
01	Rc 1/8	○	—
02	Rc 1/4	—	○
CM	Mixed port sizes	○	○

Note 1) Specify port mixture/with port plug by means of the manifold specification sheet. Port mixture and port plug are available only for one-touch fitting type.
Note 2) For inch size One-touch fittings, refer to page 1045.

CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

Option

Nil	None
D	DIN rail mounting (With standard DIN rail length)
D0	DIN rail mounting (Without DIN rail)
R	External pilot type

Note 1) Order DIN rail separately.
For DIN rail part no., refer to page 1044.
Note 2) When two or more symbols are specified, indicate them alphabetically.

Kit type

C	Connector
---	-----------

VQZ200/300 / How to Order Valve

VQZ **2** **1** **5** - **5** **M** - **1** - **□**

Series

2	VQZ200 body width 15 mm
3	VQZ300 body width 18 mm

Type of actuation

1	N.C. Metal seal
2	N.O. Metal seal
3	N.C. Rubber seal
4	N.O. Rubber seal

Body type

5	Base mouned
---	-------------

Function

Symbol	Specifications	DC	AC
Nil	Standard	(0.35 W) ○	(Note 3) ○
B	High speed response type	(0.9 W) ○	—
K	High pressure type (Metal seal type only)	(0.9 W) ○	—
R	External pilot type	○	○
BR	High speed response/External pilot type	(0.9 W) ○	—
KR	High pressure/External pilot type (Metal seal type only)	(0.9 W) ○	—

Note 1) Semi-standard
Note 2) For details on external pilot type, refer to page 1045.
Note 3) For AC specification power consumption, refer to page 1032.

CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

Note) AC-type models that are CE/UKCA-compliant have DIN terminals only.

IP65 compliant

Nil	—
W	Compliant

Note) VQZ200/300 DIN terminal rubber seal only (except external pilot). For details on IP65 enclosure, refer to page 1045.

Manual override

Nil	Non-locking push type (Tool required)
B	Locking type (Tool required)

Electrical entry

Symbol	Electrical entry	Light/surge voltage suppressor	CE/UKCA-compliant
G	Grommet (DC specification)	None	AC: ● DC: ●
L	L-type plug connector with lead wire	Yes	AC: — DC: ●
LO	L-type plug connector without connector		AC: — DC: ●
M	M-type plug connector with lead wire		AC: — DC: ●
MO	M-type plug connector without connector		AC: — DC: ●
Y	DIN terminal	None	AC: ● DC: ●
YO	DIN terminal without connector		AC: ● DC: ●
YZ	DIN terminal		AC: ● DC: ●
YS	DIN terminal (DC specification)	Yes	AC: — DC: ●
YOS	DIN terminal without connector (DC specification)	(Without light)	AC: — DC: ●

Note 1) Standard lead wire length: 300 mm
Note 2) For AC voltage valves there is no "S" type. It is already built-in to the rectifier circuit.

Caution
Use standard (DC) specification for continuous duty.


Coil voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC [115 VAC] (50/60 Hz)
4	220 VAC [230 VAC] (50/60 Hz)
5	24 VDC
6	12 VDC

Note) When ordering single unit of the base mounted type solenoid valve, the mounting screws and gaskets for the manifold are included.




Manifold Specifications



Series	Base model	Piping specifications			Applicable solenoid valve	Applicable stations	^{Note)} Manifold base weight (g)
		Piping direction	Port size				
			1(P), 3(R)	2(A)			
VQZ100	VV3QZ15-□□□	Side/Top	Rc 1/8	C3 (for ø3.2) C4 (for ø4) C6 (for ø6) M5 (M5 thread)	VQZ115	2 to 20 stations	2 stations: 83 Addition per station: 19
VQZ200	VV3QZ25-□□□	Side	Rc 1/4	C4 (for ø4) C6 (for ø6) C8 (for ø8) Rc 1/8	VQZ2□5	2 to 20 stations	2 stations: 126 Addition per station: 38
VQZ300	VV3QZ35-□□□	Side	1(P) port: Rc 3/8 3(R) port: Rc 1/4	C6 (for ø6) C8 (for ø8) C10 (for ø10) Rc 1/4	VQZ3□5	2 to 20 stations	2 stations: 209 Addition per station: 60

Note) Weight for threaded connection.

How to Order Manifold Assembly (Example)



VV3QZ25-05C6C 1 set (C kit 5-station manifold base part no.)
 VVQZ200-10A-5 1 set (Blanking plate assembly part no.)
 VQZ215-5L1 4 sets (N.C. type part no.)

→ The asterisk denotes the symbol for assembly.
 Prefix it to the part nos. of the solenoid valve, etc.


→ Enter in order starting from the first station on the D side.

Add the valve and option part number under the manifold base part number.
 When entry of part numbers becomes complicated, indicate by the manifold specification sheet.


VQZ100/200/300 Series

Dimensions: VQZ100: Top Ported

VV3QZ15- Stations Port size C



M5




Dimensions

n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	85.5	98	110.5	123	135.5	148	148	160.5	173	185.5	198	210.5	210.5	223	235.5	248	260.5	273
L2	75	75	87.5	100	112.5	125	137.5	137.5	150	162.5	175	187.5	200	200	212.5	225	237.5	250	262.5
L3	43.5	54	64.5	75	85.5	96	106.5	117	127.5	138	148.5	159	169.5	180	190.5	201	211.5	222	232.5
L4	21	16	17	18	19	20	21	15.5	16.5	17.5	18.5	19.5	20.5	15.5	16.5	17.5	18.5	19.5	20.5
L5	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5


Dimensions: VQZ100: Side Ported

VV3QZ15- Stations Port size **C**




The dashed lines indicate the DIN rail mounting [-D].

L-type plug connector (L)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

Dimensions


n: Stations (Max. 20 stations)

	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	85.5	98	110.5	123	135.5	148	148	160.5	173	185.5	198	210.5	210.5	223	235.5	248	260.5	273
L2	75.5	75	87.5	100	112.5	125	137.5	137.5	150	162.5	175	187.5	200	200	212.5	225	237.5	250	262.5
L3	43.5	54	64.5	75	85.5	96	106.5	117	127.5	138	148.5	159	169.5	180	190.5	201	211.5	222	232.5
L4	21	16	17	18	19	20	21	15.5	16.5	17.5	18.5	19.5	20.5	15.5	16.5	17.5	18.5	19.5	20.5
L5	30.5	41	51.5	62	72.5	83	93.5	104	114.5	125	135.5	146	156.5	167	177.5	188	198.5	209	219.5

VQZ100/200/300 Series


Dimensions: VQZ200

VV3QZ25- Stations Port size C




The dashed lines indicate the DIN rail mounting [-D].

L-type plug connector (L)




Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[] : AC

DIN terminal (Y)



Unless otherwise indicated, dimensions are the same as Grommet (G).




Dimensions

n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	85.5	98	123	135.5	148	173	185.5	198	210.5	235.5	248	260.5	285.5	298	310.5	323	348	360.5	373
L2	75	87.5	112.5	125	137.5	162.5	175	187.5	200	225	237.5	250	275	287.5	300	312.5	337.5	350	362.5
L3	52	68	84	100	116	132	148	164	180	196	212	228	244	260	276	292	308	324	340
L4	17	15	19.5	18	16	20.5	19	17	15.5	20	18	16.5	21	19	17.5	15.5	20	18.5	16.5
L5	42	58	74	90	106	122	138	154	170	186	202	218	234	250	266	282	298	314	330

Dimensions: VQZ300


VV3QZ35- Stations Port size C

Grommet (G)




The dashed lines indicate the DIN rail mounting [-D].

L-type plug connector (L)




Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

M-type plug connector (M)



Unless otherwise indicated, dimensions are the same as Grommet (G).
[]: AC

DIN terminal (Y)



Unless otherwise indicated, dimensions are the same as Grommet (G).

Dimensions

n	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	98	123	148	160.5	185.5	198	223	248	260.5	285.5	298	323	348	360.5	385.5	398	423	448	460.5
L2	87.5	112.5	137.5	150	175	187.5	212.5	237.5	250	275	287.5	312.5	337.5	350	375	387.5	412.5	437.5	450
L3	66	86	106	126	146	166	186	206	226	246	266	286	306	326	346	366	386	406	426
L4	16	18.5	21	17.5	20	16	18.5	21	17.5	20	16	18.5	21	17.5	20	16	18.5	21	17.5
L5	48	68	88	108	128	148	168	188	208	228	248	268	288	308	328	348	368	388	408

n: Stations (Max. 20 stations)

VQZ100/200/300 Series

Manifold Options


Blanking plate assembly

VVQZ100-10A-5 (for VQZ100)

VVQZ200-10A-5 (for VQZ200)

VVQZ300-10A-5 (for VQZ300)

It is used by attaching on the manifold block for being prepared for removing a valve for maintenance reasons or planning to mount a spare valve, etc.



Blanking plug



KQ2P-23

KQ2P-04

KQ2P-06

KQ2P-08

KQ2P-10



Dimensions (mm)				
Applicable fitting size ød	Model	A	L	D
3.2	KQ2P-23	16	31.5	5
4	KQ2P-04	16	32	6
6	KQ2P-06	18	35	8
8	KQ2P-08	20.5	39	10
10	KQ2P-10	22	43	12

DIN rail


AXT100-DR-□

□ As for □, enter the number from the DIN rail dimensions table.
For L dimension, refer to the dimensions of each kit.

Each manifold can be mounted on a DIN rail.

Insert "D" at the end of the manifold part number.

The DIN rail is approximately 30 mm longer than the length of manifold.




L Dimension

No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L dimension	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
L dimension	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5


Silencer

(for manifold EXH port)

Silencer is installed in the manifold EXH port.



AN110-01



AN20-02

Dimensions

Model	Silencer part no.
VQZ100	AN110-01
VQZ200	AN20-02
VQZ300	AN20-02

Port plug

VVQZ100-CP (for VQZ100)

This is used when changing piping location. (Side or Top)



External Pilot Specification

The external pilot specification is used when the operating pressure is below the minimum operating pressure 0.1 to 0.15 MPa or when valve is used for a vacuum application. Order a valve by adding the external pilot specification [R] to the part number.

Valve Part No.


VQZ 5R — 1 — —

• Entry is the same as standard products.

Manifold Part No.

VV3QZ 5 — C — R —

• Entry is the same as standard products.



• CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

Pressure Specifications

Series		VQZ100 <small>Note 2)</small>	VQZ200/300
External pilot pressure range <small>Note 1)</small>	Metal seal	—	0.1 to 0.7 MPa
	Rubber seal (VQZ100: poppet)	0.2 to 0.7 MPa	0.15 to 0.7 MPa
Operating pressure range <small>Note 1)</small>		-100 kPa to 0.7 MPa	

Note 1) In case of the high pressure type, upper limit of max. operating pressure and external pilot pressure range is 1 MPa.

Note 2) When using the VQZ100 series for a vacuum application, vacuum air through its 1(P) port. When supplying vacuum-release air, supply it through its 3(R) port. But do not supply vacuum-release air exceeding 50% for the external pilot pressure.

In addition, when the VQZ100 is to be used at an operating pressure greater than 0.2 MPa, please assure that the operating pressure is set to equal to or less than the external pilot pressure.

Inch Size One-touch Fittings and Optional Threads

Inch size One-touch fittings and NPT, NPTF and G thread are available.

Manifold Part No.

VV3QZ 5 — N7 T C — —

• Entry is the same as standard products.

• Cylinder port

• CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

• Thread type (Cylinder port and 1(P), 3(R) ports)

Symbol	N1	N3	N7	N9	N11	NM <small>Note 1)</small>	M5	01	02
Applicable tubing O.D.	ø1/8"	ø5/32"	ø1/4"	ø5/16"	ø3/8"	Mixed	M5 thread	1/8 thread	1/4 thread
Cylinder port	VQZ100	●	●	●	—	●	●	—	—
	VQZ200	—	●	●	●	—	—	●	—
	VQZ300	—	—	●	●	●	—	—	●

Note 1) Except VQZ100, mixing One-touch fittings and thread types is impossible.

Note 2) Metric size One-touch fittings (C□) are also available.

Nil	Rc
N	NPT
T	NPTF
F	G

Optional Threads Other than Rc

Rc specifications are standard for all ports, however, NPT, NPTF and G are available for overseas markets. Add the appropriate symbol following the port size in the standard part number.

Valve Part No.

VQZ 5 — 1 — T

• Entry is the same as standard products.

• CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

• Thread type (Cylinder port and 1(P), 3(R) ports of sub-plate)

Nil	Rc
N	NPT
T	NPTF
F	G

IP65 Enclosure (Based on IEC60529)

DIN terminal is available with IP65 enclosure.

Valve Part No.

(Applicable to the VQZ200/300 rubber seal with the exception of the external pilot type)

VQZ ²/₃ 5 — Y W1 — —

• Entry is the same as standard products.

Note) The pilot exhaust IP65 valves is common with main valve exhaust. (The standard valve has an individual exhaust for the pilot valve.)

• CE/UKCA-compliant

Nil	—
Q	CE/UKCA-compliant

VQZ Series Base Mounted

Replacement Parts

One-touch Fitting Assembly (for Cylinder port)

Fitting size	C3	C4	C6	C8	C10	M5 (VQZ100 only)
Model						
VQZ100	VVQ1000-50A-C3	VVQ1000-50A-C4	VVQ1000-50A-C6	—	—	VVQ1000-50A-M5
VQZ200	—	VVQ1000-51A-C4	VVQ1000-51A-C6	VVQ1000-51A-C8	—	—
VQZ300	—	—	VVQ2000-51A-C6	VVQ2000-51A-C8	VVQ2000-51A-C10	—

(Note) Purchasing order is available in units of 10 pieces.

<Plug connector assembly>

DC: SY100-30-4A-□

100 VAC: SY100-30-1A-□

200 VAC: SY100-30-2A-□

Other AC voltages: SY100-30-3A-□

Without lead wire: SY100-30-A
(with connector and 2 sockets only)

Lead wire length●

Nil	300 mm
6	600 mm
10	1000 mm
15	1500 mm
20	2000 mm
25	2500 mm
30	3000 mm
50	5000 mm

How to Order

Include the connector assembly part number together with the part number for the plug connector's solenoid valve without connector.

Example) In case of 2000 mm of lead wire

DC	AC
VQZ115-5LO1-M5	VQZ115-1LO1-M5
SY100-30-4A-20	SY100-30-1A-20

<Gasket and screw assembly>

Model	Part no.
VQZ100	VQZ100-GS-5
VQZ200	VQZ200-GS-5
VQZ300	VQZ300-GS-5

(Note) The above part numbers are for 10 valves
(a set of 10 gaskets and 20 screws).




<Sub-plate>

Model	Sub-plate part no.	
	For internal pilot	For external pilot
VQZ100	VQZ100-S-01 ⁰¹ ₀₂ (-Q)	VQZ100-S-01 ⁰¹ ₀₂ (-R (-Q)
VQZ200	VQZ200-S-02 ⁰² ₀₃ (-Q)	VQZ200-S-02 ⁰² ₀₃ (-R (-Q)
VQZ300	VQZ300-S-02 ⁰² ₀₃ (-Q)	VQZ300-S-02 ⁰² ₀₃ (-R (-Q)

* Thread type

<Pilot valve assembly>



Electrical entry●

Symbol	Electrical entry	Light/surge voltage suppressor
DC AC		
G	—	None
LU LZ	Grommet (DC specification)	
LOU LOZ	L-type plug connector with lead wire	
MU MZ	L-type plug connector without connector	Yes
MOU MOZ	M-type plug connector with lead wire	
	M-type plug connector without connector	

(Note) The electrical entry (L, M) for the VQZ100 pilot valve is different from that of the main valve model number.

Valve model	Pilot valve model
VQZ115 □-□ L □ 1	V111 □ M -□ M □
VQZ115 □-□ M □ 1	V111 □ M -□ L □

<DIN terminal type (Applicable to the VQZ200/300)>



(Note) For AC voltage valves there is no "S" option. It is already built-in to the rectifier circuit.

⚠ Caution

When replacing only the pilot valve assembly, use caution because it is not possible to convert to a V115 (DIN terminal) from a V111 (Grommet, L-type, M-type), or vice versa.

VQZ200/300 Series

Made to Order

Please contact SMC for detailed dimensions, specifications and lead times.




1 Pilot Valve Common Exhaust Specification

Pilot exhaust is exhausted through the main R port.

- * Not designed to prevent leakage to outside.
- * A combination of external pilots is not available.
- * "How to Order Manifold" is the same as standard products. Please specify this to "How to Order Valve."

Applicable solenoid valve series: VQZ200/300

How to Order




2 Main Valve Fluororubber Specification

The seal material, the part of the main valve in contact with fluid, is made of fluororubber.

- * "How to Order Manifold" is the same as standard products. Please specify this to "How to Order Valve."

Applicable solenoid valve series: VQZ200/300

How to Order




3 All Fluororubber Specification

The rubber material of the part in contact with fluid, is made of fluororubber.

- * "How to Order Manifold" is the same as standard products. Please specify this to "How to Order Valve."

Applicable solenoid valve series: VQZ200/300

How to Order





VQZ Series

Specific Product Precautions 1

Be sure to read this before handling the products. For safety instructions and 3/4/5-port solenoid valve precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: <https://www.smcworld.com>


Manual Override

⚠ Caution

Manual override is used to switch the main valve without inputting an electrical signal for the valve. Push type is standard. Locking type (Tool required) is available as an option.


1. VQZ100

Push type



Press in the direction of the arrow.


Locking type (Tool required)



Turn 90° in the direction of arrow.


2. VQZ200/300

Push type (Tool required)




Push down on the manual override button with a small screwdriver until it stops. Release the screwdriver and the manual override will return.

Locking type (Tool required)



Push down completely on the manual override button with a small screwdriver. While down, turn clockwise 90° to lock it. Turn it counterclockwise to release it.

Locked position



Precautions


When operating with a screwdriver, turn it gently using a watchmaker's screwdriver. (Torque: less than 0.1 N·m) Press and rotate to lock the manual operation of VQZ200/300. If rotate without pressing, manual breakage and air leakage could be occurred.

How to Use L/M-Type Plug Connector

⚠ Caution

1. Attaching and detaching connectors

To attach a connector, hold the lever and connector unit between your fingers and insert straight onto the pins of the solenoid valve and remove the pawl from the groove by pushing the lever downward with your thumb, and pull the connector straight out.




Light/Surge Voltage Suppressor


⚠ Caution

1. L/M-type plug connector

<DC>




<AC>




2. DIN terminal

<DC>

With surge voltage suppressor (YS, YOS)




Light/surge voltage suppressor (YZ)



<AC>

With light (YZ)



Note) Surge voltage suppressor of varistor has residual voltage corresponding to the protective element and rated voltage; therefore, protect the controller side from the surge.



VQZ Series

Specific Product Precautions 2

Be sure to read this before handling the products. For safety instructions and 3/4/5-port solenoid valve precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: <https://www.smcworld.com>


Lead Wire Connection

⚠ Caution

1. Crimping of lead wires and sockets

Not necessary if ordering the lead wire pre-connected model. Strip 3.2 to 3.7 mm at the end of the lead wires, insert the ends of the core wires evenly into the sockets, and then crimp with a crimping tool. When this is done, take care that the coverings of the lead wires do not enter the core wire crimping area.

(Please contact SMC for the crimping tools.)




2. Attaching and detaching sockets with lead wires

Attaching

Insert the sockets into the square holes of the connector (⊙, ⊖ indication), and continue to push the sockets all the way in until they lock by hooking into the seats in the connector. (When they are pushed in, their hooks open and they are locked automatically.) Then, confirm that they are locked by pulling lightly on the lead wires.

Detaching

To detach a socket from a connector, pull out the lead wire while pressing the socket's hook with a stick having a thin tip (approx. 1 mm). If the socket will be used again, first spread the hook outward.




Pilot Valve Replacement

⚠ Caution


1. When replacing a current type valve with a new type for maintenance or other reasons, a "conversion connector assembly" is necessary to convert the connector from 3 terminals to 2 terminals and must be ordered separately. (When ordering, refer to the below part nos.)

For pilot valves, there is no compatibility between the current type and new type. When replacing a pilot valve, be sure to confirm whether it is the new type or the current type.

[Current]



[New]





VQZ Series

Specific Product Precautions 3

Be sure to read this before handling the products. For safety instructions and 3/4/5-port solenoid valve precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: <https://www.smcworld.com>

How to Use DIN Terminal

1. EN-175301-803C (Former DIN 43650C) (8 mm between pins)

The DIN terminal type with an IP65 enclosure is protected against dust and water, however, it must not be used in water.

2. Connection

- Loosen the holding screw and pull the connector out of the solenoid valve terminal block.
- After removing the holding screw, insert a flat head screwdriver, etc. into the notch on the bottom of the terminal block and pry it open, separating the terminal block and the housing.
- Loosen the terminal screws (slotted screws) on the terminal block, insert the cores of the lead wires into the terminals according to the connection method, and fasten them securely with the terminal screws.
- Secure the cord by fastening the housing.

3. Changing the entry direction

After separating the terminal block and housing, the cord entry can be changed by attaching the housing in the desired direction (4 directions at 90° intervals).

* When equipped with a light, be careful not to damage the light with the cord's lead wires.


4. Precautions

Plug in and pull out the connector vertically without tilting to one side.

5. Compatible cable

Cable O.D.: $\phi 3.5$ to $\phi 7$

(Reference) 0.5 mm², 2-core or 3-core, equivalent to JIS C 3306



DIN Connector Part No.


Without light

Rated voltage	Voltage symbol	Part no.
All voltages	None	SY100-82-1

With light

Rated voltage	Voltage symbol	Part no.
24 VDC	24 V	SY100-82-3-05
12 VDC	12 V	SY100-82-3-06
100 VAC	100 V	SY100-82-2-01
200 VAC	200 V	SY100-82-2-02
110 VAC (115 VAC)	110 V	SY100-82-2-03
220 VAC (230 VAC)	220 V	SY100-82-2-04

Circuit diagram with light




Fitting and Silencer Part No. for P, R Ports When Using Valve as an Individual Unit

Part no. for one-touch fitting for 1(P) port and silencer/one-touch fitting for 3(R) port

Series	(1) One-touch fitting for 1(P) port	(2) For 3(R) port	
		Silencer	One-touch fitting
VQZ100	KQ2H06-M5A	AN120-M5	KJS04-M5A
VQZ200	KQ2S06-01AS	INA-25-46	IN-457-32L (for $\phi 6$)
VQZ300	KQ2H08-02AS	AN101-01	KQ2H06-01AS

The diameter of the above fitting and silencer is the maximum diameter to in the EXH port.





VQZ Series

Specific Product Precautions 4

Be sure to read this before handling the products. For safety instructions and 3/4/5-port solenoid valve precautions, refer to the "Handling Precautions for SMC Products" and the "Operation Manual" on the SMC website: <https://www.smcworld.com>

One-touch Fittings Replacement

⚠ Caution


The built-in fittings on the manifold can be changed easily. Simply remove the corresponding valve and take out the fitting clip underneath.

Take out the clip with a screwdriver, etc., then replace the fittings. About mounting the fittings, after inserting the fitting until it stops, then put the clip into the prescribed position.

VQZ200: Horizontally clipped to the valve body

VQZ100/300: Vertically clipped to the valve body

■ Valve




Valve Clip Part No. (10 pcs. included)

Series	Part number
VQZ100	VQZ100-2-FC
VQZ200	VQZ200-2-FC
VQZ300	VQZ300-2-FC

■ Manifold base

Base Clip Part No. (10 pcs. included)

Series	Part number
VV3QZ15	VQZ100-5-FC
VV3QZ25	VQZ200-5-FC
VV3QZ35	VQZ300-5-FC



Precautions

When pulling the fitting assembly away from the valve base, remove the clip, then connect a tube or plug (KQ2P-□□) with the One-touch fitting and pull it out holding the tube or plug. Do not hold the release bushing to avoid damage.

DIN Rail Removal/Mounting


⚠ Caution

1. Removing

- 1) Loosen the clamp screw on the (a) side of both ends of the manifold.
- 2) Lift the (a) side of the manifold off the DIN rail and slide it in the direction of the (b) side.

2. Mounting

- 1) Catch the hook of the DIN rail bracket on the (b) side on the DIN rail.
- 2) Push side (a) onto the DIN rail and tighten the clamp screw. The proper tightening torque for screws is 0.3 to 0.4 N·m.




Valve Mounting

⚠ Caution

1. After confirming the gasket is correctly placed under the valve, securely tighten the bolts with the proper torque shown in the table below.

Model	Proper tightening torque
VQZ100	0.13 to 0.19 N·m
VQZ200	0.25 to 0.35 N·m
VQZ300	0.5 to 0.7 N·m




VQZ100 Piping Direction Replacement

⚠ Caution

1. How to replace the port direction

Fitting and port plug are modules. After removing the clip with a flat head screwdriver, take out the fitting and port plug. The piping direction (side or top) can be altered by exchanging the fitting and port plug. During exchange, insert the fitting and the port plug until they contact the wall, then, insert the clip to specified position.




Precautions

The clip length for the valve and the base are different. Fitting may detach if the incorrect clip is used.

2. Valve piped on top can be operated independently by using PR plate.

(Refer to the below part numbers when placing an order.)



VQZ100-12A (Standard)
VQZ100-12B (External pilot type)
* 2 set screws are included.




When changing from a VZ series to a VQZ series product

⚠ Caution

1. The L and M plug connectors of the VZ series and VQZ series are not interchangeable.

When the VZ series wiring is to be used as is, order the required conversion connector assembly separately. (Refer to the part number below when ordering.)



2. The L and M plug connectors of the VZ series and VQZ series have different electrical entry directions.

	L plug connector	M plug connector
VZ series		
VQZ series		

3. The DIN connector (D type) of the VZ series and the DIN connector (Y type) of the VQZ series are not interchangeable.

4. The replacement part numbers are as shown below.

VZ2000 series ⇒ VQZ2000 series

VZ4000 series ⇒ VQZ3000 series

Refer to the table below for details on mounting interchangeability.

	Body ported	Base mounted
Side surface mounting holes	No mounting interchangeability	
Sub-plate		No mounting interchangeability
Manifold	Mountable on VZ series manifolds * VZ series manifolds can continue to be used as is. * Order the gasket and screws for the VQZ series. For the part number, refer to the "Gasket and Screw Assembly" section on page 1029.	Mountable on VZ series manifolds * VZ series manifolds can continue to be used as is. * The gaskets of VQZ series valves are built into the valve, so do not use the gasket for the VZ series. Use the screws included with the VQZ.